



Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering guide

example: 9530WH

Series	Size	Mounting	Lamping
9530			
9530 Classics Roundback	WH Matte White BK Matte Black	All Lytespan Track Systems	A19, 100W Max PAR16, PAR30 75W Max

Features

- Lytespan attachment fitting:** Die-cast zinc alloy.
- Housing: .40" aluminum
- Step baffle: Compression-molded high heat phenolic with stepped conical surface for low brightness. Integral black finish.
- Lever: Locks attachment fitting electrically and mechanically anywhere along the track.
- Movable brass Contact: Extends for connection to 2nd circuit in Advent Lytespan Track.
- Swivel: Die-cast zinc alloy. 350° horizontal adjustment.
- Pivot mounting: Tensioned with built-in stop, provides 90° vertical adjustment.

Electrical

Porcelain socket, medium base, nickel plated screw shell. No. 18 braided SF-1 leads.

Finish

All painted finishes baked enamel.

Labels

UL, I.B.E.W.

