



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering Guide

Example: BL1 N L

Product Code	BL1	Brass Bullyte
Finish	N OB	Natural Brass Oiled Brass
Shroud	L	Long Shroud

Specifications

HOUSING:

Die-cast brass. Fully-adjustable swivel arm with vibration-proof locking teeth. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately. Fully rotatable shroud, gasketed die-cast brass. Fasteners are 300 series stainless steel.

FINISH:

HADCO's Oiled Brass (OB) is chemically dipped to achieve a dark pre-aged patina finish and the appearance will vary between production runs. Finishes will continue to patina over time making each fixture unique. Natural Brass (N) is as-cast and tumble polished.

OPTICAL ASSEMBLY:

Clear tempered glass lens.

LAMPING:

50W maximum MR16 bi-pin lamp. Lamp is not included. Covered MR16 are recommended to protect lamps inner capsule.

ELECTRICAL ASSEMBLY:

Bi-pin socket type (GU5.3) with 250° C high temperature teflon coated wire leads. 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

WARRANTY:

Lifetime limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Width:

3 7/8" (98mm)

Length:

8 3/16" (208mm)

Max. Weight:

4.26 lb

