



Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

### Ordering guide

example: 9630WH

Series	Size	Mounting	Lamping
<b>9630</b>			
<b>9630</b> Classics Step Cylinder	<b>WH</b> Matte White <b>BK</b> Matte Black	All Lytespan Track Systems	A19, PAR16 PAR30 75W Max

### Features

- Lytespan attachment fitting:**  
Die-cast zinc alloy.
- Housing: .40" aluminum
- Step baffle: Compression-molded high heat phenolic with stepped conical surface for low brightness. Integral black finish.
- Lever: Locks attachment fitting electrically and mechanically anywhere along the track.
- Movable brass Contact: Extends for connection to 2nd circuit in Advent Lytespan Track.
- Swivel: Die-cast zinc alloy. 350° horizontal adjustment.
- Pivot mounting: Tensioned with built-in stop, provides 90° vertical adjustment.

### Electrical

Porcelain socket, medium base, nickel plated screw shell. No. 18 braided SF-1 leads.

### Finish

All painted finishes baked enamel.

### Labels

UL, I.B.E.W.

