



Philips Ledinaire recessed: simply great LED

Ledinaire recessed

Philips Ledinaire recessed (RC060B) is a range of popular off-the-shelf LED luminaires that come with Philips high quality levels at a competitive price. Reliable, energy efficient and affordable, Ledinaire LED recessed lights are available in a range of dimensions from 600 x 600 mm to 300 x 1200 mm. This makes Ledinaire Recessed LED lighting panels perfect for a wide range of applications from classrooms to corridors – just what you need.

Benefits

- Philips quality and reliability
- Energy saving
- Diffuse, comfortable light

Features

- Recessed and surface-mounted versions
- Modern, unobtrusive design
- Easy connector for faster installation
- Energy efficient up to 100 lm/W
- Long lifetime of 50,000 hours @L70
- Non-office compliant (NOC) versions available

Application

- Offices
- Healthcare
- Education


Ledinaire recessed

Versions




Ledinaire Recessed-RC060B W60L60

Dimensional drawing



Product details



Ledinaire recessed, backside of the luminaire connectionblock



Ledinaire_Recessed-RC060B-DP01.tif



Ledinaire recessed, backside of the luminaire connection



Ledinaire recessed frontside

Ledinaire recessed

Product details

Ledinaire recessed, backside of
the luminaire connection

