

FlexBlend - Unlocking the potential of LED lighting in offices

FlexBlend Recessed

Office owners and staff responsible for lighting operations are searching for high quality yet energy-efficient lighting that complies with norms and regulations. Designed to support these needs, Philips FlexBlend is enabling building owners to fully optimize their lighting operations, by offering office-compliant lighting with an attractive return on investment. Furthermore, FlexBlend provides the required flexibility by being easy applied on different ceiling types as well as in different office spaces like open office or meeting rooms. Though technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations and future advances that can help optimize operations further. For this reason, Philips FlexBlend is also ready to be connected to controls such as Actilume or used together with the Philips SpaceWise lighting system. It can also be connected to software-based lighting systems like Interact Office, which provides the luminaire with further intelligence and enables it to collect valuable data about its environment

Benefits

- High-quality office-compliant lighting
- Choice of three different exit-windows
- Fast return on investment
- Application flexibility
- Scalable and ready to be connected to controls and lighting systems

FlexBlend Recessed

Features

- Fully office-compliant (UGR <19)
- Homogenous and uniform light effect
- Dimensional variety, local options
- Various mounting options
- Integrated sensors
- Can be combined with Philips ActiLume and SpaceWise systems
- Ready to be connected to software based lighting systems such as Interact Office

Application

- Offices
- Education
- Healthcare
- Banks

Versions



Upgradable sensor




FlexBlend Recessed RC340B
W60L60 PCS VPC




FlexBlend Recessed RC340B
W60L60 MLO PCV

Dimensional drawing



FlexBlend Recessed

Dimensional drawing



Product details




Upgradable sensor

O_FlexBlend Recessed-
RC342B_W62L62_MLO_VPC



FlexBlend Recessed-
RC340B_MLO_DPP

FlexBlend Recessed-
RC340B_W60L60_Backcover_VP
C




FlexBlend Recessed-
RC340B_W60L60_CPC brackets

FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_B



FlexBlend Recessed

Product details



FlexBlend Recessed-
RC340B_OPA_DPP



FlexBlend Recessed-
RC340B_PCS_DPP




O_FlexBlend Recessed-
RC340B_W60L60_PCS_VPC



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_A



FlexBlend Recessed RC340B PIP
Open



FlexBlend Recessed-
RC340B_W60L60_backcover_PC
V



O_FlexBlend Recessed-
RC340B_W60L60_MLO_VPC



O_FlexBlend Recessed-
RC340B_W60L60_MLO_CPC

FlexBlend Recessed

Product details



FlexBlend Recessed-RC340B PIP
Closed



Upgradable sensor



FlexBlend Recessed-
RC340B_W60L60_backcover_CP
C

FlexBlend Recessed

General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	≥90
Optic type	Wide beam
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Temperature	
Ambient temperature range	+10 to +40 °C
Mechanical and Housing	
Housing Color	White
Approval and Application	
Mech. impact protection code	IK02
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.37) SDCM <3
Luminous flux tolerance	+/-10%
Application Conditions	
Maximum dim level	1%

General Information

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B
910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B
910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B
910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B
910925867022	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B
910925867024	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B
910925867026	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B
910925867149	RC342B LED28S/940 PSD W15L125 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC342B
910925867150	RC342B LED36S/940 PSD W15L125 VPC MLO	Temperature 650 °C, duration 30 s	-	RC342B
910925867153	RC342B LED36S/940 PSD W17L125 PCV MLO	Temperature 650 °C, duration 30 s	-	RC342B
910925867164	RC342B LED28S/940 PSD W15L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	Temperature 850 °C, duration 30 s	-	RC342B
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC342B
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC342B
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC342B

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	Temperature 650 °C, duration 30 s	Interact Ready light source with multi-sensor (upgradable)	RC340B
910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	Temperature 850 °C, duration 30 s	Interact Ready light source with multi-sensor (upgradable)	RC340B
910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	-	RC340B
910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	-	RC340B
910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC340B
910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC340B
910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	-	RC340B
910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	-	RC340B
910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s	-	RC340B
910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	Temperature 850 °C, duration 30 s	-	RC340B
910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	Temperature 850 °C, duration 30 s	-	RC340B
910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC342B
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC340B

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	-	RC340B
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	-	RC340B
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	Temperature 850 °C, duration 30 s	-	RC340B
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	-	RC340B
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	-	RC340B
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC340B
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC342B
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	Temperature 650 °C, duration 30 s	-	RC340B
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	Temperature 650 °C, duration 30 s	-	RC340B
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s	-	RC340B
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	Temperature 650 °C, duration 30 s	-	RC340B
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	Temperature 650 °C, duration 30 s	-	RC340B
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	Temperature 650 °C, duration 30 s	-	RC340B
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	Temperature 850 °C, duration 30 s	-	RC340B
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO UO	Temperature 650 °C, duration 30 s	Upgradable sensor slot empty with cover	RC340B
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS UO	Temperature 850 °C, duration 30 s	Upgradable sensor slot empty with cover	RC340B
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC342B
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC342B
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC342B
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	Temperature 850 °C, duration 30 s	-	RC342B
910925867160	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC342B
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B

Light Technical

		Luminous Efficacy				Luminous Efficacy	
Order Code	Full Product Name	(rated) (Nom)	Luminous Flux	Order Code	Full Product Name	(rated) (Nom)	Luminous Flux
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	96 lm/W	3,600 lm	910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	88 lm/W	3,600 lm
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	97.5 lm/W	3,600 lm	910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	86.5 lm/W	3,600 lm
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	95.5 lm/W	4,200 lm	910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	87.5 lm/W	4,200 lm
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	94.5 lm/W	4,200 lm	910925867022	RC340B LED42S/940 PSD W15L120 VPC MLO EL	85.5 lm/W	4,200 lm

FlexBlend Recessed

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867024	RC340B LED36S/940 PSD W15L120 VPC MLO EL	96 lm/W	3,600 lm
910925867026	RC340B LED42S/940 PSD W15L120 VPC MLO EL	94.5 lm/W	4,200 lm
910925867149	RC342B LED28S/940 PSD W15L125 VPC MLO PI	100 lm/W	2,800 lm
910925867150	RC342B LED36S/940 PSD W15L125 VPC MLO	97.5 lm/W	3,600 lm
910925867153	RC342B LED36S/940 PSD W17L125 PCV MLO	97.5 lm/W	3,600 lm
910925867164	RC342B LED28S/940 PSD W15L125 VPC PCS PI	140 lm/W	2,800 lm
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	97 lm/W	3,600 lm
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	140 lm/W	4,200 lm
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	144 lm/W	3,600 lm
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	124 lm/W	2,800 lm
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	124 lm/W	3,600 lm
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	125 lm/W	4,200 lm
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	97.5 lm/W	3,600 lm
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	97.5 lm/W	3,600 lm
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	97.5 lm/W	3,600 lm
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	100 lm/W	2,800 lm
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	140 lm/W	2,800 lm
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	97 lm/W	3,600 lm
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	140 lm/W	4,200 lm
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	124 lm/W	2,800 lm
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	124 lm/W	3,600 lm
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	125 lm/W	4,200 lm
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	97.5 lm/W	3,600 lm
910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	144 lm/W	3,600 lm
910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	111 lm/W	3,600 lm

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	109 lm/W	3,600 lm
910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	127 lm/W	4,200 lm
910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	125 lm/W	4,200 lm
910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	114 lm/W	4,200 lm
910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	112 lm/W	4,200 lm
910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	125 lm/W	4,200 lm
910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	120 lm/W	3,600 lm
910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	124 lm/W	3,600 lm
910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	97.5 lm/W	3,600 lm
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	96 lm/W	3,600 lm
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	95.5 lm/W	4,200 lm
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	94.5 lm/W	4,200 lm
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	140 lm/W	4,200 lm
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	124 lm/W	3,600 lm
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	144 lm/W	3,600 lm
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	144 lm/W	3,600 lm
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	97.5 lm/W	3,600 lm
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	124 lm/W	3,600 lm
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	122 lm/W	3,600 lm
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	141 lm/W	3,600 lm
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	140 lm/W	4,200 lm
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	140 lm/W	4,200 lm
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	125 lm/W	4,200 lm
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	124 lm/W	4,200 lm
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	144 lm/W	3,600 lm

FlexBlend Recessed

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	144 lm/W	3,600 lm
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	140 lm/W	4,200 lm
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	140 lm/W	4,200 lm
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	144 lm/W	3,600 lm
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	144 lm/W	3,600 lm
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	120 lm/W	3,600 lm
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	97.5 lm/W	3,600 lm
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	88 lm/W	3,600 lm
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	86.5 lm/W	3,600 lm
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	124 lm/W	3,600 lm
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	96 lm/W	3,600 lm
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	94.5 lm/W	4,200 lm
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	94.5 lm/W	4,200 lm
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	95.5 lm/W	4,200 lm
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	96 lm/W	3,600 lm

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	97.5 lm/W	3,600 lm
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	97.5 lm/W	3,600 lm
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	142 lm/W	4,200 lm
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO U0	97.5 lm/W	3,600 lm
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS U0	144 lm/W	3,600 lm
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	96 lm/W	3,600 lm
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	97.5 lm/W	3,600 lm
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	97.5 lm/W	3,600 lm
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	100 lm/W	2,800 lm
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	140 lm/W	2,800 lm
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	144 lm/W	3,600 lm
910925867160	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	140 lm/W	4,200 lm
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	124 lm/W	2,800 lm
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	124 lm/W	3,600 lm
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	125 lm/W	4,200 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	37.5 W
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	37 W
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	44 W
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	44.5 W
910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	41 W
910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	41.5 W
910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	48 W
910925867022	RC340B LED42S/940 PSD W15L120 VPC MLO EL	49 W
910925867024	RC340B LED36S/940 PSD W15L120 VPC MLO EL	37.5 W
910925867026	RC340B LED42S/940 PSD W15L120 VPC MLO EL	44.5 W
910925867149	RC342B LED28S/940 PSD W15L125 VPC MLO PI	28 W
910925867150	RC342B LED36S/940 PSD W15L125 VPC MLO	37 W
910925867153	RC342B LED36S/940 PSD W17L125 PCV MLO	37 W
910925867164	RC342B LED28S/940 PSD W15L125 VPC PCS PI	20 W
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	25 W
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	30 W
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	25 W

Order Code	Full Product Name	Power Consumption
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	22.5 W
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	29 W
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	33.5 W
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	37 W
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	37 W
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	37 W
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	28 W
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	20 W
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	25 W
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	30 W
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	22.5 W
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	29 W
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	33.5 W
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	37 W
910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	25 W
910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	32.5 W

FlexBlend Recessed

Order Code	Full Product Name	Power Consumption
910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	33 W
910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	33 W
910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	33.5 W
910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	37 W
910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	37.5 W
910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	33.5 W
910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	30 W
910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	29 W
910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	37 W
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	37.5 W
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	44 W
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	44.5 W
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	30 W
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	29 W
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	25 W
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	25 W
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	37 W
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	29 W
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	29.5 W
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	25.5 W
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	30 W
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	30 W
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	33.5 W
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	34 W
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	25 W
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	25 W
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	30 W
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	30 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	No
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	Yes
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	No
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	Yes
910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	No
910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Yes
910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	No

Order Code	Full Product Name	Power Consumption
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	25 W
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	25 W
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	30 W
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	37 W
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	41 W
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	41.5 W
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	29 W
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	37.5 W
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	44.5 W
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	44.5 W
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	44 W
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	37.5 W
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	37 W
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	37 W
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	29.5 W
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO U0	37 W
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS U0	25 W
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	37.5 W
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	37 W
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	37 W
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	28 W
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	20 W
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	25 W
910925867160	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	30 W
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	22.5 W
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	29 W
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	33.5 W

FlexBlend Recessed

Order Code	Full Product Name	Dimmable
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	Yes
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	Yes
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	Yes
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	Yes
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	Yes
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	Yes
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	Yes
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	No
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	Yes
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	Yes
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	Yes
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	Yes
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	Yes
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	Yes
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	Yes
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	Yes
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	Yes
910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	Yes
910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	No
910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	Yes
910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	No
910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	Yes
910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	No
910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	Yes
910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	Yes
910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	No
910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	Yes
910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Yes
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	No
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	No
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	Yes
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	Yes
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	Yes
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	No
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Yes
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	Yes
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	No

Order Code	Full Product Name	Dimmable
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	Yes
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	Yes
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	No
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	Yes
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	No
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	Yes
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	No
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	Yes
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	No
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	Yes
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	No
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Yes
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	No
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	No
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	No
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	Yes
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	Yes
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	Yes
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	Yes
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	Yes
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	No
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	No
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Yes
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	Yes
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	Yes
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO U0	Yes
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS U0	Yes
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	No
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	Yes
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	Yes
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	Yes
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	Yes
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	Yes
910925867160	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	Yes
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	Yes
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	Yes
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	Yes

Approval and Application

Order Code	Full Product Name	Protection class IEC	Ingress protection code
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	Safety class I	IP20
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	Safety class I	IP20
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	Safety class I	IP20
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	Safety class I	IP20

Order Code	Full Product Name	Protection class IEC	Ingress protection code
910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	Safety class I	IP20
910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Safety class I	IP20
910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	Safety class I	IP20
910925867022	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Safety class I	IP20

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Ingress protection code
910925867024	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Safety class I	IP20
910925867026	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Safety class I	IP20
910925867149	RC342B LED28S/940 PSD W15L125 VPC MLO PI	Safety class I	IP20
910925867150	RC342B LED36S/940 PSD W15L125 VPC MLO	Safety class I	IP20
910925867153	RC342B LED36S/940 PSD W17L125 PCV MLO	Safety class I	IP20
910925867164	RC342B LED28S/940 PSD W15L125 VPC PCS PI	Safety class I	IP54
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	Safety class I	IP54
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	Safety class I	IP54
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	Safety class I	IP54
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	Safety class I	IP54
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	Safety class I	IP54
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	Safety class I	IP54
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	Safety class I	IP20
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	Safety class I	IP20
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	Safety class I	IP20
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	Safety class I	IP20
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	Safety class I	IP54
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	Safety class I	IP54
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	Safety class I	IP54
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	Safety class I	IP54
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	Safety class I	IP54
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	Safety class I	IP54
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	Safety class III	IP20
910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	Safety class III	IP20/54
910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	Safety class I	IP54

Order Code	Full Product Name	Protection class IEC	Ingress protection code
910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	Safety class I	IP54
910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	Safety class I	IP54
910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	Safety class I	IP54
910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	Safety class I	IP54
910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	Safety class I	IP54
910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	Safety class I	IP54
910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	Safety class I	IP54
910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	Safety class I	IP54
910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Safety class I	IP20
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	Safety class I	IP20
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	Safety class I	IP20
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	Safety class I	IP20
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	Safety class I	IP54
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	Safety class I	IP54
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Safety class I	IP54
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Safety class I	IP54
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	Safety class I	IP20
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	Safety class I	IP54
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	Safety class I	IP54
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	Safety class I	IP54
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	Safety class I	IP54
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	Safety class I	IP54
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	Safety class I	IP54
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	Safety class I	IP54
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	Safety class I	IP54

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Ingress protection code
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	Safety class I	IP54
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	Safety class I	IP54
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	Safety class I	IP54
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Safety class I	IP54
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Safety class I	IP54
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	Safety class I	IP54
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	Safety class I	IP20
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	Safety class I	IP20
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	Safety class I	IP20
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	Safety class I	IP54
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	Safety class I	IP20
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	Safety class I	IP20
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	Safety class I	IP20
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	Safety class I	IP20
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Safety class I	IP20

Order Code	Full Product Name	Protection class IEC	Ingress protection code
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Safety class I	IP20
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	Safety class I	IP20
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	Safety class I	IP54
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO UO	Safety class III	IP20
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS UO	Safety class III	IP20/54
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Safety class I	IP20
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	Safety class I	IP20
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	Safety class I	IP20
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	Safety class I	IP20
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	Safety class I	IP54
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	Safety class I	IP54
910925867160	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	Safety class I	IP54
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	Safety class I	IP54
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	Safety class I	IP54
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	Safety class I	IP54

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	0.01 %
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	0.01 %
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	0.01 %
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	0.01 %
910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	0.01 %
910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	0.01 %
910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	0.01 %
910925867022	RC340B LED42S/940 PSD W15L120 VPC MLO EL	0.01 %
910925867024	RC340B LED36S/940 PSD W15L120 VPC MLO EL	0.01 %
910925867026	RC340B LED42S/940 PSD W15L120 VPC MLO EL	0.01 %
910925867149	RC342B LED28S/940 PSD W15L125 VPC MLO PI	-
910925867150	RC342B LED36S/940 PSD W15L125 VPC MLO	-
910925867153	RC342B LED36S/940 PSD W17L125 PCV MLO	-
910925867164	RC342B LED28S/940 PSD W15L125 VPC PCS PI	-
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	-
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	-
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	-
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	-
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	-
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	0.01 %
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	0.01 %
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	0.01 %
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	-
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	-
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	-
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	-
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	-
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	-
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	-

FlexBlend Recessed

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	-
910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	-
910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	0.01 %
910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	0.01 %
910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	0.01 %
910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	0.01 %
910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	0.01 %
910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	0.01 %
910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	0.01 %
910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	0.01 %
910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	0.01 %
910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	0.01 %
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	0.01 %
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	0.01 %
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	0.01 %
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	-
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	0.01 %
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	0.01 %
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	0.01 %
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	0.01 %
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	0.01 %
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	0.01 %
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	0.01 %
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	0.01 %
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	0.01 %
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	0.01 %
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	0.01 %
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	0.01 %
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	0.01 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	0.01 %
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	0.01 %
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	0.01 %
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	0.01 %
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	0.01 %
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	0.01 %
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	0.01 %
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	0.01 %
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	0.01 %
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	0.01 %
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	0.01 %
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	0.01 %
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	0.01 %
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	0.01 %
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	0.01 %
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	0.01 %
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	0.01 %
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO U0	-
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS U0	-
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	0.01 %
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	0.01 %
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	0.01 %
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	-
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	-
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	-
910925867160	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	-
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	-
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	-
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	-

Application Conditions

Order Code	Full Product Name	Suitable for random switching
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	Yes
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	Yes
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	Yes
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	Yes
910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	Yes
910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Yes
910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	Yes
910925867022	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Yes
910925867024	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Yes
910925867026	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Yes
910925867149	RC342B LED28S/940 PSD W15L125 VPC MLO PI	Yes
910925867150	RC342B LED36S/940 PSD W15L125 VPC MLO	Yes
910925867153	RC342B LED36S/940 PSD W17L125 PCV MLO	Yes
910925867164	RC342B LED28S/940 PSD W15L125 VPC PCS PI	Yes
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	Yes
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	Yes
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	Yes

Order Code	Full Product Name	Suitable for random switching
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	Yes
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	Yes
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	Yes
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	Yes
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	Yes
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	Yes
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	Yes
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	Yes
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	Yes
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	Yes
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	Yes
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	Yes
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	Yes
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	Yes (relates to presence/ movement detection and

FlexBlend Recessed

Order Code	Full Product Name	Suitable for random switching
		daylight
		harvesting)
910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	Yes (relates to presence/ movement detection and daylight harvesting)
910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	Yes
910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	Yes
910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	Yes
910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	Yes
910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	Yes
910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	Yes
910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	Yes
910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	Yes
910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	Yes
910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Yes
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	Yes
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	Yes
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	Yes
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	Yes
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	Yes
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Yes
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Yes
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	Yes
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	Yes
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	Yes
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	Yes
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	Yes
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	Yes
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	Yes
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	Yes
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	Yes
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	Yes
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	Yes
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	Yes

Order Code	Full Product Name	Suitable for random switching
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Yes
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Yes
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	Yes
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	Yes
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	Yes
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	Yes
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	Yes
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	Yes
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	Yes
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	Yes
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	Yes
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Yes
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Yes
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	Yes
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	Yes
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO U0	Yes (relates to presence/ movement detection and daylight harvesting)
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS U0	Yes (relates to presence/ movement detection and daylight harvesting)
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Yes
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	Yes
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	Yes
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	Yes
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	Yes
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	Yes
910925867160	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	Yes
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	Yes
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	Yes
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	Yes

