



Built in light sensor for added security from Dusk-to-Dawn

LED Dusk to Dawn

Philips Dusk to Dawn A19 lamp is equipped with a built in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises.

Benefits

- Long life -- lowers maintenance costs by reducing re-lamp frequency
- Excellent color consistency with high 80+ color rendering (CRI)
- Equipped with a built in light sensor that turns your light bulbs on automatically when the sun goes down and turns the light off when the sun rises

Features

- Fit standard medium base (E26) fixtures with the look and feel of a classic bulb
- Instant on
- 25,000 hour rated average life
- Emits virtually no UV/IR light
- No mercury for a safe environment

Application

- Security Lighting
- Residential & Assisted Living
- Hotels/Motels

LED Dusk to Dawn

Versions




LEDbulb E27 A19



LEDbulbD2D A19 E27 FR

Dimensional drawing



| Product | D | C |
|-----------------------------------|-------|--------|
| LED D2D 60W A60 E27 CW FR ND SRT4 | 62 mm | 114 mm |
| LED D2D 60W A60 E27 WW FR ND SRT4 | 62 mm | 114 mm |

LED Dusk to Dawn

| General Information | |
|---------------------------------------|----------------|
| Cap-Base | E27 |
| Rated Lifetime (Hours) | 15,000 hour(s) |
| Switching Cycle | 50,000 |
| Nominal lifetime | 15,000 hour(s) |
| Light Technical | |
| Beam Angle (Nom) | 250 degree(s) |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Luminous Flux | 806 lm |
| Operating and Electrical | |
| Input Frequency | 50 Hz |
| Line Frequency | 50 Hz |
| Starting Time (Nom) | 0.5 s |
| Wattage Equivalent | 60 W |
| Temperature | |
| T-Case Maximum (Nom) | 75 °C |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Bulb Finish | Frosted |
| Bulb Shape | A19 |

Light Technical

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color Code |
|------------|-----------------------------------|------------------------------------|------------|
| 78269600 | LED D2D 60W A60 E27 WW FR ND SRT4 | 2700 K | 827 |
| 78271900 | LED D2D 60W A60 E27 CW FR ND SRT4 | 4000 K | 840 |


Operating and Electrical

| Order Code | Full Product Name | Power Consumption |
|------------|-----------------------------------|-------------------|
| 78269600 | LED D2D 60W A60 E27 WW FR ND SRT4 | 7.5 W |

| Order Code | Full Product Name | Power Consumption |
|------------|-----------------------------------|-------------------|
| 78271900 | LED D2D 60W A60 E27 CW FR ND SRT4 | 6.5 W |

Approval and Application

| Order Code | Full Product Name | Energy Consumption kWh/1000 h |
|------------|-----------------------------------|-------------------------------|
| 78269600 | LED D2D 60W A60 E27 WW FR ND SRT4 | 8 kWh |
| 78271900 | LED D2D 60W A60 E27 CW FR ND SRT4 | 7 kWh |



LED Dusk to Dawn

