



Philips GreenPerform Waterproof G3: A high-performance, energy-efficient waterproof batten

GreenPerform Waterproof G3

GreenPerform Waterproof G3 is a superb choice for hard-working applications. Not only does it provide excellent optical performance, it also delivers substantial energy saving. And because it works seamlessly with IoT software like Interact, it also offers the option of customization, convenience, and data-driven insights.

Benefits

- Suit your applications with choice of two superior optics
- Excellent energy savings
- Data-driven insights via
- Interact software and platforms

Features

- Injection molding Polycarbonate Cover Opal (PCO) and Wide Beam (WB) optics
- Up to 140lm/W
- IP65/IK08
- 50,000 hours L70 B50 @ 35°C
- Works with Interact IoT software and platform

GreenPerform Waterproof G3

Application

- Parking Garages
- Manufacturing
- Warehouses

Specifications

Mounting type	Surface
	Suspended
Operating Temperature range	-20 to +45°C
Light Source	LED
Mains Voltage	220-240V / 50-60Hz
Dimming	PSD: DALI
	WIA: Wireless control, compatible with Interact Pro
Control system input	DALI/Wireless Zigbee
Material	PC
Main color of the luminaire	RAL7035
Lumen maintenance at median useful life 50.000h	L85
Flicker / Pst / SVM	<4% / 0.5 / 0.4
Luminous flux	Up to 8000lm
Power consumption	7.8W to 60W
Luminaire efficacy	Up to 140lm/W

Correlated color temperature - CCT	4000K 6500K
Color Rendering index - CRI	80
Optical cover/lens material	PC
Optical cover/lens finish	Opal Clear
Mechanical impact protection	IK08
Ingress protection	IP65
Driver replaceable	Yes
Overall height	76mm
Overall length	665mm
	1215mm
	1515mm
Overall width	80mm
Installation	Suspension
	Surface



Versions






GreenPerform Waterproof G3

GreenPerform Waterproof G3

Dimensional drawing



Type	Dimensional (mm)						Nr. Of Clips
	A	B	C	D	E min	E max	
1600		665			308	512	6
L1200	76	1215	80	38	538	1092	10
L1500		1515			838	1392	12



GreenPerform Waterproof G3

General Information

CE mark CE mark

Driver included Yes

ENEC mark -

Flammability mark -

Light Technical

Optic type -

Operating and Electrical

Input Voltage 220 to 240 V

Temperature

Ambient temperature range -20 to +45 °C

Mechanical and Housing

Housing Color Gray

Approval and Application

Protection class IEC Safety class I

Mech. impact protection code IK08

Ingress protection code IP65

General Information

Order Code	Full Product Name	Gear	Glow-wire test	Light source replaceable	Number of gear units
911401514342	WT198C LED10S/840 PSU L600	-	-	-	-
911401551502	WT198X LED20S/840 L1 W L600	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401551602	WT198X LED27S/840 L1 W L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401551702	WT198X LED40S/840 L1 W L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401551802	WT198X LED60S/840 L1 W L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401551902	WT198X LED82S/840 L1 W L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401552002	WT198X LED20S/865 L1 W L600	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401552102	WT198X LED27S/865 L1 W L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401552202	WT198X LED40S/865 L1 W L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401552302	WT198X LED60S/865 L1 W L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401552402	WT198X LED82S/865 L1 W L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401571091	WT198X LED20S/840 L1 S L600	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401571391	WT198X LED60S/840 L1 S L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401571491	WT198X LED82S/840 L1 S L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401571591	WT198X LED20S/865 L1 S L600	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401571891	WT198X LED60S/865 L1 S L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401571991	WT198X LED82S/865 L1 S L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401552502	WT198X LED19S/840 L1 W PCO L600	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401552602	WT198X LED26S/840 L1 W PCO L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401552702	WT198X LED38S/840 L1 W PCO L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401552802	WT198X LED57S/840 L1 W PCO L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401552902	WT198X LED77S/840 L1 W PCO L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401553002	WT198X LED19S/865 L1 W PCO L600	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401553102	WT198X LED26S/865 L1 W PCO L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401553202	WT198X LED38S/865 L1 W PCO L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit

Order Code	Full Product Name	Gear	Glow-wire test	Light source replaceable	Number of gear units
911401553302	WT198X LED57S/865 L1 W PCO L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401553402	WT198X LED77S/865 L1 W PCO L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401572091	WT198X LED19S/840 L1 S PCO L600	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401572391	WT198X LED57S/840 L1 S PCO L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401572491	WT198X LED77S/840 L1 S PCO L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401572591	WT198X LED19S/865 L1 S PCO L600	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401572891	WT198X LED57S/865 L1 S PCO L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401572991	WT198X LED77S/865 L1 S PCO L1500	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401571191	WT198X LED27S/840 L1 S L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401571291	WT198X LED40S/840 L1 S L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401571691	WT198X LED27S/865 L1 S L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401571791	WT198X LED40S/865 L1 S L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401572191	WT198X LED26S/840 L1 S PCO L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401572291	WT198X LED38S/840 L1 S PCO L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401572691	WT198X LED26S/865 L1 S PCO L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401572791	WT198X LED38S/865 L1 S PCO L1200	EB	Temperature 650 °C, duration 30 s	-	1 unit
911401562761	WT198C LED27S/840 PSD L1200	-	Temperature 850 °C, duration 30 s	No	1 unit
911401562861	WT198C LED40S/840 PSD L1200	-	Temperature 850 °C, duration 30 s	No	1 unit
911401562961	WT198C LED60S/840 PSD L1500	-	Temperature 850 °C, duration 30 s	No	1 unit
911401563061	WT198C LED80S/840 PSD L1500	-	Temperature 850 °C, duration 30 s	No	1 unit
911401825580	WT198C LED19S/840 PSU L600	-	Temperature 850 °C, duration 30 s	No	1 unit
911401825680	WT198C LED27S/840 PSU L1200	-	Temperature 850 °C, duration 30 s	No	1 unit
911401825780	WT198C LED40S/840 PSU L1200	-	Temperature 850 °C, duration 30 s	No	1 unit
911401825880	WT198C LED60S/840 PSU L1500	-	Temperature 850 °C, duration 30 s	No	1 unit
911401825980	WT198C LED80S/840 PSU L1500	-	Temperature 850 °C, duration 30 s	No	1 unit

GreenPerform Waterproof G3

Order Code	Full Product Name	Gear	Glow-wire test	Light source replaceable	Number of gear units
911401826080	WT198C LED18S/840 PSU PCO L600	-	Temperature 850 °C, duration 30 s	No	1 unit
911401826180	WT198C LED25S/840 PSU PCO L1200	-	Temperature 850 °C, duration 30 s	No	1 unit
911401826380	WT198C LED37S/840 PSU PCO L1200	-	Temperature 850 °C, duration 30 s	No	1 unit
911401826480	WT198C LED57S/840 PSU PCO L1500	-	Temperature 850 °C, duration 30 s	No	1 unit
911401826580	WT198C LED75S/840 PSU PCO L1500	-	Temperature 850 °C, duration 30 s	No	1 unit

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)
911401514342	WT198C LED10S/840 PSU L600	-	4000 K	Polycarbonate bowl/cover frosted	>80
911401551502	WT198X LED20S/840 L1 W L600	-	4000 K	Polycarbonate bowl/cover	80
911401551602	WT198X LED27S/840 L1 W L1200	-	4000 K	Polycarbonate bowl/cover	80
911401551702	WT198X LED40S/840 L1 W L1200	-	4000 K	Polycarbonate bowl/cover	80
911401551802	WT198X LED60S/840 L1 W L1500	-	4000 K	Polycarbonate bowl/cover	80
911401551902	WT198X LED82S/840 L1 W L1500	-	4000 K	Polycarbonate bowl/cover	80
911401552002	WT198X LED20S/865 L1 W L600	-	6500 K	Polycarbonate bowl/cover	80
911401552102	WT198X LED27S/865 L1 W L1200	-	6500 K	Polycarbonate bowl/cover	80
911401552202	WT198X LED40S/865 L1 W L1200	-	6500 K	Polycarbonate bowl/cover	80
911401552302	WT198X LED60S/865 L1 W L1500	-	6500 K	Polycarbonate bowl/cover	80
911401552402	WT198X LED82S/865 L1 W L1500	-	6500 K	Polycarbonate bowl/cover	80

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)
911401571091	WT198X LED20S/840 L1 S L600	-	4000 K	Polycarbonate bowl/cover	80
911401571391	WT198X LED60S/840 L1 S L1500	-	4000 K	Polycarbonate bowl/cover	80
911401571491	WT198X LED82S/840 L1 S L1500	-	4000 K	Polycarbonate bowl/cover	80
911401571591	WT198X LED20S/865 L1 S L600	-	6500 K	Polycarbonate bowl/cover	80
911401571891	WT198X LED60S/865 L1 S L1500	-	6500 K	Polycarbonate bowl/cover	80
911401571991	WT198X LED82S/865 L1 S L1500	-	6500 K	Polycarbonate bowl/cover	80
911401552502	WT198X LED19S/840 L1 W PCO L600	-	4000 K	Polycarbonate bowl/cover	80
911401552602	WT198X LED26S/840 L1 W PCO L1200	-	4000 K	Polycarbonate bowl/cover	80
911401552702	WT198X LED38S/840 L1 W PCO L1200	-	4000 K	Polycarbonate bowl/cover	80
911401552802	WT198X LED57S/840 L1 W PCO L1500	-	4000 K	Polycarbonate bowl/cover	80

GreenPerform Waterproof G3

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)
911401552902	WT198X LED77S/840 L1 W PCO L1500	-	4000 K	Polycarbonate bowl/cover	80
911401553002	WT198X LED19S/865 L1 W PCO L600	-	6500 K	Polycarbonate bowl/cover	80
911401553102	WT198X LED26S/865 L1 W PCO L1200	-	6500 K	Polycarbonate bowl/cover	80
911401553202	WT198X LED38S/865 L1 W PCO L1200	-	6500 K	Polycarbonate bowl/cover	80
911401553302	WT198X LED57S/865 L1 W PCO L1500	-	6500 K	Polycarbonate bowl/cover	80
911401553402	WT198X LED77S/865 L1 W PCO L1500	-	6500 K	Polycarbonate bowl/cover	80
911401572091	WT198X LED19S/840 L1 S PCO L600	-	4000 K	Polycarbonate bowl/cover	80
911401572391	WT198X LED57S/840 L1 S PCO L1500	-	4000 K	Polycarbonate bowl/cover	80
911401572491	WT198X LED77S/840 L1 S PCO L1500	-	4000 K	Polycarbonate bowl/cover	80
911401572591	WT198X LED19S/865 L1 S PCO L600	-	6500 K	Polycarbonate bowl/cover	80
911401572891	WT198X LED57S/865 L1 S PCO L1500	-	6500 K	Polycarbonate bowl/cover	80
911401572991	WT198X LED77S/865 L1 S PCO L1500	-	6500 K	Polycarbonate bowl/cover	80

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)
911401571191	WT198X LED27S/840 L1 S L1200	-	4000 K	Polycarbonate bowl/cover	80
911401571291	WT198X LED40S/840 L1 S L1200	-	4000 K	Polycarbonate bowl/cover	80
911401571691	WT198X LED27S/865 L1 S L1200	-	6500 K	Polycarbonate bowl/cover	80
911401571791	WT198X LED40S/865 L1 S L1200	-	6500 K	Polycarbonate bowl/cover	80
911401572191	WT198X LED26S/840 L1 S PCO L1200	-	4000 K	Polycarbonate bowl/cover	80
911401572291	WT198X LED38S/840 L1 S PCO L1200	-	4000 K	Polycarbonate bowl/cover	80
911401572691	WT198X LED26S/865 L1 S PCO L1200	-	6500 K	Polycarbonate bowl/cover	80
911401572791	WT198X LED38S/865 L1 S PCO L1200	-	6500 K	Polycarbonate bowl/cover	80
911401562761	WT198C LED27S/840 PSD L1200	120 degree(s)	4000 K	-	>80
911401562861	WT198C LED40S/840 PSD L1200	120 degree(s)	4000 K	-	>80
911401562961	WT198C LED60S/840 PSD L1500	120 degree(s)	4000 K	-	>80
911401563061	WT198C LED80S/840 PSD L1500	120 degree(s)	4000 K	-	>80
911401825580	WT198C LED19S/840 PSU L600	120 degree(s)	4000 K	-	>80
911401825680	WT198C LED27S/840 PSU L1200	120 degree(s)	4000 K	-	>80
911401825780	WT198C LED40S/840 PSU L1200	120 degree(s)	4000 K	-	>80

GreenPerform Waterproof G3

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)
911401825880	WT198C LED60S/840 PSU L1500	120 degree(s)	4000 K	-	>80
911401825980	WT198C LED80S/840 PSU L1500	120 degree(s)	4000 K	-	>80
911401826080	WT198C LED18S/840 PSU PCO L600	120 degree(s)	4000 K	-	>80
911401826180	WT198C LED25S/840	120 degree(s)	4000 K	-	>80

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)
	PSU PCO L1200				
911401826380	WT198C LED37S/840 PSU PCO L1200	120 degree(s)	4000 K	-	>80
911401826480	WT198C LED57S/840 PSU PCO L1500	120 degree(s)	4000 K	-	>80
911401826580	WT198C LED75S/840 PSU PCO L1500	120 degree(s)	4000 K	-	>80

Light Technical (2/2)

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
911401514342	WT198C LED10S/840 PSU L600	130 lm/W	1,000 lm	-
911401551502	WT198X LED20S/840 L1 W L600	136.1 lm/W	2,000 lm	1
911401551602	WT198X LED27S/840 L1 W L1200	143.6 lm/W	2,700 lm	1
911401551702	WT198X LED40S/840 L1 W L1200	138.4 lm/W	4,000 lm	1
911401551802	WT198X LED60S/840 L1 W L1500	137.6 lm/W	6,000 lm	1
911401551902	WT198X LED82S/840 L1 W L1500	138.7 lm/W	8,200 lm	1
911401552002	WT198X LED20S/865 L1 W L600	136.1 lm/W	2,000 lm	1
911401552102	WT198X LED27S/865 L1 W L1200	143.6 lm/W	2,700 lm	1
911401552202	WT198X LED40S/865 L1 W L1200	138.4 lm/W	4,000 lm	1
911401552302	WT198X LED60S/865 L1 W L1500	137.6 lm/W	6,000 lm	1
911401552402	WT198X LED82S/865 L1 W L1500	138.7 lm/W	8,200 lm	1
911401571091	WT198X LED20S/840 L1 S L600	136.1 lm/W	2,000 lm	1
911401571391	WT198X LED60S/840 L1 S L1500	137.6 lm/W	6,000 lm	1
911401571491	WT198X LED82S/840 L1 S L1500	138.7 lm/W	8,200 lm	1

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
911401571591	WT198X LED20S/865 L1 S L600	136.1 lm/W	2,000 lm	1
911401571891	WT198X LED60S/865 L1 S L1500	137.6 lm/W	6,000 lm	1
911401571991	WT198X LED82S/865 L1 S L1500	138.7 lm/W	8,200 lm	1
911401552502	WT198X LED19S/840 L1 W PCO L600	129.3 lm/W	1,900 lm	1
911401552602	WT198X LED26S/840 L1 W PCO L1200	138.3 lm/W	2,600 lm	1
911401552702	WT198X LED38S/840 L1 W PCO L1200	131.5 lm/W	3,800 lm	1
911401552802	WT198X LED57S/840 L1 W PCO L1500	130.7 lm/W	5,700 lm	1
911401552902	WT198X LED77S/840 L1 W PCO L1500	130.3 lm/W	7,700 lm	1
911401553002	WT198X LED19S/865 L1 W PCO L600	129.3 lm/W	1,900 lm	1
911401553102	WT198X LED26S/865 L1 W PCO L1200	138.3 lm/W	2,600 lm	1
911401553202	WT198X LED38S/865 L1 W PCO L1200	131.5 lm/W	3,800 lm	1
911401553302	WT198X LED57S/865 L1 W PCO L1500	130.7 lm/W	5,700 lm	1
911401553402	WT198X LED77S/865 L1 W PCO L1500	130.3 lm/W	7,700 lm	1
911401572091	WT198X LED19S/840 L1 S PCO L600	129.3 lm/W	1,900 lm	1

GreenPerform Waterproof G3

Order Code	Full Product Name	Luminous Efficacy (rated)		Number of light sources
		(Nom)	Luminous Flux	
911401572391	WT198X LED57S/840 L1 S PCO L1500	130.7 lm/W	5,700 lm	1
911401572491	WT198X LED77S/840 L1 S PCO L1500	130.3 lm/W	7,700 lm	1
911401572591	WT198X LED19S/865 L1 S PCO L600	129.3 lm/W	1,900 lm	1
911401572891	WT198X LED57S/865 L1 S PCO L1500	130.7 lm/W	5,700 lm	1
911401572991	WT198X LED77S/865 L1 S PCO L1500	130.3 lm/W	7,700 lm	1
911401571191	WT198X LED27S/840 L1 S L1200	143.6 lm/W	2,700 lm	1
911401571291	WT198X LED40S/840 L1 S L1200	138.4 lm/W	4,000 lm	1
911401571691	WT198X LED27S/865 L1 S L1200	143.6 lm/W	2,700 lm	1
911401571791	WT198X LED40S/865 L1 S L1200	138.4 lm/W	4,000 lm	1
911401572191	WT198X LED26S/840 L1 S PCO L1200	138.3 lm/W	2,600 lm	1
911401572291	WT198X LED38S/840 L1 S PCO L1200	131.5 lm/W	3,800 lm	1
911401572691	WT198X LED26S/865 L1 S PCO L1200	138.3 lm/W	2,600 lm	1
911401572791	WT198X LED38S/865 L1 S PCO L1200	131.5 lm/W	3,800 lm	1
911401562761	WT198C LED27S/840 PSD L1200	132 lm/W	2,700 lm	-

Order Code	Full Product Name	Luminous Efficacy (rated)		Number of light sources
		(Nom)	Luminous Flux	
911401562861	WT198C LED40S/840 PSD L1200	140 lm/W	4,000 lm	-
911401562961	WT198C LED60S/840 PSD L1500	140 lm/W	6,000 lm	-
911401563061	WT198C LED80S/840 PSD L1500	140 lm/W	8,000 lm	-
911401825580	WT198C LED19S/840 PSU L600	127 lm/W	1,900 lm	-
911401825680	WT198C LED27S/840 PSU L1200	132 lm/W	2,700 lm	-
911401825780	WT198C LED40S/840 PSU L1200	140 lm/W	4,000 lm	-
911401825880	WT198C LED60S/840 PSU L1500	140 lm/W	6,000 lm	-
911401825980	WT198C LED80S/840 PSU L1500	140 lm/W	8,000 lm	-
911401826080	WT198C LED18S/840 PSU PCO L600	121 lm/W	1,800 lm	-
911401826180	WT198C LED25S/840 PSU PCO L1200	122 lm/W	2,500 lm	-
911401826380	WT198C LED37S/840 PSU PCO L1200	128 lm/W	3,700 lm	-
911401826480	WT198C LED57S/840 PSU PCO L1500	130 lm/W	5,700 lm	-
911401826580	WT198C LED75S/840 PSU PCO L1500	133 lm/W	7,500 lm	-

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power Consumption
911401514342	WT198C LED10S/840 PSU L600	50 to 60 Hz	7.8 W
911401551502	WT198X LED20S/840 L1 W L600	50 to 60 Hz	14.7 W
911401551602	WT198X LED27S/840 L1 W L1200	50 to 60 Hz	18.8 W
911401551702	WT198X LED40S/840 L1 W L1200	50 to 60 Hz	28.9 W
911401551802	WT198X LED60S/840 L1 W L1500	50 to 60 Hz	43.6 W
911401551902	WT198X LED82S/840 L1 W L1500	50 to 60 Hz	59.1 W
911401552002	WT198X LED20S/865 L1 W L600	50 to 60 Hz	14.7 W
911401552102	WT198X LED27S/865 L1 W L1200	50 to 60 Hz	18.8 W
911401552202	WT198X LED40S/865 L1 W L1200	50 to 60 Hz	28.9 W
911401552302	WT198X LED60S/865 L1 W L1500	50 to 60 Hz	43.6 W
911401552402	WT198X LED82S/865 L1 W L1500	50 to 60 Hz	59.1 W
911401571091	WT198X LED20S/840 L1 S L600	50 to 60 Hz	14.7 W
911401571391	WT198X LED60S/840 L1 S L1500	50 to 60 Hz	43.6 W
911401571491	WT198X LED82S/840 L1 S L1500	50 to 60 Hz	59.1 W

Order Code	Full Product Name	Line Frequency	Power Consumption
911401571591	WT198X LED20S/865 L1 S L600	50 to 60 Hz	14.7 W
911401571891	WT198X LED60S/865 L1 S L1500	50 to 60 Hz	43.6 W
911401571991	WT198X LED82S/865 L1 S L1500	50 to 60 Hz	59.1 W
911401552502	WT198X LED19S/840 L1 W PCO L600	50 to 60 Hz	14.7 W
911401552602	WT198X LED26S/840 L1 W PCO L1200	50 to 60 Hz	18.8 W
911401552702	WT198X LED38S/840 L1 W PCO L1200	50 to 60 Hz	28.9 W
911401552802	WT198X LED57S/840 L1 W PCO L1500	50 to 60 Hz	43.6 W
911401552902	WT198X LED77S/840 L1 W PCO L1500	50 to 60 Hz	59.1 W
911401553002	WT198X LED19S/865 L1 W PCO L600	50 to 60 Hz	14.7 W
911401553102	WT198X LED26S/865 L1 W PCO L1200	50 to 60 Hz	18.8 W

GreenPerform Waterproof G3

Order Code	Full Product Name	Line Frequency	Power Consumption
911401553202	WT198X LED38S/865 L1 W PCO L1200	50 to 60 Hz	28.9 W
911401553302	WT198X LED57S/865 L1 W PCO L1500	50 to 60 Hz	43.6 W
911401553402	WT198X LED77S/865 L1 W PCO L1500	50 to 60 Hz	59.1 W
911401572091	WT198X LED19S/840 L1 S PCO L600	50 to 60 Hz	14.7 W
911401572391	WT198X LED57S/840 L1 S PCO L1500	50 to 60 Hz	43.6 W
911401572491	WT198X LED77S/840 L1 S PCO L1500	50 to 60 Hz	59.1 W
911401572591	WT198X LED19S/865 L1 S PCO L600	50 to 60 Hz	14.7 W
911401572891	WT198X LED57S/865 L1 S PCO L1500	50 to 60 Hz	43.6 W
911401572991	WT198X LED77S/865 L1 S PCO L1500	50 to 60 Hz	59.1 W
911401571191	WT198X LED27S/840 L1 S L1200	50 to 60 Hz	18.8 W
911401571291	WT198X LED40S/840 L1 S L1200	50 to 60 Hz	28.9 W
911401571691	WT198X LED27S/865 L1 S L1200	50 to 60 Hz	18.8 W
911401571791	WT198X LED40S/865 L1 S L1200	50 to 60 Hz	28.9 W
911401572191	WT198X LED26S/840 L1 S PCO L1200	50 to 60 Hz	18.8 W
911401572291	WT198X LED38S/840 L1 S PCO L1200	50 to 60 Hz	28.9 W

Order Code	Full Product Name	Line Frequency	Power Consumption
911401572691	WT198X LED26S/865 L1 S PCO L1200	50 to 60 Hz	18.8 W
911401572791	WT198X LED38S/865 L1 S PCO L1200	50 to 60 Hz	28.9 W
911401562761	WT198C LED27S/840 PSD L1200	50 or 60 Hz	20.5 W
911401562861	WT198C LED40S/840 PSD L1200	50 or 60 Hz	28.6 W
911401562961	WT198C LED60S/840 PSD L1500	50 or 60 Hz	42.7 W
911401563061	WT198C LED80S/840 PSD L1500	50 or 60 Hz	57 W
911401825580	WT198C LED19S/840 PSU L600	50 or 60 Hz	15 W
911401825680	WT198C LED27S/840 PSU L1200	50 or 60 Hz	20.5 W
911401825780	WT198C LED40S/840 PSU L1200	50 or 60 Hz	28.6 W
911401825880	WT198C LED60S/840 PSU L1500	50 or 60 Hz	42.7 W
911401825980	WT198C LED80S/840 PSU L1500	50 or 60 Hz	57 W
911401826080	WT198C LED18S/840 PSU PCO L600	50 or 60 Hz	15 W
911401826180	WT198C LED25S/840 PSU PCO L1200	50 or 60 Hz	20.5 W
911401826380	WT198C LED37S/840 PSU PCO L1200	50 or 60 Hz	28.6 W
911401826480	WT198C LED57S/840 PSU PCO L1500	50 or 60 Hz	42.7 W
911401826580	WT198C LED75S/840 PSU PCO L1500	50 or 60 Hz	57 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401514342	WT198C LED10S/840 PSU L600	No
911401551502	WT198X LED20S/840 L1 W L600	Wireless Dim
911401551602	WT198X LED27S/840 L1 W L1200	Step Dim
911401551702	WT198X LED40S/840 L1 W L1200	Step Dim
911401551802	WT198X LED60S/840 L1 W L1500	Wireless Dim
911401551902	WT198X LED82S/840 L1 W L1500	Step Dim
911401552002	WT198X LED20S/865 L1 W L600	Wireless Dim
911401552102	WT198X LED27S/865 L1 W L1200	Step Dim
911401552202	WT198X LED40S/865 L1 W L1200	Wireless Dim
911401552302	WT198X LED60S/865 L1 W L1500	Wireless Dim
911401552402	WT198X LED82S/865 L1 W L1500	Step Dim
911401571091	WT198X LED20S/840 L1 S L600	Step Dim
911401571391	WT198X LED60S/840 L1 S L1500	Step Dim
911401571491	WT198X LED82S/840 L1 S L1500	Wireless Dim
911401571591	WT198X LED20S/865 L1 S L600	Step Dim
911401571891	WT198X LED60S/865 L1 S L1500	Step Dim
911401571991	WT198X LED82S/865 L1 S L1500	Wireless Dim
911401552502	WT198X LED19S/840 L1 W PCO L600	Wireless Dim
911401552602	WT198X LED26S/840 L1 W PCO L1200	Wireless Dim
911401552702	WT198X LED38S/840 L1 W PCO L1200	Step Dim
911401552802	WT198X LED57S/840 L1 W PCO L1500	Wireless Dim
911401552902	WT198X LED77S/840 L1 W PCO L1500	Step Dim

Order Code	Full Product Name	Dimmable
911401553002	WT198X LED19S/865 L1 W PCO L600	Wireless Dim
911401553102	WT198X LED26S/865 L1 W PCO L1200	Step Dim
911401553202	WT198X LED38S/865 L1 W PCO L1200	Step Dim
911401553302	WT198X LED57S/865 L1 W PCO L1500	Wireless Dim
911401553402	WT198X LED77S/865 L1 W PCO L1500	Step Dim
911401572091	WT198X LED19S/840 L1 S PCO L600	Step Dim
911401572391	WT198X LED57S/840 L1 S PCO L1500	Step Dim
911401572491	WT198X LED77S/840 L1 S PCO L1500	Step Dim
911401572591	WT198X LED19S/865 L1 S PCO L600	Step Dim
911401572891	WT198X LED57S/865 L1 S PCO L1500	Step Dim
911401572991	WT198X LED77S/865 L1 S PCO L1500	Wireless Dim
911401571191	WT198X LED27S/840 L1 S L1200	Wireless Dim
911401571291	WT198X LED40S/840 L1 S L1200	Wireless Dim
911401571691	WT198X LED27S/865 L1 S L1200	Wireless Dim
911401571791	WT198X LED40S/865 L1 S L1200	Step Dim
911401572191	WT198X LED26S/840 L1 S PCO L1200	Step Dim
911401572291	WT198X LED38S/840 L1 S PCO L1200	Wireless Dim
911401572691	WT198X LED26S/865 L1 S PCO L1200	Step Dim
911401572791	WT198X LED38S/865 L1 S PCO L1200	Wireless Dim
911401562761	WT198C LED27S/840 PSD L1200	Yes
911401562861	WT198C LED40S/840 PSD L1200	Yes
911401562961	WT198C LED60S/840 PSD L1500	Yes

GreenPerform Waterproof G3

Order Code	Full Product Name	Dimmable
911401563061	WT198C LED80S/840 PSD L1500	Yes
911401825580	WT198C LED19S/840 PSU L600	No
911401825680	WT198C LED27S/840 PSU L1200	No
911401825780	WT198C LED40S/840 PSU L1200	No
911401825880	WT198C LED60S/840 PSU L1500	No
911401825980	WT198C LED80S/840 PSU L1500	No

Order Code	Full Product Name	Dimmable
911401826080	WT198C LED18S/840 PSU PCO L600	No
911401826180	WT198C LED25S/840 PSU PCO L1200	No
911401826380	WT198C LED37S/840 PSU PCO L1200	No
911401826480	WT198C LED57S/840 PSU PCO L1500	No
911401826580	WT198C LED75S/840 PSU PCO L1500	No

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401514342	WT198C LED10S/840 PSU L600	-	-10% / +10%
911401551502	WT198X LED20S/840 L1 W L600	(0.38, 0.38) SDCM≤3	-10% / +10%
911401551602	WT198X LED27S/840 L1 W L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
911401551702	WT198X LED40S/840 L1 W L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
911401551802	WT198X LED60S/840 L1 W L1500	(0.38, 0.38) SDCM≤3	-10% / +10%
911401551902	WT198X LED82S/840 L1 W L1500	(0.38, 0.38) SDCM≤3	-10% / +10%
911401552002	WT198X LED20S/865 L1 W L600	(0.32, 0.33) SDCM≤3	-10% / +10%
911401552102	WT198X LED27S/865 L1 W L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
911401552202	WT198X LED40S/865 L1 W L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
911401552302	WT198X LED60S/865 L1 W L1500	(0.32, 0.33) SDCM≤3	-10% / +10%
911401552402	WT198X LED82S/865 L1 W L1500	(0.32, 0.33) SDCM≤3	-10% / +10%
911401571091	WT198X LED20S/840 L1 S L600	(0.38, 0.38) SDCM≤3	-10% / +10%
911401571391	WT198X LED60S/840 L1 S L1500	(0.38, 0.38) SDCM≤3	-10% / +10%
911401571491	WT198X LED82S/840 L1 S L1500	(0.38, 0.38) SDCM≤3	-10% / +10%
911401571591	WT198X LED20S/865 L1 S L600	(0.32, 0.33) SDCM≤3	-10% / +10%
911401571891	WT198X LED60S/865 L1 S L1500	(0.32, 0.33) SDCM≤3	-10% / +10%
911401571991	WT198X LED82S/865 L1 S L1500	(0.32, 0.33) SDCM≤3	-10% / +10%
911401552502	WT198X LED19S/840 L1 W PCO L600	(0.38, 0.38) SDCM≤3	-10% / +10%
911401552602	WT198X LED26S/840 L1 W PCO L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
911401552702	WT198X LED38S/840 L1 W PCO L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
911401552802	WT198X LED57S/840 L1 W PCO L1500	(0.38, 0.38) SDCM≤3	-10% / +10%
911401552902	WT198X LED77S/840 L1 W PCO L1500	(0.38, 0.38) SDCM≤3	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401553002	WT198X LED19S/865 L1 W PCO L600	(0.32, 0.33) SDCM≤3	-10% / +10%
911401553102	WT198X LED26S/865 L1 W PCO L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
911401553202	WT198X LED38S/865 L1 W PCO L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
911401553302	WT198X LED57S/865 L1 W PCO L1500	(0.32, 0.33) SDCM≤3	-10% / +10%
911401553402	WT198X LED77S/865 L1 W PCO L1500	(0.32, 0.33) SDCM≤3	-10% / +10%
911401572091	WT198X LED19S/840 L1 S PCO L600	(0.38, 0.38) SDCM≤3	-10% / +10%
911401572391	WT198X LED57S/840 L1 S PCO L1500	(0.38, 0.38) SDCM≤3	-10% / +10%
911401572491	WT198X LED77S/840 L1 S PCO L1500	(0.38, 0.38) SDCM≤3	-10% / +10%
911401572591	WT198X LED19S/865 L1 S PCO L600	(0.32, 0.33) SDCM≤3	-10% / +10%
911401572891	WT198X LED57S/865 L1 S PCO L1500	(0.32, 0.33) SDCM≤3	-10% / +10%
911401572991	WT198X LED77S/865 L1 S PCO L1500	(0.32, 0.33) SDCM≤3	-10% / +10%
911401571191	WT198X LED27S/840 L1 S L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
911401571291	WT198X LED40S/840 L1 S L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
911401571691	WT198X LED27S/865 L1 S L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
911401571791	WT198X LED40S/865 L1 S L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
911401572191	WT198X LED26S/840 L1 S PCO L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
911401572291	WT198X LED38S/840 L1 S PCO L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
911401572691	WT198X LED26S/865 L1 S PCO L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
911401572791	WT198X LED38S/865 L1 S PCO L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
911401562761	WT198C LED27S/840 PSD L1200	(0.38, 0.38)	+/-10%
911401562861	WT198C LED40S/840 PSD L1200	(0.38, 0.38)	+/-10%

GreenPerform Waterproof G3

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401562961	WT198C LED60S/840 PSD L1500	(0.38,0.38)	+/-10%
911401563061	WT198C LED80S/840 PSD L1500	(0.38,0.38)	+/-10%
911401825580	WT198C LED19S/840 PSU L600	(0.38,0.38)	+/-10%
911401825680	WT198C LED27S/840 PSU L1200	(0.38,0.38)	+/-10%
911401825780	WT198C LED40S/840 PSU L1200	(0.38,0.38)	+/-10%
911401825880	WT198C LED60S/840 PSU L1500	(0.38,0.38)	+/-10%
911401825980	WT198C LED80S/840 PSU L1500	(0.38,0.38)	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401826080	WT198C LED18S/840 PSU L600	(0.38,0.38)	+/-10%
911401826180	WT198C LED25S/840 PSU L1200	(0.38,0.38)	+/-10%
911401826380	WT198C LED37S/840 PSU L1200	(0.38,0.38)	+/-10%
911401826480	WT198C LED57S/840 PSU L1500	(0.38,0.38)	+/-10%
911401826580	WT198C LED75S/840 PSU L1500	(0.38,0.38)	+/-10%

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h	Median useful life L80B50	Median useful life L90B50
911401514342	WT198C LED10S/840 PSU L600	-	-	-
911401551502	WT198X LED20S/840 L1 W L600	-	-	-
911401551602	WT198X LED27S/840 L1 W L1200	-	-	-
911401551702	WT198X LED40S/840 L1 W L1200	-	-	-
911401551802	WT198X LED60S/840 L1 W L1500	-	-	-
911401551902	WT198X LED82S/840 L1 W L1500	-	-	-
911401552002	WT198X LED20S/865 L1 W L600	-	-	-
911401552102	WT198X LED27S/865 L1 W L1200	-	-	-
911401552202	WT198X LED40S/865 L1 W L1200	-	-	-
911401552302	WT198X LED60S/865 L1 W L1500	-	-	-
911401552402	WT198X LED82S/865 L1 W L1500	-	-	-
911401571091	WT198X LED20S/840 L1 S L600	-	-	-
911401571391	WT198X LED60S/840 L1 S L1500	-	-	-
911401571491	WT198X LED82S/840 L1 S L1500	-	-	-
911401571591	WT198X LED20S/865 L1 S L600	-	-	-
911401571891	WT198X LED60S/865 L1 S L1500	-	-	-

Order Code	Full Product Name	Driver failure rate at 5000 h	Median useful life L80B50	Median useful life L90B50
911401571991	WT198X LED82S/865 L1 S L1500	-	-	-
911401552502	WT198X LED19S/840 L1 W L600	-	-	-
911401552602	WT198X LED26S/840 L1 W L1200	-	-	-
911401552702	WT198X LED38S/840 L1 W L1200	-	-	-
911401552802	WT198X LED57S/840 L1 W L1500	-	-	-
911401552902	WT198X LED77S/840 L1 W L1500	-	-	-
911401553002	WT198X LED19S/865 L1 W L600	-	-	-
911401553102	WT198X LED26S/865 L1 W L1200	-	-	-
911401553202	WT198X LED38S/865 L1 W L1200	-	-	-
911401553302	WT198X LED57S/865 L1 W L1500	-	-	-
911401553402	WT198X LED77S/865 L1 W L1500	-	-	-
911401572091	WT198X LED19S/840 L1 S L600	-	-	-
911401572391	WT198X LED57S/840 L1 S L1500	-	-	-
911401572491	WT198X LED77S/840 L1 S L1500	-	-	-
911401572591	WT198X LED19S/865 L1 S L600	-	-	-
911401572891	WT198X LED57S/865 L1 S L1500	-	-	-

GreenPerform Waterproof G3

Order Code	Full Product Name	Driver failure rate at 5000 h	Median useful life L80B50	Median useful life L90B50
911401572991	WT198X LED77S/865 L1 S PCO L1500	-	-	-
911401571191	WT198X LED27S/840 L1 S L1200	-	-	-
911401571291	WT198X LED40S/840 L1 S L1200	-	-	-
911401571691	WT198X LED27S/865 L1 S L1200	-	-	-
911401571791	WT198X LED40S/865 L1 S L1200	-	-	-
911401572191	WT198X LED26S/840 L1 S PCO L1200	-	-	-
911401572291	WT198X LED38S/840 L1 S PCO L1200	-	-	-
911401572691	WT198X LED26S/865 L1 S PCO L1200	-	-	-
911401572791	WT198X LED38S/865 L1 S PCO L1200	-	-	-
911401562761	WT198C LED27S/840 PSD L1200	0.01 %	42,000 hour(s)	20,000 hour(s)
911401562861	WT198C LED40S/840 PSD L1200	0.01 %	42,000 hour(s)	20,000 hour(s)
911401562961	WT198C LED60S/840 PSD L1500	0.01 %	42,000 hour(s)	20,000 hour(s)

Order Code	Full Product Name	Driver failure rate at 5000 h	Median useful life L80B50	Median useful life L90B50
911401563061	WT198C LED80S/840 PSD L1500	0.01 %	42,000 hour(s)	20,000 hour(s)
911401825580	WT198C LED19S/840 PSU L600	1 %	42,000 hour(s)	20,000 hour(s)
911401825680	WT198C LED27S/840 PSU L1200	1 %	42,000 hour(s)	20,000 hour(s)
911401825780	WT198C LED40S/840 PSU L1200	1 %	42,000 hour(s)	20,000 hour(s)
911401825880	WT198C LED60S/840 PSU L1500	1 %	42,000 hour(s)	20,000 hour(s)
911401825980	WT198C LED80S/840 PSU L1500	1 %	42,000 hour(s)	20,000 hour(s)
911401826080	WT198C LED18S/840 PSU PCO L600	1 %	42,000 hour(s)	20,000 hour(s)
911401826180	WT198C LED25S/840 PSU PCO L1200	1 %	42,000 hour(s)	20,000 hour(s)
911401826380	WT198C LED37S/840 PSU PCO L1200	1 %	42,000 hour(s)	20,000 hour(s)
911401826480	WT198C LED57S/840 PSU PCO L1500	1 %	42,000 hour(s)	20,000 hour(s)
911401826580	WT198C LED75S/840 PSU PCO L1500	1 %	42,000 hour(s)	20,000 hour(s)

Application Conditions

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
911401514342	WT198C LED10S/840 PSU L600	-	-
911401551502	WT198X LED20S/840 L1 W L600	20%	Yes
911401551602	WT198X LED27S/840 L1 W L1200	20%	Yes
911401551702	WT198X LED40S/840 L1 W L1200	20%	Yes
911401551802	WT198X LED60S/840 L1 W L1500	20%	Yes
911401551902	WT198X LED82S/840 L1 W L1500	20%	Yes
911401552002	WT198X LED20S/865 L1 W L600	20%	Yes
911401552102	WT198X LED27S/865 L1 W L1200	20%	Yes
911401552202	WT198X LED40S/865 L1 W L1200	20%	Yes
911401552302	WT198X LED60S/865 L1 W L1500	20%	Yes
911401552402	WT198X LED82S/865 L1 W L1500	20%	Yes
911401571091	WT198X LED20S/840 L1 S L600	20%	Yes
911401571391	WT198X LED60S/840 L1 S L1500	20%	Yes
911401571491	WT198X LED82S/840 L1 S L1500	20%	Yes
911401571591	WT198X LED20S/865 L1 S L600	20%	Yes
911401571891	WT198X LED60S/865 L1 S L1500	20%	Yes
911401571991	WT198X LED82S/865 L1 S L1500	20%	Yes
911401552502	WT198X LED19S/840 L1 W PCO L600	20%	Yes
911401552602	WT198X LED26S/840 L1 W PCO L1200	20%	Yes

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
911401552702	WT198X LED38S/840 L1 W PCO L1200	20%	Yes
911401552802	WT198X LED57S/840 L1 W PCO L1500	20%	Yes
911401552902	WT198X LED77S/840 L1 W PCO L1500	20%	Yes
911401553002	WT198X LED19S/865 L1 W PCO L600	20%	Yes
911401553102	WT198X LED26S/865 L1 W PCO L1200	20%	Yes
911401553202	WT198X LED38S/865 L1 W PCO L1200	20%	Yes
911401553302	WT198X LED57S/865 L1 W PCO L1500	20%	Yes
911401553402	WT198X LED77S/865 L1 W PCO L1500	20%	Yes
911401572091	WT198X LED19S/840 L1 S PCO L600	20%	Yes
911401572391	WT198X LED57S/840 L1 S PCO L1500	20%	Yes
911401572491	WT198X LED77S/840 L1 S PCO L1500	20%	Yes
911401572591	WT198X LED19S/865 L1 S PCO L600	20%	Yes
911401572891	WT198X LED57S/865 L1 S PCO L1500	20%	Yes

GreenPerform Waterproof G3

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
911401572991	WT198X LED77S/865 L1 S PCO L1500	20%	Yes
911401571191	WT198X LED27S/840 L1 S L1200	20%	Yes
911401571291	WT198X LED40S/840 L1 S L1200	20%	Yes
911401571691	WT198X LED27S/865 L1 S L1200	20%	Yes
911401571791	WT198X LED40S/865 L1 S L1200	20%	Yes
911401572191	WT198X LED26S/840 L1 S PCO L1200	20%	Yes
911401572291	WT198X LED38S/840 L1 S PCO L1200	20%	Yes
911401572691	WT198X LED26S/865 L1 S PCO L1200	20%	Yes
911401572791	WT198X LED38S/865 L1 S PCO L1200	20%	Yes
911401562761	WT198C LED27S/840 PSD L1200	Not applicable	Not applicable
911401562861	WT198C LED40S/840 PSD L1200	Not applicable	Not applicable
911401562961	WT198C LED60S/840 PSD L1500	Not applicable	Not applicable
911401563061	WT198C LED80S/840 PSD L1500	Not applicable	Not applicable

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
911401825580	WT198C LED19S/840 PSU L600	Not applicable	-
911401825680	WT198C LED27S/840 PSU L1200	Not applicable	-
911401825780	WT198C LED40S/840 PSU L1200	Not applicable	-
911401825880	WT198C LED60S/840 PSU L1500	Not applicable	-
911401825980	WT198C LED80S/840 PSU L1500	Not applicable	-
911401826080	WT198C LED18S/840 PSU PCO L600	Not applicable	-
911401826180	WT198C LED25S/840 PSU PCO L1200	Not applicable	-
911401826380	WT198C LED37S/840 PSU PCO L1200	Not applicable	-
911401826480	WT198C LED57S/840 PSU PCO L1500	Not applicable	-
911401826580	WT198C LED75S/840 PSU PCO L1500	Not applicable	-

