



Compact LED spot that's the right fit for energy savings

StoreFit

Retailers are always looking for ways to reduce their environmental footprint and energy cost. With this StoreFit projector, conventional CDM luminaires can be replaced effortlessly with LED, leading to significantly less power consumption. The subtle and compact design reduces the visibility of the StoreFit projector in the store, and keeps shoppers' attention on the merchandise available on the shelves. As an affordable LED projector, this spot will enable you to start saving on energy costs straight away.

Benefits

- The small spot head results in a very discreet design
- Perfect LED replacement for CDM conventional luminaires
- Low initial investment

Features

- Up to 3900 lm
- Choose from a white or black finish (ST201T and ST210Y)
- Available in 3000K, 4000K and PremiumWhite 3000K
- Medium beam or wide beam reflector options

Application

- Convenience stores
- Supermarkets & hypermarkets
- Fashion stores

Warnings and Safety



- Cleaning the optic should only be done with pressurized air. Touching the LED or reflector is forbidden.
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

Versions



StoreFit ST210Y on Coreline trunking

Dimensional drawing



Product details

StoreFit ST210T, black



General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Light Technical	
Beam angle of light source	120 degree(s)
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Approval and Application	
Mech. impact protection code	IK02
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Application Conditions	
Suitable for random switching	Not applicable

General Information

Order Code	Full Product Name	Number of gear units	Product family code
910505102057	ST210Y 19S/FMT PSU MB WH	2 units	ST210Y
910505102058	ST210Y 19S/FMT DIA MB WH	2 units	ST210Y
910505102059	ST210Y 27S/830 PSU MB WH	2 units	ST210Y
910505102060	ST210Y 27S/830 DIA MB WH	2 units	ST210Y
910505102061	ST210Y 27S/840 PSU MB WH	2 units	ST210Y
910505102062	ST210Y 27S/840 DIA MB WH	2 units	ST210Y
910505102063	ST210Y 27S/PW930 PSU MB WH	2 units	ST210Y
910505102064	ST210Y 27S/PW930 DIA MB WH	2 units	ST210Y
910505102065	ST210Y 39S/830 PSU MB WH	2 units	ST210Y
910505102066	ST210Y 39S/830 DIA MB WH	2 units	ST210Y
910505102067	ST210Y 39S/840 PSU MB WH	2 units	ST210Y
910505102068	ST210Y 39S/840 DIA MB WH	2 units	ST210Y
910505102069	ST210Y 39S/PW930 PSU MB WH	2 units	ST210Y
910505102070	ST210Y 39S/PW930 DIA MB WH	2 units	ST210Y
910505102043	ST210T 27S/830 PSU MB BK	1 unit	ST210T
910505102044	ST210T 27S/830 PSU WB BK	1 unit	ST210T
910505102047	ST210T 39S/830 PSU MB BK	1 unit	ST210T
910505102048	ST210T 39S/830 PSU WB BK	1 unit	ST210T
910505102051	ST210T 27S/840 PSU MB BK	1 unit	ST210T
910505102052	ST210T 27S/840 PSU WB BK	1 unit	ST210T
910505102055	ST210T 39S/840 PSU MB BK	1 unit	ST210T
910505102056	ST210T 39S/840 PSU WB BK	1 unit	ST210T
910505102041	ST210T 27S/830 PSU MB WH	1 unit	ST210T
910505102042	ST210T 27S/830 PSU WB WH	1 unit	ST210T
910505102045	ST210T 39S/830 PSU MB WH	1 unit	ST210T
910505102046	ST210T 39S/830 PSU WB WH	1 unit	ST210T
910505102049	ST210T 27S/840 PSU MB WH	1 unit	ST210T
910505102050	ST210T 27S/840 PSU WB WH	1 unit	ST210T
910505102053	ST210T 39S/840 PSU MB WH	1 unit	ST210T
910505102054	ST210T 39S/840 PSU WB WH	1 unit	ST210T

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505102057	ST210Y 19S/FMT PSU MB WH	3000 K	≥80	78 lm/W	3,900 lm
910505102058	ST210Y 19S/FMT DIA MB WH	3000 K	≥80	78 lm/W	3,900 lm
910505102059	ST210Y 27S/830 PSU MB WH	3000 K	≥80	120 lm/W	5,800 lm
910505102060	ST210Y 27S/830 DIA MB WH	3000 K	≥80	116 lm/W	5,800 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505102061	ST210Y 27S/840 PSU MB WH	4000 K	≥80	120 lm/W	5,900 lm
910505102062	ST210Y 27S/840 DIA MB WH	4000 K	≥80	123 lm/W	5,900 lm
910505102063	ST210Y 27S/PW930 PSU MB WH	3000 K	≥90	121 lm/W	5,700 lm
910505102064	ST210Y 27S/PW930 DIA MB WH	3000 K	≥90	121 lm/W	5,700 lm

		Correlated	Color	Luminous	
	Full Product	Color	rendering	Efficacy	
Order Code	Name	Temperature	index	(rated)	Luminous
		(Nom)	(CRI)	(Nom)	Flux
910505102065	ST210Y 39S/830 PSU MB WH	3000 K	≥80	113 lm/W	7,800 lm
910505102066	ST210Y 39S/830 DIA MB WH	3000 K	≥80	113 lm/W	7,800 lm
910505102067	ST210Y 39S/840 PSU MB WH	4000 K	≥80	108 lm/W	8,100 lm
910505102068	ST210Y 39S/840 DIA MB WH	4000 K	≥80	108 lm/W	8,100 lm
910505102069	ST210Y 39S/ PW930 PSU MB WH	3000 K	≥90	128 lm/W	7,700 lm
910505102070	ST210Y 39S/ PW930 DIA MB WH	3000 K	≥90	128 lm/W	7,700 lm
910505102043	ST210T 27S/830 PSU MB BK	3000 K	≥80	122 lm/W	2,700 lm
910505102044	ST210T 27S/830 PSU WB BK	3000 K	≥80	122 lm/W	2,700 lm
910505102047	ST210T 39S/830 PSU MB BK	3000 K	≥80	113 lm/W	3,900 lm
910505102048	ST210T 39S/830 PSU WB BK	3000 K	≥80	113 lm/W	3,900 lm
910505102051	ST210T 27S/840 PSU MB BK	4000 K	≥80	127 lm/W	2,800 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type
910505102057	ST210Y 19S/FMT PSU MB WH	Medium-beam reflector high reflectance
910505102058	ST210Y 19S/FMT DIA MB WH	Medium-beam reflector high reflectance
910505102059	ST210Y 27S/830 PSU MB WH	Medium-beam reflector high reflectance
910505102060	ST210Y 27S/830 DIA MB WH	Medium-beam reflector high reflectance
910505102061	ST210Y 27S/840 PSU MB WH	Medium-beam reflector high reflectance
910505102062	ST210Y 27S/840 DIA MB WH	Medium-beam reflector high reflectance

		Correlated	Color	Luminous	
	Full Product	Color	rendering	Efficacy	
Order Code	Name	Temperature	index	(rated)	Luminous
		(Nom)	(CRI)	(Nom)	Flux
910505102052	ST210T 27S/840 PSU WB BK	4000 K	≥80	127 lm/W	2,800 lm
910505102055	ST210T 39S/840 PSU MB BK	4000 K	≥80	109 lm/W	4,100 lm
910505102056	ST210T 39S/840 PSU WB BK	4000 K	≥80	109 lm/W	4,100 lm
910505102041	ST210T 27S/830 PSU MB WH	3000 K	≥80	122 lm/W	2,700 lm
910505102042	ST210T 27S/830 PSU WB WH	3000 K	≥80	122 lm/W	2,700 lm
910505102045	ST210T 39S/830 PSU MB WH	3000 K	≥80	113 lm/W	3,900 lm
910505102046	ST210T 39S/830 PSU WB WH	3000 K	≥80	113 lm/W	3,900 lm
910505102049	ST210T 27S/840 PSU MB WH	4000 K	≥80	127 lm/W	2,800 lm
910505102050	ST210T 27S/840 PSU WB WH	4000 K	≥80	127 lm/W	2,800 lm
910505102053	ST210T 39S/840 PSU MB WH	4000 K	≥80	109 lm/W	4,100 lm
910505102054	ST210T 39S/840 PSU WB WH	4000 K	≥80	109 lm/W	4,100 lm

Order Code	Full Product Name	Optic type
910505102063	ST210Y 27S/PW930 PSU MB WH	Medium beam
910505102064	ST210Y 27S/PW930 DIA MB WH	Medium beam
910505102065	ST210Y 39S/830 PSU MB WH	Medium-beam reflector high reflectance
910505102066	ST210Y 39S/830 DIA MB WH	Medium-beam reflector high reflectance
910505102067	ST210Y 39S/840 PSU MB WH	Medium-beam reflector high reflectance
910505102068	ST210Y 39S/840 DIA MB WH	Medium-beam reflector high reflectance
910505102069	ST210Y 39S/PW930 PSU MB WH	Medium beam
910505102070	ST210Y 39S/PW930 DIA MB WH	Medium beam

Order Code	Full Product Name	Optic type
910505102043	ST210T 27S/830 PSU MB BK	Medium-beam reflector high reflectance
910505102044	ST210T 27S/830 PSU WB BK	Wide beam
910505102047	ST210T 39S/830 PSU MB BK	Medium-beam reflector high reflectance
910505102048	ST210T 39S/830 PSU WB BK	Wide beam
910505102051	ST210T 27S/840 PSU MB BK	Medium-beam reflector high reflectance
910505102052	ST210T 27S/840 PSU WB BK	Wide beam
910505102055	ST210T 39S/840 PSU MB BK	Medium-beam reflector high reflectance
910505102056	ST210T 39S/840 PSU WB BK	Wide beam

Order Code	Full Product Name	Optic type
910505102041	ST210T 27S/830 PSU MB WH	Medium-beam reflector high reflectance
910505102042	ST210T 27S/830 PSU WB WH	Wide beam
910505102045	ST210T 39S/830 PSU MB WH	Medium-beam reflector high reflectance
910505102046	ST210T 39S/830 PSU WB WH	Wide beam
910505102049	ST210T 27S/840 PSU MB WH	Medium-beam reflector high reflectance
910505102050	ST210T 27S/840 PSU WB WH	Wide beam
910505102053	ST210T 39S/840 PSU MB WH	Medium-beam reflector high reflectance
910505102054	ST210T 39S/840 PSU WB WH	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505102057	ST210Y 19S/FMT PSU MB WH	50 W
910505102058	ST210Y 19S/FMT DIA MB WH	50 W
910505102059	ST210Y 27S/830 PSU MB WH	48.5 W
910505102060	ST210Y 27S/830 DIA MB WH	50 W
910505102061	ST210Y 27S/840 PSU MB WH	49 W
910505102062	ST210Y 27S/840 DIA MB WH	48 W
910505102063	ST210Y 27S/PW930 PSU MB WH	49 W
910505102064	ST210Y 27S/PW930 DIA MB WH	48 W
910505102065	ST210Y 39S/830 PSU MB WH	69 W
910505102066	ST210Y 39S/830 DIA MB WH	69 W
910505102067	ST210Y 39S/840 PSU MB WH	75 W
910505102068	ST210Y 39S/840 DIA MB WH	75 W
910505102069	ST210Y 39S/PW930 PSU MB WH	75 W
910505102070	ST210Y 39S/PW930 DIA MB WH	75 W
910505102043	ST210T 27S/830 PSU MB BK	22 W

Order Code	Full Product Name	Power Consumption
910505102044	ST210T 27S/830 PSU WB BK	22 W
910505102047	ST210T 39S/830 PSU MB BK	34.5 W
910505102048	ST210T 39S/830 PSU WB BK	34.5 W
910505102051	ST210T 27S/840 PSU MB BK	22 W
910505102052	ST210T 27S/840 PSU WB BK	22 W
910505102055	ST210T 39S/840 PSU MB BK	37.5 W
910505102056	ST210T 39S/840 PSU WB BK	37.5 W
910505102041	ST210T 27S/830 PSU MB WH	22 W
910505102042	ST210T 27S/830 PSU WB WH	22 W
910505102045	ST210T 39S/830 PSU MB WH	34.5 W
910505102046	ST210T 39S/830 PSU WB WH	34.5 W
910505102049	ST210T 27S/840 PSU MB WH	22 W
910505102050	ST210T 27S/840 PSU WB WH	22 W
910505102053	ST210T 39S/840 PSU MB WH	37.5 W
910505102054	ST210T 39S/840 PSU WB WH	37.5 W

Temperature

Order Code	Full Product Name	Ambient temperature range
910505102057	ST210Y 19S/FMT PSU MB WH	-10 to +35 °C
910505102058	ST210Y 19S/FMT DIA MB WH	-10 to +35 °C
910505102059	ST210Y 27S/830 PSU MB WH	-10 to +35 °C
910505102060	ST210Y 27S/830 DIA MB WH	-10 to +35 °C
910505102061	ST210Y 27S/840 PSU MB WH	-10 to +35 °C
910505102062	ST210Y 27S/840 DIA MB WH	-10 to +35 °C
910505102063	ST210Y 27S/PW930 PSU MB WH	+10 to +35 °C
910505102064	ST210Y 27S/PW930 DIA MB WH	+10 to +35 °C
910505102065	ST210Y 39S/830 PSU MB WH	-10 to +35 °C
910505102066	ST210Y 39S/830 DIA MB WH	-10 to +35 °C
910505102067	ST210Y 39S/840 PSU MB WH	-10 to +35 °C
910505102068	ST210Y 39S/840 DIA MB WH	-10 to +35 °C
910505102069	ST210Y 39S/PW930 PSU MB WH	+10 to +35 °C
910505102070	ST210Y 39S/PW930 DIA MB WH	+10 to +35 °C
910505102043	ST210T 27S/830 PSU MB BK	-10 to +35 °C

Order Code	Full Product Name	Ambient temperature range
910505102044	ST210T 27S/830 PSU WB BK	-10 to +35 °C
910505102047	ST210T 39S/830 PSU MB BK	-10 to +35 °C
910505102048	ST210T 39S/830 PSU WB BK	-10 to +35 °C
910505102051	ST210T 27S/840 PSU MB BK	-10 to +35 °C
910505102052	ST210T 27S/840 PSU WB BK	-10 to +35 °C
910505102055	ST210T 39S/840 PSU MB BK	-10 to +35 °C
910505102056	ST210T 39S/840 PSU WB BK	-10 to +35 °C
910505102041	ST210T 27S/830 PSU MB WH	-10 to +35 °C
910505102042	ST210T 27S/830 PSU WB WH	-10 to +35 °C
910505102045	ST210T 39S/830 PSU MB WH	-10 to +35 °C
910505102046	ST210T 39S/830 PSU WB WH	-10 to +35 °C
910505102049	ST210T 27S/840 PSU MB WH	-10 to +35 °C
910505102050	ST210T 27S/840 PSU WB WH	-10 to +35 °C
910505102053	ST210T 39S/840 PSU MB WH	-10 to +35 °C
910505102054	ST210T 39S/840 PSU WB WH	-10 to +35 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
910505102057	ST210Y 19S/FMT PSU MB WH	No
910505102058	ST210Y 19S/FMT DIA MB WH	Wireless Dim
910505102059	ST210Y 27S/830 PSU MB WH	No
910505102060	ST210Y 27S/830 DIA MB WH	Wireless Dim
910505102061	ST210Y 27S/840 PSU MB WH	No
910505102062	ST210Y 27S/840 DIA MB WH	Wireless Dim
910505102063	ST210Y 27S/PW930 PSU MB WH	No
910505102064	ST210Y 27S/PW930 DIA MB WH	Yes
910505102065	ST210Y 39S/830 PSU MB WH	No
910505102066	ST210Y 39S/830 DIA MB WH	Wireless Dim
910505102067	ST210Y 39S/840 PSU MB WH	No
910505102068	ST210Y 39S/840 DIA MB WH	Wireless Dim
910505102069	ST210Y 39S/PW930 PSU MB WH	No
910505102070	ST210Y 39S/PW930 DIA MB WH	Yes
910505102043	ST210T 27S/830 PSU MB BK	No

Order Code	Full Product Name	Dimmable
910505102044	ST210T 27S/830 PSU WB BK	No
910505102047	ST210T 39S/830 PSU MB BK	No
910505102048	ST210T 39S/830 PSU WB BK	No
910505102051	ST210T 27S/840 PSU MB BK	No
910505102052	ST210T 27S/840 PSU WB BK	No
910505102055	ST210T 39S/840 PSU MB BK	No
910505102056	ST210T 39S/840 PSU WB BK	No
910505102041	ST210T 27S/830 PSU MB WH	No
910505102042	ST210T 27S/830 PSU WB WH	No
910505102045	ST210T 39S/830 PSU MB WH	No
910505102046	ST210T 39S/830 PSU WB WH	No
910505102049	ST210T 27S/840 PSU MB WH	No
910505102050	ST210T 27S/840 PSU WB WH	No
910505102053	ST210T 39S/840 PSU MB WH	No
910505102054	ST210T 39S/840 PSU WB WH	No

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505102057	ST210Y 19S/FMT PSU MB WH	White
910505102058	ST210Y 19S/FMT DIA MB WH	White
910505102059	ST210Y 27S/830 PSU MB WH	White
910505102060	ST210Y 27S/830 DIA MB WH	White
910505102061	ST210Y 27S/840 PSU MB WH	White
910505102062	ST210Y 27S/840 DIA MB WH	White
910505102063	ST210Y 27S/PW930 PSU MB WH	White
910505102064	ST210Y 27S/PW930 DIA MB WH	White
910505102065	ST210Y 39S/830 PSU MB WH	White
910505102066	ST210Y 39S/830 DIA MB WH	White
910505102067	ST210Y 39S/840 PSU MB WH	White
910505102068	ST210Y 39S/840 DIA MB WH	White
910505102069	ST210Y 39S/PW930 PSU MB WH	White
910505102070	ST210Y 39S/PW930 DIA MB WH	White
910505102043	ST210T 27S/830 PSU MB BK	Black

Order Code	Full Product Name	Housing Color
910505102044	ST210T 27S/830 PSU WB BK	Black
910505102047	ST210T 39S/830 PSU MB BK	Black
910505102048	ST210T 39S/830 PSU WB BK	Black
910505102051	ST210T 27S/840 PSU MB BK	Black
910505102052	ST210T 27S/840 PSU WB BK	Black
910505102055	ST210T 39S/840 PSU MB BK	Black
910505102056	ST210T 39S/840 PSU WB BK	Black
910505102041	ST210T 27S/830 PSU MB WH	White
910505102042	ST210T 27S/830 PSU WB WH	White
910505102045	ST210T 39S/830 PSU MB WH	White
910505102046	ST210T 39S/830 PSU WB WH	White
910505102049	ST210T 27S/840 PSU MB WH	White
910505102050	ST210T 27S/840 PSU WB WH	White
910505102053	ST210T 39S/840 PSU MB WH	White
910505102054	ST210T 39S/840 PSU WB WH	White

Approval and Application

Order Code	Full Product Name	Protection class IEC
910505102057	ST210Y 19S/FMT PSU MB WH	Safety class II
910505102058	ST210Y 19S/FMT DIA MB WH	Safety class II
910505102059	ST210Y 27S/830 PSU MB WH	Safety class II
910505102060	ST210Y 27S/830 DIA MB WH	Safety class II
910505102061	ST210Y 27S/840 PSU MB WH	Safety class II
910505102062	ST210Y 27S/840 DIA MB WH	Safety class II
910505102063	ST210Y 27S/PW930 PSU MB WH	Safety class II
910505102064	ST210Y 27S/PW930 DIA MB WH	Safety class II
910505102065	ST210Y 39S/830 PSU MB WH	Safety class II
910505102066	ST210Y 39S/830 DIA MB WH	Safety class II
910505102067	ST210Y 39S/840 PSU MB WH	Safety class II
910505102068	ST210Y 39S/840 DIA MB WH	Safety class II
910505102069	ST210Y 39S/PW930 PSU MB WH	Safety class II

Order Code	Full Product Name	Protection class IEC
910505102070	ST210Y 39S/PW930 DIA MB WH	Safety class II
910505102043	ST210T 27S/830 PSU MB BK	Safety class I
910505102044	ST210T 27S/830 PSU WB BK	Safety class I
910505102047	ST210T 39S/830 PSU MB BK	Safety class I
910505102048	ST210T 39S/830 PSU WB BK	Safety class I
910505102051	ST210T 27S/840 PSU MB BK	Safety class I
910505102052	ST210T 27S/840 PSU WB BK	Safety class I
910505102055	ST210T 39S/840 PSU MB BK	Safety class I
910505102056	ST210T 39S/840 PSU WB BK	Safety class I
910505102041	ST210T 27S/830 PSU MB WH	Safety class I
910505102042	ST210T 27S/830 PSU WB WH	Safety class I
910505102045	ST210T 39S/830 PSU MB WH	Safety class I
910505102046	ST210T 39S/830 PSU WB WH	Safety class I

Order Code	Full Product Name	Protection class IEC
910505102049	ST210T 27S/840 PSU MB WH	Safety class I
910505102050	ST210T 27S/840 PSU WB WH	Safety class I

Order Code	Full Product Name	Protection class IEC
910505102053	ST210T 39S/840 PSU MB WH	Safety class I
910505102054	ST210T 39S/840 PSU WB WH	Safety class I

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505102057	ST210Y 19S/FMT PSU MB WH	(0.406, 0.350) SDCM <3
910505102058	ST210Y 19S/FMT DIA MB WH	(0.406, 0.350) SDCM <3
910505102059	ST210Y 27S/830 PSU MB WH	(0.4338, 0.4030) SDCM <3
910505102060	ST210Y 27S/830 DIA MB WH	(0.4338, 0.4030) SDCM <3
910505102061	ST210Y 27S/840 PSU MB WH	(0.3818, 0.3797) SDCM <3
910505102062	ST210Y 27S/840 DIA MB WH	(0.3818, 0.3797) SDCM <3
910505102063	ST210Y 27S/PW930 PSU MB WH	(0.422, 0.386) SDCM <2
910505102064	ST210Y 27S/PW930 DIA MB WH	(0.422, 0.386) SDCM <2
910505102065	ST210Y 39S/830 PSU MB WH	(0.4338, 0.4030) SDCM <3
910505102066	ST210Y 39S/830 DIA MB WH	(0.4338, 0.4030) SDCM <3
910505102067	ST210Y 39S/840 PSU MB WH	(0.3818, 0.3797) SDCM <3
910505102068	ST210Y 39S/840 DIA MB WH	(0.3818, 0.3797) SDCM <3
910505102069	ST210Y 39S/PW930 PSU MB WH	(0.422, 0.386) SDCM <2
910505102070	ST210Y 39S/PW930 DIA MB WH	(0.422, 0.386) SDCM <2
910505102043	ST210T 27S/830 PSU MB BK	(0.4338, 0.4030) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910505102044	ST210T 27S/830 PSU WB BK	(0.4338, 0.4030) SDCM <3
910505102047	ST210T 39S/830 PSU MB BK	(0.4338, 0.4030) SDCM <3
910505102048	ST210T 39S/830 PSU WB BK	(0.4338, 0.4030) SDCM <3
910505102051	ST210T 27S/840 PSU MB BK	(0.3818, 0.3797) SDCM <3
910505102052	ST210T 27S/840 PSU WB BK	(0.3818, 0.3797) SDCM <3
910505102055	ST210T 39S/840 PSU MB BK	(0.3818, 0.3797) SDCM <3
910505102056	ST210T 39S/840 PSU WB BK	(0.3818, 0.3797) SDCM <3
910505102041	ST210T 27S/830 PSU MB WH	(0.4338, 0.4030) SDCM <3
910505102042	ST210T 27S/830 PSU WB WH	(0.4338, 0.4030) SDCM <3
910505102045	ST210T 39S/830 PSU MB WH	(0.4338, 0.4030) SDCM <3
910505102046	ST210T 39S/830 PSU WB WH	(0.4338, 0.4030) SDCM <3
910505102049	ST210T 27S/840 PSU MB WH	(0.3818, 0.3797) SDCM <3
910505102050	ST210T 27S/840 PSU WB WH	(0.3818, 0.3797) SDCM <3
910505102053	ST210T 39S/840 PSU MB WH	(0.3818, 0.3797) SDCM <3
910505102054	ST210T 39S/840 PSU WB WH	(0.3818, 0.3797) SDCM <3

Application Conditions

Order Code	Full Product Name	Maximum dim level
910505102057	ST210Y 19S/FMT PSU MB WH	Not applicable
910505102058	ST210Y 19S/FMT DIA MB WH	1%
910505102059	ST210Y 27S/830 PSU MB WH	Not applicable
910505102060	ST210Y 27S/830 DIA MB WH	1%
910505102061	ST210Y 27S/840 PSU MB WH	Not applicable
910505102062	ST210Y 27S/840 DIA MB WH	1%
910505102063	ST210Y 27S/PW930 PSU MB WH	Not applicable
910505102064	ST210Y 27S/PW930 DIA MB WH	1%
910505102065	ST210Y 39S/830 PSU MB WH	Not applicable
910505102066	ST210Y 39S/830 DIA MB WH	1%
910505102067	ST210Y 39S/840 PSU MB WH	Not applicable
910505102068	ST210Y 39S/840 DIA MB WH	1%
910505102069	ST210Y 39S/PW930 PSU MB WH	Not applicable
910505102070	ST210Y 39S/PW930 DIA MB WH	1%
910505102043	ST210T 27S/830 PSU MB BK	Not applicable

Order Code	Full Product Name	Maximum dim level
910505102044	ST210T 27S/830 PSU WB BK	Not applicable
910505102047	ST210T 39S/830 PSU MB BK	Not applicable
910505102048	ST210T 39S/830 PSU WB BK	Not applicable
910505102051	ST210T 27S/840 PSU MB BK	Not applicable
910505102052	ST210T 27S/840 PSU WB BK	Not applicable
910505102055	ST210T 39S/840 PSU MB BK	Not applicable
910505102056	ST210T 39S/840 PSU WB BK	Not applicable
910505102041	ST210T 27S/830 PSU MB WH	Not applicable
910505102042	ST210T 27S/830 PSU WB WH	Not applicable
910505102045	ST210T 39S/830 PSU MB WH	Not applicable
910505102046	ST210T 39S/830 PSU WB WH	Not applicable
910505102049	ST210T 27S/840 PSU MB WH	Not applicable
910505102050	ST210T 27S/840 PSU WB WH	Not applicable
910505102053	ST210T 39S/840 PSU MB WH	Not applicable
910505102054	ST210T 39S/840 PSU WB WH	Not applicable

