



CoreLine Trunking gen2 – Innovative LED light lines have never been so simple

CoreLine Trunking gen2

CoreLine Trunking gen2 is a light-line system that is designed for simplicity. It comes in a choice of lengths, flux packages and beam shapes to suit every project and application. Easy to use and integrate with spots and sensors, CoreLine Trunking gen2 provides consistent, high-quality lighting with added protection against accidental water ingress. The innovative system is also easy to assemble and install for faster retrofits and refurbishments.

Benefits

- Optimized, efficient design and light effect
- Consistent, high-quality light - no Color over Angle or striping artefacts
- Improved light continuity
- Easy to order, assemble and install
- InterAct ready for enhanced use in Retail and Industry applications

Features




- Intuitive, single layer architecture – only 2 12NCs needed to create a line
- Choice of 3 lengths, each with 3 flux packages
- 8 different optics with consistent light quality
- Dedicated sensor units to upgrade to InterAct system propositions
- Lumen maintenance @ 50,000 hours - L80
- Available as trunking and standalone versions

CoreLine Trunking gen2

Application

- Food and Large Retailers
- Warehouses
- Manufacturing

Dimensional drawing



Product details



CoreLine Trunking Gen2 Half Blind

CoreLine Trunking gen2

General Information

CE mark	Yes
Driver included	Yes
ENEC mark	ENEC plus mark
Flammability mark	-
Glow-wire test	Temperature 850 °C, duration 30 s
Light source replaceable	No
Service tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz

Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

Mechanical and Housing

Housing Color	White RAL9016
---------------	---------------

Approval and Application

Protection class IEC	Safety class I
Mech. impact protection code	IK02
Ingress protection code	IP20

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Lamp family code	Embedded control	Number of gear units	Product family code
10753300	LL212X 53S/840 1x PSU WB 5x1.5 HE	-	-	1 unit	LL212X
10772400	LL212X 53S/840 1x PSD WB 7x1.5	-	-	1 unit	LL212X
10779300	LL212X 53S/840 1x PSD WB 7x1.5 HE	-	-	1 unit	LL212X
10780900	LL212X 53S/840 1x PSD WB 7x2.5 HE	-	-	1 unit	LL212X
10781600	LL212X 53S/840 1x PSU WB 5x2.5 HE	-	-	1 unit	LL212X
10763200	LL217X 120S/840 1x PSU WB 5x2.5 HE	-	-	1 unit	LL217X
10766300	LL217X 80S/840 1x PSD WB 7x2.5 VLC	-	-	1 unit	LL217X
10775500	LL217X 80S/840 1x PSD WB 7x1.5	-	-	1 unit	LL217X
10783000	LL217X 120S/840 1x PSD WB 7x1.5 HE	120S	-	1 unit	LL217X
10784700	LL217X 120S/840 1x PSD WB 7x2.5 HE	120S	-	1 unit	LL217X
10785400	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	120S	Visible light communication	1 unit	LL217X
10786100	LL217X 120S/840 1x PSU WB 5x1.5 HE	120S	-	1 unit	LL217X
10788500	LL217X 80S/840 1x PSD WB 7x2.5 HE	80S	-	1 unit	LL217X
10789200	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	80S	Visible light communication	1 unit	LL217X
10790800	LL217X 80S/840 1x PSU WB 5x2.5 HE	80S	-	1 unit	LL217X
10791500	LL217X 80S/840 1x PSU WB 5x1.5 HE	80S	-	1 unit	LL217X
10793900	LL217X 80S/840 1x PSD WB 7x2.5	80S	-	1 unit	LL217X
10794600	LL217X 80S/840 1x PSU WB 5x1.5	80S	-	1 unit	LL217X
10795300	LL217X 80S/840 1x PSU WB 5x2.5	80S	-	1 unit	LL217X
10797700	LL234X 160S/840 2x PSD WB 7x1.5 HE	160S	-	2 units	LL234X
10798400	LL234X 160S/840 2x PSD WB 7x2.5 HE	160S	-	2 units	LL234X
10799100	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	160S	Visible light communication	2 units	LL234X
10800400	LL234X 160S/840 2x PSU WB 5x1.5 HE	160S	-	2 units	LL234X
10801100	LL234X 160S/840 2x PSU WB 5x2.5 HE	160S	-	2 units	LL234X
10802800	LL234X 240S/840 2x PSD WB 7x1.5 HE	240S	-	2 units	LL234X
10803500	LL234X 240S/840 2x PSD WB 7x2.5 HE	240S	-	2 units	LL234X
10804200	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	240S	Visible light communication	2 units	LL234X

CoreLine Trunking gen2

Order Code	Full Product Name	Lamp family code	Embedded control	Number of gear units	Product family code
10805900	LL234X 240S/840 2x PSU WB 5x1.5 HE	240S	-	2 units	LL234X
10806600	LL234X 240S/840 2x PSU WB 5x2.5 HE	240S	-	2 units	LL234X
10809700	LL234X 160S/840 2x PSD O 7x2.5	160S	-	2 units	LL234X
10810300	LL234X 160S/840 2x PSD WB 7x1.5	160S	-	2 units	LL234X
10811000	LL234X 160S/840 2x PSD WB 7x2.5	160S	-	2 units	LL234X
10812700	LL234X 160S/840 2x PSD WB 7x2.5 VLC	160S	Visible light communication	2 units	LL234X
10815800	LL234X 160S/840 2x PSU WB 5x1.5	160S	-	2 units	LL234X
10816500	LL234X 160S/840 2x PSU WB 5x2.5	160S	-	2 units	LL234X
10817200	LL217X 80S/840 1x PSD WB 7x1.5 HE	80S	-	1 unit	LL217X
10818900	LL234X 90S/840 2x PSD WB 7x1.5	90S	-	2 units	LL234X
19921700	LL234X 160S/840 1x PSD WB 7x1.5	-	-	1 unit	LL234X
19933000	LL234X 160S/840 2x PSU NB 5x1.5	-	-	2 units	LL234X
19934700	LL217X 80S/840 1x PSU NB 5x1.5	-	-	1 unit	LL217X
61792600	LL234X 90S/840 2x PSU WB 5x1.5	-	-	2 units	LL234X
61793300	LL234X 90S/840 1x PSD WB 7x1.5	-	-	1 unit	LL234X
61794000	LL217X 45S/840 1x PSU WB 5x1.5	-	-	1 unit	LL217X
61795700	LL217X 45S/840 1x PSD WB 7x1.5	-	-	1 unit	LL217X
63367400	LL234X 45S/840 1x PSU HB WB 5x1.5	-	-	1 unit	LL234X
63368100	LL234X 45S/840 1x PSD HB WB 7x1.5	-	-	1 unit	LL234X
63369800	LL234X 80S/840 1x PSU HB WB 5x1.5	-	-	1 unit	LL234X
63370400	LL234X 80S/840 1x PSD HB WB 7x1.5	-	-	1 unit	LL234X
63371100	LL234X 45S/840 1x PSU HB NB 5x1.5	-	-	1 unit	LL234X
63372800	LL234X 45S/840 1x PSD HB NB 7x1.5	-	-	1 unit	LL234X
63373500	LL234X 80S/840 1x PSU HB NB 5x1.5	-	-	1 unit	LL234X
63374200	LL234X 80S/840 1x PSD HB NB 7x1.5	-	-	1 unit	LL234X
63376600	LL234X 90S/840 1x PSD NB 7x1.5	-	-	1 unit	LL234X
63378000	LL234X 160S/840 1x PSD NB 7x1.5	-	-	1 unit	LL234X
63382700	LL217X 80S/840 1x PSD NB 7x1.5	-	-	1 unit	LL217X
63813600	LL212X 30S/840 1x PSU MB 5x2.5	-	-	1 unit	LL212X
63814300	LL212X 30S/840 1x PSU NB 5x2.5	-	-	1 unit	LL212X
63815000	LL212X 53S/840 1x PSU MB 5x2.5	-	-	1 unit	LL212X
63816700	LL212X 53S/840 1x PSU NB 5x2.5	-	-	1 unit	LL212X
63817400	LL212X 80S/840 1x PSU MB 5x2.5 HE	-	-	1 unit	LL212X
63818100	LL212X 80S/840 1x PSU NB 5x2.5 HE	-	-	1 unit	LL212X
63819800	LL217X 45S/840 1x PSU MB 5x2.5	-	-	1 unit	LL217X
63820400	LL217X 45S/840 1x PSU NB 5x2.5	-	-	1 unit	LL217X

CoreLine Trunking gen2

Order Code	Full Product Name	Lamp family code	Embedded control	Number of gear units	Product family code
63821100	LL217X 80S/840 1x PSU MB 5x2.5	-	-	1 unit	LL217X
63822800	LL217X 80S/840 1x PSU NB 5x2.5	-	-	1 unit	LL217X
63823500	LL217X 120S/840 1x PSU MB 5x2.5 HE	-	-	1 unit	LL217X
63824200	LL217X 120S/840 1x PSU NB 5x2.5 HE	-	-	1 unit	LL217X
63825900	LL234X 90S/840 2x PSU MB 5x2.5	-	-	2 units	LL234X
63826600	LL234X 90S/840 2x PSU NB 5x2.5	-	-	2 units	LL234X
63827300	LL234X 160S/840 2x PSU MB 5x2.5	-	-	2 units	LL234X
63828000	LL234X 160S/840 2x PSU NB 5x2.5	-	-	2 units	LL234X
63829700	LL234X 240S/840 2x PSU MB 5x2.5 HE	-	-	2 units	LL234X
63830300	LL234X 240S/840 2x PSU NB 5x2.5 HE	-	-	2 units	LL234X
10756400	LL217X 80S/840 1x PSD BV WB	-	-	1 unit	LL217X
10782300	LL217X 120S/840 1x PSU BV WB HE	120S	-	1 unit	LL217X
10796000	LL234X 240S/840 2x PSD BV WB HE	240S	-	2 units	LL234X
10807300	LL234X 160S/840 2x PSU BV WB	160S	-	2 units	LL234X
10954400	LL217X 80S/840 1X PSU BV WB TW3	-	-	1 unit	LL217X
10955100	LL234X 160S/840 1X PSU BV WB TW3	-	-	1 unit	LL234X
10956800	LL234X 160S/840 2X PSU BV WB TW3	-	-	2 units	LL234X
61796400	LL217X 45S/840 1x PSU BV WB	-	-	1 unit	LL217X
61797100	LL217X 45S/840 1x PSD BV WB	-	-	1 unit	LL217X
61798800	LL217X 45S/840 1x PSU BV O	-	-	1 unit	LL217X
61799500	LL217X 45S/840 1x PSD BV O	-	-	1 unit	LL217X
61800800	LL217X 80S/840 1x PSU BV WB	-	-	1 unit	LL217X
61801500	LL217X 80S/840 1x PSU BV O	-	-	1 unit	LL217X
61802200	LL217X 80S/840 1x PSD BV O	-	-	1 unit	LL217X
62455900	LL217X 120S/840 1x PSU BV WB TW3	-	-	1 unit	LL217X
62456600	LL217X 120S/840 1x PSU BV MB TW3	-	-	1 unit	LL217X
62457300	LL217X 120S/840 1x PSU BV NB TW3	-	-	1 unit	LL217X
62458000	LL217X 80S/840 1x PSU BV MB TW3	-	-	1 unit	LL217X
62459700	LL217X 80S/840 1x PSU BV NB TW3	-	-	1 unit	LL217X
10787800	LL217X 80S/840 1x PSD O 7x2.5 HE	80S	-	1 unit	LL217X
10792200	LL217X 80S/840 1x PSD O 7x2.5	80S	-	1 unit	LL217X
10808000	LL234X 160S/840 2x PSD O 7x1.5	160S	-	2 units	LL234X
10813400	LL234X 160S/840 2x PSU O 5x1.5	160S	-	2 units	LL234X
10814100	LL234X 160S/840 2x PSU O 5x2.5	160S	-	2 units	LL234X

Light Technical

CoreLine Trunking gen2

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
10753300	LL212X 53S/840 1x PSU WB 5x1.5 HE	161 lm/W	5,300 lm	Wide beam
10772400	LL212X 53S/840 1x PSD WB 7x1.5	156 lm/W	5,300 lm	Wide beam
10779300	LL212X 53S/840 1x PSD WB 7x1.5 HE	161 lm/W	5,300 lm	Wide beam
10780900	LL212X 53S/840 1x PSD WB 7x2.5 HE	161 lm/W	5,300 lm	Wide beam
10781600	LL212X 53S/840 1x PSU WB 5x2.5 HE	161 lm/W	5,300 lm	Wide beam
10763200	LL217X 120S/840 1x PSU WB 5x2.5 HE	150 lm/W	12,000 lm	Wide beam
10766300	LL217X 80S/840 1x PSD WB 7x2.5 VLC	160 lm/W	8,000 lm	Wide beam
10775500	LL217X 80S/840 1x PSD WB 7x1.5	160 lm/W	8,000 lm	Wide beam
10783000	LL217X 120S/840 1x PSD WB 7x1.5 HE	152 lm/W	12,000 lm	Wide beam
10784700	LL217X 120S/840 1x PSD WB 7x2.5 HE	152 lm/W	12,000 lm	Wide beam
10785400	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	152 lm/W	12,000 lm	Wide beam
10786100	LL217X 120S/840 1x PSU WB 5x1.5 HE	150 lm/W	12,000 lm	Wide beam
10788500	LL217X 80S/840 1x PSD WB 7x2.5 HE	165 lm/W	8,000 lm	Wide beam
10789200	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	165 lm/W	8,000 lm	Wide beam
10790800	LL217X 80S/840 1x PSU WB 5x2.5 HE	163 lm/W	8,000 lm	Wide beam
10791500	LL217X 80S/840 1x PSU WB 5x1.5 HE	163 lm/W	8,000 lm	Wide beam
10793900	LL217X 80S/840 1x PSD WB 7x2.5	160 lm/W	8,000 lm	Wide beam
10794600	LL217X 80S/840 1x PSU WB 5x1.5	157 lm/W	8,000 lm	Wide beam
10795300	LL217X 80S/840 1x PSU WB 5x2.5	157 lm/W	8,000 lm	Wide beam
10797700	LL234X 160S/840 2x PSD WB 7x1.5 HE	165 lm/W	16,000 lm	Wide beam
10798400	LL234X 160S/840 2x PSD WB 7x2.5 HE	165 lm/W	16,000 lm	Wide beam
10799100	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	165 lm/W	16,000 lm	Wide beam
10800400	LL234X 160S/840 2x PSU WB 5x1.5 HE	165 lm/W	16,000 lm	Wide beam
10801100	LL234X 160S/840 2x PSU WB 5x2.5 HE	165 lm/W	16,000 lm	Wide beam
10802800	LL234X 240S/840 2x PSD WB 7x1.5 HE	152 lm/W	24,000 lm	Wide beam

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
10803500	LL234X 240S/840 2x PSD WB 7x2.5 HE	152 lm/W	24,000 lm	Wide beam
10804200	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	152 lm/W	24,000 lm	Wide beam
10805900	LL234X 240S/840 2x PSU WB 5x1.5 HE	150 lm/W	24,000 lm	Wide beam
10806600	LL234X 240S/840 2x PSU WB 5x2.5 HE	150 lm/W	24,000 lm	Wide beam
10809700	LL234X 160S/840 2x PSD O 7x2.5	150 lm/W	15,000 lm	Symmetrical
10810300	LL234X 160S/840 2x PSD WB 7x1.5	160 lm/W	16,000 lm	Wide beam
10811000	LL234X 160S/840 2x PSD WB 7x2.5	160 lm/W	16,000 lm	Wide beam
10812700	LL234X 160S/840 2x PSD WB 7x2.5 VLC	160 lm/W	16,000 lm	Wide beam
10815800	LL234X 160S/840 2x PSU WB 5x1.5	157 lm/W	16,000 lm	Wide beam
10816500	LL234X 160S/840 2x PSU WB 5x2.5	157 lm/W	16,000 lm	Wide beam
10817200	LL217X 80S/840 1x PSD WB 7x1.5 HE	165 lm/W	8,000 lm	Wide beam
10818900	LL234X 90S/840 2x PSD WB 7x1.5	161 lm/W	9,000 lm	Wide beam
19921700	LL234X 160S/840 1x PSD WB 7x1.5	160 lm/W	16,000 lm	Wide beam
19933000	LL234X 160S/840 2x PSU NB 5x1.5	157 lm/W	16,000 lm	Narrow beam
19934700	LL217X 80S/840 1x PSU NB 5x1.5	157 lm/W	8,000 lm	Narrow beam
61792600	LL234X 90S/840 2x PSU WB 5x1.5	161 lm/W	9,000 lm	Wide beam
61793300	LL234X 90S/840 1x PSD WB 7x1.5	158 lm/W	9,000 lm	Wide beam
61794000	LL217X 45S/840 1x PSU WB 5x1.5	161 lm/W	4,500 lm	Wide beam
61795700	LL217X 45S/840 1x PSD WB 7x1.5	164 lm/W	4,500 lm	Wide beam
63367400	LL234X 45S/840 1x PSU HB WB 5x1.5	161 lm/W	4,500 lm	Wide beam
63368100	LL234X 45S/840 1x PSD HB WB 7x1.5	150 lm/W	4,500 lm	Wide beam
63369800	LL234X 80S/840 1x PSU HB WB 5x1.5	157 lm/W	8,000 lm	Wide beam
63370400	LL234X 80S/840 1x PSD HB WB 7x1.5	160 lm/W	8,000 lm	Wide beam
63371100	LL234X 45S/840 1x PSU HB NB 5x1.5	161 lm/W	4,500 lm	Narrow beam
63372800	LL234X 45S/840 1x PSD HB NB 7x1.5	150 lm/W	4,500 lm	Narrow beam

CoreLine Trunking gen2

Order Code	Full Product Name	Luminous		
		Efficacy (rated) (Nom)	Luminous Flux	Optic type
63373500	LL234X 80S/840 1x PSU HB NB 5x1.5	157 lm/W	8,000 lm	Narrow beam
63374200	LL234X 80S/840 1x PSD HB NB 7x1.5	160 lm/W	8,000 lm	Narrow beam
63376600	LL234X 90S/840 1x PSD NB 7x1.5	158 lm/W	9,000 lm	Narrow beam
63378000	LL234X 160S/840 1x PSD NB 7x1.5	160 lm/W	16,000 lm	Narrow beam
63382700	LL217X 80S/840 1x PSD NB 7x1.5	160 lm/W	8,000 lm	Narrow beam
63813600	LL212X 30S/840 1x PSU MB 5x2.5	161 lm/W	3,000 lm	Medium beam
63814300	LL212X 30S/840 1x PSU NB 5x2.5	161 lm/W	3,000 lm	Narrow beam
63815000	LL212X 53S/840 1x PSU MB 5x2.5	160 lm/W	5,300 lm	Medium beam
63816700	LL212X 53S/840 1x PSU NB 5x2.5	160 lm/W	5,300 lm	Narrow beam
63817400	LL212X 80S/840 1x PSU MB 5x2.5 HE	163 lm/W	8,000 lm	Medium beam
63818100	LL212X 80S/840 1x PSU NB 5x2.5 HE	163 lm/W	8,000 lm	Narrow beam
63819800	LL217X 45S/840 1x PSU MB 5x2.5	161 lm/W	4,500 lm	Medium beam
63820400	LL217X 45S/840 1x PSU NB 5x2.5	161 lm/W	4,500 lm	Narrow beam
63821100	LL217X 80S/840 1x PSU MB 5x2.5	157 lm/W	8,000 lm	Medium beam
63822800	LL217X 80S/840 1x PSU NB 5x2.5	157 lm/W	8,000 lm	Narrow beam
63823500	LL217X 120S/840 1x PSU MB 5x2.5 HE	150 lm/W	12,000 lm	Medium beam
63824200	LL217X 120S/840 1x PSU NB 5x2.5 HE	150 lm/W	12,000 lm	Narrow beam
63825900	LL234X 90S/840 2x PSU MB 5x2.5	161 lm/W	9,000 lm	Medium beam
63826600	LL234X 90S/840 2x PSU NB 5x2.5	161 lm/W	9,000 lm	Narrow beam
63827300	LL234X 160S/840 2x PSU MB 5x2.5	157 lm/W	16,000 lm	Medium beam
63828000	LL234X 160S/840 2x PSU NB 5x2.5	157 lm/W	16,000 lm	Narrow beam
63829700	LL234X 240S/840 2x PSU MB 5x2.5 HE	150 lm/W	24,000 lm	Medium beam
63830300	LL234X 240S/840 2x PSU NB 5x2.5 HE	150 lm/W	24,000 lm	Narrow beam
10756400	LL217X 80S/840 1x PSD BV WB	160 lm/W	8,000 lm	Wide beam

Order Code	Full Product Name	Luminous		
		Efficacy (rated) (Nom)	Luminous Flux	Optic type
10782300	LL217X 120S/840 1x PSU BV WB HE	150 lm/W	12,000 lm	Wide beam
10796000	LL234X 240S/840 2x PSD BV WB HE	152 lm/W	24,000 lm	Wide beam
10807300	LL234X 160S/840 2x PSU BV WB	157 lm/W	16,000 lm	Wide beam
10954400	LL217X 80S/840 1X PSU BV WB TW3	157 lm/W	8,000 lm	Wide beam
10955100	LL234X 160S/840 1X PSU BV WB TW3	157 lm/W	16,000 lm	Wide beam
10956800	LL234X 160S/840 2X PSU BV WB TW3	157 lm/W	16,000 lm	Wide beam
61796400	LL217X 45S/840 1x PSU BV WB	161 lm/W	4,500 lm	Wide beam
61797100	LL217X 45S/840 1x PSD BV WB	164 lm/W	4,500 lm	Wide beam
61798800	LL217X 45S/840 1x PSU BV O	150 lm/W	4,200 lm	Symmetrical
61799500	LL217X 45S/840 1x PSD BV O	150 lm/W	4,200 lm	Symmetrical
61800800	LL217X 80S/840 1x PSU BV WB	157 lm/W	8,000 lm	Wide beam
61801500	LL217X 80S/840 1x PSU BV O	148 lm/W	7,400 lm	Symmetrical
61802200	LL217X 80S/840 1x PSD BV O	148 lm/W	7,400 lm	Symmetrical
62455900	LL217X 120S/840 1x PSU BV WB TW3	139 lm/W	12,000 lm	Wide beam
62456600	LL217X 120S/840 1x PSU BV MB TW3	139 lm/W	12,000 lm	Medium beam
62457300	LL217X 120S/840 1x PSU BV NB TW3	139 lm/W	12,000 lm	Narrow beam
62458000	LL217X 80S/840 1x PSU BV MB TW3	160 lm/W	8,000 lm	Medium beam
62459700	LL217X 80S/840 1x PSU BV NB TW3	160 lm/W	8,000 lm	Narrow beam
10787800	LL217X 80S/840 1x PSD O 7x2.5 HE	148 lm/W	7,400 lm	Symmetrical
10792200	LL217X 80S/840 1x PSD O 7x2.5	148 lm/W	7,400 lm	Symmetrical
10808000	LL234X 160S/840 2x PSD O 7x1.5	150 lm/W	15,000 lm	Symmetrical
10813400	LL234X 160S/840 2x PSU O 5x1.5	150 lm/W	15,000 lm	Symmetrical
10814100	LL234X 160S/840 2x PSU O 5x2.5	150 lm/W	15,000 lm	Symmetrical

Operating and Electrical

CoreLine Trunking gen2

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
10753300	LL212X 53S/840 1x PSU WB 5x1.5 HE	33 W	63372800	LL234X 45S/840 1x PSD HB NB 7x1.5	27.5 W
10772400	LL212X 53S/840 1x PSD WB 7x1.5	34 W	63373500	LL234X 80S/840 1x PSU HB NB 5x1.5	51 W
10779300	LL212X 53S/840 1x PSD WB 7x1.5 HE	33 W	63374200	LL234X 80S/840 1x PSD HB NB 7x1.5	50 W
10780900	LL212X 53S/840 1x PSD WB 7x2.5 HE	33 W	63376600	LL234X 90S/840 1x PSD NB 7x1.5	57 W
10781600	LL212X 53S/840 1x PSU WB 5x2.5 HE	33 W	63378000	LL234X 160S/840 1x PSD NB 7x1.5	98 W
10763200	LL217X 120S/840 1x PSU WB 5x2.5 HE	80 W	63382700	LL217X 80S/840 1x PSD NB 7x1.5	50 W
10766300	LL217X 80S/840 1x PSD WB 7x2.5 VLC	50 W	63813600	LL212X 30S/840 1x PSU MB 5x2.5	19 W
10775500	LL217X 80S/840 1x PSD WB 7x1.5	50 W	63814300	LL212X 30S/840 1x PSU NB 5x2.5	19 W
10783000	LL217X 120S/840 1x PSD WB 7x1.5 HE	79 W	63815000	LL212X 53S/840 1x PSU MB 5x2.5	33 W
10784700	LL217X 120S/840 1x PSD WB 7x2.5 HE	79 W	63816700	LL212X 53S/840 1x PSU NB 5x2.5	33 W
10785400	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	79 W	63817400	LL212X 80S/840 1x PSU MB 5x2.5 HE	49 W
10786100	LL217X 120S/840 1x PSU WB 5x1.5 HE	80 W	63818100	LL212X 80S/840 1x PSU NB 5x2.5 HE	49 W
10788500	LL217X 80S/840 1x PSD WB 7x2.5 HE	48.5 W	63819800	LL217X 45S/840 1x PSU MB 5x2.5	28 W
10789200	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	48 W	63820400	LL217X 45S/840 1x PSU NB 5x2.5	28 W
10790800	LL217X 80S/840 1x PSU WB 5x2.5 HE	49 W	63821100	LL217X 80S/840 1x PSU MB 5x2.5	50 W
10791500	LL217X 80S/840 1x PSU WB 5x1.5 HE	49 W	63822800	LL217X 80S/840 1x PSU NB 5x2.5	50 W
10793900	LL217X 80S/840 1x PSD WB 7x2.5	50 W	63823500	LL217X 120S/840 1x PSU MB 5x2.5 HE	79 W
10794600	LL217X 80S/840 1x PSU WB 5x1.5	51 W	63824200	LL217X 120S/840 1x PSU NB 5x2.5 HE	79 W
10795300	LL217X 80S/840 1x PSU WB 5x2.5	51 W	63825900	LL234X 90S/840 2x PSU MB 5x2.5	56 W
10797700	LL234X 160S/840 2x PSD WB 7x1.5 HE	97 W	63826600	LL234X 90S/840 2x PSU NB 5x2.5	56 W
10798400	LL234X 160S/840 2x PSD WB 7x2.5 HE	97 W	63827300	LL234X 160S/840 2x PSU MB 5x2.5	102 W
10799100	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	96 W	63828000	LL234X 160S/840 2x PSU NB 5x2.5	102 W
10800400	LL234X 160S/840 2x PSU WB 5x1.5 HE	98 W	63829700	LL234X 240S/840 2x PSU MB 5x2.5 HE	158 W
10801100	LL234X 160S/840 2x PSU WB 5x2.5 HE	98 W	63830300	LL234X 240S/840 2x PSU NB 5x2.5 HE	158 W
10802800	LL234X 240S/840 2x PSD WB 7x1.5 HE	158 W	10756400	LL217X 80S/840 1x PSD BV WB	50 W
10803500	LL234X 240S/840 2x PSD WB 7x2.5 HE	158 W	10782300	LL217X 120S/840 1x PSU BV WB HE	80 W
10804200	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	158 W	10796000	LL234X 240S/840 2x PSD BV WB HE	158 W
10805900	LL234X 240S/840 2x PSU WB 5x1.5 HE	160 W	10807300	LL234X 160S/840 2x PSU BV WB	102 W
10806600	LL234X 240S/840 2x PSU WB 5x2.5 HE	160 W	10954400	LL217X 80S/840 1X PSU BV WB TW3	51 W
10809700	LL234X 160S/840 2x PSD O 7x2.5	100 W	10955100	LL234X 160S/840 1X PSU BV WB TW3	102 W
10810300	LL234X 160S/840 2x PSD WB 7x1.5	100 W	10956800	LL234X 160S/840 2X PSU BV WB TW3	102 W
10811000	LL234X 160S/840 2x PSD WB 7x2.5	100 W	61796400	LL217X 45S/840 1x PSU BV WB	28 W
10812700	LL234X 160S/840 2x PSD WB 7x2.5 VLC	100 W	61797100	LL217X 45S/840 1x PSD BV WB	27.5 W
10815800	LL234X 160S/840 2x PSU WB 5x1.5	102 W	61798800	LL217X 45S/840 1x PSU BV O	28 W
10816500	LL234X 160S/840 2x PSU WB 5x2.5	102 W	61799500	LL217X 45S/840 1x PSD BV O	27.5 W
10817200	LL217X 80S/840 1x PSD WB 7x1.5 HE	48.5 W	61800800	LL217X 80S/840 1x PSU BV WB	51 W
10818900	LL234X 90S/840 2x PSD WB 7x1.5	55 W	61801500	LL217X 80S/840 1x PSU BV O	51 W
19921700	LL234X 160S/840 1x PSD WB 7x1.5	98 W	61802200	LL217X 80S/840 1x PSD BV O	50 W
19933000	LL234X 160S/840 2x PSU NB 5x1.5	102 W	62455900	LL217X 120S/840 1x PSU BV WB TW3	80 W
19934700	LL217X 80S/840 1x PSU NB 5x1.5	51 W	62456600	LL217X 120S/840 1x PSU BV MB TW3	80 W
61792600	LL234X 90S/840 2x PSU WB 5x1.5	56 W	62457300	LL217X 120S/840 1x PSU BV NB TW3	80 W
61793300	LL234X 90S/840 1x PSD WB 7x1.5	57 W	62458000	LL217X 80S/840 1x PSU BV MB TW3	50 W
61794000	LL217X 45S/840 1x PSU WB 5x1.5	28 W	62459700	LL217X 80S/840 1x PSU BV NB TW3	50 W
61795700	LL217X 45S/840 1x PSD WB 7x1.5	27.5 W	10787800	LL217X 80S/840 1x PSD O 7x2.5 HE	48.5 W
63367400	LL234X 45S/840 1x PSU HB WB 5x1.5	28 W	10792200	LL217X 80S/840 1x PSD O 7x2.5	50 W
63368100	LL234X 45S/840 1x PSD HB WB 7x1.5	27.5 W	10808000	LL234X 160S/840 2x PSD O 7x1.5	100 W
63369800	LL234X 80S/840 1x PSU HB WB 5x1.5	51 W	10813400	LL234X 160S/840 2x PSU O 5x1.5	102 W
63370400	LL234X 80S/840 1x PSD HB WB 7x1.5	50 W	10814100	LL234X 160S/840 2x PSU O 5x2.5	102 W
63371100	LL234X 45S/840 1x PSU HB NB 5x1.5	28 W			

Controls and Dimming

CoreLine Trunking gen2

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
10753300	LL212X 53S/840 1x PSU WB 5x1.5 HE	No	63372800	LL234X 45S/840 1x PSD HB NB 7x1.5	Yes
10772400	LL212X 53S/840 1x PSD WB 7x1.5	Yes	63373500	LL234X 80S/840 1x PSU HB NB 5x1.5	No
10779300	LL212X 53S/840 1x PSD WB 7x1.5 HE	Yes	63374200	LL234X 80S/840 1x PSD HB NB 7x1.5	Yes
10780900	LL212X 53S/840 1x PSD WB 7x2.5 HE	Yes	63376600	LL234X 90S/840 1x PSD NB 7x1.5	Yes
10781600	LL212X 53S/840 1x PSU WB 5x2.5 HE	No	63378000	LL234X 160S/840 1x PSD NB 7x1.5	Yes
10763200	LL217X 120S/840 1x PSU WB 5x2.5 HE	No	63382700	LL217X 80S/840 1x PSD NB 7x1.5	Yes
10766300	LL217X 80S/840 1x PSD WB 7x2.5 VLC	Yes	63813600	LL212X 30S/840 1x PSU MB 5x2.5	No
10775500	LL217X 80S/840 1x PSD WB 7x1.5	Yes	63814300	LL212X 30S/840 1x PSU NB 5x2.5	No
10783000	LL217X 120S/840 1x PSD WB 7x1.5 HE	Yes	63815000	LL212X 53S/840 1x PSU MB 5x2.5	No
10784700	LL217X 120S/840 1x PSD WB 7x2.5 HE	Yes	63816700	LL212X 53S/840 1x PSU NB 5x2.5	No
10785400	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	Yes	63817400	LL212X 80S/840 1x PSU MB 5x2.5 HE	No
10786100	LL217X 120S/840 1x PSU WB 5x1.5 HE	No	63818100	LL212X 80S/840 1x PSU NB 5x2.5 HE	No
10788500	LL217X 80S/840 1x PSD WB 7x2.5 HE	Yes	63819800	LL217X 45S/840 1x PSU MB 5x2.5	No
10789200	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	Yes	63820400	LL217X 45S/840 1x PSU NB 5x2.5	No
10790800	LL217X 80S/840 1x PSU WB 5x2.5 HE	No	63821100	LL217X 80S/840 1x PSU MB 5x2.5	No
10791500	LL217X 80S/840 1x PSU WB 5x1.5 HE	No	63822800	LL217X 80S/840 1x PSU NB 5x2.5	No
10793900	LL217X 80S/840 1x PSD WB 7x2.5	Yes	63823500	LL217X 120S/840 1x PSU MB 5x2.5 HE	No
10794600	LL217X 80S/840 1x PSU WB 5x1.5	No	63824200	LL217X 120S/840 1x PSU NB 5x2.5 HE	No
10795300	LL217X 80S/840 1x PSU WB 5x2.5	No	63825900	LL234X 90S/840 2x PSU MB 5x2.5	No
10797700	LL234X 160S/840 2x PSD WB 7x1.5 HE	Yes	63826600	LL234X 90S/840 2x PSU NB 5x2.5	No
10798400	LL234X 160S/840 2x PSD WB 7x2.5 HE	Yes	63827300	LL234X 160S/840 2x PSU MB 5x2.5	No
10799100	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	Yes	63828000	LL234X 160S/840 2x PSU NB 5x2.5	No
10800400	LL234X 160S/840 2x PSU WB 5x1.5 HE	No	63829700	LL234X 240S/840 2x PSU MB 5x2.5 HE	No
10801100	LL234X 160S/840 2x PSU WB 5x2.5 HE	No	63830300	LL234X 240S/840 2x PSU NB 5x2.5 HE	No
10802800	LL234X 240S/840 2x PSD WB 7x1.5 HE	Yes	10756400	LL217X 80S/840 1x PSD BV WB	Yes
10803500	LL234X 240S/840 2x PSD WB 7x2.5 HE	Yes	10782300	LL217X 120S/840 1x PSU BV WB HE	No
10804200	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	Yes	10796000	LL234X 240S/840 2x PSD BV WB HE	Yes
10805900	LL234X 240S/840 2x PSU WB 5x1.5 HE	No	10807300	LL234X 160S/840 2x PSU BV WB	No
10806600	LL234X 240S/840 2x PSU WB 5x2.5 HE	No	10954400	LL217X 80S/840 1X PSU BV WB TW3	No
10809700	LL234X 160S/840 2x PSD O 7x2.5	Yes	10955100	LL234X 160S/840 1X PSU BV WB TW3	No
10810300	LL234X 160S/840 2x PSD WB 7x1.5	Yes	10956800	LL234X 160S/840 2X PSU BV WB TW3	No
10811000	LL234X 160S/840 2x PSD WB 7x2.5	Yes	61796400	LL217X 45S/840 1x PSU BV WB	No
10812700	LL234X 160S/840 2x PSD WB 7x2.5 VLC	Yes	61797100	LL217X 45S/840 1x PSD BV WB	Yes
10815800	LL234X 160S/840 2x PSU WB 5x1.5	No	61798800	LL217X 45S/840 1x PSU BV O	No
10816500	LL234X 160S/840 2x PSU WB 5x2.5	No	61799500	LL217X 45S/840 1x PSD BV O	Yes
10817200	LL217X 80S/840 1x PSD WB 7x1.5 HE	Yes	61800800	LL217X 80S/840 1x PSU BV WB	No
10818900	LL234X 90S/840 2x PSD WB 7x1.5	Yes	61801500	LL217X 80S/840 1x PSU BV O	No
19921700	LL234X 160S/840 1x PSD WB 7x1.5	Yes	61802200	LL217X 80S/840 1x PSD BV O	Yes
19933000	LL234X 160S/840 2x PSU NB 5x1.5	No	62455900	LL217X 120S/840 1x PSU BV WB TW3	No
19934700	LL217X 80S/840 1x PSU NB 5x1.5	No	62456600	LL217X 120S/840 1x PSU BV MB TW3	No
61792600	LL234X 90S/840 2x PSU WB 5x1.5	No	62457300	LL217X 120S/840 1x PSU BV NB TW3	No
61793300	LL234X 90S/840 1x PSD WB 7x1.5	Yes	62458000	LL217X 80S/840 1x PSU BV MB TW3	No
61794000	LL217X 45S/840 1x PSU WB 5x1.5	No	62459700	LL217X 80S/840 1x PSU BV NB TW3	No
61795700	LL217X 45S/840 1x PSD WB 7x1.5	Yes	10787800	LL217X 80S/840 1x PSD O 7x2.5 HE	Yes
63367400	LL234X 45S/840 1x PSU HB WB 5x1.5	No	10792200	LL217X 80S/840 1x PSD O 7x2.5	Yes
63368100	LL234X 45S/840 1x PSD HB WB 7x1.5	Yes	10808000	LL234X 160S/840 2x PSD O 7x1.5	Yes
63369800	LL234X 80S/840 1x PSU HB WB 5x1.5	No	10813400	LL234X 160S/840 2x PSU O 5x1.5	No
63370400	LL234X 80S/840 1x PSD HB WB 7x1.5	Yes	10814100	LL234X 160S/840 2x PSU O 5x2.5	No
63371100	LL234X 45S/840 1x PSU HB NB 5x1.5	No			

Application Conditions

CoreLine Trunking gen2

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
10753300	LL212X 53S/840 1x PSU WB 5x1.5 HE	Not applicable	Yes
10772400	LL212X 53S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
10779300	LL212X 53S/840 1x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10780900	LL212X 53S/840 1x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10781600	LL212X 53S/840 1x PSU WB 5x2.5 HE	Not applicable	Yes
10763200	LL217X 120S/840 1x PSU WB 5x2.5 HE	Not applicable	Yes
10766300	LL217X 80S/840 1x PSD WB 7x2.5 VLC	1%	Yes (relates to presence/movement detection and daylight harvesting)
10775500	LL217X 80S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
10783000	LL217X 120S/840 1x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10784700	LL217X 120S/840 1x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10785400	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10786100	LL217X 120S/840 1x PSU WB 5x1.5 HE	Not applicable	Yes
10788500	LL217X 80S/840 1x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10789200	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10790800	LL217X 80S/840 1x PSU WB 5x2.5 HE	Not applicable	Yes
10791500	LL217X 80S/840 1x PSU WB 5x1.5 HE	Not applicable	Yes
10793900	LL217X 80S/840 1x PSD WB 7x2.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
10794600	LL217X 80S/840 1x PSU WB 5x1.5	Not applicable	Yes
10795300	LL217X 80S/840 1x PSU WB 5x2.5	Not applicable	Yes

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
10797700	LL234X 160S/840 2x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10798400	LL234X 160S/840 2x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10799100	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10800400	LL234X 160S/840 2x PSU WB 5x1.5 HE	Not applicable	Yes
10801100	LL234X 160S/840 2x PSU WB 5x2.5 HE	Not applicable	Yes
10802800	LL234X 240S/840 2x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10803500	LL234X 240S/840 2x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10804200	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10805900	LL234X 240S/840 2x PSU WB 5x1.5 HE	Not applicable	Yes
10806600	LL234X 240S/840 2x PSU WB 5x2.5 HE	Not applicable	Yes
10809700	LL234X 160S/840 2x PSD O 7x2.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
10810300	LL234X 160S/840 2x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
10811000	LL234X 160S/840 2x PSD WB 7x2.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
10812700	LL234X 160S/840 2x PSD WB 7x2.5 VLC	1%	Yes (relates to presence/movement detection and daylight harvesting)
10815800	LL234X 160S/840 2x PSU WB 5x1.5	Not applicable	Yes
10816500	LL234X 160S/840 2x PSU WB 5x2.5	Not applicable	Yes
10817200	LL217X 80S/840 1x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10818900	LL234X 90S/840 2x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
19921700	LL234X 160S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)

CoreLine Trunking gen2

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
19933000	LL234X 160S/840 2x PSU NB 5x1.5	Not applicable	Yes
19934700	LL217X 80S/840 1x PSU NB 5x1.5	Not applicable	Yes
61792600	LL234X 90S/840 2x PSU WB 5x1.5	Not applicable	Yes
61793300	LL234X 90S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
61794000	LL217X 45S/840 1x PSU WB 5x1.5	Not applicable	Yes
61795700	LL217X 45S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
63367400	LL234X 45S/840 1x PSU HB WB 5x1.5	Not applicable	Yes
63368100	LL234X 45S/840 1x PSD HB WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
63369800	LL234X 80S/840 1x PSU HB WB 5x1.5	Not applicable	Yes
63370400	LL234X 80S/840 1x PSD HB WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
63371100	LL234X 45S/840 1x PSU HB NB 5x1.5	Not applicable	Yes
63372800	LL234X 45S/840 1x PSD HB NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
63373500	LL234X 80S/840 1x PSU HB NB 5x1.5	Not applicable	Yes
63374200	LL234X 80S/840 1x PSD HB NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
63376600	LL234X 90S/840 1x PSD NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
63378000	LL234X 160S/840 1x PSD NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
63382700	LL217X 80S/840 1x PSD NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
63813600	LL212X 30S/840 1x PSU MB 5x2.5	Not applicable	Yes
63814300	LL212X 30S/840 1x PSU NB 5x2.5	Not applicable	Yes
63815000	LL212X 53S/840 1x PSU MB 5x2.5	Not applicable	Yes
63816700	LL212X 53S/840 1x PSU NB 5x2.5	Not applicable	Yes

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
63817400	LL212X 80S/840 1x PSU MB 5x2.5 HE	Not applicable	Yes
63818100	LL212X 80S/840 1x PSU NB 5x2.5 HE	Not applicable	Yes
63819800	LL217X 45S/840 1x PSU MB 5x2.5	Not applicable	Yes
63820400	LL217X 45S/840 1x PSU NB 5x2.5	Not applicable	Yes
63821100	LL217X 80S/840 1x PSU MB 5x2.5	Not applicable	Yes
63822800	LL217X 80S/840 1x PSU NB 5x2.5	Not applicable	Yes
63823500	LL217X 120S/840 1x PSU MB 5x2.5 HE	Not applicable	Yes
63824200	LL217X 120S/840 1x PSU NB 5x2.5 HE	Not applicable	Yes
63825900	LL234X 90S/840 2x PSU MB 5x2.5	Not applicable	Yes
63826600	LL234X 90S/840 2x PSU NB 5x2.5	Not applicable	Yes
63827300	LL234X 160S/840 2x PSU MB 5x2.5	Not applicable	Yes
63828000	LL234X 160S/840 2x PSU NB 5x2.5	Not applicable	Yes
63829700	LL234X 240S/840 2x PSU MB 5x2.5 HE	Not applicable	Yes
63830300	LL234X 240S/840 2x PSU NB 5x2.5 HE	Not applicable	Yes
10756400	LL217X 80S/840 1x PSD BV WB 5x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
10782300	LL217X 120S/840 1x PSU BV WB HE	Not applicable	Yes
10796000	LL234X 240S/840 2x PSD BV WB HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10807300	LL234X 160S/840 2x PSU BV WB	Not applicable	Yes
10954400	LL217X 80S/840 1x PSU BV WB TW3	Not applicable	Yes
10955100	LL234X 160S/840 1x PSU BV WB TW3	Not applicable	Yes
10956800	LL234X 160S/840 2x PSU BV WB TW3	Not applicable	Yes
61796400	LL217X 45S/840 1x PSU BV WB 5x1.5	Not applicable	Yes
61797100	LL217X 45S/840 1x PSD BV WB 5x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
61798800	LL217X 45S/840 1x PSU BV O 5x1.5	Not applicable	Yes

CoreLine Trunking gen2

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
61799500	LL217X 45S/840 1x PSD BV O	1%	Yes (relates to presence/movement detection and daylight harvesting)
61800800	LL217X 80S/840 1x PSU BV WB	Not applicable	Yes
61801500	LL217X 80S/840 1x PSU BV O	Not applicable	Yes
61802200	LL217X 80S/840 1x PSD BV O	1%	Yes (relates to presence/movement detection and daylight harvesting)
62455900	LL217X 120S/840 1x PSU BV WB TW3	Not applicable	Yes
62456600	LL217X 120S/840 1x PSU BV MB TW3	Not applicable	Yes
62457300	LL217X 120S/840 1x PSU BV NB TW3	Not applicable	Yes
62458000	LL217X 80S/840 1x PSU BV MB TW3	Not applicable	Yes

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
62459700	LL217X 80S/840 1x PSU BV NB TW3	Not applicable	Yes
10787800	LL217X 80S/840 1x PSD O 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
10792200	LL217X 80S/840 1x PSD O 7x2.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
10808000	LL234X 160S/840 2x PSD O 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
10813400	LL234X 160S/840 2x PSU O 5x1.5	Not applicable	Yes
10814100	LL234X 160S/840 2x PSU O 5x2.5	Not applicable	Yes

