



Comfortable LED ceiling light that's easy on your eyes

Apex Ceiling light

With its EyeComfort design, Apex provides comfortable high quality LED light for home and residential project. Its long lifetime and high lumen maintenance ensures bright light level over time. With various shapes, sizes, it enables to serve from bedroom to big living room, and dining to kitchen space. Installation becomes easier with easy connector and installation bracket.

Benefits

- Ensure comfortable LED light all around home, residential application
- Hassle free easy installation saves time and effort
- Stay bright along the long life time

Features

- high quality LED light with EyeComfort feature, safe from Blue light hazard risk
- Easy to install with easy connector and bracket
- various models and size to fit for all rooms in residential application
- long lifetime of 20,000 hours with high lumen maintenance
- uniform light distribution

Application

- Residential, home: living room, bedroom, dining room, kitchen

Apex Ceiling light

Versions



Ceiling APEX S LED 25W







Ceiling APEX RT LED 40W



Ceiling APEX SQ LED 55W

Dimensional drawing



Product details



Ceiling APEX RT LED 40W ON 1-DPP



Ceiling APEX L LED 45W ON 1-DPP

Apex Ceiling light

Product details



Ceiling APEX S LED 25W ON 2-DPP



Ceiling APEX S LED 25W ON 1-DPP



Ceiling APEX SQ LED 55W ON 1-DPP



Ceiling APEX RT LED 40W ON 2-DPP



Ceiling APEX SQ LED 55W ON 2-DPP



Ceiling APEX L LED 45W ON 2-DPP

Apex Ceiling light

General Information	
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No
Light Technical	
Color rendering index (CRI)	80
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	White
Approval and Application	
Protection class IEC	Safety class I
Ingress protection code	IP20

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy (rated)	
		Temperature (Nom)	(Nom)	Luminous Flux
929002612481	Apex S LED 25W 5700K	5700 K	88.00 lm/W	2,200 lm
929002612681	Apex RT LED 40W 5700K	5700 K	85.00 lm/W	3,400 lm
929002612781	Apex L LED 45W 4000K	4000 K	88.00 lm/W	4,000 lm
929002612881	Apex L LED 45W 5700K	5700 K	88.00 lm/W	4,000 lm
929002613281	Apex SQ LED 55W 5700K	5700 K	84.00 lm/W	4,200 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
929002612481	Apex S LED 25W 5700K	25 W
929002612681	Apex RT LED 40W 5700K	40 W
929002612781	Apex L LED 45W 4000K	45 W

Order Code	Full Product Name	Power Consumption
929002612881	Apex L LED 45W 5700K	45 W
929002613281	Apex SQ LED 55W 5700K	55 W

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
929002612481	Apex S LED 25W 5700K	(0.3287, 0.3425) 6
929002612681	Apex RT LED 40W 5700K	(0.3287, 0.3425) 6
929002612781	Apex L LED 45W 4000K	(ANSI4000K, 0.3818, 0.3797) 6

Order Code	Full Product Name	Initial chromaticity
929002612881	Apex L LED 45W 5700K	(0.3287, 0.3425) 6
929002613281	Apex SQ LED 55W 5700K	(0.3287, 0.3425) 6

Apex Ceiling light

