



Philips UniFlood M gen2: A high power floodlight with true modularity

UniFlood M G2

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

Benefits

- Great design flexibility with individually tilting heads and controls
- Create the right lighting effect with six different spread lenses (narrow spot to wide flood)
- Easy to control with DMX512/RDM
- A robust choice that's IP66-rated for outdoor use

Features

- Standard: RGBW, RGB, 2700K, 3000K and 4000K
- Optional 5000K, monochromatic colors and tunable white
- Flexible lengths from 155 to 569 mm
- Adjustable tilting angles for each head and for the whole set
- Steel brackets

UniFlood M G2







Application

- Bridges, Monuments, Facades
- Parks and Plazas
- Landscape

Warnings and Safety









- For outdoor use only.

Dimensional drawing



UniFlood M G2

Dimensional drawing



General Information

CE mark	CE mark
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces

Light Technical

Optical cover type	Clear glass
Color rendering index (CRI)	>80

Mechanical and Housing

Housing Color	Dark gray
---------------	-----------

Approval and Application

Mech. impact protection code	IK06
Ingress protection code	IP66

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
92607399	BVP353 30LED 27K 220V L30 10	827 warm white	2700 K		4,515 lm
92608099	BVP353 30LED 30K 220V L30 10	830 warm white	3000 K		4,710 lm
92609799	BVP353 30LED 40K 220V L30 10	840 neutral white	4000 K		5,255 lm
92610399	BVP353 30LED 27K 220V L30 10 DMX	827 warm white	2700 K		4,220 lm
92611099	BVP353 30LED 30K 220V L30 10 DMX	830 warm white	3000 K		4,400 lm
92612799	BVP353 30LED 40K 220V L30 10 DMX	840 neutral white	4000 K		4,910 lm
92613499	BVP353 30LED RGB 220V L30 10 DMX	RGB	-		2,495 lm
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	RGBW	-		2,855 lm
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	RGBW	-		2,985 lm
92616599	BVP353 30LED 27K 220V L30 15	827 warm white	2700 K		4,740 lm
92617299	BVP353 30LED 30K 220V L30 15	830 warm white	3000 K		4,945 lm
92618999	BVP353 30LED 40K 220V L30 15	840 neutral white	4000 K		5,520 lm
92619699	BVP353 30LED 27K 220V L30 15 DMX	827 warm white	2700 K		4,430 lm
92620299	BVP353 30LED 30K 220V L30 15 DMX	830 warm white	3000 K		4,620 lm
92621999	BVP353 30LED 40K 220V L30 15 DMX	840 neutral white	4000 K		5,155 lm
92622699	BVP353 30LED RGB 220V L30 15 DMX	RGB	-		2,620 lm
92623399	BVP353 32LED RGBWW 220V L30 15 DMX	RGBW	-		3,000 lm
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	RGBW	-		3,130 lm
92625799	BVP353 30LED 27K 220V L30 30	827 warm white	2700 K		4,910 lm
92626499	BVP353 30LED 30K 220V L30 30	830 warm white	3000 K		5,125 lm
92627199	BVP353 30LED 40K 220V L30 30	840 neutral white	4000 K		5,715 lm
92628899	BVP353 30LED 27K 220V L30 30 DMX	827 warm white	2700 K		4,585 lm
92629599	BVP353 30LED 30K 220V L30 30 DMX	830 warm white	3000 K		4,785 lm
92630199	BVP353 30LED 40K 220V L30 30 DMX	840 neutral white	4000 K		5,340 lm
92631899	BVP353 30LED RGB 220V L30 30 DMX	RGB	-		2,715 lm
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	RGBW	-		3,105 lm
92633299	BVP353 32LED RGBNW 220V L30 30 DMX	RGBW	-		3,245 lm
92634999	BVP353 30LED 27K 220V L30 45	827 warm white	2700 K		4,740 lm
92635699	BVP353 30LED 30K 220V L30 45	830 warm white	3000 K		4,945 lm
92636399	BVP353 30LED 40K 220V L30 45	840 neutral white	4000 K		5,520 lm
92637099	BVP353 30LED 27K 220V L30 45 DMX	827 warm white	2700 K		4,430 lm
92638799	BVP353 30LED 30K 220V L30 45 DMX	830 warm white	3000 K		4,620 lm
92639499	BVP353 30LED 40K 220V L30 45 DMX	840 neutral white	4000 K		5,155 lm
92640099	BVP353 30LED RGB 220V L30 45 DMX	RGB	-		2,620 lm
92641799	BVP353 32LED RGBWW 220V L30 45 DMX	RGBW	-		3,000 lm
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	RGBW	-		3,130 lm
92787200	BVP354 96LED 27K 220V L40 10	827 warm white	2700 K		15,870 lm
92788900	BVP354 96LED 30K 220V L40 10	830 warm white	3000 K		16,555 lm
92789600	BVP354 96LED 40K 220V L40 10	840 neutral white	4000 K		18,470 lm
92790200	BVP354 96LED 27K 220V L40 10 DMX	827 warm white	2700 K		14,640 lm
92791900	BVP354 96LED 30K 220V L40 10 DMX	830 warm white	3000 K		15,270 lm
92792600	BVP354 96LED 40K 220V L40 10 DMX	840 neutral white	4000 K		17,035 lm

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
92793300	BVP354 96LED RGB 220V L40 10 DMX	RGB	-		8,170 lm
92794000	BVP354 96LED RGBWW 220V L40 10 DMX	RGBW	-		10,505 lm
92795700	BVP354 96LED RGBNW 220V L40 10 DMX	RGBW	-		10,975 lm
92796400	BVP354 96LED 27K 220V L40 15	827 warm white	2700 K		16,665 lm
92797100	BVP354 96LED 30K 220V L40 15	830 warm white	3000 K		17,385 lm
92798800	BVP354 96LED 40K 220V L40 15	840 neutral white	4000 K		19,395 lm
92799500	BVP354 96LED 27K 220V L40 15 DMX	827 warm white	2700 K		15,370 lm
92800800	BVP354 96LED 30K 220V L40 15 DMX	830 warm white	3000 K		16,035 lm
92801500	BVP354 96LED 40K 220V L40 15 DMX	840 neutral white	4000 K		17,890 lm
92802200	BVP354 96LED RGB 220V L40 15 DMX	RGB	-		8,580 lm
92803900	BVP354 96LED RGBWW 220V L40 15 DMX	RGBW	-		11,030 lm
92804600	BVP354 96LED RGBNW 220V L40 15 DMX	RGBW	-		11,520 lm
92805300	BVP354 96LED 27K 220V L40 30	827 warm white	2700 K		17,260 lm
92806000	BVP354 96LED 30K 220V L40 30	830 warm white	3000 K		18,005 lm
92807700	BVP354 96LED 40K 220V L40 30	840 neutral white	4000 K		20,085 lm
92808400	BVP354 96LED 27K 220V L40 30 DMX	827 warm white	2700 K		15,920 lm
92809100	BVP354 96LED 30K 220V L40 30 DMX	830 warm white	3000 K		16,605 lm
92810700	BVP354 96LED 40K 220V L40 30 DMX	840 neutral white	4000 K		18,525 lm
92811400	BVP354 96LED RGB 220V L40 30 DMX	RGB	-		8,885 lm
92812100	BVP354 96LED RGBWW 220V L40 30 DMX	RGBW	-		11,425 lm
92813800	BVP354 96LED RGBNW 220V L40 30 DMX	RGBW	-		11,935 lm
92814500	BVP354 96LED 27K 220V L40 45	827 warm white	2700 K		16,665 lm
92815200	BVP354 96LED 30K 220V L40 45	830 warm white	3000 K		17,385 lm
92816900	BVP354 96LED 40K 220V L40 45	840 neutral white	4000 K		19,395 lm
92817600	BVP354 96LED 27K 220V L40 45 DMX	827 warm white	2700 K		15,370 lm
92818300	BVP354 96LED 30K 220V L40 45 DMX	830 warm white	3000 K		16,035 lm
92819000	BVP354 96LED 40K 220V L40 45 DMX	840 neutral white	4000 K		17,890 lm
92820600	BVP354 96LED RGB 220V L40 45 DMX	RGB	-		8,580 lm
92821300	BVP354 96LED RGBWW 220V L40 45 DMX	RGBW	-		11,030 lm
92822000	BVP354 96LED RGBNW 220V L40 45 DMX	RGBW	-		11,520 lm
92823700	BVP354 120LED 27K 220V L50 10	827 warm white	2700 K		18,075 lm
92824400	BVP354 120LED 30K 220V L50 10	830 warm white	3000 K		18,850 lm
92825100	BVP354 120LED 40K 220V L50 10	840 neutral white	4000 K		21,035 lm
92826800	BVP354 120LED 27K 220V L50 10 DMX	827 warm white	2700 K		16,880 lm
92827500	BVP354 120LED 30K 220V L50 10 DMX	830 warm white	3000 K		17,605 lm
92828200	BVP354 120LED 40K 220V L50 10 DMX	840 neutral white	4000 K		19,645 lm
92829900	BVP354 120LED RGB 220V L50 10 DMX	RGB	-		9,985 lm
92830500	BVP354 120LED RGBWW 220V L50 10 DMX	RGBW	-		10,720 lm
92831200	BVP354 120LED RGBNW 220V L50 10 DMX	RGBW	-		11,190 lm
92832900	BVP354 120LED 27K 220V L50 15	827 warm white	2700 K		18,975 lm
92833600	BVP354 120LED 30K 220V L50 15	830 warm white	3000 K		19,795 lm

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
92834300	BVP354 120LED 40K 220V L50 15	840 neutral white	4000 K		22,085 lm
92835000	BVP354 120LED 27K 220V L50 15 DMX	827 warm white	2700 K		17,720 lm
92836700	BVP354 120LED 30K 220V L50 15 DMX	830 warm white	3000 K		18,485 lm
92837400	BVP354 120LED 40K 220V L50 15 DMX	840 neutral white	4000 K		20,625 lm
92838100	BVP354 120LED RGB 220V L50 15 DMX	RGB	-		10,485 lm
92839800	BVP354 120LED RGBWW 220V L50 15 DMX	RGBW	-		11,255 lm
92840400	BVP354 120LED RGBNW 220V L50 15 DMX	RGBW	-		11,750 lm
92841100	BVP354 120LED 27K 220V L50 30	827 warm white	2700 K		19,655 lm
92842800	BVP354 120LED 30K 220V L50 30	830 warm white	3000 K		20,500 lm
92843500	BVP354 120LED 40K 220V L50 30	840 neutral white	4000 K		22,875 lm
92844200	BVP354 120LED 27K 220V L50 30 DMX	827 warm white	2700 K		18,355 lm
92845900	BVP354 120LED 30K 220V L50 30 DMX	830 warm white	3000 K		19,145 lm
92846600	BVP354 120LED 40K 220V L50 30 DMX	840 neutral white	4000 K		21,360 lm
92847300	BVP354 120LED RGB 220V L50 30 DMX	RGB	-		10,860 lm
92848000	BVP354 120LED RGBWW 220V L50 30 DMX	RGBW	-		11,655 lm
92849700	BVP354 120LED RGBNW 220V L50 30 DMX	RGBW	-		12,170 lm
92850300	BVP354 120LED 27K 220V L50 45	827 warm white	2700 K		18,975 lm
92851000	BVP354 120LED 30K 220V L50 45	830 warm white	3000 K		19,795 lm
92852700	BVP354 120LED 40K 220V L50 45	840 neutral white	4000 K		22,085 lm
92853400	BVP354 120LED 27K 220V L50 45 DMX	827 warm white	2700 K		17,720 lm
92854100	BVP354 120LED 30K 220V L50 45 DMX	830 warm white	3000 K		18,485 lm
92855800	BVP354 120LED 40K 220V L50 45 DMX	840 neutral white	4000 K		20,625 lm
92856500	BVP354 120LED RGB 220V L50 45 DMX	RGB	-		10,485 lm
92857200	BVP354 120LED RGBWW 220V L50 45 DMX	RGBW	-		11,255 lm
92858900	BVP354 120LED RGBNW 220V L50 45 DMX	RGBW	-		11,750 lm
92859600	BVP354 144LED 27K 220V L57 10	827 warm white	2700 K		22,765 lm
92860200	BVP354 144LED 30K 220V L57 10	830 warm white	3000 K		23,745 lm
92861900	BVP354 144LED 40K 220V L57 10	840 neutral white	4000 K		26,490 lm
92862600	BVP354 144LED 27K 220V L57 10 DMX	827 warm white	2700 K		21,690 lm
92863300	BVP354 144LED 30K 220V L57 10 DMX	830 warm white	3000 K		22,625 lm
92864000	BVP354 144LED 40K 220V L57 10 DMX	840 neutral white	4000 K		25,240 lm
92865700	BVP354 144LED RGB 220V L57 10 DMX	RGB	-		13,410 lm
92866400	BVP354 144LED RGBWW 220V L57 10 DMX	RGBW	-		14,395 lm
92867100	BVP354 144LED RGBNW 220V L57 10 DMX	RGBW	-		15,030 lm
92868800	BVP354 144LED 27K 220V L57 15	827 warm white	2700 K		23,900 lm
92869500	BVP354 144LED 30K 220V L57 15	830 warm white	3000 K		24,930 lm
92870100	BVP354 144LED 40K 220V L57 15	840 neutral white	4000 K		27,815 lm
92871800	BVP354 144LED 27K 220V L57 15 DMX	827 warm white	2700 K		22,775 lm
92872500	BVP354 144LED 30K 220V L57 15 DMX	830 warm white	3000 K		23,755 lm
92873200	BVP354 144LED 40K 220V L57 15 DMX	840 neutral white	4000 K		26,505 lm
92874900	BVP354 144LED RGB 220V L57 15 DMX	RGB	-		14,080 lm
92875600	BVP354 144LED RGBWW 220V L57 15 DMX	RGBW	-		15,115 lm

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	RGBW	-		15,785 lm
92877000	BVP354 144LED 27K 220V L57 30	827 warm white	2700 K		24,755 lm
92878700	BVP354 144LED 30K 220V L57 30	830 warm white	3000 K		25,820 lm
92879400	BVP354 144LED 40K 220V L57 30	840 neutral white	4000 K		28,810 lm
92880000	BVP354 144LED 27K 220V L57 30 DMX	827 warm white	2700 K		23,585 lm
92881700	BVP354 144LED 30K 220V L57 30 DMX	830 warm white	3000 K		24,605 lm
92882400	BVP354 144LED 40K 220V L57 30 DMX	840 neutral white	4000 K		27,450 lm
92883100	BVP354 144LED RGB 220V L57 30 DMX	RGB	-		14,585 lm
92884800	BVP354 144LED RGBWW 220V L57 30 DMX	RGBW	-		15,655 lm
92885500	BVP354 144LED RGBNW 220V L57 30 DMX	RGBW	-		16,345 lm
92886200	BVP354 144LED 27K 220V L57 45	827 warm white	2700 K		23,900 lm
92887900	BVP354 144LED 30K 220V L57 45	830 warm white	3000 K		24,930 lm
92888600	BVP354 144LED 40K 220V L57 45	840 neutral white	4000 K		27,815 lm
92889300	BVP354 144LED 27K 220V L57 45 DMX	827 warm white	2700 K		22,775 lm
92890900	BVP354 144LED 30K 220V L57 45 DMX	830 warm white	3000 K		23,755 lm
92891600	BVP354 144LED 40K 220V L57 45 DMX	840 neutral white	4000 K		26,505 lm
92892300	BVP354 144LED RGB 220V L57 45 DMX	RGB	-		14,080 lm
92893000	BVP354 144LED RGBWW 220V L57 45 DMX	RGBW	-		15,115 lm
92894700	BVP354 144LED RGBNW 220V L57 45 DMX	RGBW	-		15,785 lm
92751399	BVP353 72LED 27K 220V L57 10	827 warm white	2700 K		11,380 lm
92752099	BVP353 72LED 30K 220V L57 10	830 warm white	3000 K		11,870 lm
92753799	BVP353 72LED 40K 220V L57 10	840 neutral white	4000 K		13,245 lm
92754499	BVP353 72LED 27K 220V L57 10 DMX	827 warm white	2700 K		10,845 lm
92755199	BVP353 72LED 30K 220V L57 10 DMX	830 warm white	3000 K		11,310 lm
92756899	BVP353 72LED 40K 220V L57 10 DMX	840 neutral white	4000 K		12,620 lm
92757599	BVP353 72LED RGB 220V L57 10 DMX	RGB	-		6,705 lm
92758299	BVP353 72LED RGBWW 220V L57 10 DMX	RGBW	-		7,195 lm
92759999	BVP353 72LED RGBNW 220V L57 10 DMX	RGBW	-		7,515 lm
92760599	BVP353 72LED 27K 220V L57 15	827 warm white	2700 K		11,950 lm
92761299	BVP353 72LED 30K 220V L57 15	830 warm white	3000 K		12,465 lm
92762999	BVP353 72LED 40K 220V L57 15	840 neutral white	4000 K		13,905 lm
92763699	BVP353 72LED 27K 220V L57 15 DMX	827 warm white	2700 K		11,385 lm
92764399	BVP353 72LED 30K 220V L57 15 DMX	830 warm white	3000 K		11,875 lm
92765099	BVP353 72LED 40K 220V L57 15 DMX	840 neutral white	4000 K		13,250 lm
92766799	BVP353 72LED RGB 220V L57 15 DMX	RGB	-		7,040 lm
92767499	BVP353 72LED RGBWW 220V L57 15 DMX	RGBW	-		7,555 lm
92768199	BVP353 72LED RGBNW 220V L57 15 DMX	RGBW	-		7,890 lm
92769899	BVP353 72LED 27K 220V L57 30	827 warm white	2700 K		12,375 lm
92770499	BVP353 72LED 30K 220V L57 30	830 warm white	3000 K		12,910 lm
92771199	BVP353 72LED 40K 220V L57 30	840 neutral white	4000 K		14,405 lm
92772899	BVP353 72LED 27K 220V L57 30 DMX	827 warm white	2700 K		11,790 lm
92773599	BVP353 72LED 30K 220V L57 30 DMX	830 warm white	3000 K		12,300 lm

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
92774299	BVP353 72LED 40K 220V L57 30 DMX	840 neutral white	4000 K		13,725 lm
92775999	BVP353 72LED RGB 220V L57 30 DMX	RGB	-		7,290 lm
92776699	BVP353 72LED RGBWW 220V L57 30 DMX	RGBW	-		7,825 lm
92777399	BVP353 72LED RGBNW 220V L57 30 DMX	RGBW	-		8,170 lm
92778099	BVP353 72LED 27K 220V L57 45	827 warm white	2700 K		11,950 lm
92779799	BVP353 72LED 30K 220V L57 45	830 warm white	3000 K		12,465 lm
92780399	BVP353 72LED 40K 220V L57 45	840 neutral white	4000 K		13,905 lm
92781099	BVP353 72LED 27K 220V L57 45 DMX	827 warm white	2700 K		11,385 lm
92782799	BVP353 72LED 30K 220V L57 45 DMX	830 warm white	3000 K		11,875 lm
92783499	BVP353 72LED 40K 220V L57 45 DMX	840 neutral white	4000 K		13,250 lm
92784199	BVP353 72LED RGB 220V L57 45 DMX	RGB	-		7,040 lm
92785899	BVP353 72LED RGBWW 220V L57 45 DMX	RGBW	-		7,555 lm
92786599	BVP353 72LED RGBNW 220V L57 45 DMX	RGBW	-		7,890 lm
92535999	BVP353 18LED 27K 220V L21 10	827 warm white	2700 K		2,845 lm
92536699	BVP353 18LED 30K 220V L21 10	830 warm white	3000 K		2,965 lm
92537399	BVP353 18LED 40K 220V L21 10	840 neutral white	4000 K		3,310 lm
92538099	BVP353 18LED 27K 220V L21 10 DMX	827 warm white	2700 K		2,640 lm
92539799	BVP353 18LED 30K 220V L21 10 DMX	830 warm white	3000 K		2,755 lm
92540399	BVP353 18LED 40K 220V L21 10 DMX	840 neutral white	4000 K		3,075 lm
92541099	BVP353 18LED RGB 220V L21 10 DMX	RGB	-		1,565 lm
92542799	BVP353 20LED RGBWW 220V L21 10 DMX	RGBW	-		1,860 lm
92543499	BVP353 20LED RGBNW 220V L21 10 DMX	RGBW	-		1,945 lm
92544199	BVP353 18LED 27K 220V L21 15	827 warm white	2700 K		2,985 lm
92545899	BVP353 18LED 30K 220V L21 15	830 warm white	3000 K		3,115 lm
92546599	BVP353 18LED 40K 220V L21 15	840 neutral white	4000 K		3,475 lm
92547299	BVP353 18LED 27K 220V L21 15 DMX	827 warm white	2700 K		2,770 lm
92548999	BVP353 18LED 30K 220V L21 15 DMX	830 warm white	3000 K		2,890 lm
92549699	BVP353 18LED 40K 220V L21 15 DMX	840 neutral white	4000 K		3,225 lm
92550299	BVP353 18LED RGB 220V L21 15 DMX	RGB	-		1,640 lm
92551999	BVP353 20LED RGBWW 220V L21 15 DMX	RGBW	-		1,955 lm
92552699	BVP353 20LED RGBNW 220V L21 15 DMX	RGBW	-		2,040 lm
92553399	BVP353 18LED 27K 220V L21 30	827 warm white	2700 K		3,090 lm
92554099	BVP353 18LED 30K 220V L21 30	830 warm white	3000 K		3,225 lm
92555799	BVP353 18LED 40K 220V L21 30	840 neutral white	4000 K		3,600 lm
92556499	BVP353 18LED 27K 220V L21 30 DMX	827 warm white	2700 K		2,870 lm
92557199	BVP353 18LED 30K 220V L21 30 DMX	830 warm white	3000 K		2,995 lm
92558899	BVP353 18LED 40K 220V L21 30 DMX	840 neutral white	4000 K		3,340 lm
92559599	BVP353 18LED RGB 220V L21 30 DMX	RGB	-		1,700 lm
92560199	BVP353 20LED RGBWW 220V L21 30 DMX	RGBW	-		2,025 lm
92561899	BVP353 20LED RGBNW 220V L21 30 DMX	RGBW	-		2,115 lm
92562599	BVP353 18LED 27K 220V L21 45	827 warm white	2700 K		2,985 lm

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
92563299	BVP353 18LED 30K 220V L21 45	830 warm white	3000 K		3,115 lm
92564999	BVP353 18LED 40K 220V L21 45	840 neutral white	4000 K		3,475 lm
92565699	BVP353 18LED 27K 220V L21 45 DMX	827 warm white	2700 K		2,770 lm
92566399	BVP353 18LED 30K 220V L21 45 DMX	830 warm white	3000 K		2,890 lm
92567099	BVP353 18LED 40K 220V L21 45 DMX	840 neutral white	4000 K		3,225 lm
92568799	BVP353 18LED RGB 220V L21 45 DMX	RGB	-		1,640 lm
92569499	BVP353 20LED RGBWW 220V L21 45 DMX	RGBW	-		1,955 lm
92570099	BVP353 20LED RGBNW 220V L21 45 DMX	RGBW	-		2,040 lm
92463599	BVP353 12LED 27K 220V L15 10	827 warm white	2700 K		1,760 lm
92464299	BVP353 12LED 30K 220V L15 10	830 warm white	3000 K		1,835 lm
92465999	BVP353 12LED 40K 220V L15 10	840 neutral white	4000 K		2,050 lm
92466699	BVP353 12LED 27K 220V L15 10 DMX	827 warm white	2700 K		1,615 lm
92467399	BVP353 12LED 30K 220V L15 10 DMX	830 warm white	3000 K		1,685 lm
92468099	BVP353 12LED 40K 220V L15 10 DMX	840 neutral white	4000 K		1,880 lm
92469799	BVP353 12LED RGB 220V L15 10 DMX	RGB	-		960 lm
92470399	BVP353 12LED RGBWW 220V L15 10 DMX	RGBW	-		1,175 lm
92471099	BVP353 12LED RGBNW 220V L15 10 DMX	RGBW	-		1,225 lm
92481999	BVP353 12LED 27K 220V L15 30	827 warm white	2700 K		1,915 lm
92482699	BVP353 12LED 30K 220V L15 30	830 warm white	3000 K		1,995 lm
92483399	BVP353 12LED 40K 220V L15 30	840 neutral white	4000 K		2,225 lm
92484099	BVP353 12LED 27K 220V L15 30 DMX	827 warm white	2700 K		1,755 lm
92485799	BVP353 12LED 30K 220V L15 30 DMX	830 warm white	3000 K		1,830 lm
92486499	BVP353 12LED 40K 220V L15 30 DMX	840 neutral white	4000 K		2,045 lm
92487199	BVP353 12LED RGB 220V L15 30 DMX	RGB	-		1,045 lm
92488899	BVP353 12LED RGBWW 220V L15 30 DMX	RGBW	-		1,275 lm
92489599	BVP353 12LED RGBNW 220V L15 30 DMX	RGBW	-		1,330 lm
92490199	BVP353 12LED 27K 220V L15 45	827 warm white	2700 K		1,845 lm
92491899	BVP353 12LED 30K 220V L15 45	830 warm white	3000 K		1,925 lm
92492599	BVP353 12LED 40K 220V L15 45	840 neutral white	4000 K		2,150 lm
92493299	BVP353 12LED 27K 220V L15 45 DMX	827 warm white	2700 K		1,695 lm
92494999	BVP353 12LED 30K 220V L15 45 DMX	830 warm white	3000 K		1,770 lm
92495699	BVP353 12LED 40K 220V L15 45 DMX	840 neutral white	4000 K		1,975 lm
92496399	BVP353 12LED RGB 220V L15 45 DMX	RGB	-		1,010 lm
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	RGBW	-		1,230 lm
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	RGBW	-		1,285 lm
92643199	BVP353 36LED 27K 220V L35 10	827 warm white	2700 K		5,950 lm
92644899	BVP353 36LED 30K 220V L35 10	830 warm white	3000 K		6,205 lm
92645599	BVP353 36LED 40K 220V L35 10	840 neutral white	4000 K		6,925 lm
92646299	BVP353 36LED 27K 220V L35 10 DMX	827 warm white	2700 K		5,350 lm
92647999	BVP353 36LED 30K 220V L35 10 DMX	830 warm white	3000 K		5,585 lm
92648699	BVP353 36LED 40K 220V L35 10 DMX	840 neutral white	4000 K		6,230 lm
92649399	BVP353 36LED RGB 220V L35 10 DMX	RGB	-		3,290 lm

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
92650999	BVP353 36LED RGBWW 220V L35 10 DMX	RGBW	-		3,640 lm
92651699	BVP353 36LED RGBNW 220V L35 10 DMX	RGBW	-		3,805 lm
92652399	BVP353 36LED 27K 220V L35 15	827 warm white	2700 K		6,245 lm
92653099	BVP353 36LED 30K 220V L35 15	830 warm white	3000 K		6,515 lm
92654799	BVP353 36LED 40K 220V L35 15	840 neutral white	4000 K		7,270 lm
92655499	BVP353 36LED 27K 220V L35 15 DMX	827 warm white	2700 K		5,620 lm
92656199	BVP353 36LED 30K 220V L35 15 DMX	830 warm white	3000 K		5,860 lm
92657899	BVP353 36LED 40K 220V L35 15 DMX	840 neutral white	4000 K		6,540 lm
92658599	BVP353 36LED RGB 220V L35 15 DMX	RGB	-		3,455 lm
92659299	BVP353 36LED RGBWW 220V L35 15 DMX	RGBW	-		3,825 lm
92660899	BVP353 36LED RGBNW 220V L35 15 DMX	RGBW	-		3,995 lm
92661599	BVP353 36LED 27K 220V L35 30	827 warm white	2700 K		6,470 lm
92662299	BVP353 36LED 30K 220V L35 30	830 warm white	3000 K		6,750 lm
92663999	BVP353 36LED 40K 220V L35 30	840 neutral white	4000 K		7,530 lm
92664699	BVP353 36LED 27K 220V L35 30 DMX	827 warm white	2700 K		5,820 lm
92665399	BVP353 36LED 30K 220V L35 30 DMX	830 warm white	3000 K		6,070 lm
92666099	BVP353 36LED 40K 220V L35 30 DMX	840 neutral white	4000 K		6,775 lm
92667799	BVP353 36LED RGB 220V L35 30 DMX	RGB	-		3,580 lm
92668499	BVP353 36LED RGBWW 220V L35 30 DMX	RGBW	-		3,960 lm
92669199	BVP353 36LED RGBNW 220V L35 30 DMX	RGBW	-		4,135 lm
92670799	BVP353 36LED 27K 220V L35 45	827 warm white	2700 K		6,245 lm
92671499	BVP353 36LED 30K 220V L35 45	830 warm white	3000 K		6,515 lm
92672199	BVP353 36LED 40K 220V L35 45	840 neutral white	4000 K		7,270 lm
92673899	BVP353 36LED 27K 220V L35 45 DMX	827 warm white	2700 K		5,620 lm
92674599	BVP353 36LED 30K 220V L35 45 DMX	830 warm white	3000 K		5,860 lm
92675299	BVP353 36LED 40K 220V L35 45 DMX	840 neutral white	4000 K		6,540 lm
92676999	BVP353 36LED RGB 220V L35 45 DMX	RGB	-		3,455 lm
92677699	BVP353 36LED RGBWW 220V L35 45 DMX	RGBW	-		3,825 lm
92678399	BVP353 36LED RGBNW 220V L35 45 DMX	RGBW	-		3,995 lm
92571799	BVP353 24LED 27K 220V L24 10	827 warm white	2700 K		3,615 lm
92572499	BVP353 24LED 30K 220V L24 10	830 warm white	3000 K		3,770 lm
92573199	BVP353 24LED 40K 220V L24 10	840 neutral white	4000 K		4,205 lm
92574899	BVP353 24LED 27K 220V L24 10 DMX	827 warm white	2700 K		3,465 lm
92575599	BVP353 24LED 30K 220V L24 10 DMX	830 warm white	3000 K		3,615 lm
92576299	BVP353 24LED 40K 220V L24 10 DMX	840 neutral white	4000 K		4,035 lm
92577999	BVP353 24LED RGB 220V L24 10 DMX	RGB	-		2,085 lm
92578699	BVP353 24LED RGBWW 220V L24 10 DMX	RGBW	-		2,350 lm
92579399	BVP353 24LED RGBNW 220V L24 10 DMX	RGBW	-		2,450 lm
92580999	BVP353 24LED 27K 220V L24 15	827 warm white	2700 K		3,795 lm
92581699	BVP353 24LED 30K 220V L24 15	830 warm white	3000 K		3,955 lm
92582399	BVP353 24LED 40K 220V L24 15	840 neutral white	4000 K		4,415 lm

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
92583099	BVP353 24LED 27K 220V L24 15 DMX	827 warm white	2700 K		3,640 lm
92584799	BVP353 24LED 30K 220V L24 15 DMX	830 warm white	3000 K		3,800 lm
92585499	BVP353 24LED 40K 220V L24 15 DMX	840 neutral white	4000 K		4,235 lm
92586199	BVP353 24LED RGB 220V L24 15 DMX	RGB	-		2,190 lm
92587899	BVP353 24LED RGBWW 220V L24 15 DMX	RGBW	-		2,465 lm
92588599	BVP353 24LED RGBNW 220V L24 15 DMX	RGBW	-		2,575 lm
92589299	BVP353 24LED 27K 220V L24 30	827 warm white	2700 K		3,930 lm
92590899	BVP353 24LED 30K 220V L24 30	830 warm white	3000 K		4,100 lm
92591599	BVP353 24LED 40K 220V L24 30	840 neutral white	4000 K		4,575 lm
92592299	BVP353 24LED 27K 220V L24 30 DMX	827 warm white	2700 K		3,770 lm
92593999	BVP353 24LED 30K 220V L24 30 DMX	830 warm white	3000 K		3,935 lm
92594699	BVP353 24LED 40K 220V L24 30 DMX	840 neutral white	4000 K		4,390 lm
92595399	BVP353 24LED RGB 220V L24 30 DMX	RGB	-		2,270 lm
92596099	BVP353 24LED RGBWW 220V L24 30 DMX	RGBW	-		2,555 lm
92597799	BVP353 24LED RGBNW 220V L24 30 DMX	RGBW	-		2,665 lm
92598499	BVP353 24LED 27K 220V L24 45	827 warm white	2700 K		3,795 lm
92599199	BVP353 24LED 30K 220V L24 45	830 warm white	3000 K		3,955 lm
92600499	BVP353 24LED 40K 220V L24 45	840 neutral white	4000 K		4,415 lm
92601199	BVP353 24LED 27K 220V L24 45 DMX	827 warm white	2700 K		3,640 lm
92602899	BVP353 24LED 30K 220V L24 45 DMX	830 warm white	3000 K		3,800 lm
92603599	BVP353 24LED 40K 220V L24 45 DMX	840 neutral white	4000 K		4,235 lm
92604299	BVP353 24LED RGB 220V L24 45 DMX	RGB	-		2,190 lm
92605999	BVP353 24LED RGBWW 220V L24 45 DMX	RGBW	-		2,465 lm
92606699	BVP353 24LED RGBNW 220V L24 45 DMX	RGBW	-		2,575 lm
92715599	BVP353 60LED 27K 220V L50 10	827 warm white	2700 K		9,150 lm
92716299	BVP353 60LED 30K 220V L50 10	830 warm white	3000 K		9,540 lm
92717999	BVP353 60LED 40K 220V L50 10	840 neutral white	4000 K		10,645 lm
92718699	BVP353 60LED 27K 220V L50 10 DMX	827 warm white	2700 K		8,805 lm
92719399	BVP353 60LED 30K 220V L50 10 DMX	830 warm white	3000 K		9,185 lm
92720999	BVP353 60LED 40K 220V L50 10 DMX	840 neutral white	4000 K		10,250 lm
92721699	BVP353 60LED RGB 220V L50 10 DMX	RGB	-		5,215 lm
92722399	BVP353 60LED RGBWW 220V L50 10 DMX	RGBW	-		5,995 lm
92723099	BVP353 60LED RGBNW 220V L50 10 DMX	RGBW	-		6,260 lm
92724799	BVP353 60LED 27K 220V L50 15	827 warm white	2700 K		9,605 lm
92725499	BVP353 60LED 30K 220V L50 15	830 warm white	3000 K		10,020 lm
92726199	BVP353 60LED 40K 220V L50 15	840 neutral white	4000 K		11,180 lm
92727899	BVP353 60LED 27K 220V L50 15 DMX	827 warm white	2700 K		9,245 lm
92728599	BVP353 60LED 30K 220V L50 15 DMX	830 warm white	3000 K		9,645 lm
92729299	BVP353 60LED 40K 220V L50 15 DMX	840 neutral white	4000 K		10,760 lm
92730899	BVP353 60LED RGB 220V L50 15 DMX	RGB	-		5,480 lm
92731599	BVP353 60LED RGBWW 220V L50 15 DMX	RGBW	-		6,295 lm

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	RGBW	-		6,575 lm
92733999	BVP353 60LED 27K 220V L50 30	827 warm white	2700 K		9,950 lm
92734699	BVP353 60LED 30K 220V L50 30	830 warm white	3000 K		10,380 lm
92735399	BVP353 60LED 40K 220V L50 30	840 neutral white	4000 K		11,580 lm
92736099	BVP353 60LED 27K 220V L50 30 DMX	827 warm white	2700 K		9,575 lm
92737799	BVP353 60LED 30K 220V L50 30 DMX	830 warm white	3000 K		9,990 lm
92738499	BVP353 60LED 40K 220V L50 30 DMX	840 neutral white	4000 K		11,145 lm
92739199	BVP353 60LED RGB 220V L50 30 DMX	RGB	-		5,675 lm
92740799	BVP353 60LED RGBWW 220V L50 30 DMX	RGBW	-		6,520 lm
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	RGBW	-		6,810 lm
92742199	BVP353 60LED 27K 220V L50 45	827 warm white	2700 K		9,605 lm
92743899	BVP353 60LED 30K 220V L50 45	830 warm white	3000 K		10,020 lm
92744599	BVP353 60LED 40K 220V L50 45	840 neutral white	4000 K		11,180 lm
92745299	BVP353 60LED 27K 220V L50 45 DMX	827 warm white	2700 K		9,245 lm
92746999	BVP353 60LED 30K 220V L50 45 DMX	830 warm white	3000 K		9,645 lm
92747699	BVP353 60LED 40K 220V L50 45 DMX	840 neutral white	4000 K		10,760 lm
92748399	BVP353 60LED RGB 220V L50 45 DMX	RGB	-		5,480 lm
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	RGBW	-		6,295 lm
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	RGBW	-		6,575 lm
92499499	BVP353 16LED 27K 220V L18 10	827 warm white	2700 K		2,755 lm
92500799	BVP353 16LED 30K 220V L18 10	830 warm white	3000 K		2,875 lm
92501499	BVP353 16LED 40K 220V L18 10	840 neutral white	4000 K		3,205 lm
92502199	BVP353 16LED 27K 220V L18 10 DMX	827 warm white	2700 K		2,060 lm
92503899	BVP353 16LED 30K 220V L18 10 DMX	830 warm white	3000 K		2,145 lm
92504599	BVP353 16LED 40K 220V L18 10 DMX	840 neutral white	4000 K		2,395 lm
92505299	BVP353 15LED RGB 220V L18 10 DMX	RGB	-		1,200 lm
92506999	BVP353 16LED RGBWW 220V L18 10 DMX	RGBW	-		1,425 lm
92507699	BVP353 16LED RGBNW 220V L18 10 DMX	RGBW	-		1,490 lm
92508399	BVP353 16LED 27K 220V L18 15	827 warm white	2700 K		2,895 lm
92509099	BVP353 16LED 30K 220V L18 15	830 warm white	3000 K		3,020 lm
92510699	BVP353 16LED 40K 220V L18 15	840 neutral white	4000 K		3,365 lm
92511399	BVP353 16LED 27K 220V L18 15 DMX	827 warm white	2700 K		2,160 lm
92512099	BVP353 16LED 30K 220V L18 15 DMX	830 warm white	3000 K		2,255 lm
92513799	BVP353 16LED 40K 220V L18 15 DMX	840 neutral white	4000 K		2,515 lm
92514499	BVP353 15LED RGB 220V L18 15 DMX	RGB	-		1,260 lm
92515199	BVP353 16LED RGBWW 220V L18 15 DMX	RGBW	-		1,500 lm
92516899	BVP353 16LED RGBNW 220V L18 15 DMX	RGBW	-		1,565 lm
92517599	BVP353 16LED 27K 220V L18 30	827 warm white	2700 K		2,995 lm
92518299	BVP353 16LED 30K 220V L18 30	830 warm white	3000 K		3,125 lm
92519999	BVP353 16LED 40K 220V L18 30	840 neutral white	4000 K		3,490 lm
92520599	BVP353 16LED 27K 220V L18 30 DMX	827 warm white	2700 K		2,240 lm
92521299	BVP353 16LED 30K 220V L18 30 DMX	830 warm white	3000 K		2,335 lm

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
92522999	BVP353 16LED 40K 220V L18 30 DMX	840 neutral white	4000 K		2,605 lm
92523699	BVP353 15LED RGB 220V L18 30 DMX	RGB	-		1,305 lm
92524399	BVP353 16LED RGBWW 220V L18 30 DMX	RGBW	-		1,550 lm
92525099	BVP353 16LED RGBNW 220V L18 30 DMX	RGBW	-		1,620 lm
92526799	BVP353 16LED 27K 220V L18 45	827 warm white	2700 K		2,895 lm
92527499	BVP353 16LED 30K 220V L18 45	830 warm white	3000 K		3,020 lm
92528199	BVP353 16LED 40K 220V L18 45	840 neutral white	4000 K		3,365 lm
92529899	BVP353 16LED 27K 220V L18 45 DMX	827 warm white	2700 K		2,160 lm
92530499	BVP353 16LED 30K 220V L18 45 DMX	830 warm white	3000 K		2,255 lm
92531199	BVP353 16LED 40K 220V L18 45 DMX	840 neutral white	4000 K		2,515 lm
92532899	BVP353 15LED RGB 220V L18 45 DMX	RGB	-		1,260 lm
92533599	BVP353 16LED RGBWW 220V L18 45 DMX	RGBW	-		1,500 lm
92534299	BVP353 16LED RGBNW 220V L18 45 DMX	RGBW	-		1,565 lm
92895400	BVP355 216LED 27K 220V L57 10	827 warm white	2700 K		34,145 lm
92896100	BVP355 216LED 30K 220V L57 10	830 warm white	3000 K		35,615 lm
92897800	BVP355 216LED 40K 220V L57 10	840 neutral white	4000 K		39,740 lm
92898500	BVP355 216LED 27K 220V L57 10 DMX	827 warm white	2700 K		32,535 lm
92899200	BVP355 216LED 30K 220V L57 10 DMX	830 warm white	3000 K		33,935 lm
92900500	BVP355 216LED 40K 220V L57 10 DMX	840 neutral white	4000 K		37,860 lm
92901200	BVP355 216LED RGB 220V L57 10 DMX	RGB	-		20,115 lm
92902900	BVP355 216LED RGBWW 220V L57 10 DMX	RGBW	-		21,590 lm
92903600	BVP355 216LED RGBNW 220V L57 10 DMX	RGBW	-		22,550 lm
92904300	BVP355 216LED 27K 220V L57 15	827 warm white	2700 K		35,850 lm
92905000	BVP355 216LED 30K 220V L57 15	830 warm white	3000 K		37,400 lm
92906700	BVP355 216LED 40K 220V L57 15	840 neutral white	4000 K		41,725 lm
92907400	BVP355 216LED 27K 220V L57 15 DMX	827 warm white	2700 K		34,160 lm
92908100	BVP355 216LED 30K 220V L57 15 DMX	830 warm white	3000 K		35,635 lm
92909800	BVP355 216LED 40K 220V L57 15 DMX	840 neutral white	4000 K		39,755 lm
92910400	BVP355 216LED RGB 220V L57 15 DMX	RGB	-		21,120 lm
92911100	BVP355 216LED RGBWW 220V L57 15 DMX	RGBW	-		22,670 lm
92912800	BVP355 216LED RGBNW 220V L57 15 DMX	RGBW	-		23,675 lm
92913500	BVP355 216LED 27K 220V L57 30	827 warm white	2700 K		37,135 lm
92914200	BVP355 216LED 30K 220V L57 30	830 warm white	3000 K		38,735 lm
92915900	BVP355 216LED 40K 220V L57 30	840 neutral white	4000 K		43,215 lm
92916600	BVP355 216LED 27K 220V L57 30 DMX	827 warm white	2700 K		35,380 lm
92917300	BVP355 216LED 30K 220V L57 30 DMX	830 warm white	3000 K		36,905 lm
92918000	BVP355 216LED 40K 220V L57 30 DMX	840 neutral white	4000 K		41,175 lm
92919700	BVP355 216LED RGB 220V L57 30 DMX	RGB	-		21,875 lm
92920300	BVP355 216LED RGBWW 220V L57 30 DMX	RGBW	-		23,480 lm
92921000	BVP355 216LED RGBNW 220V L57 30 DMX	RGBW	-		24,520 lm
92922700	BVP355 216LED 27K 220V L57 45	827 warm white	2700 K		35,850 lm

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
92923400	BVP355 216LED 30K 220V L57 45	830 warm white	3000 K		37,400 lm
92924100	BVP355 216LED 40K 220V L57 45	840 neutral white	4000 K		41,725 lm
92925800	BVP355 216LED 27K 220V L57 45 DMX	827 warm white	2700 K		34,160 lm
92926500	BVP355 216LED 30K 220V L57 45 DMX	830 warm white	3000 K		35,635 lm
92927200	BVP355 216LED 40K 220V L57 45 DMX	840 neutral white	4000 K		39,755 lm
92928900	BVP355 216LED RGB 220V L57 45 DMX	RGB	-		21,120 lm
92929600	BVP355 216LED RGBWW 220V L57 45 DMX	RGBW	-		22,670 lm
92930200	BVP355 216LED RGBNW 220V L57 45 DMX	RGBW	-		23,675 lm
92931900	BVP355 180LED 27K 220V L50 10	827 warm white	2700 K		27,450 lm
92932600	BVP355 180LED 30K 220V L50 10	830 warm white	3000 K		28,630 lm
92933300	BVP355 180LED 40K 220V L50 10	840 neutral white	4000 K		31,945 lm
92934000	BVP355 180LED 27K 220V L50 10 DMX	827 warm white	2700 K		26,425 lm
92935700	BVP355 180LED 30K 220V L50 10 DMX	830 warm white	3000 K		27,565 lm
92936400	BVP355 180LED 40K 220V L50 10 DMX	840 neutral white	4000 K		30,750 lm
92937100	BVP355 180LED RGB 220V L50 10 DMX	RGB	-		15,655 lm
92938800	BVP355 180LED RGBWW 220V L50 10 DMX	RGBW	-		17,990 lm
92939500	BVP355 180LED RGBNW 220V L50 10 DMX	RGBW	-		18,790 lm
92940100	BVP355 180LED 27K 220V L50 15	827 warm white	2700 K		28,820 lm
92941800	BVP355 180LED 30K 220V L50 15	830 warm white	3000 K		30,065 lm
92942500	BVP355 180LED 40K 220V L50 15	840 neutral white	4000 K		33,540 lm
92943200	BVP355 180LED 27K 220V L50 15 DMX	827 warm white	2700 K		27,745 lm
92944900	BVP355 180LED 30K 220V L50 15 DMX	830 warm white	3000 K		28,940 lm
92945600	BVP355 180LED 40K 220V L50 15 DMX	840 neutral white	4000 K		32,290 lm
92946300	BVP355 180LED RGB 220V L50 15 DMX	RGB	-		16,440 lm
92947000	BVP355 180LED RGBWW 220V L50 15 DMX	RGBW	-		18,890 lm
92948700	BVP355 180LED RGBNW 220V L50 15 DMX	RGBW	-		19,730 lm
92949400	BVP355 180LED 27K 220V L50 30	827 warm white	2700 K		29,850 lm
92950000	BVP355 180LED 30K 220V L50 30	830 warm white	3000 K		31,140 lm
92951700	BVP355 180LED 40K 220V L50 30	840 neutral white	4000 K		34,740 lm
92952400	BVP355 180LED 27K 220V L50 30 DMX	827 warm white	2700 K		28,735 lm
92953100	BVP355 180LED 30K 220V L50 30 DMX	830 warm white	3000 K		29,975 lm
92954800	BVP355 180LED 40K 220V L50 30 DMX	840 neutral white	4000 K		33,445 lm
92955500	BVP355 180LED RGB 220V L50 30 DMX	RGB	-		17,025 lm
92956200	BVP355 180LED RGBWW 220V L50 30 DMX	RGBW	-		19,565 lm
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	RGBW	-		20,435 lm
92958600	BVP355 180LED 27K 220V L50 45	827 warm white	2700 K		28,820 lm
92959300	BVP355 180LED 30K 220V L50 45	830 warm white	3000 K		30,065 lm
92960900	BVP355 180LED 40K 220V L50 45	840 neutral white	4000 K		33,540 lm
92961600	BVP355 180LED 27K 220V L50 45 DMX	827 warm white	2700 K		27,745 lm
92962300	BVP355 180LED 30K 220V L50 45 DMX	830 warm white	3000 K		28,940 lm
92963000	BVP355 180LED 40K 220V L50 45 DMX	840 neutral white	4000 K		32,290 lm
92964700	BVP355 180LED RGB 220V L50 45 DMX	RGB	-		16,440 lm

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
92965400	BVP355 180LED RGBWW 220V L50 45 DMX	RGBW	-		18,890 lm
92966100	BVP355 180LED RGBNW 220V L50 45 DMX	RGBW	-		19,730 lm
92679099	BVP353 48LED 27K 220V L40 10	827 warm white	2700 K		7,440 lm
92680699	BVP353 48LED 30K 220V L40 10	830 warm white	3000 K		7,760 lm
92681399	BVP353 48LED 40K 220V L40 10	840 neutral white	4000 K		8,655 lm
92682099	BVP353 48LED 27K 220V L40 10 DMX	827 warm white	2700 K		6,860 lm
92683799	BVP353 48LED 30K 220V L40 10 DMX	830 warm white	3000 K		7,155 lm
92684499	BVP353 48LED 40K 220V L40 10 DMX	840 neutral white	4000 K		7,985 lm
92685199	BVP353 48LED RGB 220V L40 10 DMX	RGB	-		3,830 lm
92686899	BVP353 48LED RGBWW 220V L40 10 DMX	RGBW	-		5,250 lm
92687599	BVP353 48LED RGBNW 220V L40 10 DMX	RGBW	-		5,485 lm
92688299	BVP353 48LED 27K 220V L40 15	827 warm white	2700 K		7,810 lm
92689999	BVP353 48LED 30K 220V L40 15	830 warm white	3000 K		8,145 lm
92690599	BVP353 48LED 40K 220V L40 15	840 neutral white	4000 K		9,090 lm
92691299	BVP353 48LED 27K 220V L40 15 DMX	827 warm white	2700 K		7,205 lm
92692999	BVP353 48LED 30K 220V L40 15 DMX	830 warm white	3000 K		7,515 lm
92693699	BVP353 48LED 40K 220V L40 15 DMX	840 neutral white	4000 K		8,385 lm
92694399	BVP353 48LED RGB 220V L40 15 DMX	RGB	-		4,020 lm
92695099	BVP353 48LED RGBWW 220V L40 15 DMX	RGBW	-		5,515 lm
92696799	BVP353 48LED RGBNW 220V L40 15 DMX	RGBW	-		5,760 lm
92697499	BVP353 48LED 27K 220V L40 30	827 warm white	2700 K		8,090 lm
92698199	BVP353 48LED 30K 220V L40 30	830 warm white	3000 K		8,440 lm
92699899	BVP353 48LED 40K 220V L40 30	840 neutral white	4000 K		9,415 lm
92700199	BVP353 48LED 27K 220V L40 30 DMX	827 warm white	2700 K		7,460 lm
92701899	BVP353 48LED 30K 220V L40 30 DMX	830 warm white	3000 K		7,785 lm
92702599	BVP353 48LED 40K 220V L40 30 DMX	840 neutral white	4000 K		8,685 lm
92703299	BVP353 48LED RGB 220V L40 30 DMX	RGB	-		4,165 lm
92704999	BVP353 48LED RGBWW 220V L40 30 DMX	RGBW	-		5,710 lm
92705699	BVP353 48LED RGBNW 220V L40 30 DMX	RGBW	-		5,965 lm
92706399	BVP353 48LED 27K 220V L40 45	827 warm white	2700 K		7,810 lm
92707099	BVP353 48LED 30K 220V L40 45	830 warm white	3000 K		8,145 lm
92708799	BVP353 48LED 40K 220V L40 45	840 neutral white	4000 K		9,090 lm
92709499	BVP353 48LED 27K 220V L40 45 DMX	827 warm white	2700 K		7,205 lm
92710099	BVP353 48LED 30K 220V L40 45 DMX	830 warm white	3000 K		7,515 lm
92711799	BVP353 48LED 40K 220V L40 45 DMX	840 neutral white	4000 K		8,385 lm
92712499	BVP353 48LED RGB 220V L40 45 DMX	RGB	-		4,020 lm
92713199	BVP353 48LED RGBWW 220V L40 45 DMX	RGBW	-		5,515 lm
92714899	BVP353 48LED RGBNW 220V L40 45 DMX	RGBW	-		5,760 lm

Operating and Electrical

UniFlood M G2

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
92607399	BVP353 30LED 27K 220V L30 10	60 W	92803900	BVP354 96LED RGBWW 220V L40 15 DMX	200 W
92608099	BVP353 30LED 30K 220V L30 10	60 W	92804600	BVP354 96LED RGBNW 220V L40 15 DMX	200 W
92609799	BVP353 30LED 40K 220V L30 10	60 W	92805300	BVP354 96LED 27K 220V L40 30	200 W
92610399	BVP353 30LED 27K 220V L30 10 DMX	60 W	92806000	BVP354 96LED 30K 220V L40 30	200 W
92611099	BVP353 30LED 30K 220V L30 10 DMX	60 W	92807700	BVP354 96LED 40K 220V L40 30	200 W
92612799	BVP353 30LED 40K 220V L30 10 DMX	60 W	92808400	BVP354 96LED 27K 220V L40 30 DMX	200 W
92613499	BVP353 30LED RGB 220V L30 10 DMX	60 W	92809100	BVP354 96LED 30K 220V L40 30 DMX	200 W
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	60 W	92810700	BVP354 96LED 40K 220V L40 30 DMX	200 W
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	60 W	92811400	BVP354 96LED RGB 220V L40 30 DMX	200 W
92616599	BVP353 30LED 27K 220V L30 15	60 W	92812100	BVP354 96LED RGBWW 220V L40 30 DMX	200 W
92617299	BVP353 30LED 30K 220V L30 15	60 W	92813800	BVP354 96LED RGBNW 220V L40 30 DMX	200 W
92618999	BVP353 30LED 40K 220V L30 15	60 W	92814500	BVP354 96LED 27K 220V L40 45	200 W
92619699	BVP353 30LED 27K 220V L30 15 DMX	60 W	92815200	BVP354 96LED 30K 220V L40 45	200 W
92620299	BVP353 30LED 30K 220V L30 15 DMX	60 W	92816900	BVP354 96LED 40K 220V L40 45	200 W
92621999	BVP353 30LED 40K 220V L30 15 DMX	60 W	92817600	BVP354 96LED 27K 220V L40 45 DMX	200 W
92622699	BVP353 30LED RGB 220V L30 15 DMX	60 W	92818300	BVP354 96LED 30K 220V L40 45 DMX	200 W
92623399	BVP353 32LED RGBWW 220V L30 15 DMX	60 W	92819000	BVP354 96LED 40K 220V L40 45 DMX	200 W
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	60 W	92820600	BVP354 96LED RGB 220V L40 45 DMX	200 W
92625799	BVP353 30LED 27K 220V L30 30	60 W	92821300	BVP354 96LED RGBWW 220V L40 45 DMX	200 W
92626499	BVP353 30LED 30K 220V L30 30	60 W	92822000	BVP354 96LED RGBNW 220V L40 45 DMX	200 W
92627199	BVP353 30LED 40K 220V L30 30	60 W	92823700	BVP354 120LED 27K 220V L50 10	240 W
92628899	BVP353 30LED 27K 220V L30 30 DMX	60 W	92824400	BVP354 120LED 30K 220V L50 10	240 W
92629599	BVP353 30LED 30K 220V L30 30 DMX	60 W	92825100	BVP354 120LED 40K 220V L50 10	240 W
92630199	BVP353 30LED 40K 220V L30 30 DMX	60 W	92826800	BVP354 120LED 27K 220V L50 10 DMX	240 W
92631899	BVP353 30LED RGB 220V L30 30 DMX	60 W	92827500	BVP354 120LED 30K 220V L50 10 DMX	240 W
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	60 W	92828200	BVP354 120LED 40K 220V L50 10 DMX	240 W
92633299	BVP353 32LED RGBNW 220V L30 30 DMX	60 W	92829900	BVP354 120LED RGB 220V L50 10 DMX	240 W
92634999	BVP353 30LED 27K 220V L30 45	60 W	92830500	BVP354 120LED RGBWW 220V L50 10 DMX	240 W
92635699	BVP353 30LED 30K 220V L30 45	60 W	92831200	BVP354 120LED RGBNW 220V L50 10 DMX	240 W
92636399	BVP353 30LED 40K 220V L30 45	60 W	92832900	BVP354 120LED 27K 220V L50 15	240 W
92637099	BVP353 30LED 27K 220V L30 45 DMX	60 W	92833600	BVP354 120LED 30K 220V L50 15	240 W
92638799	BVP353 30LED 30K 220V L30 45 DMX	60 W	92834300	BVP354 120LED 40K 220V L50 15	240 W
92639499	BVP353 30LED 40K 220V L30 45 DMX	60 W	92835000	BVP354 120LED 27K 220V L50 15 DMX	240 W
92640099	BVP353 30LED RGB 220V L30 45 DMX	60 W	92836700	BVP354 120LED 30K 220V L50 15 DMX	240 W
92641799	BVP353 32LED RGBWW 220V L30 45 DMX	60 W	92837400	BVP354 120LED 40K 220V L50 15 DMX	240 W
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	60 W	92838100	BVP354 120LED RGB 220V L50 15 DMX	240 W
92787200	BVP354 96LED 27K 220V L40 10	200 W	92839800	BVP354 120LED RGBWW 220V L50 15 DMX	240 W
92788900	BVP354 96LED 30K 220V L40 10	200 W	92840400	BVP354 120LED RGBNW 220V L50 15 DMX	240 W
92789600	BVP354 96LED 40K 220V L40 10	200 W	92841100	BVP354 120LED 27K 220V L50 30	240 W
92790200	BVP354 96LED 27K 220V L40 10 DMX	200 W	92842800	BVP354 120LED 30K 220V L50 30	240 W
92791900	BVP354 96LED 30K 220V L40 10 DMX	200 W	92843500	BVP354 120LED 40K 220V L50 30	240 W
92792600	BVP354 96LED 40K 220V L40 10 DMX	200 W	92844200	BVP354 120LED 27K 220V L50 30 DMX	240 W
92793300	BVP354 96LED RGB 220V L40 10 DMX	200 W	92845900	BVP354 120LED 30K 220V L50 30 DMX	240 W
92794000	BVP354 96LED RGBWW 220V L40 10 DMX	200 W	92846600	BVP354 120LED 40K 220V L50 30 DMX	240 W
92795700	BVP354 96LED RGBNW 220V L40 10 DMX	200 W	92847300	BVP354 120LED RGB 220V L50 30 DMX	240 W
92796400	BVP354 96LED 27K 220V L40 15	200 W	92848000	BVP354 120LED RGBWW 220V L50 30 DMX	240 W
92797100	BVP354 96LED 30K 220V L40 15	200 W	92849700	BVP354 120LED RGBNW 220V L50 30 DMX	240 W
92798800	BVP354 96LED 40K 220V L40 15	200 W	92850300	BVP354 120LED 27K 220V L50 45	240 W
92799500	BVP354 96LED 27K 220V L40 15 DMX	200 W	92851000	BVP354 120LED 30K 220V L50 45	240 W
92800800	BVP354 96LED 30K 220V L40 15 DMX	200 W	92852700	BVP354 120LED 40K 220V L50 45	240 W
92801500	BVP354 96LED 40K 220V L40 15 DMX	200 W	92853400	BVP354 120LED 27K 220V L50 45 DMX	240 W
92802200	BVP354 96LED RGB 220V L40 15 DMX	200 W	92854100	BVP354 120LED 30K 220V L50 45 DMX	240 W

UniFlood M G2

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
92855800	BVP354 120LED 40K 220V L50 45 DMX	240 W	92763699	BVP353 72LED 27K 220V L57 15 DMX	150 W
92856500	BVP354 120LED RGB 220V L50 45 DMX	240 W	92764399	BVP353 72LED 30K 220V L57 15 DMX	150 W
92857200	BVP354 120LED RGBWW 220V L50 45 DMX	240 W	92765099	BVP353 72LED 40K 220V L57 15 DMX	150 W
92858900	BVP354 120LED RGBNW 220V L50 45 DMX	240 W	92766799	BVP353 72LED RGB 220V L57 15 DMX	150 W
92859600	BVP354 144LED 27K 220V L57 10	300 W	92767499	BVP353 72LED RGBWW 220V L57 15 DMX	150 W
92860200	BVP354 144LED 30K 220V L57 10	300 W	92768199	BVP353 72LED RGBNW 220V L57 15 DMX	150 W
92861900	BVP354 144LED 40K 220V L57 10	300 W	92769899	BVP353 72LED 27K 220V L57 30	150 W
92862600	BVP354 144LED 27K 220V L57 10 DMX	300 W	92770499	BVP353 72LED 30K 220V L57 30	150 W
92863300	BVP354 144LED 30K 220V L57 10 DMX	300 W	92771199	BVP353 72LED 40K 220V L57 30	150 W
92864000	BVP354 144LED 40K 220V L57 10 DMX	300 W	92772899	BVP353 72LED 27K 220V L57 30 DMX	150 W
92865700	BVP354 144LED RGB 220V L57 10 DMX	300 W	92773599	BVP353 72LED 30K 220V L57 30 DMX	150 W
92866400	BVP354 144LED RGBWW 220V L57 10 DMX	300 W	92774299	BVP353 72LED 40K 220V L57 30 DMX	150 W
92867100	BVP354 144LED RGBNW 220V L57 10 DMX	300 W	92775999	BVP353 72LED RGB 220V L57 30 DMX	150 W
92868800	BVP354 144LED 27K 220V L57 15	300 W	92776699	BVP353 72LED RGBWW 220V L57 30 DMX	150 W
92869500	BVP354 144LED 30K 220V L57 15	300 W	92777399	BVP353 72LED RGBNW 220V L57 30 DMX	150 W
92870100	BVP354 144LED 40K 220V L57 15	300 W	92778099	BVP353 72LED 27K 220V L57 45	150 W
92871800	BVP354 144LED 27K 220V L57 15 DMX	300 W	92779799	BVP353 72LED 30K 220V L57 45	150 W
92872500	BVP354 144LED 30K 220V L57 15 DMX	300 W	92780399	BVP353 72LED 40K 220V L57 45	150 W
92873200	BVP354 144LED 40K 220V L57 15 DMX	300 W	92781099	BVP353 72LED 27K 220V L57 45 DMX	150 W
92874900	BVP354 144LED RGB 220V L57 15 DMX	300 W	92782799	BVP353 72LED 30K 220V L57 45 DMX	150 W
92875600	BVP354 144LED RGBWW 220V L57 15 DMX	300 W	92783499	BVP353 72LED 40K 220V L57 45 DMX	150 W
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	300 W	92784199	BVP353 72LED RGB 220V L57 45 DMX	150 W
92877000	BVP354 144LED 27K 220V L57 30	300 W	92785899	BVP353 72LED RGBWW 220V L57 45 DMX	150 W
92878700	BVP354 144LED 30K 220V L57 30	300 W	92786599	BVP353 72LED RGBNW 220V L57 45 DMX	150 W
92879400	BVP354 144LED 40K 220V L57 30	300 W	92535999	BVP353 18LED 27K 220V L21 10	40 W
92880000	BVP354 144LED 27K 220V L57 30 DMX	300 W	92536699	BVP353 18LED 30K 220V L21 10	40 W
92881700	BVP354 144LED 30K 220V L57 30 DMX	300 W	92537399	BVP353 18LED 40K 220V L21 10	40 W
92882400	BVP354 144LED 40K 220V L57 30 DMX	300 W	92538099	BVP353 18LED 27K 220V L21 10 DMX	40 W
92883100	BVP354 144LED RGB 220V L57 30 DMX	300 W	92539799	BVP353 18LED 30K 220V L21 10 DMX	40 W
92884800	BVP354 144LED RGBWW 220V L57 30 DMX	300 W	92540399	BVP353 18LED 40K 220V L21 10 DMX	40 W
92885500	BVP354 144LED RGBNW 220V L57 30 DMX	300 W	92541099	BVP353 18LED RGB 220V L21 10 DMX	40 W
92886200	BVP354 144LED 27K 220V L57 45	300 W	92542799	BVP353 20LED RGBWW 220V L21 10 DMX	40 W
92887900	BVP354 144LED 30K 220V L57 45	300 W	92543499	BVP353 20LED RGBNW 220V L21 10 DMX	40 W
92888600	BVP354 144LED 40K 220V L57 45	300 W	92544199	BVP353 18LED 27K 220V L21 15	40 W
92889300	BVP354 144LED 27K 220V L57 45 DMX	300 W	92545899	BVP353 18LED 30K 220V L21 15	40 W
92890900	BVP354 144LED 30K 220V L57 45 DMX	300 W	92546599	BVP353 18LED 40K 220V L21 15	40 W
92891600	BVP354 144LED 40K 220V L57 45 DMX	300 W	92547299	BVP353 18LED 27K 220V L21 15 DMX	40 W
92892300	BVP354 144LED RGB 220V L57 45 DMX	300 W	92548999	BVP353 18LED 30K 220V L21 15 DMX	40 W
92893000	BVP354 144LED RGBWW 220V L57 45 DMX	300 W	92549699	BVP353 18LED 40K 220V L21 15 DMX	40 W
92894700	BVP354 144LED RGBNW 220V L57 45 DMX	300 W	92550299	BVP353 18LED RGB 220V L21 15 DMX	40 W
92751399	BVP353 72LED 27K 220V L57 10	150 W	92551999	BVP353 20LED RGBWW 220V L21 15 DMX	40 W
92752099	BVP353 72LED 30K 220V L57 10	150 W	92552699	BVP353 20LED RGBNW 220V L21 15 DMX	40 W
92753799	BVP353 72LED 40K 220V L57 10	150 W	92553399	BVP353 18LED 27K 220V L21 30	40 W
92754499	BVP353 72LED 27K 220V L57 10 DMX	150 W	92554099	BVP353 18LED 30K 220V L21 30	40 W
92755199	BVP353 72LED 30K 220V L57 10 DMX	150 W	92555799	BVP353 18LED 40K 220V L21 30	40 W
92756899	BVP353 72LED 40K 220V L57 10 DMX	150 W	92556499	BVP353 18LED 27K 220V L21 30 DMX	40 W
92757599	BVP353 72LED RGB 220V L57 10 DMX	150 W	92557199	BVP353 18LED 30K 220V L21 30 DMX	40 W
92758299	BVP353 72LED RGBWW 220V L57 10 DMX	150 W	92558899	BVP353 18LED 40K 220V L21 30 DMX	40 W
92759999	BVP353 72LED RGBNW 220V L57 10 DMX	150 W	92559599	BVP353 18LED RGB 220V L21 30 DMX	40 W
92760599	BVP353 72LED 27K 220V L57 15	150 W	92560199	BVP353 20LED RGBWW 220V L21 30 DMX	40 W
92761299	BVP353 72LED 30K 220V L57 15	150 W	92561899	BVP353 20LED RGBNW 220V L21 30 DMX	40 W
92762999	BVP353 72LED 40K 220V L57 15	150 W	92562599	BVP353 18LED 27K 220V L21 45	40 W

UniFlood M G2

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
92563299	BVP353 18LED 30K 220V L21 45	40 W	92660899	BVP353 36LED RGBNW 220V L35 15 DMX	80 W
92564999	BVP353 18LED 40K 220V L21 45	40 W	92661599	BVP353 36LED 27K 220V L35 30	80 W
92565699	BVP353 18LED 27K 220V L21 45 DMX	40 W	92662299	BVP353 36LED 30K 220V L35 30	80 W
92566399	BVP353 18LED 30K 220V L21 45 DMX	40 W	92663999	BVP353 36LED 40K 220V L35 30	80 W
92567099	BVP353 18LED 40K 220V L21 45 DMX	40 W	92664699	BVP353 36LED 27K 220V L35 30 DMX	80 W
92568799	BVP353 18LED RGB 220V L21 45 DMX	40 W	92665399	BVP353 36LED 30K 220V L35 30 DMX	80 W
92569499	BVP353 20LED RGBWW 220V L21 45 DMX	40 W	92666099	BVP353 36LED 40K 220V L35 30 DMX	80 W
92570099	BVP353 20LED RGBNW 220V L21 45 DMX	40 W	92667799	BVP353 36LED RGB 220V L35 30 DMX	80 W
92463599	BVP353 12LED 27K 220V L15 10	24 W	92668499	BVP353 36LED RGBWW 220V L35 30 DMX	80 W
92464299	BVP353 12LED 30K 220V L15 10	24 W	92669199	BVP353 36LED RGBNW 220V L35 30 DMX	80 W
92465999	BVP353 12LED 40K 220V L15 10	24 W	92670799	BVP353 36LED 27K 220V L35 45	80 W
92466699	BVP353 12LED 27K 220V L15 10 DMX	24 W	92671499	BVP353 36LED 30K 220V L35 45	80 W
92467399	BVP353 12LED 30K 220V L15 10 DMX	24 W	92672199	BVP353 36LED 40K 220V L35 45	80 W
92468099	BVP353 12LED 40K 220V L15 10 DMX	24 W	92673899	BVP353 36LED 27K 220V L35 45 DMX	80 W
92469799	BVP353 12LED RGB 220V L15 10 DMX	24 W	92674599	BVP353 36LED 30K 220V L35 45 DMX	80 W
92470399	BVP353 12LED RGBWW 220V L15 10 DMX	24 W	92675299	BVP353 36LED 40K 220V L35 45 DMX	80 W
92471099	BVP353 12LED RGBNW 220V L15 10 DMX	24 W	92676999	BVP353 36LED RGB 220V L35 45 DMX	80 W
92481999	BVP353 12LED 27K 220V L15 30	24 W	92677699	BVP353 36LED RGBWW 220V L35 45 DMX	80 W
92482699	BVP353 12LED 30K 220V L15 30	24 W	92678399	BVP353 36LED RGBNW 220V L35 45 DMX	80 W
92483399	BVP353 12LED 40K 220V L15 30	24 W	92571799	BVP353 24LED 27K 220V L24 10	50 W
92484099	BVP353 12LED 27K 220V L15 30 DMX	24 W	92572499	BVP353 24LED 30K 220V L24 10	50 W
92485799	BVP353 12LED 30K 220V L15 30 DMX	24 W	92573199	BVP353 24LED 40K 220V L24 10	50 W
92486499	BVP353 12LED 40K 220V L15 30 DMX	24 W	92574899	BVP353 24LED 27K 220V L24 10 DMX	50 W
92487199	BVP353 12LED RGB 220V L15 30 DMX	24 W	92575599	BVP353 24LED 30K 220V L24 10 DMX	50 W
92488899	BVP353 12LED RGBWW 220V L15 30 DMX	24 W	92576299	BVP353 24LED 40K 220V L24 10 DMX	50 W
92489599	BVP353 12LED RGBNW 220V L15 30 DMX	24 W	92577999	BVP353 24LED RGB 220V L24 10 DMX	50 W
92490199	BVP353 12LED 27K 220V L15 45	24 W	92578699	BVP353 24LED RGBWW 220V L24 10 DMX	50 W
92491899	BVP353 12LED 30K 220V L15 45	24 W	92579399	BVP353 24LED RGBNW 220V L24 10 DMX	50 W
92492599	BVP353 12LED 40K 220V L15 45	24 W	92580999	BVP353 24LED 27K 220V L24 15	50 W
92493299	BVP353 12LED 27K 220V L15 45 DMX	24 W	92581699	BVP353 24LED 30K 220V L24 15	50 W
92494999	BVP353 12LED 30K 220V L15 45 DMX	24 W	92582399	BVP353 24LED 40K 220V L24 15	50 W
92495699	BVP353 12LED 40K 220V L15 45 DMX	24 W	92583099	BVP353 24LED 27K 220V L24 15 DMX	50 W
92496399	BVP353 12LED RGB 220V L15 45 DMX	24 W	92584799	BVP353 24LED 30K 220V L24 15 DMX	50 W
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	24 W	92585499	BVP353 24LED 40K 220V L24 15 DMX	50 W
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	24 W	92586199	BVP353 24LED RGB 220V L24 15 DMX	50 W
92643199	BVP353 36LED 27K 220V L35 10	80 W	92587899	BVP353 24LED RGBWW 220V L24 15 DMX	50 W
92644899	BVP353 36LED 30K 220V L35 10	80 W	92588599	BVP353 24LED RGBNW 220V L24 15 DMX	50 W
92645599	BVP353 36LED 40K 220V L35 10	80 W	92589299	BVP353 24LED 27K 220V L24 30	50 W
92646299	BVP353 36LED 27K 220V L35 10 DMX	80 W	92590899	BVP353 24LED 30K 220V L24 30	50 W
92647999	BVP353 36LED 30K 220V L35 10 DMX	80 W	92591599	BVP353 24LED 40K 220V L24 30	50 W
92648699	BVP353 36LED 40K 220V L35 10 DMX	80 W	92592299	BVP353 24LED 27K 220V L24 30 DMX	50 W
92649399	BVP353 36LED RGB 220V L35 10 DMX	80 W	92593999	BVP353 24LED 30K 220V L24 30 DMX	50 W
92650999	BVP353 36LED RGBWW 220V L35 10 DMX	80 W	92594699	BVP353 24LED 40K 220V L24 30 DMX	50 W
92651699	BVP353 36LED RGBNW 220V L35 10 DMX	80 W	92595399	BVP353 24LED RGB 220V L24 30 DMX	50 W
92652399	BVP353 36LED 27K 220V L35 15	80 W	92596099	BVP353 24LED RGBWW 220V L24 30 DMX	50 W
92653099	BVP353 36LED 30K 220V L35 15	80 W	92597799	BVP353 24LED RGBNW 220V L24 30 DMX	50 W
92654799	BVP353 36LED 40K 220V L35 15	80 W	92598499	BVP353 24LED 27K 220V L24 45	50 W
92655499	BVP353 36LED 27K 220V L35 15 DMX	80 W	92599199	BVP353 24LED 30K 220V L24 45	50 W
92656199	BVP353 36LED 30K 220V L35 15 DMX	80 W	92600499	BVP353 24LED 40K 220V L24 45	50 W
92657899	BVP353 36LED 40K 220V L35 15 DMX	80 W	92601199	BVP353 24LED 27K 220V L24 45 DMX	50 W
92658599	BVP353 36LED RGB 220V L35 15 DMX	80 W	92602899	BVP353 24LED 30K 220V L24 45 DMX	50 W
92659299	BVP353 36LED RGBWW 220V L35 15 DMX	80 W	92603599	BVP353 24LED 40K 220V L24 45 DMX	50 W

UniFlood M G2

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
92604299	BVP353 24LED RGB 220V L24 45 DMX	50 W	92512099	BVP353 16LED 30K 220V L18 15 DMX	30 W
92605999	BVP353 24LED RGBWW 220V L24 45 DMX	50 W	92513799	BVP353 16LED 40K 220V L18 15 DMX	30 W
92606699	BVP353 24LED RGBNW 220V L24 45 DMX	50 W	92514499	BVP353 15LED RGB 220V L18 15 DMX	30 W
92715599	BVP353 60LED 27K 220V L50 10	120 W	92515199	BVP353 16LED RGBWW 220V L18 15 DMX	30 W
92716299	BVP353 60LED 30K 220V L50 10	120 W	92516899	BVP353 16LED RGBNW 220V L18 15 DMX	30 W
92717999	BVP353 60LED 40K 220V L50 10	120 W	92517599	BVP353 16LED 27K 220V L18 30	30 W
92718699	BVP353 60LED 27K 220V L50 10 DMX	120 W	92518299	BVP353 16LED 30K 220V L18 30	30 W
92719399	BVP353 60LED 30K 220V L50 10 DMX	120 W	92519999	BVP353 16LED 40K 220V L18 30	30 W
92720999	BVP353 60LED 40K 220V L50 10 DMX	120 W	92520599	BVP353 16LED 27K 220V L18 30 DMX	30 W
92721699	BVP353 60LED RGB 220V L50 10 DMX	120 W	92521299	BVP353 16LED 30K 220V L18 30 DMX	30 W
92722399	BVP353 60LED RGBWW 220V L50 10 DMX	120 W	92522999	BVP353 16LED 40K 220V L18 30 DMX	30 W
92723099	BVP353 60LED RGBNW 220V L50 10 DMX	120 W	92523699	BVP353 15LED RGB 220V L18 30 DMX	30 W
92724799	BVP353 60LED 27K 220V L50 15	120 W	92524399	BVP353 16LED RGBWW 220V L18 30 DMX	30 W
92725499	BVP353 60LED 30K 220V L50 15	120 W	92525099	BVP353 16LED RGBNW 220V L18 30 DMX	30 W
92726199	BVP353 60LED 40K 220V L50 15	120 W	92526799	BVP353 16LED 27K 220V L18 45	30 W
92727899	BVP353 60LED 27K 220V L50 15 DMX	120 W	92527499	BVP353 16LED 30K 220V L18 45	30 W
92728599	BVP353 60LED 30K 220V L50 15 DMX	120 W	92528199	BVP353 16LED 40K 220V L18 45	30 W
92729299	BVP353 60LED 40K 220V L50 15 DMX	120 W	92529899	BVP353 16LED 27K 220V L18 45 DMX	30 W
92730899	BVP353 60LED RGB 220V L50 15 DMX	120 W	92530499	BVP353 16LED 30K 220V L18 45 DMX	30 W
92731599	BVP353 60LED RGBWW 220V L50 15 DMX	120 W	92531199	BVP353 16LED 40K 220V L18 45 DMX	30 W
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	120 W	92532899	BVP353 15LED RGB 220V L18 45 DMX	30 W
92733999	BVP353 60LED 27K 220V L50 30	120 W	92533599	BVP353 16LED RGBWW 220V L18 45 DMX	30 W
92734699	BVP353 60LED 30K 220V L50 30	120 W	92534299	BVP353 16LED RGBNW 220V L18 45 DMX	30 W
92735399	BVP353 60LED 40K 220V L50 30	120 W	92895400	BVP355 216LED 27K 220V L57 10	450 W
92736099	BVP353 60LED 27K 220V L50 30 DMX	120 W	92896100	BVP355 216LED 30K 220V L57 10	450 W
92737799	BVP353 60LED 30K 220V L50 30 DMX	120 W	92897800	BVP355 216LED 40K 220V L57 10	450 W
92738499	BVP353 60LED 40K 220V L50 30 DMX	120 W	92898500	BVP355 216LED 27K 220V L57 10 DMX	450 W
92739199	BVP353 60LED RGB 220V L50 30 DMX	120 W	92899200	BVP355 216LED 30K 220V L57 10 DMX	450 W
92740799	BVP353 60LED RGBWW 220V L50 30 DMX	120 W	92900500	BVP355 216LED 40K 220V L57 10 DMX	450 W
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	120 W	92901200	BVP355 216LED RGB 220V L57 10 DMX	450 W
92742199	BVP353 60LED 27K 220V L50 45	120 W	92902900	BVP355 216LED RGBWW 220V L57 10 DMX	450 W
92743899	BVP353 60LED 30K 220V L50 45	120 W	92903600	BVP355 216LED RGBNW 220V L57 10 DMX	450 W
92744599	BVP353 60LED 40K 220V L50 45	120 W	92904300	BVP355 216LED 27K 220V L57 15	450 W
92745299	BVP353 60LED 27K 220V L50 45 DMX	120 W	92905000	BVP355 216LED 30K 220V L57 15	450 W
92746999	BVP353 60LED 30K 220V L50 45 DMX	120 W	92906700	BVP355 216LED 40K 220V L57 15	450 W
92747699	BVP353 60LED 40K 220V L50 45 DMX	120 W	92907400	BVP355 216LED 27K 220V L57 15 DMX	450 W
92748399	BVP353 60LED RGB 220V L50 45 DMX	120 W	92908100	BVP355 216LED 30K 220V L57 15 DMX	450 W
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	120 W	92909800	BVP355 216LED 40K 220V L57 15 DMX	450 W
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	120 W	92910400	BVP355 216LED RGB 220V L57 15 DMX	450 W
92499499	BVP353 16LED 27K 220V L18 10	30 W	92911100	BVP355 216LED RGBWW 220V L57 15 DMX	450 W
92500799	BVP353 16LED 30K 220V L18 10	30 W	92912800	BVP355 216LED RGBNW 220V L57 15 DMX	450 W
92501499	BVP353 16LED 40K 220V L18 10	30 W	92913500	BVP355 216LED 27K 220V L57 30	450 W
92502199	BVP353 16LED 27K 220V L18 10 DMX	30 W	92914200	BVP355 216LED 30K 220V L57 30	450 W
92503899	BVP353 16LED 30K 220V L18 10 DMX	30 W	92915900	BVP355 216LED 40K 220V L57 30	450 W
92504599	BVP353 16LED 40K 220V L18 10 DMX	30 W	92916600	BVP355 216LED 27K 220V L57 30 DMX	450 W
92505299	BVP353 15LED RGB 220V L18 10 DMX	30 W	92917300	BVP355 216LED 30K 220V L57 30 DMX	450 W
92506999	BVP353 16LED RGBWW 220V L18 10 DMX	30 W	92918000	BVP355 216LED 40K 220V L57 30 DMX	450 W
92507699	BVP353 16LED RGBNW 220V L18 10 DMX	30 W	92919700	BVP355 216LED RGB 220V L57 30 DMX	450 W
92508399	BVP353 16LED 27K 220V L18 15	30 W	92920300	BVP355 216LED RGBWW 220V L57 30 DMX	450 W
92509099	BVP353 16LED 30K 220V L18 15	30 W	92921000	BVP355 216LED RGBNW 220V L57 30 DMX	450 W
92510699	BVP353 16LED 40K 220V L18 15	30 W	92922700	BVP355 216LED 27K 220V L57 45	450 W
92511399	BVP353 16LED 27K 220V L18 15 DMX	30 W	92923400	BVP355 216LED 30K 220V L57 45	450 W

UniFlood M G2

Order Code	Full Product Name	Power Consumption
92924100	BVP355 216LED 40K 220V L57 45	450 W
92925800	BVP355 216LED 27K 220V L57 45 DMX	450 W
92926500	BVP355 216LED 30K 220V L57 45 DMX	450 W
92927200	BVP355 216LED 40K 220V L57 45 DMX	450 W
92928900	BVP355 216LED RGB 220V L57 45 DMX	450 W
92929600	BVP355 216LED RGBWW 220V L57 45 DMX	450 W
92930200	BVP355 216LED RGBNW 220V L57 45 DMX	450 W
92931900	BVP355 180LED 27K 220V L50 10	360 W
92932600	BVP355 180LED 30K 220V L50 10	360 W
92933300	BVP355 180LED 40K 220V L50 10	360 W
92934000	BVP355 180LED 27K 220V L50 10 DMX	360 W
92935700	BVP355 180LED 30K 220V L50 10 DMX	360 W
92936400	BVP355 180LED 40K 220V L50 10 DMX	360 W
92937100	BVP355 180LED RGB 220V L50 10 DMX	360 W
92938800	BVP355 180LED RGBWW 220V L50 10 DMX	360 W
92939500	BVP355 180LED RGBNW 220V L50 10 DMX	360 W
92940100	BVP355 180LED 27K 220V L50 15	360 W
92941800	BVP355 180LED 30K 220V L50 15	360 W
92942500	BVP355 180LED 40K 220V L50 15	360 W
92943200	BVP355 180LED 27K 220V L50 15 DMX	360 W
92944900	BVP355 180LED 30K 220V L50 15 DMX	360 W
92945600	BVP355 180LED 40K 220V L50 15 DMX	360 W
92946300	BVP355 180LED RGB 220V L50 15 DMX	360 W
92947000	BVP355 180LED RGBWW 220V L50 15 DMX	360 W
92948700	BVP355 180LED RGBNW 220V L50 15 DMX	360 W
92949400	BVP355 180LED 27K 220V L50 30	360 W
92950000	BVP355 180LED 30K 220V L50 30	360 W
92951700	BVP355 180LED 40K 220V L50 30	360 W
92952400	BVP355 180LED 27K 220V L50 30 DMX	360 W
92953100	BVP355 180LED 30K 220V L50 30 DMX	360 W
92954800	BVP355 180LED 40K 220V L50 30 DMX	360 W
92955500	BVP355 180LED RGB 220V L50 30 DMX	360 W
92956200	BVP355 180LED RGBWW 220V L50 30 DMX	360 W
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	360 W
92958600	BVP355 180LED 27K 220V L50 45	360 W
92959300	BVP355 180LED 30K 220V L50 45	360 W
92960900	BVP355 180LED 40K 220V L50 45	360 W
92961600	BVP355 180LED 27K 220V L50 45 DMX	360 W
92962300	BVP355 180LED 30K 220V L50 45 DMX	360 W
92963000	BVP355 180LED 40K 220V L50 45 DMX	360 W

Order Code	Full Product Name	Power Consumption
92964700	BVP355 180LED RGB 220V L50 45 DMX	360 W
92965400	BVP355 180LED RGBWW 220V L50 45 DMX	360 W
92966100	BVP355 180LED RGBNW 220V L50 45 DMX	360 W
92679099	BVP353 48LED 27K 220V L40 10	100 W
92680699	BVP353 48LED 30K 220V L40 10	100 W
92681399	BVP353 48LED 40K 220V L40 10	100 W
92682099	BVP353 48LED 27K 220V L40 10 DMX	100 W
92683799	BVP353 48LED 30K 220V L40 10 DMX	100 W
92684499	BVP353 48LED 40K 220V L40 10 DMX	100 W
92685199	BVP353 48LED RGB 220V L40 10 DMX	100 W
92686899	BVP353 48LED RGBWW 220V L40 10 DMX	100 W
92687599	BVP353 48LED RGBNW 220V L40 10 DMX	100 W
92688299	BVP353 48LED 27K 220V L40 15	100 W
92689999	BVP353 48LED 30K 220V L40 15	100 W
92690599	BVP353 48LED 40K 220V L40 15	100 W
92691299	BVP353 48LED 27K 220V L40 15 DMX	100 W
92692999	BVP353 48LED 30K 220V L40 15 DMX	100 W
92693699	BVP353 48LED 40K 220V L40 15 DMX	100 W
92694399	BVP353 48LED RGB 220V L40 15 DMX	100 W
92695099	BVP353 48LED RGBWW 220V L40 15 DMX	100 W
92696799	BVP353 48LED RGBNW 220V L40 15 DMX	100 W
92697499	BVP353 48LED 27K 220V L40 30	100 W
92698199	BVP353 48LED 30K 220V L40 30	100 W
92699899	BVP353 48LED 40K 220V L40 30	100 W
92700199	BVP353 48LED 27K 220V L40 30 DMX	100 W
92701899	BVP353 48LED 30K 220V L40 30 DMX	100 W
92702599	BVP353 48LED 40K 220V L40 30 DMX	100 W
92703299	BVP353 48LED RGB 220V L40 30 DMX	100 W
92704999	BVP353 48LED RGBWW 220V L40 30 DMX	100 W
92705699	BVP353 48LED RGBNW 220V L40 30 DMX	100 W
92706399	BVP353 48LED 27K 220V L40 45	100 W
92707099	BVP353 48LED 30K 220V L40 45	100 W
92708799	BVP353 48LED 40K 220V L40 45	100 W
92709499	BVP353 48LED 27K 220V L40 45 DMX	100 W
92710099	BVP353 48LED 30K 220V L40 45 DMX	100 W
92711799	BVP353 48LED 40K 220V L40 45 DMX	100 W
92712499	BVP353 48LED RGB 220V L40 45 DMX	100 W
92713199	BVP353 48LED RGBWW 220V L40 45 DMX	100 W
92714899	BVP353 48LED RGBNW 220V L40 45 DMX	100 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
92607399	BVP353 30LED 27K 220V L30 10	No
92608099	BVP353 30LED 30K 220V L30 10	No
92609799	BVP353 30LED 40K 220V L30 10	No
92610399	BVP353 30LED 27K 220V L30 10 DMX	Yes
92611099	BVP353 30LED 30K 220V L30 10 DMX	Yes
92612799	BVP353 30LED 40K 220V L30 10 DMX	Yes
92613499	BVP353 30LED RGB 220V L30 10 DMX	Yes
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	Yes

Order Code	Full Product Name	Dimmable
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	Yes
92616599	BVP353 30LED 27K 220V L30 15	No
92617299	BVP353 30LED 30K 220V L30 15	No
92618999	BVP353 30LED 40K 220V L30 15	No
92619699	BVP353 30LED 27K 220V L30 15 DMX	Yes
92620299	BVP353 30LED 30K 220V L30 15 DMX	Yes
92621999	BVP353 30LED 40K 220V L30 15 DMX	Yes
92622699	BVP353 30LED RGB 220V L30 15 DMX	Yes

UniFlood M G2

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
92623399	BVP353 32LED RGBWW 220V L30 15 DMX	Yes	92819000	BVP354 96LED 40K 220V L40 45 DMX	Yes
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	Yes	92820600	BVP354 96LED RGB 220V L40 45 DMX	Yes
92625799	BVP353 30LED 27K 220V L30 30	No	92821300	BVP354 96LED RGBWW 220V L40 45 DMX	Yes
92626499	BVP353 30LED 30K 220V L30 30	No	92822000	BVP354 96LED RGBNW 220V L40 45 DMX	Yes
92627199	BVP353 30LED 40K 220V L30 30	No	92823700	BVP354 120LED 27K 220V L50 10	No
92628899	BVP353 30LED 27K 220V L30 30 DMX	Yes	92824400	BVP354 120LED 30K 220V L50 10	No
92629599	BVP353 30LED 30K 220V L30 30 DMX	Yes	92825100	BVP354 120LED 40K 220V L50 10	No
92630199	BVP353 30LED 40K 220V L30 30 DMX	Yes	92826800	BVP354 120LED 27K 220V L50 10 DMX	Yes
92631899	BVP353 30LED RGB 220V L30 30 DMX	Yes	92827500	BVP354 120LED 30K 220V L50 10 DMX	Yes
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	Yes	92828200	BVP354 120LED 40K 220V L50 10 DMX	Yes
92633299	BVP353 32LED RGBNW 220V L30 30 DMX	Yes	92829900	BVP354 120LED RGB 220V L50 10 DMX	Yes
92634999	BVP353 30LED 27K 220V L30 45	No	92830500	BVP354 120LED RGBWW 220V L50 10 DMX	Yes
92635699	BVP353 30LED 30K 220V L30 45	No	92831200	BVP354 120LED RGBNW 220V L50 10 DMX	Yes
92636399	BVP353 30LED 40K 220V L30 45	No	92832900	BVP354 120LED 27K 220V L50 15	No
92637099	BVP353 30LED 27K 220V L30 45 DMX	Yes	92833600	BVP354 120LED 30K 220V L50 15	No
92638799	BVP353 30LED 30K 220V L30 45 DMX	Yes	92834300	BVP354 120LED 40K 220V L50 15	No
92639499	BVP353 30LED 40K 220V L30 45 DMX	Yes	92835000	BVP354 120LED 27K 220V L50 15 DMX	Yes
92640099	BVP353 30LED RGB 220V L30 45 DMX	Yes	92836700	BVP354 120LED 30K 220V L50 15 DMX	Yes
92641799	BVP353 32LED RGBWW 220V L30 45 DMX	Yes	92837400	BVP354 120LED 40K 220V L50 15 DMX	Yes
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	Yes	92838100	BVP354 120LED RGB 220V L50 15 DMX	Yes
92787200	BVP354 96LED 27K 220V L40 10	No	92839800	BVP354 120LED RGBWW 220V L50 15 DMX	Yes
92788900	BVP354 96LED 30K 220V L40 10	No	92840400	BVP354 120LED RGBNW 220V L50 15 DMX	Yes
92789600	BVP354 96LED 40K 220V L40 10	No	92841100	BVP354 120LED 27K 220V L50 30	No
92790200	BVP354 96LED 27K 220V L40 10 DMX	Yes	92842800	BVP354 120LED 30K 220V L50 30	No
92791900	BVP354 96LED 30K 220V L40 10 DMX	Yes	92843500	BVP354 120LED 40K 220V L50 30	No
92792600	BVP354 96LED 40K 220V L40 10 DMX	Yes	92844200	BVP354 120LED 27K 220V L50 30 DMX	Yes
92793300	BVP354 96LED RGB 220V L40 10 DMX	Yes	92845900	BVP354 120LED 30K 220V L50 30 DMX	Yes
92794000	BVP354 96LED RGBWW 220V L40 10 DMX	Yes	92846600	BVP354 120LED 40K 220V L50 30 DMX	Yes
92795700	BVP354 96LED RGBNW 220V L40 10 DMX	Yes	92847300	BVP354 120LED RGB 220V L50 30 DMX	Yes
92796400	BVP354 96LED 27K 220V L40 15	No	92848000	BVP354 120LED RGBWW 220V L50 30 DMX	Yes
92797100	BVP354 96LED 30K 220V L40 15	No	92849700	BVP354 120LED RGBNW 220V L50 30 DMX	Yes
92798800	BVP354 96LED 40K 220V L40 15	No	92850300	BVP354 120LED 27K 220V L50 45	No
92799500	BVP354 96LED 27K 220V L40 15 DMX	Yes	92851000	BVP354 120LED 30K 220V L50 45	No
92800800	BVP354 96LED 30K 220V L40 15 DMX	Yes	92852700	BVP354 120LED 40K 220V L50 45	No
92801500	BVP354 96LED 40K 220V L40 15 DMX	Yes	92853400	BVP354 120LED 27K 220V L50 45 DMX	Yes
92802200	BVP354 96LED RGB 220V L40 15 DMX	Yes	92854100	BVP354 120LED 30K 220V L50 45 DMX	Yes
92803900	BVP354 96LED RGBWW 220V L40 15 DMX	Yes	92855800	BVP354 120LED 40K 220V L50 45 DMX	Yes
92804600	BVP354 96LED RGBNW 220V L40 15 DMX	Yes	92856500	BVP354 120LED RGB 220V L50 45 DMX	Yes
92805300	BVP354 96LED 27K 220V L40 30	No	92857200	BVP354 120LED RGBWW 220V L50 45 DMX	Yes
92806000	BVP354 96LED 30K 220V L40 30	No	92858900	BVP354 120LED RGBNW 220V L50 45 DMX	Yes
92807700	BVP354 96LED 40K 220V L40 30	No	92859600	BVP354 144LED 27K 220V L57 10	No
92808400	BVP354 96LED 27K 220V L40 30 DMX	Yes	92860200	BVP354 144LED 30K 220V L57 10	No
92809100	BVP354 96LED 30K 220V L40 30 DMX	Yes	92861900	BVP354 144LED 40K 220V L57 10	No
92810700	BVP354 96LED 40K 220V L40 30 DMX	Yes	92862600	BVP354 144LED 27K 220V L57 10 DMX	Yes
92811400	BVP354 96LED RGB 220V L40 30 DMX	Yes	92863300	BVP354 144LED 30K 220V L57 10 DMX	Yes
92812100	BVP354 96LED RGBWW 220V L40 30 DMX	Yes	92864000	BVP354 144LED 40K 220V L57 10 DMX	Yes
92813800	BVP354 96LED RGBNW 220V L40 30 DMX	Yes	92865700	BVP354 144LED RGB 220V L57 10 DMX	Yes
92814500	BVP354 96LED 27K 220V L40 45	No	92866400	BVP354 144LED RGBWW 220V L57 10 DMX	Yes
92815200	BVP354 96LED 30K 220V L40 45	No	92867100	BVP354 144LED RGBNW 220V L57 10 DMX	Yes
92816900	BVP354 96LED 40K 220V L40 45	No	92868800	BVP354 144LED 27K 220V L57 15	No
92817600	BVP354 96LED 27K 220V L40 45 DMX	Yes	92869500	BVP354 144LED 30K 220V L57 15	No
92818300	BVP354 96LED 30K 220V L40 45 DMX	Yes	92870100	BVP354 144LED 40K 220V L57 15	No

UniFlood M G2

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
92871800	BVP354 144LED 27K 220V L57 15 DMX	Yes	92779799	BVP353 72LED 30K 220V L57 45	No
92872500	BVP354 144LED 30K 220V L57 15 DMX	Yes	92780399	BVP353 72LED 40K 220V L57 45	No
92873200	BVP354 144LED 40K 220V L57 15 DMX	Yes	92781099	BVP353 72LED 27K 220V L57 45 DMX	Yes
92874900	BVP354 144LED RGB 220V L57 15 DMX	Yes	92782799	BVP353 72LED 30K 220V L57 45 DMX	Yes
92875600	BVP354 144LED RGBWW 220V L57 15 DMX	Yes	92783499	BVP353 72LED 40K 220V L57 45 DMX	Yes
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	Yes	92784199	BVP353 72LED RGB 220V L57 45 DMX	Yes
92877000	BVP354 144LED 27K 220V L57 30	No	92785899	BVP353 72LED RGBWW 220V L57 45 DMX	Yes
92878700	BVP354 144LED 30K 220V L57 30	No	92786599	BVP353 72LED RGBNW 220V L57 45 DMX	Yes
92879400	BVP354 144LED 40K 220V L57 30	No	92535999	BVP353 18LED 27K 220V L21 10	No
92880000	BVP354 144LED 27K 220V L57 30 DMX	Yes	92536699	BVP353 18LED 30K 220V L21 10	No
92881700	BVP354 144LED 30K 220V L57 30 DMX	Yes	92537399	BVP353 18LED 40K 220V L21 10	No
92882400	BVP354 144LED 40K 220V L57 30 DMX	Yes	92538099	BVP353 18LED 27K 220V L21 10 DMX	Yes
92883100	BVP354 144LED RGB 220V L57 30 DMX	Yes	92539799	BVP353 18LED 30K 220V L21 10 DMX	Yes
92884800	BVP354 144LED RGBWW 220V L57 30 DMX	Yes	92540399	BVP353 18LED 40K 220V L21 10 DMX	Yes
92885500	BVP354 144LED RGBNW 220V L57 30 DMX	Yes	92541099	BVP353 18LED RGB 220V L21 10 DMX	Yes
92886200	BVP354 144LED 27K 220V L57 45	No	92542799	BVP353 20LED RGBWW 220V L21 10 DMX	Yes
92887900	BVP354 144LED 30K 220V L57 45	No	92543499	BVP353 20LED RGBNW 220V L21 10 DMX	Yes
92888600	BVP354 144LED 40K 220V L57 45	No	92544199	BVP353 18LED 27K 220V L21 15	No
92889300	BVP354 144LED 27K 220V L57 45 DMX	Yes	92545899	BVP353 18LED 30K 220V L21 15	No
92890900	BVP354 144LED 30K 220V L57 45 DMX	Yes	92546599	BVP353 18LED 40K 220V L21 15	No
92891600	BVP354 144LED 40K 220V L57 45 DMX	Yes	92547299	BVP353 18LED 27K 220V L21 15 DMX	Yes
92892300	BVP354 144LED RGB 220V L57 45 DMX	Yes	92548999	BVP353 18LED 30K 220V L21 15 DMX	Yes
92893000	BVP354 144LED RGBWW 220V L57 45 DMX	Yes	92549699	BVP353 18LED 40K 220V L21 15 DMX	Yes
92894700	BVP354 144LED RGBNW 220V L57 45 DMX	Yes	92550299	BVP353 18LED RGB 220V L21 15 DMX	Yes
92751399	BVP353 72LED 27K 220V L57 10	No	92551999	BVP353 20LED RGBWW 220V L21 15 DMX	Yes
92752099	BVP353 72LED 30K 220V L57 10	No	92552699	BVP353 20LED RGBNW 220V L21 15 DMX	Yes
92753799	BVP353 72LED 40K 220V L57 10	No	92553399	BVP353 18LED 27K 220V L21 30	No
92754499	BVP353 72LED 27K 220V L57 10 DMX	Yes	92554099	BVP353 18LED 30K 220V L21 30	No
92755199	BVP353 72LED 30K 220V L57 10 DMX	Yes	92555799	BVP353 18LED 40K 220V L21 30	No
92756899	BVP353 72LED 40K 220V L57 10 DMX	Yes	92556499	BVP353 18LED 27K 220V L21 30 DMX	Yes
92757599	BVP353 72LED RGB 220V L57 10 DMX	Yes	92557199	BVP353 18LED 30K 220V L21 30 DMX	Yes
92758299	BVP353 72LED RGBWW 220V L57 10 DMX	Yes	92558899	BVP353 18LED 40K 220V L21 30 DMX	Yes
92759999	BVP353 72LED RGBNW 220V L57 10 DMX	Yes	92559599	BVP353 18LED RGB 220V L21 30 DMX	Yes
92760599	BVP353 72LED 27K 220V L57 15	No	92560199	BVP353 20LED RGBWW 220V L21 30 DMX	Yes
92761299	BVP353 72LED 30K 220V L57 15	No	92561899	BVP353 20LED RGBNW 220V L21 30 DMX	Yes
92762999	BVP353 72LED 40K 220V L57 15	No	92562599	BVP353 18LED 27K 220V L21 45	No
92763699	BVP353 72LED 27K 220V L57 15 DMX	Yes	92563299	BVP353 18LED 30K 220V L21 45	No
92764399	BVP353 72LED 30K 220V L57 15 DMX	Yes	92564999	BVP353 18LED 40K 220V L21 45	No
92765099	BVP353 72LED 40K 220V L57 15 DMX	Yes	92565699	BVP353 18LED 27K 220V L21 45 DMX	Yes
92766799	BVP353 72LED RGB 220V L57 15 DMX	Yes	92566399	BVP353 18LED 30K 220V L21 45 DMX	Yes
92767499	BVP353 72LED RGBWW 220V L57 15 DMX	Yes	92567099	BVP353 18LED 40K 220V L21 45 DMX	Yes
92768199	BVP353 72LED RGBNW 220V L57 15 DMX	Yes	92568799	BVP353 18LED RGB 220V L21 45 DMX	Yes
92769899	BVP353 72LED 27K 220V L57 30	No	92569499	BVP353 20LED RGBWW 220V L21 45 DMX	Yes
92770499	BVP353 72LED 30K 220V L57 30	No	92570099	BVP353 20LED RGBNW 220V L21 45 DMX	Yes
92771199	BVP353 72LED 40K 220V L57 30	No	92463599	BVP353 12LED 27K 220V L15 10	No
92772899	BVP353 72LED 27K 220V L57 30 DMX	Yes	92464299	BVP353 12LED 30K 220V L15 10	No
92773599	BVP353 72LED 30K 220V L57 30 DMX	Yes	92465999	BVP353 12LED 40K 220V L15 10	No
92774299	BVP353 72LED 40K 220V L57 30 DMX	Yes	92466699	BVP353 12LED 27K 220V L15 10 DMX	Yes
92775999	BVP353 72LED RGB 220V L57 30 DMX	Yes	92467399	BVP353 12LED 30K 220V L15 10 DMX	Yes
92776699	BVP353 72LED RGBWW 220V L57 30 DMX	Yes	92468099	BVP353 12LED 40K 220V L15 10 DMX	Yes
92777399	BVP353 72LED RGBNW 220V L57 30 DMX	Yes	92469799	BVP353 12LED RGB 220V L15 10 DMX	Yes
92778099	BVP353 72LED 27K 220V L57 45	No	92470399	BVP353 12LED RGBWW 220V L15 10 DMX	Yes

UniFlood M G2

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
92471099	BVP353 12LED RGBNW 220V L15 10 DMX	Yes	92676999	BVP353 36LED RGB 220V L35 45 DMX	Yes
92481999	BVP353 12LED 27K 220V L15 30	No	92677699	BVP353 36LED RGBWW 220V L35 45 DMX	Yes
92482699	BVP353 12LED 30K 220V L15 30	No	92678399	BVP353 36LED RGBNW 220V L35 45 DMX	Yes
92483399	BVP353 12LED 40K 220V L15 30	No	92571799	BVP353 24LED 27K 220V L24 10	No
92484099	BVP353 12LED 27K 220V L15 30 DMX	Yes	92572499	BVP353 24LED 30K 220V L24 10	No
92485799	BVP353 12LED 30K 220V L15 30 DMX	Yes	92573199	BVP353 24LED 40K 220V L24 10	No
92486499	BVP353 12LED 40K 220V L15 30 DMX	Yes	92574899	BVP353 24LED 27K 220V L24 10 DMX	Yes
92487199	BVP353 12LED RGB 220V L15 30 DMX	Yes	92575599	BVP353 24LED 30K 220V L24 10 DMX	Yes
92488899	BVP353 12LED RGBWW 220V L15 30 DMX	Yes	92576299	BVP353 24LED 40K 220V L24 10 DMX	Yes
92489599	BVP353 12LED RGBNW 220V L15 30 DMX	Yes	92577999	BVP353 24LED RGB 220V L24 10 DMX	Yes
92490199	BVP353 12LED 27K 220V L15 45	No	92578699	BVP353 24LED RGBWW 220V L24 10 DMX	Yes
92491899	BVP353 12LED 30K 220V L15 45	No	92579399	BVP353 24LED RGBNW 220V L24 10 DMX	Yes
92492599	BVP353 12LED 40K 220V L15 45	No	92580999	BVP353 24LED 27K 220V L24 15	No
92493299	BVP353 12LED 27K 220V L15 45 DMX	Yes	92581699	BVP353 24LED 30K 220V L24 15	No
92494999	BVP353 12LED 30K 220V L15 45 DMX	Yes	92582399	BVP353 24LED 40K 220V L24 15	No
92495699	BVP353 12LED 40K 220V L15 45 DMX	Yes	92583099	BVP353 24LED 27K 220V L24 15 DMX	Yes
92496399	BVP353 12LED RGB 220V L15 45 DMX	Yes	92584799	BVP353 24LED 30K 220V L24 15 DMX	Yes
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	Yes	92585499	BVP353 24LED 40K 220V L24 15 DMX	Yes
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	Yes	92586199	BVP353 24LED RGB 220V L24 15 DMX	Yes
92643199	BVP353 36LED 27K 220V L35 10	No	92587899	BVP353 24LED RGBWW 220V L24 15 DMX	Yes
92644899	BVP353 36LED 30K 220V L35 10	No	92588599	BVP353 24LED RGBNW 220V L24 15 DMX	Yes
92645599	BVP353 36LED 40K 220V L35 10	No	92589299	BVP353 24LED 27K 220V L24 30	No
92646299	BVP353 36LED 27K 220V L35 10 DMX	Yes	92590899	BVP353 24LED 30K 220V L24 30	No
92647999	BVP353 36LED 30K 220V L35 10 DMX	Yes	92591599	BVP353 24LED 40K 220V L24 30	No
92648699	BVP353 36LED 40K 220V L35 10 DMX	Yes	92592299	BVP353 24LED 27K 220V L24 30 DMX	Yes
92649399	BVP353 36LED RGB 220V L35 10 DMX	Yes	92593999	BVP353 24LED 30K 220V L24 30 DMX	Yes
92650999	BVP353 36LED RGBWW 220V L35 10 DMX	Yes	92594699	BVP353 24LED 40K 220V L24 30 DMX	Yes
92651699	BVP353 36LED RGBNW 220V L35 10 DMX	Yes	92595399	BVP353 24LED RGB 220V L24 30 DMX	Yes
92652399	BVP353 36LED 27K 220V L35 15	No	92596099	BVP353 24LED RGBWW 220V L24 30 DMX	Yes
92653099	BVP353 36LED 30K 220V L35 15	No	92597799	BVP353 24LED RGBNW 220V L24 30 DMX	Yes
92654799	BVP353 36LED 40K 220V L35 15	No	92598499	BVP353 24LED 27K 220V L24 45	No
92655499	BVP353 36LED 27K 220V L35 15 DMX	Yes	92599199	BVP353 24LED 30K 220V L24 45	No
92656199	BVP353 36LED 30K 220V L35 15 DMX	Yes	92600499	BVP353 24LED 40K 220V L24 45	No
92657899	BVP353 36LED 40K 220V L35 15 DMX	Yes	92601199	BVP353 24LED 27K 220V L24 45 DMX	Yes
92658599	BVP353 36LED RGB 220V L35 15 DMX	Yes	92602899	BVP353 24LED 30K 220V L24 45 DMX	Yes
92659299	BVP353 36LED RGBWW 220V L35 15 DMX	Yes	92603599	BVP353 24LED 40K 220V L24 45 DMX	Yes
92660899	BVP353 36LED RGBNW 220V L35 15 DMX	Yes	92604299	BVP353 24LED RGB 220V L24 45 DMX	Yes
92661599	BVP353 36LED 27K 220V L35 30	No	92605999	BVP353 24LED RGBWW 220V L24 45 DMX	Yes
92662299	BVP353 36LED 30K 220V L35 30	No	92606699	BVP353 24LED RGBNW 220V L24 45 DMX	Yes
92663999	BVP353 36LED 40K 220V L35 30	No	92715599	BVP353 60LED 27K 220V L50 10	No
92664699	BVP353 36LED 27K 220V L35 30 DMX	Yes	92716299	BVP353 60LED 30K 220V L50 10	No
92665399	BVP353 36LED 30K 220V L35 30 DMX	Yes	92717999	BVP353 60LED 40K 220V L50 10	No
92666099	BVP353 36LED 40K 220V L35 30 DMX	Yes	92718699	BVP353 60LED 27K 220V L50 10 DMX	Yes
92667799	BVP353 36LED RGB 220V L35 30 DMX	Yes	92719399	BVP353 60LED 30K 220V L50 10 DMX	Yes
92668499	BVP353 36LED RGBWW 220V L35 30 DMX	Yes	92720999	BVP353 60LED 40K 220V L50 10 DMX	Yes
92669199	BVP353 36LED RGBNW 220V L35 30 DMX	Yes	92721699	BVP353 60LED RGB 220V L50 10 DMX	Yes
92670799	BVP353 36LED 27K 220V L35 45	No	92722399	BVP353 60LED RGBWW 220V L50 10 DMX	Yes
92671499	BVP353 36LED 30K 220V L35 45	No	92723099	BVP353 60LED RGBNW 220V L50 10 DMX	Yes
92672199	BVP353 36LED 40K 220V L35 45	No	92724799	BVP353 60LED 27K 220V L50 15	No
92673899	BVP353 36LED 27K 220V L35 45 DMX	Yes	92725499	BVP353 60LED 30K 220V L50 15	No
92674599	BVP353 36LED 30K 220V L35 45 DMX	Yes	92726199	BVP353 60LED 40K 220V L50 15	No
92675299	BVP353 36LED 40K 220V L35 45 DMX	Yes	92727899	BVP353 60LED 27K 220V L50 15 DMX	Yes

UniFlood M G2

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
92728599	BVP353 60LED 30K 220V L50 15 DMX	Yes	92528199	BVP353 16LED 40K 220V L18 45	No
92729299	BVP353 60LED 40K 220V L50 15 DMX	Yes	92529899	BVP353 16LED 27K 220V L18 45 DMX	Yes
92730899	BVP353 60LED RGB 220V L50 15 DMX	Yes	92530499	BVP353 16LED 30K 220V L18 45 DMX	Yes
92731599	BVP353 60LED RGBWW 220V L50 15 DMX	Yes	92531199	BVP353 16LED 40K 220V L18 45 DMX	Yes
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	Yes	92532899	BVP353 15LED RGB 220V L18 45 DMX	Yes
92733999	BVP353 60LED 27K 220V L50 30	No	92533599	BVP353 16LED RGBWW 220V L18 45 DMX	Yes
92734699	BVP353 60LED 30K 220V L50 30	No	92534299	BVP353 16LED RGBNW 220V L18 45 DMX	Yes
92735399	BVP353 60LED 40K 220V L50 30	No	92895400	BVP355 216LED 27K 220V L57 10	No
92736099	BVP353 60LED 27K 220V L50 30 DMX	Yes	92896100	BVP355 216LED 30K 220V L57 10	No
92737799	BVP353 60LED 30K 220V L50 30 DMX	Yes	92897800	BVP355 216LED 40K 220V L57 10	No
92738499	BVP353 60LED 40K 220V L50 30 DMX	Yes	92898500	BVP355 216LED 27K 220V L57 10 DMX	Yes
92739199	BVP353 60LED RGB 220V L50 30 DMX	Yes	92899200	BVP355 216LED 30K 220V L57 10 DMX	Yes
92740799	BVP353 60LED RGBWW 220V L50 30 DMX	Yes	92900500	BVP355 216LED 40K 220V L57 10 DMX	Yes
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	Yes	92901200	BVP355 216LED RGB 220V L57 10 DMX	Yes
92742199	BVP353 60LED 27K 220V L50 45	No	92902900	BVP355 216LED RGBWW 220V L57 10 DMX	Yes
92743899	BVP353 60LED 30K 220V L50 45	No	92903600	BVP355 216LED RGBNW 220V L57 10 DMX	Yes
92744599	BVP353 60LED 40K 220V L50 45	No	92904300	BVP355 216LED 27K 220V L57 15	No
92745299	BVP353 60LED 27K 220V L50 45 DMX	Yes	92905000	BVP355 216LED 30K 220V L57 15	No
92746999	BVP353 60LED 30K 220V L50 45 DMX	Yes	92906700	BVP355 216LED 40K 220V L57 15	No
92747699	BVP353 60LED 40K 220V L50 45 DMX	Yes	92907400	BVP355 216LED 27K 220V L57 15 DMX	Yes
92748399	BVP353 60LED RGB 220V L50 45 DMX	Yes	92908100	BVP355 216LED 30K 220V L57 15 DMX	Yes
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	Yes	92909800	BVP355 216LED 40K 220V L57 15 DMX	Yes
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	Yes	92910400	BVP355 216LED RGB 220V L57 15 DMX	Yes
92499499	BVP353 16LED 27K 220V L18 10	No	92911100	BVP355 216LED RGBWW 220V L57 15 DMX	Yes
92500799	BVP353 16LED 30K 220V L18 10	No	92912800	BVP355 216LED RGBNW 220V L57 15 DMX	Yes
92501499	BVP353 16LED 40K 220V L18 10	No	92913500	BVP355 216LED 27K 220V L57 30	No
92502199	BVP353 16LED 27K 220V L18 10 DMX	Yes	92914200	BVP355 216LED 30K 220V L57 30	No
92503899	BVP353 16LED 30K 220V L18 10 DMX	Yes	92915900	BVP355 216LED 40K 220V L57 30	No
92504599	BVP353 16LED 40K 220V L18 10 DMX	Yes	92916600	BVP355 216LED 27K 220V L57 30 DMX	Yes
92505299	BVP353 15LED RGB 220V L18 10 DMX	Yes	92917300	BVP355 216LED 30K 220V L57 30 DMX	Yes
92506999	BVP353 16LED RGBWW 220V L18 10 DMX	Yes	92918000	BVP355 216LED 40K 220V L57 30 DMX	Yes
92507699	BVP353 16LED RGBNW 220V L18 10 DMX	Yes	92919700	BVP355 216LED RGB 220V L57 30 DMX	Yes
92508399	BVP353 16LED 27K 220V L18 15	No	92920300	BVP355 216LED RGBWW 220V L57 30 DMX	Yes
92509099	BVP353 16LED 30K 220V L18 15	No	92921000	BVP355 216LED RGBNW 220V L57 30 DMX	Yes
92510699	BVP353 16LED 40K 220V L18 15	No	92922700	BVP355 216LED 27K 220V L57 45	No
92511399	BVP353 16LED 27K 220V L18 15 DMX	Yes	92923400	BVP355 216LED 30K 220V L57 45	No
92512099	BVP353 16LED 30K 220V L18 15 DMX	Yes	92924100	BVP355 216LED 40K 220V L57 45	No
92513799	BVP353 16LED 40K 220V L18 15 DMX	Yes	92925800	BVP355 216LED 27K 220V L57 45 DMX	Yes
92514499	BVP353 15LED RGB 220V L18 15 DMX	Yes	92926500	BVP355 216LED 30K 220V L57 45 DMX	Yes
92515199	BVP353 16LED RGBWW 220V L18 15 DMX	Yes	92927200	BVP355 216LED 40K 220V L57 45 DMX	Yes
92516899	BVP353 16LED RGBNW 220V L18 15 DMX	Yes	92928900	BVP355 216LED RGB 220V L57 45 DMX	Yes
92517599	BVP353 16LED 27K 220V L18 30	No	92929600	BVP355 216LED RGBWW 220V L57 45 DMX	Yes
92518299	BVP353 16LED 30K 220V L18 30	No	92930200	BVP355 216LED RGBNW 220V L57 45 DMX	Yes
92519999	BVP353 16LED 40K 220V L18 30	No	92931900	BVP355 180LED 27K 220V L50 10	No
92520599	BVP353 16LED 27K 220V L18 30 DMX	Yes	92932600	BVP355 180LED 30K 220V L50 10	No
92521299	BVP353 16LED 30K 220V L18 30 DMX	Yes	92933300	BVP355 180LED 40K 220V L50 10	No
92522999	BVP353 16LED 40K 220V L18 30 DMX	Yes	92934000	BVP355 180LED 27K 220V L50 10 DMX	Yes
92523699	BVP353 15LED RGB 220V L18 30 DMX	Yes	92935700	BVP355 180LED 30K 220V L50 10 DMX	Yes
92524399	BVP353 16LED RGBWW 220V L18 30 DMX	Yes	92936400	BVP355 180LED 40K 220V L50 10 DMX	Yes
92525099	BVP353 16LED RGBNW 220V L18 30 DMX	Yes	92937100	BVP355 180LED RGB 220V L50 10 DMX	Yes
92526799	BVP353 16LED 27K 220V L18 45	No	92938800	BVP355 180LED RGBWW 220V L50 10 DMX	Yes
92527499	BVP353 16LED 30K 220V L18 45	No	92939500	BVP355 180LED RGBNW 220V L50 10 DMX	Yes

UniFlood M G2

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
92940100	BVP355 180LED 27K 220V L50 15	No	92684499	BVP353 48LED 40K 220V L40 10 DMX	Yes
92941800	BVP355 180LED 30K 220V L50 15	No	92685199	BVP353 48LED RGB 220V L40 10 DMX	Yes
92942500	BVP355 180LED 40K 220V L50 15	No	92686899	BVP353 48LED RGBWW 220V L40 10 DMX	Yes
92943200	BVP355 180LED 27K 220V L50 15 DMX	Yes	92687599	BVP353 48LED RGBNW 220V L40 10 DMX	Yes
92944900	BVP355 180LED 30K 220V L50 15 DMX	Yes	92688299	BVP353 48LED 27K 220V L40 15	No
92945600	BVP355 180LED 40K 220V L50 15 DMX	Yes	92689999	BVP353 48LED 30K 220V L40 15	No
92946300	BVP355 180LED RGB 220V L50 15 DMX	Yes	92690599	BVP353 48LED 40K 220V L40 15	No
92947000	BVP355 180LED RGBWW 220V L50 15 DMX	Yes	92691299	BVP353 48LED 27K 220V L40 15 DMX	Yes
92948700	BVP355 180LED RGBNW 220V L50 15 DMX	Yes	92692999	BVP353 48LED 30K 220V L40 15 DMX	Yes
92949400	BVP355 180LED 27K 220V L50 30	No	92693699	BVP353 48LED 40K 220V L40 15 DMX	Yes
92950000	BVP355 180LED 30K 220V L50 30	No	92694399	BVP353 48LED RGB 220V L40 15 DMX	Yes
92951700	BVP355 180LED 40K 220V L50 30	No	92695099	BVP353 48LED RGBWW 220V L40 15 DMX	Yes
92952400	BVP355 180LED 27K 220V L50 30 DMX	Yes	92696799	BVP353 48LED RGBNW 220V L40 15 DMX	Yes
92953100	BVP355 180LED 30K 220V L50 30 DMX	Yes	92697499	BVP353 48LED 27K 220V L40 30	No
92954800	BVP355 180LED 40K 220V L50 30 DMX	Yes	92698199	BVP353 48LED 30K 220V L40 30	No
92955500	BVP355 180LED RGB 220V L50 30 DMX	Yes	92699899	BVP353 48LED 40K 220V L40 30	No
92956200	BVP355 180LED RGBWW 220V L50 30 DMX	Yes	92700199	BVP353 48LED 27K 220V L40 30 DMX	Yes
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	Yes	92701899	BVP353 48LED 30K 220V L40 30 DMX	Yes
92958600	BVP355 180LED 27K 220V L50 45	No	92702599	BVP353 48LED 40K 220V L40 30 DMX	Yes
92959300	BVP355 180LED 30K 220V L50 45	No	92703299	BVP353 48LED RGB 220V L40 30 DMX	Yes
92960900	BVP355 180LED 40K 220V L50 45	No	92704999	BVP353 48LED RGBWW 220V L40 30 DMX	Yes
92961600	BVP355 180LED 27K 220V L50 45 DMX	Yes	92705699	BVP353 48LED RGBNW 220V L40 30 DMX	Yes
92962300	BVP355 180LED 30K 220V L50 45 DMX	Yes	92706399	BVP353 48LED 27K 220V L40 45	No
92963000	BVP355 180LED 40K 220V L50 45 DMX	Yes	92707099	BVP353 48LED 30K 220V L40 45	No
92964700	BVP355 180LED RGB 220V L50 45 DMX	Yes	92708799	BVP353 48LED 40K 220V L40 45	No
92965400	BVP355 180LED RGBWW 220V L50 45 DMX	Yes	92709499	BVP353 48LED 27K 220V L40 45 DMX	Yes
92966100	BVP355 180LED RGBNW 220V L50 45 DMX	Yes	92710099	BVP353 48LED 30K 220V L40 45 DMX	Yes
92679099	BVP353 48LED 27K 220V L40 10	No	92711799	BVP353 48LED 40K 220V L40 45 DMX	Yes
92680699	BVP353 48LED 30K 220V L40 10	No	92712499	BVP353 48LED RGB 220V L40 45 DMX	Yes
92681399	BVP353 48LED 40K 220V L40 10	No	92713199	BVP353 48LED RGBWW 220V L40 45 DMX	Yes
92682099	BVP353 48LED 27K 220V L40 10 DMX	Yes	92714899	BVP353 48LED RGBNW 220V L40 45 DMX	Yes
92683799	BVP353 48LED 30K 220V L40 10 DMX	Yes			

