



# CoreLine Recessed Spot gen2 – for every project, where light really matters

## CoreLine Recessed Spot gen2

CoreLine Recessed Spot gen2 delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. Its modular design allows “configure to fit” option that better responds to your specific needs. The range offers a wide range choice on light colour (CCT), light output, colour finish, frame types and connectivity options. The compact and lite design of CoreLine Recessed Spot gen2, always incorporating a push in connector allowing through-wiring and supporting a wide range of wire diameters/cross-sectional area, makes installation hassle-free. High quality of light, numerous connectivity options, long luminaire lifetime and high system efficacy makes CoreLine Recessed Spot gen2 an ideal accent solution for your indoor spot lighting applications.

### Benefits

- Diversity thanks to modular design, responding to a wide range of needs
- Notably easy to install and maintain
- Compact and light product design with high-quality materials and finish
- Good quality of light
- Good performance
- Good value for money

# CoreLine Recessed Spot gen2

## Features

- Available in fixed or adjustable versions
- CE, UKCA and ENEC certified
- White, black or aluminium finish
- 650, 900 or 1200 lumens (system output)
- L70 at 50.000 h
- System efficacy of 88 to 107 lm/w, depending on configuration
- Colour Rendering Index, CRI >80
- Standard colour deviation, SDCM < 3
- Correlated light colour temperature of 2,700 K, 3,000 K or 4,000 K
- LED Modules with sparkly lens optics
- Chip-on-board LED light source
- Various interchangeable frame accessories
- All configurations support basic insulation coverability as per IEC 60598-1:edit 8.1
- Various connectivity options: Phase-Cut (PSR), DALI (PSD) or Interact Pro (WIA)
- High-performance dimming driver (PSR) compatible with most wall-dimmers in the market
- Halox® 100 concrete installation housing compatible options available

## Application

- Hospitality
- Retail
- Offices
- Residential
- HoReCa
- Wide range of general indoor applications
- Corridors
- Meeting rooms
- Bathrooms and toilets
- Break-out areas
- Shelf and cabinets

## Warnings and Safety

- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements, as per the product mounting instructions.

## Versions



CoreLine\_Recessed\_Spot-  
RS140B-SPP.TIF



CoreLine Recessed Spot-RS140B  
Fixed ALU

# CoreLine Recessed Spot gen2

## Versions









CoreLine Recessed Spot gen2  
D68mm 650-950-1200lm  
Adjustable WH SPP




CoreLine Recessed Spot gen2  
D68mm 650-950-1200lm Fix WH

## Dimensional drawing



CoreLine Recessed Spot gen2

Dimensional drawing



Product details



CoreLine\_Recessed\_Spot-RS140B-DPP.TIF



CoreLine\_Recessed\_Spot-RS141B-DPP.TIF



CoreLine\_Recessed\_Spot-RS140B\_Fixed\_ALU-DPP.TIF



CoreLine\_Recessed\_Spot-RS141B\_Adjustable\_ALU-DPP.TIF

CoreLine Recessed Spot gen2


Product details



CoreLine Recessed Spot gen2  
D68mm 650-950-1200lm  
Adjustable WH DDP




CoreLine Recessed Spot gen2  
D68mm 650-950-1200lm Fix WH  
DDP



CoreLine Recessed Spot gen2  
D68mm 650-950-1200lm Fix WH  
DDP




CoreLine Recessed Spot gen2  
D68mm 650-950-1200lm  
Adjustable WH DDP




CoreLine Recessed Spot gen2  
D68mm 1200lm Adjustable PSD  
WH DDP



CoreLine Recessed Spot gen2  
D78mm 1200lm PSD Adjustable



CoreLine Recessed Spot gen2  
D68mm 650-950-1200lm  
Adjustable WH DDP




CoreLine Recessed Spot gen2  
D78mm 1200lm PSR Fix

# CoreLine Recessed Spot gen2


## Product details



CoreLine Recessed Spot gen2  
D78mm 650-950lm Fix




CoreLine Recessed Spot gen2  
D78mm 650-900lm PSR  
Adjustable



CoreLine Recessed Spot gen2  
D68mm 1200lm Adjustable WIA  
WH DDP



CoreLine Recessed Spot gen2  
D78mm 1200lm WIA Adjustable



CoreLine Recessed Spot gen2  
D78mm 1200lm PSR Adjustable

# CoreLine Recessed Spot gen2

## General Information

|                          |                                             |
|--------------------------|---------------------------------------------|
| CE mark                  | Yes                                         |
| Driver included          | Yes                                         |
| ENEC mark                | ENEC mark                                   |
| Flammability mark        | For mounting on normally flammable surfaces |
| Glow-wire test           | Temperature 650 °C, duration 30 s           |
| Light source replaceable | Yes                                         |
| Number of gear units     | Unit                                        |

## Light Technical

|                              |               |
|------------------------------|---------------|
| Beam angle of light source   | 120 degree(s) |
| Colour rendering index (CRI) | >80           |
| Optic type                   | Wide beam     |
| Flickering value (PstLM)     | 1             |
| Stroboscopic effect          | 0.4           |

## Operating and Electrical

|                |              |
|----------------|--------------|
| Input Voltage  | 220 to 240 V |
| Line Frequency | 50 or 60 Hz  |

## Temperature

|                           |             |
|---------------------------|-------------|
| Ambient temperature range | 0 to +35 °C |
|---------------------------|-------------|

## Controls and Dimming

|          |     |
|----------|-----|
| Dimmable | Yes |
|----------|-----|

## Approval and Application

|                              |                 |
|------------------------------|-----------------|
| Protection class IEC         | Safety class II |
| Mech. impact protection code | IK03            |

## Initial Performance (IEC Compliant)

|                         |        |
|-------------------------|--------|
| Luminous flux tolerance | +/-10% |
|-------------------------|--------|

## Application Conditions

|                               |                              |
|-------------------------------|------------------------------|
| Maximum dim level             | 10% (depends on dimmer, ELV) |
| Suitable for random switching | No                           |

## Light Technical

| Order Code | Full Product Name                       | Correlated Colour Temperature | Luminous efficacy (rated) (nom.) | Luminous Flux |
|------------|-----------------------------------------|-------------------------------|----------------------------------|---------------|
| 54826899   | RS150B LED6-WB-/830 D78 PSR PI6 WH      | 3000 K                        | 94 lm/W                          | 680 lm        |
| 54827599   | RS150B LED6-WB-/840 D78 PSR PI6 WH      | 4000 K                        | 100 lm/W                         | 720 lm        |
| 54828299   | RS150B LED9-WB-/830 D78 PSR PI6 WH      | 3000 K                        | 88 lm/W                          | 900 lm        |
| 54830599   | RS150B LED12-WB-/830 D78 PSR PI6 WH     | 3000 K                        | 104 lm/W                         | 1,280 lm      |
| 54831299   | RS150B LED12-WB-/840 D78 PSR PI6 WH     | 4000 K                        | 107 lm/W                         | 1,320 lm      |
| 93843499   | RS151B LED6-WB-/830 D78HALOX PSR PI6 WH | 3000 K                        | 94 lm/W                          | 680 lm        |
| 54811499   | RS151B LED6-WB-/830 D78 PSR PI6 WH      | 3000 K                        | 94 lm/W                          | 680 lm        |
| 54813899   | RS151B LED6-WB-/840 D78 PSR PI6 WH      | 4000 K                        | 100 lm/W                         | 720 lm        |
| 54819099   | RS151B LED12-WB-/830 D78 PSR PI6 WH     | 3000 K                        | 104 lm/W                         | 1,280 lm      |
| 54821399   | RS151B LED12-WB-/840 D78 PSR PI6 WH     | 4000 K                        | 107 lm/W                         | 1,320 lm      |
| 54822099   | RS151B LED12-WB-/830 D78 WIA PI6 WH     | 3000 K                        | 106 lm/W                         | 1,280 lm      |
| 54823799   | RS151B LED12-WB-/840 D78 WIA PI6 WH     | 4000 K                        | 110 lm/W                         | 1,320 lm      |
| 54825199   | RS151B LED12-WB-/840 D78 PSD PI10 WH    | 4000 K                        | 107 lm/W                         | 1,320 lm      |
| 93822999   | RS150B LED12-WB-/830 D78 PSR PI6 ALU    | 3000 K                        | 104 lm/W                         | 1,280 lm      |
| 93818299   | RS151B LED9-WB-/840 D78 PSR PI6 ALU     | 4000 K                        | 93 lm/W                          | 950 lm        |
| 54824499   | RS151B LED12-WB-/830 D78 PSD PI10 WH    | 3000 K                        | 104 lm/W                         | 1,280 lm      |
| 94084099   | RS156B LED6-WB-/830 D68HALOX PSR PI6 WH | 3000 K                        | 104 lm/W                         | 750 lm        |
| 94079699   | RS156B LED6-WB-/830 D68 PSR PI6 WH      | 3000 K                        | 104 lm/W                         | 750 lm        |
| 94081999   | RS156B LED6-WB-/840 D68 PSR PI6 WH      | 4000 K                        | 110 lm/W                         | 800 lm        |
| 94089599   | RS156B LED12-WB-/830 D68 PSR PI6 WH     | 3000 K                        | 105 lm/W                         | 1,300 lm      |
| 94091899   | RS156B LED12-WB-/840 D68 PSR PI6 WH     | 4000 K                        | 112 lm/W                         | 1,380 lm      |
| 94093299   | RS156B LED12-WB-/830 D68 WIA PI6 WH     | 3000 K                        | 108 lm/W                         | 1,300 lm      |
| 94094999   | RS156B LED12-WB-/840 D68 WIA PI6 WH     | 4000 K                        | 115 lm/W                         | 1,380 lm      |
| 94095699   | RS156B LED12-WB-/830 D68 PSD PI10 WH    | 3000 K                        | 105 lm/W                         | 1,300 lm      |
| 94096399   | RS156B LED12-WB-/840 D68 PSD PI10 WH    | 4000 K                        | 112 lm/W                         | 1,380 lm      |

CoreLine Recessed Spot gen2

| Order Code | Full Product Name                   | Correlated Colour | Luminous efficacy |               |
|------------|-------------------------------------|-------------------|-------------------|---------------|
|            |                                     | Temperature       | (rated) (nom.)    | Luminous Flux |
| 94097099   | RS155B LED6-WB-/830 D68 PSR PI6 WH  | 3000 K            | 104 lm/W          | 750 lm        |
| 94099499   | RS155B LED6-WB-/840 D68 PSR PI6 WH  | 4000 K            | 110 lm/W          | 800 lm        |
| 94103899   | RS155B LED12-WB-/830 D68 PSR PI6 WH | 3000 K            | 105 lm/W          | 1,300 lm      |
| 94105299   | RS155B LED12-WB-/840 D68 PSR PI6 WH | 4000 K            | 112 lm/W          | 1,380 lm      |

Operating and Electrical

| Order Code | Full Product Name                       | Power Consumption |
|------------|-----------------------------------------|-------------------|
| 54826899   | RS150B LED6-WB-/830 D78 PSR PI6 WH      | 7.2 W             |
| 54827599   | RS150B LED6-WB-/840 D78 PSR PI6 WH      | 7.2 W             |
| 54828299   | RS150B LED9-WB-/830 D78 PSR PI6 WH      | 10.2 W            |
| 54830599   | RS150B LED12-WB-/830 D78 PSR PI6 WH     | 12.3 W            |
| 54831299   | RS150B LED12-WB-/840 D78 PSR PI6 WH     | 12.3 W            |
| 93843499   | RS151B LED6-WB-/830 D78HALOX PSR PI6 WH | 7.2 W             |
| 54811499   | RS151B LED6-WB-/830 D78 PSR PI6 WH      | 7.2 W             |
| 54813899   | RS151B LED6-WB-/840 D78 PSR PI6 WH      | 7.2 W             |
| 54819099   | RS151B LED12-WB-/830 D78 PSR PI6 WH     | 12.3 W            |
| 54821399   | RS151B LED12-WB-/840 D78 PSR PI6 WH     | 12.3 W            |
| 54822099   | RS151B LED12-WB-/830 D78 WIA PI6 WH     | 12 W              |
| 54823799   | RS151B LED12-WB-/840 D78 WIA PI6 WH     | 12 W              |
| 54825199   | RS151B LED12-WB-/840 D78 PSD PI10 WH    | 12.3 W            |
| 93822999   | RS150B LED12-WB-/830 D78 PSR PI6 ALU    | 12.3 W            |
| 93818299   | RS151B LED9-WB-/840 D78 PSR PI6 ALU     | 10.2 W            |

| Order Code | Full Product Name                       | Power Consumption |
|------------|-----------------------------------------|-------------------|
| 54824499   | RS151B LED12-WB-/830 D78 PSD PI10 WH    | 12.3 W            |
| 94084099   | RS156B LED6-WB-/830 D68HALOX PSR PI6 WH | 7.2 W             |
| 94079699   | RS156B LED6-WB-/830 D68 PSR PI6 WH      | 7.2 W             |
| 94081999   | RS156B LED6-WB-/840 D68 PSR PI6 WH      | 7.2 W             |
| 94089599   | RS156B LED12-WB-/830 D68 PSR PI6 WH     | 12.3 W            |
| 94091899   | RS156B LED12-WB-/840 D68 PSR PI6 WH     | 12.3 W            |
| 94093299   | RS156B LED12-WB-/830 D68 WIA PI6 WH     | 12 W              |
| 94094999   | RS156B LED12-WB-/840 D68 WIA PI6 WH     | 12 W              |
| 94095699   | RS156B LED12-WB-/830 D68 PSD PI10 WH    | 12.3 W            |
| 94096399   | RS156B LED12-WB-/840 D68 PSD PI10 WH    | 12.3 W            |
| 94097099   | RS155B LED6-WB-/830 D68 PSR PI6 WH      | 7.2 W             |
| 94099499   | RS155B LED6-WB-/840 D68 PSR PI6 WH      | 7.2 W             |
| 94103899   | RS155B LED12-WB-/830 D68 PSR PI6 WH     | 12.3 W            |
| 94105299   | RS155B LED12-WB-/840 D68 PSR PI6 WH     | 12.3 W            |

Mechanical and Housing

| Order Code | Full Product Name                       | Housing Colour |
|------------|-----------------------------------------|----------------|
| 54826899   | RS150B LED6-WB-/830 D78 PSR PI6 WH      | White          |
| 54827599   | RS150B LED6-WB-/840 D78 PSR PI6 WH      | White          |
| 54828299   | RS150B LED9-WB-/830 D78 PSR PI6 WH      | White          |
| 54830599   | RS150B LED12-WB-/830 D78 PSR PI6 WH     | White          |
| 54831299   | RS150B LED12-WB-/840 D78 PSR PI6 WH     | White          |
| 93843499   | RS151B LED6-WB-/830 D78HALOX PSR PI6 WH | White          |
| 54811499   | RS151B LED6-WB-/830 D78 PSR PI6 WH      | White          |
| 54813899   | RS151B LED6-WB-/840 D78 PSR PI6 WH      | White          |
| 54819099   | RS151B LED12-WB-/830 D78 PSR PI6 WH     | White          |
| 54821399   | RS151B LED12-WB-/840 D78 PSR PI6 WH     | White          |
| 54822099   | RS151B LED12-WB-/830 D78 WIA PI6 WH     | White          |
| 54823799   | RS151B LED12-WB-/840 D78 WIA PI6 WH     | White          |
| 54825199   | RS151B LED12-WB-/840 D78 PSD PI10 WH    | White          |
| 93822999   | RS150B LED12-WB-/830 D78 PSR PI6 ALU    | Aluminium      |
| 93818299   | RS151B LED9-WB-/840 D78 PSR PI6 ALU     | Aluminium      |

| Order Code | Full Product Name                       | Housing Colour |
|------------|-----------------------------------------|----------------|
| 54824499   | RS151B LED12-WB-/830 D78 PSD PI10 WH    | White          |
| 94084099   | RS156B LED6-WB-/830 D68HALOX PSR PI6 WH | White          |
| 94079699   | RS156B LED6-WB-/830 D68 PSR PI6 WH      | White          |
| 94081999   | RS156B LED6-WB-/840 D68 PSR PI6 WH      | White          |
| 94089599   | RS156B LED12-WB-/830 D68 PSR PI6 WH     | White          |
| 94091899   | RS156B LED12-WB-/840 D68 PSR PI6 WH     | White          |
| 94093299   | RS156B LED12-WB-/830 D68 WIA PI6 WH     | White          |
| 94094999   | RS156B LED12-WB-/840 D68 WIA PI6 WH     | White          |
| 94095699   | RS156B LED12-WB-/830 D68 PSD PI10 WH    | White          |
| 94096399   | RS156B LED12-WB-/840 D68 PSD PI10 WH    | White          |
| 94097099   | RS155B LED6-WB-/830 D68 PSR PI6 WH      | White          |
| 94099499   | RS155B LED6-WB-/840 D68 PSR PI6 WH      | White          |
| 94103899   | RS155B LED12-WB-/830 D68 PSR PI6 WH     | White          |
| 94105299   | RS155B LED12-WB-/840 D68 PSR PI6 WH     | White          |

Approval and Application

## CoreLine Recessed Spot gen2

| Order Code | Full Product Name                       | Ingress protection code |
|------------|-----------------------------------------|-------------------------|
| 54826899   | RS150B LED6-WB-/830 D78 PSR PI6 WH      | IP20/54                 |
| 54827599   | RS150B LED6-WB-/840 D78 PSR PI6 WH      | IP20/54                 |
| 54828299   | RS150B LED9-WB-/830 D78 PSR PI6 WH      | IP20/54                 |
| 54830599   | RS150B LED12-WB-/830 D78 PSR PI6 WH     | IP20/54                 |
| 54831299   | RS150B LED12-WB-/840 D78 PSR PI6 WH     | IP20/54                 |
| 93843499   | RS151B LED6-WB-/830 D78HALOX PSR PI6 WH | IP20/44                 |
| 54811499   | RS151B LED6-WB-/830 D78 PSR PI6 WH      | IP20/44                 |
| 54813899   | RS151B LED6-WB-/840 D78 PSR PI6 WH      | IP20/44                 |
| 54819099   | RS151B LED12-WB-/830 D78 PSR PI6 WH     | IP20/44                 |
| 54821399   | RS151B LED12-WB-/840 D78 PSR PI6 WH     | IP20/44                 |
| 54822099   | RS151B LED12-WB-/830 D78 WIA PI6 WH     | IP20/44                 |
| 54823799   | RS151B LED12-WB-/840 D78 WIA PI6 WH     | IP20/44                 |
| 54825199   | RS151B LED12-WB-/840 D78 PSD PI10 WH    | IP20/44                 |
| 93822999   | RS150B LED12-WB-/830 D78 PSR PI6 ALU    | IP20/54                 |
| 93818299   | RS151B LED9-WB-/840 D78 PSR PI6 ALU     | IP20/44                 |

| Order Code | Full Product Name                       | Ingress protection code |
|------------|-----------------------------------------|-------------------------|
| 54824499   | RS151B LED12-WB-/830 D78 PSD PI10 WH    | IP20/44                 |
| 94084099   | RS156B LED6-WB-/830 D68HALOX PSR PI6 WH | IP20/44                 |
| 94079699   | RS156B LED6-WB-/830 D68 PSR PI6 WH      | IP20/44                 |
| 94081999   | RS156B LED6-WB-/840 D68 PSR PI6 WH      | IP20/44                 |
| 94089599   | RS156B LED12-WB-/830 D68 PSR PI6 WH     | IP20/44                 |
| 94091899   | RS156B LED12-WB-/840 D68 PSR PI6 WH     | IP20/44                 |
| 94093299   | RS156B LED12-WB-/830 D68 WIA PI6 WH     | IP20/44                 |
| 94094999   | RS156B LED12-WB-/840 D68 WIA PI6 WH     | IP20/44                 |
| 94095699   | RS156B LED12-WB-/830 D68 PSD PI10 WH    | IP20/44                 |
| 94096399   | RS156B LED12-WB-/840 D68 PSD PI10 WH    | IP20/44                 |
| 94097099   | RS155B LED6-WB-/830 D68 PSR PI6 WH      | IP20/54                 |
| 94099499   | RS155B LED6-WB-/840 D68 PSR PI6 WH      | IP20/54                 |
| 94103899   | RS155B LED12-WB-/830 D68 PSR PI6 WH     | IP20/54                 |
| 94105299   | RS155B LED12-WB-/840 D68 PSR PI6 WH     | IP20/54                 |

### Initial Performance (IEC Compliant)

| Order Code | Full Product Name                       | Initial chromaticity |
|------------|-----------------------------------------|----------------------|
| 54826899   | RS150B LED6-WB-/830 D78 PSR PI6 WH      | (0.43, 0.40) SDCM <5 |
| 54827599   | RS150B LED6-WB-/840 D78 PSR PI6 WH      | (0.38, 0.38) SDCM <5 |
| 54828299   | RS150B LED9-WB-/830 D78 PSR PI6 WH      | (0.43, 0.40) SDCM <5 |
| 54830599   | RS150B LED12-WB-/830 D78 PSR PI6 WH     | (0.43, 0.40) SDCM <5 |
| 54831299   | RS150B LED12-WB-/840 D78 PSR PI6 WH     | (0.38, 0.38) SDCM <5 |
| 93843499   | RS151B LED6-WB-/830 D78HALOX PSR PI6 WH | (0.43, 0.40) SDCM <5 |
| 54811499   | RS151B LED6-WB-/830 D78 PSR PI6 WH      | (0.43, 0.40) SDCM <5 |
| 54813899   | RS151B LED6-WB-/840 D78 PSR PI6 WH      | (0.38, 0.38) SDCM <5 |
| 54819099   | RS151B LED12-WB-/830 D78 PSR PI6 WH     | (0.43, 0.40) SDCM <5 |
| 54821399   | RS151B LED12-WB-/840 D78 PSR PI6 WH     | (0.38, 0.38) SDCM <5 |
| 54822099   | RS151B LED12-WB-/830 D78 WIA PI6 WH     | (0.43, 0.40) SDCM <5 |
| 54823799   | RS151B LED12-WB-/840 D78 WIA PI6 WH     | (0.38, 0.38) SDCM <5 |
| 54825199   | RS151B LED12-WB-/840 D78 PSD PI10 WH    | (0.38, 0.38) SDCM <5 |
| 93822999   | RS150B LED12-WB-/830 D78 PSR PI6 ALU    | (0.43, 0.40) SDCM <5 |
| 93818299   | RS151B LED9-WB-/840 D78 PSR PI6 ALU     | (0.38, 0.38) SDCM <5 |

| Order Code | Full Product Name                       | Initial chromaticity |
|------------|-----------------------------------------|----------------------|
| 54824499   | RS151B LED12-WB-/830 D78 PSD PI10 WH    | (0.43, 0.40) SDCM <5 |
| 94084099   | RS156B LED6-WB-/830 D68HALOX PSR PI6 WH | (0.43, 0.40) SDCM <5 |
| 94079699   | RS156B LED6-WB-/830 D68 PSR PI6 WH      | (0.43, 0.40) SDCM <5 |
| 94081999   | RS156B LED6-WB-/840 D68 PSR PI6 WH      | (0.38, 0.38) SDCM <5 |
| 94089599   | RS156B LED12-WB-/830 D68 PSR PI6 WH     | (0.43, 0.40) SDCM <5 |
| 94091899   | RS156B LED12-WB-/840 D68 PSR PI6 WH     | (0.38, 0.38) SDCM <5 |
| 94093299   | RS156B LED12-WB-/830 D68 WIA PI6 WH     | (0.43, 0.40) SDCM <5 |
| 94094999   | RS156B LED12-WB-/840 D68 WIA PI6 WH     | (0.38, 0.38) SDCM <5 |
| 94095699   | RS156B LED12-WB-/830 D68 PSD PI10 WH    | (0.43, 0.40) SDCM <5 |
| 94096399   | RS156B LED12-WB-/840 D68 PSD PI10 WH    | (0.38, 0.38) SDCM <5 |
| 94097099   | RS155B LED6-WB-/830 D68 PSR PI6 WH      | (0.43, 0.40) SDCM <5 |
| 94099499   | RS155B LED6-WB-/840 D68 PSR PI6 WH      | (0.38, 0.38) SDCM <5 |
| 94103899   | RS155B LED12-WB-/830 D68 PSR PI6 WH     | (0.43, 0.40) SDCM <5 |
| 94105299   | RS155B LED12-WB-/840 D68 PSR PI6 WH     | (0.38, 0.38) SDCM <5 |

