



# Shining in a linear way

## GreenSpace linear accent

GreenSpace Linear accent is a comprehensive product offer with multiple modules available. By means of its modular design, it offers flexible lumen output for different indoor applications, such as office, retail and hospitality. This family provides both surface mounted and recessed installations with high CRI90 and 3 different beam angles to perfectly fit the light requirement of the indoor applications. Dali and 1-10V control interfaces give the way for future system connections as well.

### Benefits

- Flexible lumen output by means of multiple modules design
- High color rendering index helps better visual comfort in office and retail applications
- 3 different beams facilitate the lighting designer for wide lighting applications
- System interface available to easily control the lights

### Features





- Multiple modules combinations available
- Both surface mounted and recessed installations are offered
- CRI 90 high color rendering index available
- Narrow/medium/wide beams options
- Dali / 1-10V control system interface available

### Application

- Open offices
- Retail
- Meeting rooms
- Hospitality

GreenSpace linear accent

Dimensional drawing



| General Information                 |                                                     |
|-------------------------------------|-----------------------------------------------------|
| CE mark                             | -                                                   |
| Light Technical                     |                                                     |
| Optical cover type                  | Polycarbonate cover and gloss high-reflective optic |
| Color rendering index (CRI)         | >90                                                 |
| Operating and Electrical            |                                                     |
| Input Voltage                       | 220 to 240 V                                        |
| Line Frequency                      | 50 or 60 Hz                                         |
| Temperature                         |                                                     |
| Ambient temperature range           | -20 to +40 °C                                       |
| Mechanical and Housing              |                                                     |
| Housing Color                       | Black and white                                     |
| Approval and Application            |                                                     |
| Protection class IEC                | Safety class II                                     |
| Mech. impact protection code        | IK02                                                |
| Ingress protection code             | IP20                                                |
| Initial Performance (IEC Compliant) |                                                     |
| Luminous flux tolerance             | +/-10%                                              |

Light Technical

| Order Code | Full Product Name             | Correlated Color  | Luminous Efficacy | Luminous Flux |
|------------|-------------------------------|-------------------|-------------------|---------------|
|            |                               | Temperature (Nom) | (rated) (Nom)     |               |
| 66260899   | RS386B S5 P10 930 PSU-E NB WH | 3000 K            | 64 lm/W           | 575 lm        |
| 66261599   | RS386B S5 P10 930 PSU-E MB WH | 3000 K            | 64 lm/W           | 575 lm        |
| 66262299   | RS386B S5 P10 930 PSU-E WB WH | 3000 K            | 64 lm/W           | 575 lm        |
| 66263999   | RS386B S5 P10 935 PSU-E NB WH | 3500 K            | 64 lm/W           | 575 lm        |
| 66264699   | RS386B S5 P10 935 PSU-E MB WH | 3500 K            | 64 lm/W           | 575 lm        |
| 66265399   | RS386B S5 P10 935 PSU-E WB WH | 3500 K            | 64 lm/W           | 575 lm        |
| 66266099   | RS386B S5 P10 940 PSU-E WB WH | 4000 K            | 64 lm/W           | 575 lm        |
| 66288299   | RS386B S5 P10 930 PSR-E NB WH | 3000 K            | 64 lm/W           | 575 lm        |
| 66289999   | RS386B S5 P10 930 PSR-E MB WH | 3000 K            | 64 lm/W           | 575 lm        |
| 66290599   | RS386B S5 P10 930 PSR-E WB WH | 3000 K            | 64 lm/W           | 575 lm        |
| 66291299   | RS386B S5 P10 935 PSR-E NB WH | 3500 K            | 64 lm/W           | 575 lm        |
| 66292999   | RS386B S5 P10 935 PSR-E MB WH | 3500 K            | 64 lm/W           | 575 lm        |
| 66293699   | RS386B S5 P10 935 PSR-E WB WH | 3500 K            | 64 lm/W           | 575 lm        |
| 66294399   | RS386B S5 P10 940 PSR-E WB WH | 4000 K            | 64 lm/W           | 575 lm        |
| 66372899   | RS386B S5 P10 930 PSD-E NB WH | 3000 K            | 64 lm/W           | 575 lm        |
| 66373599   | RS386B S5 P10 930 PSD-E MB WH | 3000 K            | 64 lm/W           | 575 lm        |
| 66374299   | RS386B S5 P10 930 PSD-E WB WH | 3000 K            | 64 lm/W           | 575 lm        |
| 66375999   | RS386B S5 P10 935 PSD-E NB WH | 3500 K            | 64 lm/W           | 575 lm        |
| 66376699   | RS386B S5 P10 935 PSD-E MB WH | 3500 K            | 64 lm/W           | 575 lm        |
| 66377399   | RS386B S5 P10 935 PSD-E WB WH | 3500 K            | 64 lm/W           | 575 lm        |
| 66378099   | RS386B S5 P10 940 PSD-E WB WH | 4000 K            | 64 lm/W           | 575 lm        |
| 66337799   | SM386C S10 P20 930 PSU NB BK  | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66338499   | SM386C S10 P20 930 PSU MB BK  | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66339199   | SM386C S10 P20 930 PSU WB BK  | 3000 K            | 65 lm/W           | 1,150 lm      |

| Order Code | Full Product Name            | Correlated Color  | Luminous Efficacy |               |
|------------|------------------------------|-------------------|-------------------|---------------|
|            |                              | Temperature (Nom) | (rated) (Nom)     | Luminous Flux |
| 66340799   | SM386C S10 P20 935 PSU NB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66341499   | SM386C S10 P20 935 PSU MB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66342199   | SM386C S10 P20 935 PSU WB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66343899   | SM386C S10 P20 940 PSU WB BK | 4000 K            | 65 lm/W           | 1,150 lm      |
| 66365099   | SM386C S10 P20 930 PSR NB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66366799   | SM386C S10 P20 930 PSR MB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66367499   | SM386C S10 P20 930 PSR WB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66368199   | SM386C S10 P20 935 PSR NB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66369899   | SM386C S10 P20 935 PSR MB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66370499   | SM386C S10 P20 935 PSR WB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66371199   | SM386C S10 P20 940 PSR WB BK | 4000 K            | 65 lm/W           | 1,150 lm      |
| 66427599   | SM386C S10 P20 930 PSD NB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66428299   | SM386C S10 P20 930 PSD MB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66429999   | SM386C S10 P20 930 PSD WB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66430599   | SM386C S10 P20 935 PSD NB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66433699   | SM386C S10 P20 935 PSD MB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66434399   | SM386C S10 P20 935 PSD WB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66435099   | SM386C S10 P20 940 PSD WB BK | 4000 K            | 65 lm/W           | 1,150 lm      |
| 66330899   | SM386C S10 P20 930 PSU NB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66331599   | SM386C S10 P20 930 PSU MB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66332299   | SM386C S10 P20 930 PSU WB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66333999   | SM386C S10 P20 935 PSU NB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66334699   | SM386C S10 P20 935 PSU MB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66335399   | SM386C S10 P20 935 PSU WB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66336099   | SM386C S10 P20 940 PSU WB WH | 4000 K            | 65 lm/W           | 1,150 lm      |
| 66358299   | SM386C S10 P20 930 PSR NB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66359999   | SM386C S10 P20 930 PSR MB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66360599   | SM386C S10 P20 930 PSR WB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66361299   | SM386C S10 P20 935 PSR NB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66362999   | SM386C S10 P20 935 PSR MB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66363699   | SM386C S10 P20 935 PSR WB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66364399   | SM386C S10 P20 940 PSR WB WH | 4000 K            | 65 lm/W           | 1,150 lm      |
| 66418399   | SM386C S10 P20 930 PSD NB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66419099   | SM386C S10 P20 930 PSD MB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66420699   | SM386C S10 P20 930 PSD WB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66423799   | SM386C S10 P20 935 PSD NB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66424499   | SM386C S10 P20 935 PSD MB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66425199   | SM386C S10 P20 935 PSD WB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66426899   | SM386C S10 P20 940 PSD WB WH | 4000 K            | 65 lm/W           | 1,150 lm      |
| 66316299   | SM386C S5 P10 930 PSU NB WH  | 3000 K            | 64 lm/W           | 575 lm        |
| 66317999   | SM386C S5 P10 930 PSU MB WH  | 3000 K            | 64 lm/W           | 575 lm        |
| 66318699   | SM386C S5 P10 930 PSU WB WH  | 3000 K            | 64 lm/W           | 575 lm        |
| 66319399   | SM386C S5 P10 935 PSU NB WH  | 3500 K            | 64 lm/W           | 575 lm        |
| 66320999   | SM386C S5 P10 935 PSU MB WH  | 3500 K            | 64 lm/W           | 575 lm        |
| 66321699   | SM386C S5 P10 935 PSU WB WH  | 3500 K            | 64 lm/W           | 575 lm        |
| 66322399   | SM386C S5 P10 940 PSU WB WH  | 4000 K            | 64 lm/W           | 575 lm        |
| 66344599   | SM386C S5 P10 930 PSR NB WH  | 3000 K            | 64 lm/W           | 575 lm        |
| 66345299   | SM386C S5 P10 930 PSR MB WH  | 3000 K            | 64 lm/W           | 575 lm        |
| 66346999   | SM386C S5 P10 930 PSR WB WH  | 3000 K            | 64 lm/W           | 575 lm        |
| 66347699   | SM386C S5 P10 935 PSR NB WH  | 3500 K            | 64 lm/W           | 575 lm        |
| 66348399   | SM386C S5 P10 935 PSR MB WH  | 3500 K            | 64 lm/W           | 575 lm        |

| Order Code | Full Product Name              | Correlated Color  | Luminous Efficacy |               |
|------------|--------------------------------|-------------------|-------------------|---------------|
|            |                                | Temperature (Nom) | (rated) (Nom)     | Luminous Flux |
| 66349099   | SM386C S5 P10 935 PSR WB WH    | 3500 K            | 64 lm/W           | 575 lm        |
| 66350699   | SM386C S5 P10 940 PSR WB WH    | 4000 K            | 64 lm/W           | 575 lm        |
| 66400899   | SM386C S5 P10 930 PSD NB WH    | 3000 K            | 64 lm/W           | 575 lm        |
| 66403999   | SM386C S5 P10 930 PSD MB WH    | 3000 K            | 64 lm/W           | 575 lm        |
| 66404699   | SM386C S5 P10 930 PSD WB WH    | 3000 K            | 64 lm/W           | 575 lm        |
| 66405399   | SM386C S5 P10 935 PSD NB WH    | 3500 K            | 64 lm/W           | 575 lm        |
| 66406099   | SM386C S5 P10 935 PSD MB WH    | 3500 K            | 64 lm/W           | 575 lm        |
| 66407799   | SM386C S5 P10 935 PSD WB WH    | 3500 K            | 64 lm/W           | 575 lm        |
| 66408499   | SM386C S5 P10 940 PSD WB WH    | 4000 K            | 64 lm/W           | 575 lm        |
| 66274599   | RS386B S10 P20 930 PSU-E NB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66275299   | RS386B S10 P20 930 PSU-E MB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66276999   | RS386B S10 P20 930 PSU-E WB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66277699   | RS386B S10 P20 935 PSU-E NB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66278399   | RS386B S10 P20 935 PSU-E MB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66279099   | RS386B S10 P20 935 PSU-E WB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66280699   | RS386B S10 P20 940 PSU-E WB WH | 4000 K            | 65 lm/W           | 1,150 lm      |
| 66302599   | RS386B S10 P20 930 PSR-E NB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66303299   | RS386B S10 P20 930 PSR-E MB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66304999   | RS386B S10 P20 930 PSR-E WB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66305699   | RS386B S10 P20 935 PSR-E NB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66306399   | RS386B S10 P20 935 PSR-E MB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66307099   | RS386B S10 P20 935 PSR-E WB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66308799   | RS386B S10 P20 940 PSR-E WB WH | 4000 K            | 65 lm/W           | 1,150 lm      |
| 66386599   | RS386B S10 P20 930 PSD-E NB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66387299   | RS386B S10 P20 930 PSD-E MB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66388999   | RS386B S10 P20 930 PSD-E WB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66389699   | RS386B S10 P20 935 PSD-E NB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66390299   | RS386B S10 P20 935 PSD-E MB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66391999   | RS386B S10 P20 935 PSD-E WB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66392699   | RS386B S10 P20 940 PSD-E WB WH | 4000 K            | 65 lm/W           | 1,150 lm      |
| 66323099   | SM386C S5 P10 930 PSU NB BK    | 3000 K            | 64 lm/W           | 575 lm        |
| 66324799   | SM386C S5 P10 930 PSU MB BK    | 3000 K            | 64 lm/W           | 575 lm        |
| 66325499   | SM386C S5 P10 930 PSU WB BK    | 3000 K            | 64 lm/W           | 575 lm        |
| 66326199   | SM386C S5 P10 935 PSU NB BK    | 3500 K            | 64 lm/W           | 575 lm        |
| 66327899   | SM386C S5 P10 935 PSU MB BK    | 3500 K            | 64 lm/W           | 575 lm        |
| 66328599   | SM386C S5 P10 935 PSU WB BK    | 3500 K            | 64 lm/W           | 575 lm        |
| 66329299   | SM386C S5 P10 940 PSU WB BK    | 4000 K            | 64 lm/W           | 575 lm        |
| 66351399   | SM386C S5 P10 930 PSR NB BK    | 3000 K            | 64 lm/W           | 575 lm        |
| 66352099   | SM386C S5 P10 930 PSR MB BK    | 3000 K            | 64 lm/W           | 575 lm        |
| 66353799   | SM386C S5 P10 930 PSR WB BK    | 3000 K            | 64 lm/W           | 575 lm        |
| 66354499   | SM386C S5 P10 935 PSR NB BK    | 3500 K            | 64 lm/W           | 575 lm        |
| 66355199   | SM386C S5 P10 935 PSR MB BK    | 3500 K            | 64 lm/W           | 575 lm        |
| 66356899   | SM386C S5 P10 935 PSR WB BK    | 3500 K            | 64 lm/W           | 575 lm        |
| 66357599   | SM386C S5 P10 940 PSR WB BK    | 4000 K            | 64 lm/W           | 575 lm        |
| 66409199   | SM386C S5 P10 930 PSD NB BK    | 3000 K            | 64 lm/W           | 575 lm        |
| 66410799   | SM386C S5 P10 930 PSD MB BK    | 3000 K            | 64 lm/W           | 575 lm        |
| 66413899   | SM386C S5 P10 930 PSD WB BK    | 3000 K            | 64 lm/W           | 575 lm        |
| 66414599   | SM386C S5 P10 935 PSD NB BK    | 3500 K            | 64 lm/W           | 575 lm        |
| 66415299   | SM386C S5 P10 935 PSD MB BK    | 3500 K            | 64 lm/W           | 575 lm        |

| Order Code | Full Product Name              | Correlated Color  | Luminous Efficacy |               |
|------------|--------------------------------|-------------------|-------------------|---------------|
|            |                                | Temperature (Nom) | (rated) (Nom)     | Luminous Flux |
| 66416999   | SM386C S5 P10 935 PSD WB BK    | 3500 K            | 64 lm/W           | 575 lm        |
| 66417699   | SM386C S5 P10 940 PSD WB BK    | 4000 K            | 64 lm/W           | 575 lm        |
| 66267799   | RS386B S5 P10 930 PSU-E NB BK  | 3000 K            | 64 lm/W           | 575 lm        |
| 66268499   | RS386B S5 P10 930 PSU-E MB BK  | 3000 K            | 64 lm/W           | 575 lm        |
| 66269199   | RS386B S5 P10 930 PSU-E WB BK  | 3000 K            | 64 lm/W           | 575 lm        |
| 66270799   | RS386B S5 P10 935 PSU-E NB BK  | 3500 K            | 64 lm/W           | 575 lm        |
| 66271499   | RS386B S5 P10 935 PSU-E MB BK  | 3500 K            | 64 lm/W           | 575 lm        |
| 66272199   | RS386B S5 P10 935 PSU-E WB BK  | 3500 K            | 64 lm/W           | 575 lm        |
| 66273899   | RS386B S5 P10 940 PSU-E WB BK  | 4000 K            | 64 lm/W           | 575 lm        |
| 66295099   | RS386B S5 P10 930 PSR-E NB BK  | 3000 K            | 64 lm/W           | 575 lm        |
| 66296799   | RS386B S5 P10 930 PSR-E MB BK  | 3000 K            | 64 lm/W           | 575 lm        |
| 66297499   | RS386B S5 P10 930 PSR-E WB BK  | 3000 K            | 64 lm/W           | 575 lm        |
| 66298199   | RS386B S5 P10 935 PSR-E NB BK  | 3500 K            | 64 lm/W           | 575 lm        |
| 66299899   | RS386B S5 P10 935 PSR-E MB BK  | 3500 K            | 64 lm/W           | 575 lm        |
| 66300199   | RS386B S5 P10 935 PSR-E WB BK  | 3500 K            | 64 lm/W           | 575 lm        |
| 66301899   | RS386B S5 P10 940 PSR-E WB BK  | 4000 K            | 64 lm/W           | 575 lm        |
| 66379799   | RS386B S5 P10 930 PSD-E NB BK  | 3000 K            | 64 lm/W           | 575 lm        |
| 66380399   | RS386B S5 P10 930 PSD-E MB BK  | 3000 K            | 64 lm/W           | 575 lm        |
| 66381099   | RS386B S5 P10 930 PSD-E WB BK  | 3000 K            | 64 lm/W           | 575 lm        |
| 66382799   | RS386B S5 P10 935 PSD-E NB BK  | 3500 K            | 64 lm/W           | 575 lm        |
| 66383499   | RS386B S5 P10 935 PSD-E MB BK  | 3500 K            | 64 lm/W           | 575 lm        |
| 66384199   | RS386B S5 P10 935 PSD-E WB BK  | 3500 K            | 64 lm/W           | 575 lm        |
| 66385899   | RS386B S5 P10 940 PSD-E WB BK  | 4000 K            | 64 lm/W           | 575 lm        |
| 66281399   | RS386B S10 P20 930 PSU-E NB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66282099   | RS386B S10 P20 930 PSU-E MB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66283799   | RS386B S10 P20 930 PSU-E WB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66284499   | RS386B S10 P20 935 PSU-E NB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66285199   | RS386B S10 P20 935 PSU-E MB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66286899   | RS386B S10 P20 935 PSU-E WB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66287599   | RS386B S10 P20 940 PSU-E WB BK | 4000 K            | 65 lm/W           | 1,150 lm      |
| 66309499   | RS386B S10 P20 930 PSR-E NB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66310099   | RS386B S10 P20 930 PSR-E MB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66311799   | RS386B S10 P20 930 PSR-E WB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66312499   | RS386B S10 P20 935 PSR-E NB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66313199   | RS386B S10 P20 935 PSR-E MB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66314899   | RS386B S10 P20 935 PSR-E WB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66315599   | RS386B S10 P20 940 PSR-E WB BK | 4000 K            | 65 lm/W           | 1,150 lm      |
| 66393399   | RS386B S10 P20 930 PSD-E NB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66394099   | RS386B S10 P20 930 PSD-E MB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66395799   | RS386B S10 P20 930 PSD-E WB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 66396499   | RS386B S10 P20 935 PSD-E NB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66397199   | RS386B S10 P20 935 PSD-E MB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66398899   | RS386B S10 P20 935 PSD-E WB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 66399599   | RS386B S10 P20 940 PSD-E WB BK | 4000 K            | 65 lm/W           | 1,150 lm      |

Operating and Electrical

| Order Code | Full Product Name             | Power Consumption | Order Code | Full Product Name             | Power Consumption |
|------------|-------------------------------|-------------------|------------|-------------------------------|-------------------|
| 66260899   | RS386B S5 P10 930 PSU-E NB WH | 9 W               | 66263999   | RS386B S5 P10 935 PSU-E NB WH | 9 W               |
| 66261599   | RS386B S5 P10 930 PSU-E MB WH | 9 W               | 66264699   | RS386B S5 P10 935 PSU-E MB WH | 9 W               |
| 66262299   | RS386B S5 P10 930 PSU-E WB WH | 9 W               | 66265399   | RS386B S5 P10 935 PSU-E WB WH | 9 W               |

GreenSpace linear accent

| Order Code | Full Product Name             | Power Consumption |
|------------|-------------------------------|-------------------|
| 66266099   | RS386B S5 P10 940 PSU-E WB WH | 9 W               |
| 66288299   | RS386B S5 P10 930 PSR-E NB WH | 10 W              |
| 66289999   | RS386B S5 P10 930 PSR-E MB WH | 10 W              |
| 66290599   | RS386B S5 P10 930 PSR-E WB WH | 10 W              |
| 66291299   | RS386B S5 P10 935 PSR-E NB WH | 10 W              |
| 66292999   | RS386B S5 P10 935 PSR-E MB WH | 10 W              |
| 66293699   | RS386B S5 P10 935 PSR-E WB WH | 10 W              |
| 66294399   | RS386B S5 P10 940 PSR-E WB WH | 10 W              |
| 66372899   | RS386B S5 P10 930 PSD-E NB WH | 10 W              |
| 66373599   | RS386B S5 P10 930 PSD-E MB WH | 10 W              |
| 66374299   | RS386B S5 P10 930 PSD-E WB WH | 10 W              |
| 66375999   | RS386B S5 P10 935 PSD-E NB WH | 10 W              |
| 66376699   | RS386B S5 P10 935 PSD-E MB WH | 10 W              |
| 66377399   | RS386B S5 P10 935 PSD-E WB WH | 10 W              |
| 66378099   | RS386B S5 P10 940 PSD-E WB WH | 10 W              |
| 66337799   | SM386C S10 P20 930 PSU NB BK  | 18 W              |
| 66338499   | SM386C S10 P20 930 PSU MB BK  | 18 W              |
| 66339199   | SM386C S10 P20 930 PSU WB BK  | 18 W              |
| 66340799   | SM386C S10 P20 935 PSU NB BK  | 18 W              |
| 66341499   | SM386C S10 P20 935 PSU MB BK  | 18 W              |
| 66342199   | SM386C S10 P20 935 PSU WB BK  | 18 W              |
| 66343899   | SM386C S10 P20 940 PSU WB BK  | 18 W              |
| 66365099   | SM386C S10 P20 930 PSR NB BK  | 18 W              |
| 66366799   | SM386C S10 P20 930 PSR MB BK  | 18 W              |
| 66367499   | SM386C S10 P20 930 PSR WB BK  | 18 W              |
| 66368199   | SM386C S10 P20 935 PSR NB BK  | 18 W              |
| 66369899   | SM386C S10 P20 935 PSR MB BK  | 18 W              |
| 66370499   | SM386C S10 P20 935 PSR WB BK  | 18 W              |
| 66371199   | SM386C S10 P20 940 PSR WB BK  | 18 W              |
| 66427599   | SM386C S10 P20 930 PSD NB BK  | 18 W              |
| 66428299   | SM386C S10 P20 930 PSD MB BK  | 18 W              |
| 66429999   | SM386C S10 P20 930 PSD WB BK  | 18 W              |
| 66430599   | SM386C S10 P20 935 PSD NB BK  | 18 W              |
| 66433699   | SM386C S10 P20 935 PSD MB BK  | 18 W              |
| 66434399   | SM386C S10 P20 935 PSD WB BK  | 18 W              |
| 66435099   | SM386C S10 P20 940 PSD WB BK  | 18 W              |
| 66330899   | SM386C S10 P20 930 PSU NB WH  | 18 W              |
| 66331599   | SM386C S10 P20 930 PSU MB WH  | 18 W              |
| 66332299   | SM386C S10 P20 930 PSU WB WH  | 18 W              |
| 66333999   | SM386C S10 P20 935 PSU NB WH  | 18 W              |
| 66334699   | SM386C S10 P20 935 PSU MB WH  | 18 W              |
| 66335399   | SM386C S10 P20 935 PSU WB WH  | 18 W              |
| 66336099   | SM386C S10 P20 940 PSU WB WH  | 18 W              |
| 66358299   | SM386C S10 P20 930 PSR NB WH  | 18 W              |
| 66359999   | SM386C S10 P20 930 PSR MB WH  | 18 W              |
| 66360599   | SM386C S10 P20 930 PSR WB WH  | 18 W              |
| 66361299   | SM386C S10 P20 935 PSR NB WH  | 18 W              |
| 66362999   | SM386C S10 P20 935 PSR MB WH  | 18 W              |
| 66363699   | SM386C S10 P20 935 PSR WB WH  | 18 W              |
| 66364399   | SM386C S10 P20 940 PSR WB WH  | 18 W              |
| 66418399   | SM386C S10 P20 930 PSD NB WH  | 18 W              |
| 66419099   | SM386C S10 P20 930 PSD MB WH  | 18 W              |

| Order Code | Full Product Name              | Power Consumption |
|------------|--------------------------------|-------------------|
| 66420699   | SM386C S10 P20 930 PSD WB WH   | 18 W              |
| 66423799   | SM386C S10 P20 935 PSD NB WH   | 18 W              |
| 66424499   | SM386C S10 P20 935 PSD MB WH   | 18 W              |
| 66425199   | SM386C S10 P20 935 PSD WB WH   | 18 W              |
| 66426899   | SM386C S10 P20 940 PSD WB WH   | 18 W              |
| 66316299   | SM386C S5 P10 930 PSU NB WH    | 9 W               |
| 66317999   | SM386C S5 P10 930 PSU MB WH    | 9 W               |
| 66318699   | SM386C S5 P10 930 PSU WB WH    | 9 W               |
| 66319399   | SM386C S5 P10 935 PSU NB WH    | 9 W               |
| 66320999   | SM386C S5 P10 935 PSU MB WH    | 9 W               |
| 66321699   | SM386C S5 P10 935 PSU WB WH    | 9 W               |
| 66322399   | SM386C S5 P10 940 PSU WB WH    | 9 W               |
| 66344599   | SM386C S5 P10 930 PSR NB WH    | 10 W              |
| 66345299   | SM386C S5 P10 930 PSR MB WH    | 10 W              |
| 66346999   | SM386C S5 P10 930 PSR WB WH    | 10 W              |
| 66347699   | SM386C S5 P10 935 PSR NB WH    | 10 W              |
| 66348399   | SM386C S5 P10 935 PSR MB WH    | 10 W              |
| 66349099   | SM386C S5 P10 935 PSR WB WH    | 10 W              |
| 66350699   | SM386C S5 P10 940 PSR WB WH    | 10 W              |
| 66400899   | SM386C S5 P10 930 PSD NB WH    | 10 W              |
| 66403999   | SM386C S5 P10 930 PSD MB WH    | 10 W              |
| 66404699   | SM386C S5 P10 930 PSD WB WH    | 10 W              |
| 66405399   | SM386C S5 P10 935 PSD NB WH    | 10 W              |
| 66406099   | SM386C S5 P10 935 PSD MB WH    | 10 W              |
| 66407799   | SM386C S5 P10 935 PSD WB WH    | 10 W              |
| 66408499   | SM386C S5 P10 940 PSD WB WH    | 10 W              |
| 66274599   | RS386B S10 P20 930 PSU-E NB WH | 18 W              |
| 66275299   | RS386B S10 P20 930 PSU-E MB WH | 18 W              |
| 66276999   | RS386B S10 P20 930 PSU-E WB WH | 18 W              |
| 66277699   | RS386B S10 P20 935 PSU-E NB WH | 18 W              |
| 66278399   | RS386B S10 P20 935 PSU-E MB WH | 18 W              |
| 66279099   | RS386B S10 P20 935 PSU-E WB WH | 18 W              |
| 66280699   | RS386B S10 P20 940 PSU-E WB WH | 18 W              |
| 66302599   | RS386B S10 P20 930 PSR-E NB WH | 18 W              |
| 66303299   | RS386B S10 P20 930 PSR-E MB WH | 18 W              |
| 66304999   | RS386B S10 P20 930 PSR-E WB WH | 18 W              |
| 66305699   | RS386B S10 P20 935 PSR-E NB WH | 18 W              |
| 66306399   | RS386B S10 P20 935 PSR-E MB WH | 18 W              |
| 66307099   | RS386B S10 P20 935 PSR-E WB WH | 18 W              |
| 66308799   | RS386B S10 P20 940 PSR-E WB WH | 18 W              |
| 66386599   | RS386B S10 P20 930 PSD-E NB WH | 18 W              |
| 66387299   | RS386B S10 P20 930 PSD-E MB WH | 18 W              |
| 66388999   | RS386B S10 P20 930 PSD-E WB WH | 18 W              |
| 66389699   | RS386B S10 P20 935 PSD-E NB WH | 18 W              |
| 66390299   | RS386B S10 P20 935 PSD-E MB WH | 18 W              |
| 66391999   | RS386B S10 P20 935 PSD-E WB WH | 18 W              |
| 66392699   | RS386B S10 P20 940 PSD-E WB WH | 18 W              |
| 66323099   | SM386C S5 P10 930 PSU NB BK    | 9 W               |
| 66324799   | SM386C S5 P10 930 PSU MB BK    | 9 W               |
| 66325499   | SM386C S5 P10 930 PSU WB BK    | 9 W               |
| 66326199   | SM386C S5 P10 935 PSU NB BK    | 9 W               |
| 66327899   | SM386C S5 P10 935 PSU MB BK    | 9 W               |

GreenSpace linear accent

| Order Code | Full Product Name             | Power Consumption |
|------------|-------------------------------|-------------------|
| 66328599   | SM386C S5 P10 935 PSU WB BK   | 9 W               |
| 66329299   | SM386C S5 P10 940 PSU WB BK   | 9 W               |
| 66351399   | SM386C S5 P10 930 PSR NB BK   | 10 W              |
| 66352099   | SM386C S5 P10 930 PSR MB BK   | 10 W              |
| 66353799   | SM386C S5 P10 930 PSR WB BK   | 10 W              |
| 66354499   | SM386C S5 P10 935 PSR NB BK   | 10 W              |
| 66355199   | SM386C S5 P10 935 PSR MB BK   | 10 W              |
| 66356899   | SM386C S5 P10 935 PSR WB BK   | 10 W              |
| 66357599   | SM386C S5 P10 940 PSR WB BK   | 10 W              |
| 66409199   | SM386C S5 P10 930 PSD NB BK   | 10 W              |
| 66410799   | SM386C S5 P10 930 PSD MB BK   | 10 W              |
| 66413899   | SM386C S5 P10 930 PSD WB BK   | 10 W              |
| 66414599   | SM386C S5 P10 935 PSD NB BK   | 10 W              |
| 66415299   | SM386C S5 P10 935 PSD MB BK   | 10 W              |
| 66416999   | SM386C S5 P10 935 PSD WB BK   | 10 W              |
| 66417699   | SM386C S5 P10 940 PSD WB BK   | 10 W              |
| 66267799   | RS386B S5 P10 930 PSU-E NB BK | 9 W               |
| 66268499   | RS386B S5 P10 930 PSU-E MB BK | 9 W               |
| 66269199   | RS386B S5 P10 930 PSU-E WB BK | 9 W               |
| 66270799   | RS386B S5 P10 935 PSU-E NB BK | 9 W               |
| 66271499   | RS386B S5 P10 935 PSU-E MB BK | 9 W               |
| 66272199   | RS386B S5 P10 935 PSU-E WB BK | 9 W               |
| 66273899   | RS386B S5 P10 940 PSU-E WB BK | 9 W               |
| 66295099   | RS386B S5 P10 930 PSR-E NB BK | 10 W              |
| 66296799   | RS386B S5 P10 930 PSR-E MB BK | 10 W              |
| 66297499   | RS386B S5 P10 930 PSR-E WB BK | 10 W              |
| 66298199   | RS386B S5 P10 935 PSR-E NB BK | 10 W              |
| 66299899   | RS386B S5 P10 935 PSR-E MB BK | 10 W              |
| 66300199   | RS386B S5 P10 935 PSR-E WB BK | 10 W              |

| Order Code | Full Product Name              | Power Consumption |
|------------|--------------------------------|-------------------|
| 66301899   | RS386B S5 P10 940 PSR-E WB BK  | 10 W              |
| 66379799   | RS386B S5 P10 930 PSD-E NB BK  | 10 W              |
| 66380399   | RS386B S5 P10 930 PSD-E MB BK  | 10 W              |
| 66381099   | RS386B S5 P10 930 PSD-E WB BK  | 10 W              |
| 66382799   | RS386B S5 P10 935 PSD-E NB BK  | 10 W              |
| 66383499   | RS386B S5 P10 935 PSD-E MB BK  | 10 W              |
| 66384199   | RS386B S5 P10 935 PSD-E WB BK  | 10 W              |
| 66385899   | RS386B S5 P10 940 PSD-E WB BK  | 10 W              |
| 66281399   | RS386B S10 P20 930 PSU-E NB BK | 18 W              |
| 66282099   | RS386B S10 P20 930 PSU-E MB BK | 18 W              |
| 66283799   | RS386B S10 P20 930 PSU-E WB BK | 18 W              |
| 66284499   | RS386B S10 P20 935 PSU-E NB BK | 18 W              |
| 66285199   | RS386B S10 P20 935 PSU-E MB BK | 18 W              |
| 66286899   | RS386B S10 P20 935 PSU-E WB BK | 18 W              |
| 66287599   | RS386B S10 P20 940 PSU-E WB BK | 18 W              |
| 66309499   | RS386B S10 P20 930 PSR-E NB BK | 18 W              |
| 66310099   | RS386B S10 P20 930 PSR-E MB BK | 18 W              |
| 66311799   | RS386B S10 P20 930 PSR-E WB BK | 18 W              |
| 66312499   | RS386B S10 P20 935 PSR-E NB BK | 18 W              |
| 66313199   | RS386B S10 P20 935 PSR-E MB BK | 18 W              |
| 66314899   | RS386B S10 P20 935 PSR-E WB BK | 18 W              |
| 66315599   | RS386B S10 P20 940 PSR-E WB BK | 18 W              |
| 66393399   | RS386B S10 P20 930 PSD-E NB BK | 18 W              |
| 66394099   | RS386B S10 P20 930 PSD-E MB BK | 18 W              |
| 66395799   | RS386B S10 P20 930 PSD-E WB BK | 18 W              |
| 66396499   | RS386B S10 P20 935 PSD-E NB BK | 18 W              |
| 66397199   | RS386B S10 P20 935 PSD-E MB BK | 18 W              |
| 66398899   | RS386B S10 P20 935 PSD-E WB BK | 18 W              |
| 66399599   | RS386B S10 P20 940 PSD-E WB BK | 18 W              |

Controls and Dimming

| Order Code | Full Product Name             | Dimmable |
|------------|-------------------------------|----------|
| 66260899   | RS386B S5 P10 930 PSU-E NB WH | No       |
| 66261599   | RS386B S5 P10 930 PSU-E MB WH | No       |
| 66262299   | RS386B S5 P10 930 PSU-E WB WH | No       |
| 66263999   | RS386B S5 P10 935 PSU-E NB WH | No       |
| 66264699   | RS386B S5 P10 935 PSU-E MB WH | No       |
| 66265399   | RS386B S5 P10 935 PSU-E WB WH | No       |
| 66266099   | RS386B S5 P10 940 PSU-E WB WH | No       |
| 66288299   | RS386B S5 P10 930 PSR-E NB WH | Yes      |
| 66289999   | RS386B S5 P10 930 PSR-E MB WH | Yes      |
| 66290599   | RS386B S5 P10 930 PSR-E WB WH | Yes      |
| 66291299   | RS386B S5 P10 935 PSR-E NB WH | Yes      |
| 66292999   | RS386B S5 P10 935 PSR-E MB WH | Yes      |
| 66293699   | RS386B S5 P10 935 PSR-E WB WH | Yes      |
| 66294399   | RS386B S5 P10 940 PSR-E WB WH | Yes      |
| 66372899   | RS386B S5 P10 930 PSD-E NB WH | Yes      |
| 66373599   | RS386B S5 P10 930 PSD-E MB WH | Yes      |
| 66374299   | RS386B S5 P10 930 PSD-E WB WH | Yes      |
| 66375999   | RS386B S5 P10 935 PSD-E NB WH | Yes      |
| 66376699   | RS386B S5 P10 935 PSD-E MB WH | Yes      |

| Order Code | Full Product Name             | Dimmable |
|------------|-------------------------------|----------|
| 66377399   | RS386B S5 P10 935 PSD-E WB WH | Yes      |
| 66378099   | RS386B S5 P10 940 PSD-E WB WH | Yes      |
| 66337799   | SM386C S10 P20 930 PSU NB BK  | No       |
| 66338499   | SM386C S10 P20 930 PSU MB BK  | No       |
| 66339199   | SM386C S10 P20 930 PSU WB BK  | No       |
| 66340799   | SM386C S10 P20 935 PSU NB BK  | No       |
| 66341499   | SM386C S10 P20 935 PSU MB BK  | No       |
| 66342199   | SM386C S10 P20 935 PSU WB BK  | No       |
| 66343899   | SM386C S10 P20 940 PSU WB BK  | No       |
| 66365099   | SM386C S10 P20 930 PSR NB BK  | Yes      |
| 66366799   | SM386C S10 P20 930 PSR MB BK  | Yes      |
| 66367499   | SM386C S10 P20 930 PSR WB BK  | Yes      |
| 66368199   | SM386C S10 P20 935 PSR NB BK  | Yes      |
| 66369899   | SM386C S10 P20 935 PSR MB BK  | Yes      |
| 66370499   | SM386C S10 P20 935 PSR WB BK  | Yes      |
| 66371199   | SM386C S10 P20 940 PSR WB BK  | Yes      |
| 66427599   | SM386C S10 P20 930 PSD NB BK  | Yes      |
| 66428299   | SM386C S10 P20 930 PSD MB BK  | Yes      |
| 66429999   | SM386C S10 P20 930 PSD WB BK  | Yes      |



## GreenSpace linear accent

| Order Code | Full Product Name              | Dimmable |
|------------|--------------------------------|----------|
| 66430599   | SM386C S10 P20 935 PSD NB BK   | Yes      |
| 66433699   | SM386C S10 P20 935 PSD MB BK   | Yes      |
| 66434399   | SM386C S10 P20 935 PSD WB BK   | Yes      |
| 66435099   | SM386C S10 P20 940 PSD WB BK   | Yes      |
| 66330899   | SM386C S10 P20 930 PSU NB WH   | No       |
| 66331599   | SM386C S10 P20 930 PSU MB WH   | No       |
| 66332299   | SM386C S10 P20 930 PSU WB WH   | No       |
| 66333999   | SM386C S10 P20 935 PSU NB WH   | No       |
| 66334699   | SM386C S10 P20 935 PSU MB WH   | No       |
| 66335399   | SM386C S10 P20 935 PSU WB WH   | No       |
| 66336099   | SM386C S10 P20 940 PSU WB WH   | No       |
| 66358299   | SM386C S10 P20 930 PSR NB WH   | Yes      |
| 66359999   | SM386C S10 P20 930 PSR MB WH   | Yes      |
| 66360599   | SM386C S10 P20 930 PSR WB WH   | Yes      |
| 66361299   | SM386C S10 P20 935 PSR NB WH   | Yes      |
| 66362999   | SM386C S10 P20 935 PSR MB WH   | Yes      |
| 66363699   | SM386C S10 P20 935 PSR WB WH   | Yes      |
| 66364399   | SM386C S10 P20 940 PSR WB WH   | Yes      |
| 66418399   | SM386C S10 P20 930 PSD NB WH   | Yes      |
| 66419099   | SM386C S10 P20 930 PSD MB WH   | Yes      |
| 66420699   | SM386C S10 P20 930 PSD WB WH   | Yes      |
| 66423799   | SM386C S10 P20 935 PSD NB WH   | Yes      |
| 66424499   | SM386C S10 P20 935 PSD MB WH   | Yes      |
| 66425199   | SM386C S10 P20 935 PSD WB WH   | Yes      |
| 66426899   | SM386C S10 P20 940 PSD WB WH   | Yes      |
| 66316299   | SM386C S5 P10 930 PSU NB WH    | No       |
| 66317999   | SM386C S5 P10 930 PSU MB WH    | No       |
| 66318699   | SM386C S5 P10 930 PSU WB WH    | No       |
| 66319399   | SM386C S5 P10 935 PSU NB WH    | No       |
| 66320999   | SM386C S5 P10 935 PSU MB WH    | No       |
| 66321699   | SM386C S5 P10 935 PSU WB WH    | No       |
| 66322399   | SM386C S5 P10 940 PSU WB WH    | No       |
| 66344599   | SM386C S5 P10 930 PSR NB WH    | Yes      |
| 66345299   | SM386C S5 P10 930 PSR MB WH    | Yes      |
| 66346999   | SM386C S5 P10 930 PSR WB WH    | Yes      |
| 66347699   | SM386C S5 P10 935 PSR NB WH    | Yes      |
| 66348399   | SM386C S5 P10 935 PSR MB WH    | Yes      |
| 66349099   | SM386C S5 P10 935 PSR WB WH    | Yes      |
| 66350699   | SM386C S5 P10 940 PSR WB WH    | Yes      |
| 66400899   | SM386C S5 P10 930 PSD NB WH    | Yes      |
| 66403999   | SM386C S5 P10 930 PSD MB WH    | Yes      |
| 66404699   | SM386C S5 P10 930 PSD WB WH    | Yes      |
| 66405399   | SM386C S5 P10 935 PSD NB WH    | Yes      |
| 66406099   | SM386C S5 P10 935 PSD MB WH    | Yes      |
| 66407799   | SM386C S5 P10 935 PSD WB WH    | Yes      |
| 66408499   | SM386C S5 P10 940 PSD WB WH    | Yes      |
| 66274599   | RS386B S10 P20 930 PSU-E NB WH | No       |
| 66275299   | RS386B S10 P20 930 PSU-E MB WH | No       |
| 66276999   | RS386B S10 P20 930 PSU-E WB WH | No       |
| 66277699   | RS386B S10 P20 935 PSU-E NB WH | No       |
| 66278399   | RS386B S10 P20 935 PSU-E MB WH | No       |
| 66279099   | RS386B S10 P20 935 PSU-E WB WH | No       |

| Order Code | Full Product Name              | Dimmable |
|------------|--------------------------------|----------|
| 66280699   | RS386B S10 P20 940 PSU-E WB WH | No       |
| 66302599   | RS386B S10 P20 930 PSR-E NB WH | Yes      |
| 66303299   | RS386B S10 P20 930 PSR-E MB WH | Yes      |
| 66304999   | RS386B S10 P20 930 PSR-E WB WH | Yes      |
| 66305699   | RS386B S10 P20 935 PSR-E NB WH | Yes      |
| 66306399   | RS386B S10 P20 935 PSR-E MB WH | Yes      |
| 66307099   | RS386B S10 P20 935 PSR-E WB WH | Yes      |
| 66308799   | RS386B S10 P20 940 PSR-E WB WH | Yes      |
| 66386599   | RS386B S10 P20 930 PSD-E NB WH | Yes      |
| 66387299   | RS386B S10 P20 930 PSD-E MB WH | Yes      |
| 66388999   | RS386B S10 P20 930 PSD-E WB WH | Yes      |
| 66389699   | RS386B S10 P20 935 PSD-E NB WH | Yes      |
| 66390299   | RS386B S10 P20 935 PSD-E MB WH | Yes      |
| 66391999   | RS386B S10 P20 935 PSD-E WB WH | Yes      |
| 66392699   | RS386B S10 P20 940 PSD-E WB WH | Yes      |
| 66323099   | SM386C S5 P10 930 PSU NB BK    | No       |
| 66324799   | SM386C S5 P10 930 PSU MB BK    | No       |
| 66325499   | SM386C S5 P10 930 PSU WB BK    | No       |
| 66326199   | SM386C S5 P10 935 PSU NB BK    | No       |
| 66327899   | SM386C S5 P10 935 PSU MB BK    | No       |
| 66328599   | SM386C S5 P10 935 PSU WB BK    | No       |
| 66329299   | SM386C S5 P10 940 PSU WB BK    | No       |
| 66351399   | SM386C S5 P10 930 PSR NB BK    | Yes      |
| 66352099   | SM386C S5 P10 930 PSR MB BK    | Yes      |
| 66353799   | SM386C S5 P10 930 PSR WB BK    | Yes      |
| 66354499   | SM386C S5 P10 935 PSR NB BK    | Yes      |
| 66355199   | SM386C S5 P10 935 PSR MB BK    | Yes      |
| 66356899   | SM386C S5 P10 935 PSR WB BK    | Yes      |
| 66357599   | SM386C S5 P10 940 PSR WB BK    | Yes      |
| 66409199   | SM386C S5 P10 930 PSD NB BK    | Yes      |
| 66410799   | SM386C S5 P10 930 PSD MB BK    | Yes      |
| 66413899   | SM386C S5 P10 930 PSD WB BK    | Yes      |
| 66414599   | SM386C S5 P10 935 PSD NB BK    | Yes      |
| 66415299   | SM386C S5 P10 935 PSD MB BK    | Yes      |
| 66416999   | SM386C S5 P10 935 PSD WB BK    | Yes      |
| 66417699   | SM386C S5 P10 940 PSD WB BK    | Yes      |
| 66267799   | RS386B S5 P10 930 PSU-E NB BK  | No       |
| 66268499   | RS386B S5 P10 930 PSU-E MB BK  | No       |
| 66269199   | RS386B S5 P10 930 PSU-E WB BK  | No       |
| 66270799   | RS386B S5 P10 935 PSU-E NB BK  | No       |
| 66271499   | RS386B S5 P10 935 PSU-E MB BK  | No       |
| 66272199   | RS386B S5 P10 935 PSU-E WB BK  | No       |
| 66273899   | RS386B S5 P10 940 PSU-E WB BK  | No       |
| 66295099   | RS386B S5 P10 930 PSR-E NB BK  | Yes      |
| 66296799   | RS386B S5 P10 930 PSR-E MB BK  | Yes      |
| 66297499   | RS386B S5 P10 930 PSR-E WB BK  | Yes      |
| 66298199   | RS386B S5 P10 935 PSR-E NB BK  | Yes      |
| 66299899   | RS386B S5 P10 935 PSR-E MB BK  | Yes      |
| 66300199   | RS386B S5 P10 935 PSR-E WB BK  | Yes      |
| 66301899   | RS386B S5 P10 940 PSR-E WB BK  | Yes      |
| 66379799   | RS386B S5 P10 930 PSD-E NB BK  | Yes      |
| 66380399   | RS386B S5 P10 930 PSD-E MB BK  | Yes      |



GreenSpace linear accent

| Order Code | Full Product Name              | Dimmable |
|------------|--------------------------------|----------|
| 66381099   | RS386B S5 P10 930 PSD-E WB BK  | Yes      |
| 66382799   | RS386B S5 P10 935 PSD-E NB BK  | Yes      |
| 66383499   | RS386B S5 P10 935 PSD-E MB BK  | Yes      |
| 66384199   | RS386B S5 P10 935 PSD-E WB BK  | Yes      |
| 66385899   | RS386B S5 P10 940 PSD-E WB BK  | Yes      |
| 66281399   | RS386B S10 P20 930 PSU-E NB BK | No       |
| 66282099   | RS386B S10 P20 930 PSU-E MB BK | No       |
| 66283799   | RS386B S10 P20 930 PSU-E WB BK | No       |
| 66284499   | RS386B S10 P20 935 PSU-E NB BK | No       |
| 66285199   | RS386B S10 P20 935 PSU-E MB BK | No       |
| 66286899   | RS386B S10 P20 935 PSU-E WB BK | No       |
| 66287599   | RS386B S10 P20 940 PSU-E WB BK | No       |
| 66309499   | RS386B S10 P20 930 PSR-E NB BK | Yes      |

| Order Code | Full Product Name              | Dimmable |
|------------|--------------------------------|----------|
| 66310099   | RS386B S10 P20 930 PSR-E MB BK | Yes      |
| 66311799   | RS386B S10 P20 930 PSR-E WB BK | Yes      |
| 66312499   | RS386B S10 P20 935 PSR-E NB BK | Yes      |
| 66313199   | RS386B S10 P20 935 PSR-E MB BK | Yes      |
| 66314899   | RS386B S10 P20 935 PSR-E WB BK | Yes      |
| 66315599   | RS386B S10 P20 940 PSR-E WB BK | Yes      |
| 66393399   | RS386B S10 P20 930 PSD-E NB BK | Yes      |
| 66394099   | RS386B S10 P20 930 PSD-E MB BK | Yes      |
| 66395799   | RS386B S10 P20 930 PSD-E WB BK | Yes      |
| 66396499   | RS386B S10 P20 935 PSD-E NB BK | Yes      |
| 66397199   | RS386B S10 P20 935 PSD-E MB BK | Yes      |
| 66398899   | RS386B S10 P20 935 PSD-E WB BK | Yes      |
| 66399599   | RS386B S10 P20 940 PSD-E WB BK | Yes      |

