



Shining in a linear way

GreenSpace linear accent

GreenSpace Linear accent is a comprehensive product offer with multiple modules available. By means of its modular design, it offers flexible lumen output for different indoor applications, such as office, retail and hospitality. This family provides both surface mounted and recessed installations with high CRI90 and 3 different beam angles to perfectly fit the light requirement of the indoor applications. Dali and 1-10V control interfaces give the way for future system connections as well.

Benefits

- Flexible lumen output by means of multiple modules design
- High color rendering index helps better visual comfort in office and retail applications
- 3 different beams facilitate the lighting designer for wide lighting applications
- System interface available to easily control the lights

Features

- Multiple modules combinations available
- Both surface mounted and recessed installations are offered
- CRI 90 high color rendering index available
- Narrow/medium/wide beams options
- Dali / 1-10V control system interface available

Application

- Open offices
- Retail
- Meeting rooms
- Hospitality

GreenSpace linear accent





Versions



GreenSpace Linear Accent

GreenSpace Linear Accent

Dimensional drawing



GreenSpace linear accent

General Information	
CE mark	-
Light Technical	
Optical cover type	Polycarbonate cover and gloss high-reflective optic
Color rendering index (CRI)	>90
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	-20 to +40 °C
Mechanical and Housing	
Housing Color	Black and white
Approval and Application	
Protection class IEC	Safety class II
Mech. impact protection code	IK02
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401510202	RS386B S5 P10 930 PSU-E NB WH	3000 K	64 lm/W	575 lm
911401510302	RS386B S5 P10 930 PSU-E MB WH	3000 K	64 lm/W	575 lm
911401510402	RS386B S5 P10 930 PSU-E WB WH	3000 K	64 lm/W	575 lm
911401510502	RS386B S5 P10 935 PSU-E NB WH	3500 K	64 lm/W	575 lm
911401510602	RS386B S5 P10 935 PSU-E MB WH	3500 K	64 lm/W	575 lm
911401510702	RS386B S5 P10 935 PSU-E WB WH	3500 K	64 lm/W	575 lm
911401510802	RS386B S5 P10 940 PSU-E WB WH	4000 K	64 lm/W	575 lm
911401513002	RS386B S5 P10 930 PSR-E NB WH	3000 K	64 lm/W	575 lm
911401513102	RS386B S5 P10 930 PSR-E MB WH	3000 K	64 lm/W	575 lm
911401513202	RS386B S5 P10 930 PSR-E WB WH	3000 K	64 lm/W	575 lm
911401513302	RS386B S5 P10 935 PSR-E NB WH	3500 K	64 lm/W	575 lm
911401513402	RS386B S5 P10 935 PSR-E MB WH	3500 K	64 lm/W	575 lm
911401513502	RS386B S5 P10 935 PSR-E WB WH	3500 K	64 lm/W	575 lm
911401513602	RS386B S5 P10 940 PSR-E WB WH	4000 K	64 lm/W	575 lm
911401521402	RS386B S5 P10 930 PSD-E NB WH	3000 K	64 lm/W	575 lm
911401521502	RS386B S5 P10 930 PSD-E MB WH	3000 K	64 lm/W	575 lm
911401521602	RS386B S5 P10 930 PSD-E WB WH	3000 K	64 lm/W	575 lm
911401521702	RS386B S5 P10 935 PSD-E NB WH	3500 K	64 lm/W	575 lm
911401521802	RS386B S5 P10 935 PSD-E MB WH	3500 K	64 lm/W	575 lm
911401521902	RS386B S5 P10 935 PSD-E WB WH	3500 K	64 lm/W	575 lm
911401522002	RS386B S5 P10 940 PSD-E WB WH	4000 K	64 lm/W	575 lm
911401517902	SM386C S10 P20 930 PSU NB BK	3000 K	65 lm/W	1,150 lm
911401518002	SM386C S10 P20 930 PSU MB BK	3000 K	65 lm/W	1,150 lm
911401518102	SM386C S10 P20 930 PSU WB BK	3000 K	65 lm/W	1,150 lm
911401518202	SM386C S10 P20 935 PSU NB BK	3500 K	65 lm/W	1,150 lm
911401518302	SM386C S10 P20 935 PSU MB BK	3500 K	65 lm/W	1,150 lm
911401518402	SM386C S10 P20 935 PSU WB BK	3500 K	65 lm/W	1,150 lm
911401518502	SM386C S10 P20 940 PSU WB BK	4000 K	65 lm/W	1,150 lm
911401520702	SM386C S10 P20 930 PSR NB BK	3000 K	65 lm/W	1,150 lm
911401520802	SM386C S10 P20 930 PSR MB BK	3000 K	65 lm/W	1,150 lm
911401520902	SM386C S10 P20 930 PSR WB BK	3000 K	65 lm/W	1,150 lm
911401521002	SM386C S10 P20 935 PSR NB BK	3500 K	65 lm/W	1,150 lm
911401521102	SM386C S10 P20 935 PSR MB BK	3500 K	65 lm/W	1,150 lm
911401521202	SM386C S10 P20 935 PSR WB BK	3500 K	65 lm/W	1,150 lm
911401521302	SM386C S10 P20 940 PSR WB BK	4000 K	65 lm/W	1,150 lm
911401526302	SM386C S10 P20 930 PSD NB BK	3000 K	65 lm/W	1,150 lm
911401526402	SM386C S10 P20 930 PSD MB BK	3000 K	65 lm/W	1,150 lm
911401526502	SM386C S10 P20 930 PSD WB BK	3000 K	65 lm/W	1,150 lm
911401526602	SM386C S10 P20 935 PSD NB BK	3500 K	65 lm/W	1,150 lm
911401526702	SM386C S10 P20 935 PSD MB BK	3500 K	65 lm/W	1,150 lm
911401526802	SM386C S10 P20 935 PSD WB BK	3500 K	65 lm/W	1,150 lm
911401526902	SM386C S10 P20 940 PSD WB BK	4000 K	65 lm/W	1,150 lm
911401517202	SM386C S10 P20 930 PSU NB WH	3000 K	65 lm/W	1,150 lm
911401517302	SM386C S10 P20 930 PSU MB WH	3000 K	65 lm/W	1,150 lm
911401517402	SM386C S10 P20 930 PSU WB WH	3000 K	65 lm/W	1,150 lm
911401517502	SM386C S10 P20 935 PSU NB WH	3500 K	65 lm/W	1,150 lm
911401517602	SM386C S10 P20 935 PSU MB WH	3500 K	65 lm/W	1,150 lm
911401517702	SM386C S10 P20 935 PSU WB WH	3500 K	65 lm/W	1,150 lm
911401517802	SM386C S10 P20 940 PSU WB WH	4000 K	65 lm/W	1,150 lm
911401520002	SM386C S10 P20 930 PSR NB WH	3000 K	65 lm/W	1,150 lm

GreenSpace linear accent

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401520102	SM386C S10 P20 930 PSR MB WH	3000 K	65 lm/W	1,150 lm
911401520202	SM386C S10 P20 930 PSR WB WH	3000 K	65 lm/W	1,150 lm
911401520302	SM386C S10 P20 935 PSR NB WH	3500 K	65 lm/W	1,150 lm
911401520402	SM386C S10 P20 935 PSR MB WH	3500 K	65 lm/W	1,150 lm
911401520502	SM386C S10 P20 935 PSR WB WH	3500 K	65 lm/W	1,150 lm
911401520602	SM386C S10 P20 940 PSR WB WH	4000 K	65 lm/W	1,150 lm
911401525602	SM386C S10 P20 930 PSD NB WH	3000 K	65 lm/W	1,150 lm
911401525702	SM386C S10 P20 930 PSD MB WH	3000 K	65 lm/W	1,150 lm
911401525802	SM386C S10 P20 930 PSD WB WH	3000 K	65 lm/W	1,150 lm
911401525902	SM386C S10 P20 935 PSD NB WH	3500 K	65 lm/W	1,150 lm
911401526002	SM386C S10 P20 935 PSD MB WH	3500 K	65 lm/W	1,150 lm
911401526102	SM386C S10 P20 935 PSD WB WH	3500 K	65 lm/W	1,150 lm
911401526202	SM386C S10 P20 940 PSD WB WH	4000 K	65 lm/W	1,150 lm
911401515802	SM386C S5 P10 930 PSU NB WH	3000 K	64 lm/W	575 lm
911401515902	SM386C S5 P10 930 PSU MB WH	3000 K	64 lm/W	575 lm
911401516002	SM386C S5 P10 930 PSU WB WH	3000 K	64 lm/W	575 lm
911401516102	SM386C S5 P10 935 PSU NB WH	3500 K	64 lm/W	575 lm
911401516202	SM386C S5 P10 935 PSU MB WH	3500 K	64 lm/W	575 lm
911401516302	SM386C S5 P10 935 PSU WB WH	3500 K	64 lm/W	575 lm
911401516402	SM386C S5 P10 940 PSU WB WH	4000 K	64 lm/W	575 lm
911401518602	SM386C S5 P10 930 PSR NB WH	3000 K	64 lm/W	575 lm
911401518702	SM386C S5 P10 930 PSR MB WH	3000 K	64 lm/W	575 lm
911401518802	SM386C S5 P10 930 PSR WB WH	3000 K	64 lm/W	575 lm
911401518902	SM386C S5 P10 935 PSR NB WH	3500 K	64 lm/W	575 lm
911401519002	SM386C S5 P10 935 PSR MB WH	3500 K	64 lm/W	575 lm
911401519102	SM386C S5 P10 935 PSR WB WH	3500 K	64 lm/W	575 lm
911401519202	SM386C S5 P10 940 PSR WB WH	4000 K	64 lm/W	575 lm
911401524202	SM386C S5 P10 930 PSD NB WH	3000 K	64 lm/W	575 lm
911401524302	SM386C S5 P10 930 PSD MB WH	3000 K	64 lm/W	575 lm
911401524402	SM386C S5 P10 930 PSD WB WH	3000 K	64 lm/W	575 lm
911401524502	SM386C S5 P10 935 PSD NB WH	3500 K	64 lm/W	575 lm
911401524602	SM386C S5 P10 935 PSD MB WH	3500 K	64 lm/W	575 lm
911401524702	SM386C S5 P10 935 PSD WB WH	3500 K	64 lm/W	575 lm
911401524802	SM386C S5 P10 940 PSD WB WH	4000 K	64 lm/W	575 lm
911401511602	RS386B S10 P20 930 PSU-E NB WH	3000 K	65 lm/W	1,150 lm
911401511702	RS386B S10 P20 930 PSU-E MB WH	3000 K	65 lm/W	1,150 lm
911401511802	RS386B S10 P20 930 PSU-E WB WH	3000 K	65 lm/W	1,150 lm
911401511902	RS386B S10 P20 935 PSU-E NB WH	3500 K	65 lm/W	1,150 lm
911401512002	RS386B S10 P20 935 PSU-E MB WH	3500 K	65 lm/W	1,150 lm
911401512102	RS386B S10 P20 935 PSU-E WB WH	3500 K	65 lm/W	1,150 lm
911401512202	RS386B S10 P20 940 PSU-E WB WH	4000 K	65 lm/W	1,150 lm
911401514402	RS386B S10 P20 930 PSR-E NB WH	3000 K	65 lm/W	1,150 lm

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401514502	RS386B S10 P20 930 PSR-E MB WH	3000 K	65 lm/W	1,150 lm
911401514602	RS386B S10 P20 930 PSR-E WB WH	3000 K	65 lm/W	1,150 lm
911401514702	RS386B S10 P20 935 PSR-E NB WH	3500 K	65 lm/W	1,150 lm
911401514802	RS386B S10 P20 935 PSR-E MB WH	3500 K	65 lm/W	1,150 lm
911401514902	RS386B S10 P20 935 PSR-E WB WH	3500 K	65 lm/W	1,150 lm
911401515002	RS386B S10 P20 940 PSR-E WB WH	4000 K	65 lm/W	1,150 lm
911401522802	RS386B S10 P20 930 PSD-E NB WH	3000 K	65 lm/W	1,150 lm
911401522902	RS386B S10 P20 930 PSD-E MB WH	3000 K	65 lm/W	1,150 lm
911401523002	RS386B S10 P20 930 PSD-E WB WH	3000 K	65 lm/W	1,150 lm
911401523102	RS386B S10 P20 935 PSD-E NB WH	3500 K	65 lm/W	1,150 lm
911401523202	RS386B S10 P20 935 PSD-E MB WH	3500 K	65 lm/W	1,150 lm
911401523302	RS386B S10 P20 935 PSD-E WB WH	3500 K	65 lm/W	1,150 lm
911401523402	RS386B S10 P20 940 PSD-E WB WH	4000 K	65 lm/W	1,150 lm
911401516502	SM386C S5 P10 930 PSU NB BK	3000 K	64 lm/W	575 lm
911401516602	SM386C S5 P10 930 PSU MB BK	3000 K	64 lm/W	575 lm
911401516702	SM386C S5 P10 930 PSU WB BK	3000 K	64 lm/W	575 lm
911401516802	SM386C S5 P10 935 PSU NB BK	3500 K	64 lm/W	575 lm
911401516902	SM386C S5 P10 935 PSU MB BK	3500 K	64 lm/W	575 lm
911401517002	SM386C S5 P10 935 PSU WB BK	3500 K	64 lm/W	575 lm
911401517102	SM386C S5 P10 940 PSU WB BK	4000 K	64 lm/W	575 lm
911401519302	SM386C S5 P10 930 PSR NB BK	3000 K	64 lm/W	575 lm
911401519402	SM386C S5 P10 930 PSR MB BK	3000 K	64 lm/W	575 lm
911401519502	SM386C S5 P10 930 PSR WB BK	3000 K	64 lm/W	575 lm
911401519602	SM386C S5 P10 935 PSR NB BK	3500 K	64 lm/W	575 lm
911401519702	SM386C S5 P10 935 PSR MB BK	3500 K	64 lm/W	575 lm
911401519802	SM386C S5 P10 935 PSR WB BK	3500 K	64 lm/W	575 lm
911401519902	SM386C S5 P10 940 PSR WB BK	4000 K	64 lm/W	575 lm
911401524902	SM386C S5 P10 930 PSD NB BK	3000 K	64 lm/W	575 lm
911401525002	SM386C S5 P10 930 PSD MB BK	3000 K	64 lm/W	575 lm
911401525102	SM386C S5 P10 930 PSD WB BK	3000 K	64 lm/W	575 lm
911401525202	SM386C S5 P10 935 PSD NB BK	3500 K	64 lm/W	575 lm
911401525302	SM386C S5 P10 935 PSD MB BK	3500 K	64 lm/W	575 lm
911401525402	SM386C S5 P10 935 PSD WB BK	3500 K	64 lm/W	575 lm
911401525502	SM386C S5 P10 940 PSD WB BK	4000 K	64 lm/W	575 lm
911401510902	RS386B S5 P10 930 PSU-E NB BK	3000 K	64 lm/W	575 lm
911401511002	RS386B S5 P10 930 PSU-E MB BK	3000 K	64 lm/W	575 lm
911401511102	RS386B S5 P10 930 PSU-E WB BK	3000 K	64 lm/W	575 lm
911401511202	RS386B S5 P10 935 PSU-E NB BK	3500 K	64 lm/W	575 lm

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401511302	RS386B S5 P10 935 PSU-E MB BK	3500 K	64 lm/W	575 lm
911401511402	RS386B S5 P10 935 PSU-E WB BK	3500 K	64 lm/W	575 lm
911401511502	RS386B S5 P10 940 PSU-E WB BK	4000 K	64 lm/W	575 lm
911401513702	RS386B S5 P10 930 PSR-E NB BK	3000 K	64 lm/W	575 lm
911401513802	RS386B S5 P10 930 PSR-E MB BK	3000 K	64 lm/W	575 lm
911401513902	RS386B S5 P10 930 PSR-E WB BK	3000 K	64 lm/W	575 lm
911401514002	RS386B S5 P10 935 PSR-E NB BK	3500 K	64 lm/W	575 lm
911401514102	RS386B S5 P10 935 PSR-E MB BK	3500 K	64 lm/W	575 lm
911401514202	RS386B S5 P10 935 PSR-E WB BK	3500 K	64 lm/W	575 lm
911401514302	RS386B S5 P10 940 PSR-E WB BK	4000 K	64 lm/W	575 lm
911401522102	RS386B S5 P10 930 PSD-E NB BK	3000 K	64 lm/W	575 lm
911401522202	RS386B S5 P10 930 PSD-E MB BK	3000 K	64 lm/W	575 lm
911401522302	RS386B S5 P10 930 PSD-E WB BK	3000 K	64 lm/W	575 lm
911401522402	RS386B S5 P10 935 PSD-E NB BK	3500 K	64 lm/W	575 lm
911401522502	RS386B S5 P10 935 PSD-E MB BK	3500 K	64 lm/W	575 lm
911401522602	RS386B S5 P10 935 PSD-E WB BK	3500 K	64 lm/W	575 lm
911401522702	RS386B S5 P10 940 PSD-E WB BK	4000 K	64 lm/W	575 lm
911401512302	RS386B S10 P20 930 PSU-E NB BK	3000 K	65 lm/W	1,150 lm
911401512402	RS386B S10 P20 930 PSU-E MB BK	3000 K	65 lm/W	1,150 lm
911401512502	RS386B S10 P20 930 PSU-E WB BK	3000 K	65 lm/W	1,150 lm
911401512602	RS386B S10 P20 935 PSU-E NB BK	3500 K	65 lm/W	1,150 lm
911401512702	RS386B S10 P20 935 PSU-E MB BK	3500 K	65 lm/W	1,150 lm
911401512802	RS386B S10 P20 935 PSU-E WB BK	3500 K	65 lm/W	1,150 lm
911401512902	RS386B S10 P20 940 PSU-E WB BK	4000 K	65 lm/W	1,150 lm
911401515102	RS386B S10 P20 930 PSR-E NB BK	3000 K	65 lm/W	1,150 lm
911401515202	RS386B S10 P20 930 PSR-E MB BK	3000 K	65 lm/W	1,150 lm
911401515302	RS386B S10 P20 930 PSR-E WB BK	3000 K	65 lm/W	1,150 lm
911401515402	RS386B S10 P20 935 PSR-E NB BK	3500 K	65 lm/W	1,150 lm
911401515502	RS386B S10 P20 935 PSR-E MB BK	3500 K	65 lm/W	1,150 lm
911401515602	RS386B S10 P20 935 PSR-E WB BK	3500 K	65 lm/W	1,150 lm
911401515702	RS386B S10 P20 940 PSR-E WB BK	4000 K	65 lm/W	1,150 lm
911401523502	RS386B S10 P20 930 PSD-E NB BK	3000 K	65 lm/W	1,150 lm
911401523602	RS386B S10 P20 930 PSD-E MB BK	3000 K	65 lm/W	1,150 lm
911401523702	RS386B S10 P20 930 PSD-E WB BK	3000 K	65 lm/W	1,150 lm
911401523802	RS386B S10 P20 935 PSD-E NB BK	3500 K	65 lm/W	1,150 lm
911401523902	RS386B S10 P20 935 PSD-E MB BK	3500 K	65 lm/W	1,150 lm
911401524002	RS386B S10 P20 935 PSD-E WB BK	3500 K	65 lm/W	1,150 lm

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401524102	RS386B S10 P20 940 PSD-E WB	4000 K	65 lm/W	1,150 lm
	BK			

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401510202	RS386B S5 P10 930 PSU-E NB WH	9 W	911401517502	SM386C S10 P20 935 PSU NB WH	18 W
911401510302	RS386B S5 P10 930 PSU-E MB WH	9 W	911401517602	SM386C S10 P20 935 PSU MB WH	18 W
911401510402	RS386B S5 P10 930 PSU-E WB WH	9 W	911401517702	SM386C S10 P20 935 PSU WB WH	18 W
911401510502	RS386B S5 P10 935 PSU-E NB WH	9 W	911401517802	SM386C S10 P20 940 PSU WB WH	18 W
911401510602	RS386B S5 P10 935 PSU-E MB WH	9 W	911401520002	SM386C S10 P20 930 PSR NB WH	18 W
911401510702	RS386B S5 P10 935 PSU-E WB WH	9 W	911401520102	SM386C S10 P20 930 PSR MB WH	18 W
911401510802	RS386B S5 P10 940 PSU-E WB WH	9 W	911401520202	SM386C S10 P20 930 PSR WB WH	18 W
911401513002	RS386B S5 P10 930 PSR-E NB WH	10 W	911401520302	SM386C S10 P20 935 PSR NB WH	18 W
911401513102	RS386B S5 P10 930 PSR-E MB WH	10 W	911401520402	SM386C S10 P20 935 PSR MB WH	18 W
911401513202	RS386B S5 P10 930 PSR-E WB WH	10 W	911401520502	SM386C S10 P20 935 PSR WB WH	18 W
911401513302	RS386B S5 P10 935 PSR-E NB WH	10 W	911401520602	SM386C S10 P20 940 PSR WB WH	18 W
911401513402	RS386B S5 P10 935 PSR-E MB WH	10 W	911401525602	SM386C S10 P20 930 PSD NB WH	18 W
911401513502	RS386B S5 P10 935 PSR-E WB WH	10 W	911401525702	SM386C S10 P20 930 PSD MB WH	18 W
911401513602	RS386B S5 P10 940 PSR-E WB WH	10 W	911401525802	SM386C S10 P20 930 PSD WB WH	18 W
911401521402	RS386B S5 P10 930 PSD-E NB WH	10 W	911401525902	SM386C S10 P20 935 PSD NB WH	18 W
911401521502	RS386B S5 P10 930 PSD-E MB WH	10 W	911401526002	SM386C S10 P20 935 PSD MB WH	18 W
911401521602	RS386B S5 P10 930 PSD-E WB WH	10 W	911401526102	SM386C S10 P20 935 PSD WB WH	18 W
911401521702	RS386B S5 P10 935 PSD-E NB WH	10 W	911401526202	SM386C S10 P20 940 PSD WB WH	18 W
911401521802	RS386B S5 P10 935 PSD-E MB WH	10 W	911401515802	SM386C S5 P10 930 PSU NB WH	9 W
911401521902	RS386B S5 P10 935 PSD-E WB WH	10 W	911401515902	SM386C S5 P10 930 PSU MB WH	9 W
911401522002	RS386B S5 P10 940 PSD-E WB WH	10 W	911401516002	SM386C S5 P10 930 PSU WB WH	9 W
911401517902	SM386C S10 P20 930 PSU NB BK	18 W	911401516102	SM386C S5 P10 935 PSU NB WH	9 W
911401518002	SM386C S10 P20 930 PSU MB BK	18 W	911401516202	SM386C S5 P10 935 PSU MB WH	9 W
911401518102	SM386C S10 P20 930 PSU WB BK	18 W	911401516302	SM386C S5 P10 935 PSU WB WH	9 W
911401518202	SM386C S10 P20 935 PSU NB BK	18 W	911401516402	SM386C S5 P10 940 PSU WB WH	9 W
911401518302	SM386C S10 P20 935 PSU MB BK	18 W	911401518602	SM386C S5 P10 930 PSR NB WH	10 W
911401518402	SM386C S10 P20 935 PSU WB BK	18 W	911401518702	SM386C S5 P10 930 PSR MB WH	10 W
911401518502	SM386C S10 P20 940 PSU WB BK	18 W	911401518802	SM386C S5 P10 930 PSR WB WH	10 W
911401520702	SM386C S10 P20 930 PSR NB BK	18 W	911401518902	SM386C S5 P10 935 PSR NB WH	10 W
911401520802	SM386C S10 P20 930 PSR MB BK	18 W	911401519002	SM386C S5 P10 935 PSR MB WH	10 W
911401520902	SM386C S10 P20 930 PSR WB BK	18 W	911401519102	SM386C S5 P10 935 PSR WB WH	10 W
911401521002	SM386C S10 P20 935 PSR NB BK	18 W	911401519202	SM386C S5 P10 940 PSR WB WH	10 W
911401521102	SM386C S10 P20 935 PSR MB BK	18 W	911401524202	SM386C S5 P10 930 PSD NB WH	10 W
911401521202	SM386C S10 P20 935 PSR WB BK	18 W	911401524302	SM386C S5 P10 930 PSD MB WH	10 W
911401521302	SM386C S10 P20 940 PSR WB BK	18 W	911401524402	SM386C S5 P10 930 PSD WB WH	10 W
911401526302	SM386C S10 P20 930 PSD NB BK	18 W	911401524502	SM386C S5 P10 935 PSD NB WH	10 W
911401526402	SM386C S10 P20 930 PSD MB BK	18 W	911401524602	SM386C S5 P10 935 PSD MB WH	10 W
911401526502	SM386C S10 P20 930 PSD WB BK	18 W	911401524702	SM386C S5 P10 935 PSD WB WH	10 W
911401526602	SM386C S10 P20 935 PSD NB BK	18 W	911401524802	SM386C S5 P10 940 PSD WB WH	10 W
911401526702	SM386C S10 P20 935 PSD MB BK	18 W	911401511602	RS386B S10 P20 930 PSU-E NB WH	18 W
911401526802	SM386C S10 P20 935 PSD WB BK	18 W	911401511702	RS386B S10 P20 930 PSU-E MB WH	18 W
911401526902	SM386C S10 P20 940 PSD WB BK	18 W	911401511802	RS386B S10 P20 930 PSU-E WB WH	18 W
911401517202	SM386C S10 P20 930 PSU NB WH	18 W	911401511902	RS386B S10 P20 935 PSU-E NB WH	18 W
911401517302	SM386C S10 P20 930 PSU MB WH	18 W	911401512002	RS386B S10 P20 935 PSU-E MB WH	18 W
911401517402	SM386C S10 P20 930 PSU WB WH	18 W	911401512102	RS386B S10 P20 935 PSU-E WB WH	18 W

GreenSpace linear accent

Order Code	Full Product Name	Power Consumption
911401512202	RS386B S10 P20 940 PSU-E WB WH	18 W
911401514402	RS386B S10 P20 930 PSR-E NB WH	18 W
911401514502	RS386B S10 P20 930 PSR-E MB WH	18 W
911401514602	RS386B S10 P20 930 PSR-E WB WH	18 W
911401514702	RS386B S10 P20 935 PSR-E NB WH	18 W
911401514802	RS386B S10 P20 935 PSR-E MB WH	18 W
911401514902	RS386B S10 P20 935 PSR-E WB WH	18 W
911401515002	RS386B S10 P20 940 PSR-E WB WH	18 W
911401522802	RS386B S10 P20 930 PSD-E NB WH	18 W
911401522902	RS386B S10 P20 930 PSD-E MB WH	18 W
911401523002	RS386B S10 P20 930 PSD-E WB WH	18 W
911401523102	RS386B S10 P20 935 PSD-E NB WH	18 W
911401523202	RS386B S10 P20 935 PSD-E MB WH	18 W
911401523302	RS386B S10 P20 935 PSD-E WB WH	18 W
911401523402	RS386B S10 P20 940 PSD-E WB WH	18 W
911401516502	SM386C S5 P10 930 PSU NB BK	9 W
911401516602	SM386C S5 P10 930 PSU MB BK	9 W
911401516702	SM386C S5 P10 930 PSU WB BK	9 W
911401516802	SM386C S5 P10 935 PSU NB BK	9 W
911401516902	SM386C S5 P10 935 PSU MB BK	9 W
911401517002	SM386C S5 P10 935 PSU WB BK	9 W
911401517102	SM386C S5 P10 940 PSU WB BK	9 W
911401519302	SM386C S5 P10 930 PSR NB BK	10 W
911401519402	SM386C S5 P10 930 PSR MB BK	10 W
911401519502	SM386C S5 P10 930 PSR WB BK	10 W
911401519602	SM386C S5 P10 935 PSR NB BK	10 W
911401519702	SM386C S5 P10 935 PSR MB BK	10 W
911401519802	SM386C S5 P10 935 PSR WB BK	10 W
911401519902	SM386C S5 P10 940 PSR WB BK	10 W
911401524902	SM386C S5 P10 930 PSD NB BK	10 W
911401525002	SM386C S5 P10 930 PSD MB BK	10 W
911401525102	SM386C S5 P10 930 PSD WB BK	10 W
911401525202	SM386C S5 P10 935 PSD NB BK	10 W
911401525302	SM386C S5 P10 935 PSD MB BK	10 W
911401525402	SM386C S5 P10 935 PSD WB BK	10 W
911401525502	SM386C S5 P10 940 PSD WB BK	10 W
911401510902	RS386B S5 P10 930 PSU-E NB BK	9 W
911401511002	RS386B S5 P10 930 PSU-E MB BK	9 W
911401511102	RS386B S5 P10 930 PSU-E WB BK	9 W

Order Code	Full Product Name	Power Consumption
911401511202	RS386B S5 P10 935 PSU-E NB BK	9 W
911401511302	RS386B S5 P10 935 PSU-E MB BK	9 W
911401511402	RS386B S5 P10 935 PSU-E WB BK	9 W
911401511502	RS386B S5 P10 940 PSU-E WB BK	9 W
911401513702	RS386B S5 P10 930 PSR-E NB BK	10 W
911401513802	RS386B S5 P10 930 PSR-E MB BK	10 W
911401513902	RS386B S5 P10 930 PSR-E WB BK	10 W
911401514002	RS386B S5 P10 935 PSR-E NB BK	10 W
911401514102	RS386B S5 P10 935 PSR-E MB BK	10 W
911401514202	RS386B S5 P10 935 PSR-E WB BK	10 W
911401514302	RS386B S5 P10 940 PSR-E WB BK	10 W
911401522102	RS386B S5 P10 930 PSD-E NB BK	10 W
911401522202	RS386B S5 P10 930 PSD-E MB BK	10 W
911401522302	RS386B S5 P10 930 PSD-E WB BK	10 W
911401522402	RS386B S5 P10 935 PSD-E NB BK	10 W
911401522502	RS386B S5 P10 935 PSD-E MB BK	10 W
911401522602	RS386B S5 P10 935 PSD-E WB BK	10 W
911401522702	RS386B S5 P10 940 PSD-E WB BK	10 W
911401512302	RS386B S10 P20 930 PSU-E NB BK	18 W
911401512402	RS386B S10 P20 930 PSU-E MB BK	18 W
911401512502	RS386B S10 P20 930 PSU-E WB BK	18 W
911401512602	RS386B S10 P20 935 PSU-E NB BK	18 W
911401512702	RS386B S10 P20 935 PSU-E MB BK	18 W
911401512802	RS386B S10 P20 935 PSU-E WB BK	18 W
911401512902	RS386B S10 P20 940 PSU-E WB BK	18 W
911401515102	RS386B S10 P20 930 PSR-E NB BK	18 W
911401515202	RS386B S10 P20 930 PSR-E MB BK	18 W
911401515302	RS386B S10 P20 930 PSR-E WB BK	18 W
911401515402	RS386B S10 P20 935 PSR-E NB BK	18 W
911401515502	RS386B S10 P20 935 PSR-E MB BK	18 W
911401515602	RS386B S10 P20 935 PSR-E WB BK	18 W
911401515702	RS386B S10 P20 940 PSR-E WB BK	18 W
911401523502	RS386B S10 P20 930 PSD-E NB BK	18 W
911401523602	RS386B S10 P20 930 PSD-E MB BK	18 W
911401523702	RS386B S10 P20 930 PSD-E WB BK	18 W
911401523802	RS386B S10 P20 935 PSD-E NB BK	18 W
911401523902	RS386B S10 P20 935 PSD-E MB BK	18 W
911401524002	RS386B S10 P20 935 PSD-E WB BK	18 W
911401524102	RS386B S10 P20 940 PSD-E WB BK	18 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401510202	RS386B S5 P10 930 PSU-E NB WH	No
911401510302	RS386B S5 P10 930 PSU-E MB WH	No
911401510402	RS386B S5 P10 930 PSU-E WB WH	No
911401510502	RS386B S5 P10 935 PSU-E NB WH	No
911401510602	RS386B S5 P10 935 PSU-E MB WH	No
911401510702	RS386B S5 P10 935 PSU-E WB WH	No
911401510802	RS386B S5 P10 940 PSU-E WB WH	No
911401513002	RS386B S5 P10 930 PSR-E NB WH	Yes
911401513102	RS386B S5 P10 930 PSR-E MB WH	Yes

Order Code	Full Product Name	Dimmable
911401513202	RS386B S5 P10 930 PSR-E WB WH	Yes
911401513302	RS386B S5 P10 935 PSR-E NB WH	Yes
911401513402	RS386B S5 P10 935 PSR-E MB WH	Yes
911401513502	RS386B S5 P10 935 PSR-E WB WH	Yes
911401513602	RS386B S5 P10 940 PSR-E WB WH	Yes
911401521402	RS386B S5 P10 930 PSD-E NB WH	Yes
911401521502	RS386B S5 P10 930 PSD-E MB WH	Yes
911401521602	RS386B S5 P10 930 PSD-E WB WH	Yes
911401521702	RS386B S5 P10 935 PSD-E NB WH	Yes

GreenSpace linear accent

Order Code	Full Product Name	Dimmable
911401521802	RS386B S5 P10 935 PSD-E MB WH	Yes
911401521902	RS386B S5 P10 935 PSD-E WB WH	Yes
911401522002	RS386B S5 P10 940 PSD-E WB WH	Yes
911401517902	SM386C S10 P20 930 PSU NB BK	No
911401518002	SM386C S10 P20 930 PSU MB BK	No
911401518102	SM386C S10 P20 930 PSU WB BK	No
911401518202	SM386C S10 P20 935 PSU NB BK	No
911401518302	SM386C S10 P20 935 PSU MB BK	No
911401518402	SM386C S10 P20 935 PSU WB BK	No
911401518502	SM386C S10 P20 940 PSU WB BK	No
911401520702	SM386C S10 P20 930 PSR NB BK	Yes
911401520802	SM386C S10 P20 930 PSR MB BK	Yes
911401520902	SM386C S10 P20 930 PSR WB BK	Yes
911401521002	SM386C S10 P20 935 PSR NB BK	Yes
911401521102	SM386C S10 P20 935 PSR MB BK	Yes
911401521202	SM386C S10 P20 935 PSR WB BK	Yes
911401521302	SM386C S10 P20 940 PSR WB BK	Yes
911401526302	SM386C S10 P20 930 PSD NB BK	Yes
911401526402	SM386C S10 P20 930 PSD MB BK	Yes
911401526502	SM386C S10 P20 930 PSD WB BK	Yes
911401526602	SM386C S10 P20 935 PSD NB BK	Yes
911401526702	SM386C S10 P20 935 PSD MB BK	Yes
911401526802	SM386C S10 P20 935 PSD WB BK	Yes
911401526902	SM386C S10 P20 940 PSD WB BK	Yes
911401517202	SM386C S10 P20 930 PSU NB WH	No
911401517302	SM386C S10 P20 930 PSU MB WH	No
911401517402	SM386C S10 P20 930 PSU WB WH	No
911401517502	SM386C S10 P20 935 PSU NB WH	No
911401517602	SM386C S10 P20 935 PSU MB WH	No
911401517702	SM386C S10 P20 935 PSU WB WH	No
911401517802	SM386C S10 P20 940 PSU WB WH	No
911401520002	SM386C S10 P20 930 PSR NB WH	Yes
911401520102	SM386C S10 P20 930 PSR MB WH	Yes
911401520202	SM386C S10 P20 930 PSR WB WH	Yes
911401520302	SM386C S10 P20 935 PSR NB WH	Yes
911401520402	SM386C S10 P20 935 PSR MB WH	Yes
911401520502	SM386C S10 P20 935 PSR WB WH	Yes
911401520602	SM386C S10 P20 940 PSR WB WH	Yes
911401525602	SM386C S10 P20 930 PSD NB WH	Yes
911401525702	SM386C S10 P20 930 PSD MB WH	Yes
911401525802	SM386C S10 P20 930 PSD WB WH	Yes
911401525902	SM386C S10 P20 935 PSD NB WH	Yes
911401526002	SM386C S10 P20 935 PSD MB WH	Yes
911401526102	SM386C S10 P20 935 PSD WB WH	Yes
911401526202	SM386C S10 P20 940 PSD WB WH	Yes
911401515802	SM386C S5 P10 930 PSU NB WH	No
911401515902	SM386C S5 P10 930 PSU MB WH	No
911401516002	SM386C S5 P10 930 PSU WB WH	No
911401516102	SM386C S5 P10 935 PSU NB WH	No
911401516202	SM386C S5 P10 935 PSU MB WH	No
911401516302	SM386C S5 P10 935 PSU WB WH	No
911401516402	SM386C S5 P10 940 PSU WB WH	No

Order Code	Full Product Name	Dimmable
911401518602	SM386C S5 P10 930 PSR NB WH	Yes
911401518702	SM386C S5 P10 930 PSR MB WH	Yes
911401518802	SM386C S5 P10 930 PSR WB WH	Yes
911401518902	SM386C S5 P10 935 PSR NB WH	Yes
911401519002	SM386C S5 P10 935 PSR MB WH	Yes
911401519102	SM386C S5 P10 935 PSR WB WH	Yes
911401519202	SM386C S5 P10 940 PSR WB WH	Yes
911401524202	SM386C S5 P10 930 PSD NB WH	Yes
911401524302	SM386C S5 P10 930 PSD MB WH	Yes
911401524402	SM386C S5 P10 930 PSD WB WH	Yes
911401524502	SM386C S5 P10 935 PSD NB WH	Yes
911401524602	SM386C S5 P10 935 PSD MB WH	Yes
911401524702	SM386C S5 P10 935 PSD WB WH	Yes
911401524802	SM386C S5 P10 940 PSD WB WH	Yes
911401511602	RS386B S10 P20 930 PSU-E NB WH	No
911401511702	RS386B S10 P20 930 PSU-E MB WH	No
911401511802	RS386B S10 P20 930 PSU-E WB WH	No
911401511902	RS386B S10 P20 935 PSU-E NB WH	No
911401512002	RS386B S10 P20 935 PSU-E MB WH	No
911401512102	RS386B S10 P20 935 PSU-E WB WH	No
911401512202	RS386B S10 P20 940 PSU-E WB WH	No
911401514402	RS386B S10 P20 930 PSR-E NB WH	Yes
911401514502	RS386B S10 P20 930 PSR-E MB WH	Yes
911401514602	RS386B S10 P20 930 PSR-E WB WH	Yes
911401514702	RS386B S10 P20 935 PSR-E NB WH	Yes
911401514802	RS386B S10 P20 935 PSR-E MB WH	Yes
911401514902	RS386B S10 P20 935 PSR-E WB WH	Yes
911401515002	RS386B S10 P20 940 PSR-E WB WH	Yes
911401522802	RS386B S10 P20 930 PSD-E NB WH	Yes
911401522902	RS386B S10 P20 930 PSD-E MB WH	Yes
911401523002	RS386B S10 P20 930 PSD-E WB WH	Yes
911401523102	RS386B S10 P20 935 PSD-E NB WH	Yes
911401523202	RS386B S10 P20 935 PSD-E MB WH	Yes
911401523302	RS386B S10 P20 935 PSD-E WB WH	Yes
911401523402	RS386B S10 P20 940 PSD-E WB WH	Yes
911401516502	SM386C S5 P10 930 PSU NB BK	No
911401516602	SM386C S5 P10 930 PSU MB BK	No
911401516702	SM386C S5 P10 930 PSU WB BK	No
911401516802	SM386C S5 P10 935 PSU NB BK	No
911401516902	SM386C S5 P10 935 PSU MB BK	No
911401517002	SM386C S5 P10 935 PSU WB BK	No
911401517102	SM386C S5 P10 940 PSU WB BK	No
911401519302	SM386C S5 P10 930 PSR NB BK	Yes
911401519402	SM386C S5 P10 930 PSR MB BK	Yes
911401519502	SM386C S5 P10 930 PSR WB BK	Yes
911401519602	SM386C S5 P10 935 PSR NB BK	Yes
911401519702	SM386C S5 P10 935 PSR MB BK	Yes
911401519802	SM386C S5 P10 935 PSR WB BK	Yes
911401519902	SM386C S5 P10 940 PSR WB BK	Yes
911401524902	SM386C S5 P10 930 PSD NB BK	Yes
911401525002	SM386C S5 P10 930 PSD MB BK	Yes
911401525102	SM386C S5 P10 930 PSD WB BK	Yes

GreenSpace linear accent

Order Code	Full Product Name	Dimmable
911401525202	SM386C S5 P10 935 PSD NB BK	Yes
911401525302	SM386C S5 P10 935 PSD MB BK	Yes
911401525402	SM386C S5 P10 935 PSD WB BK	Yes
911401525502	SM386C S5 P10 940 PSD WB BK	Yes
911401510902	RS386B S5 P10 930 PSU-E NB BK	No
911401511002	RS386B S5 P10 930 PSU-E MB BK	No
911401511102	RS386B S5 P10 930 PSU-E WB BK	No
911401511202	RS386B S5 P10 935 PSU-E NB BK	No
911401511302	RS386B S5 P10 935 PSU-E MB BK	No
911401511402	RS386B S5 P10 935 PSU-E WB BK	No
911401511502	RS386B S5 P10 940 PSU-E WB BK	No
911401513702	RS386B S5 P10 930 PSR-E NB BK	Yes
911401513802	RS386B S5 P10 930 PSR-E MB BK	Yes
911401513902	RS386B S5 P10 930 PSR-E WB BK	Yes
911401514002	RS386B S5 P10 935 PSR-E NB BK	Yes
911401514102	RS386B S5 P10 935 PSR-E MB BK	Yes
911401514202	RS386B S5 P10 935 PSR-E WB BK	Yes
911401514302	RS386B S5 P10 940 PSR-E WB BK	Yes
911401522102	RS386B S5 P10 930 PSD-E NB BK	Yes
911401522202	RS386B S5 P10 930 PSD-E MB BK	Yes
911401522302	RS386B S5 P10 930 PSD-E WB BK	Yes
911401522402	RS386B S5 P10 935 PSD-E NB BK	Yes
911401522502	RS386B S5 P10 935 PSD-E MB BK	Yes

Order Code	Full Product Name	Dimmable
911401522602	RS386B S5 P10 935 PSD-E WB BK	Yes
911401522702	RS386B S5 P10 940 PSD-E WB BK	Yes
911401512302	RS386B S10 P20 930 PSU-E NB BK	No
911401512402	RS386B S10 P20 930 PSU-E MB BK	No
911401512502	RS386B S10 P20 930 PSU-E WB BK	No
911401512602	RS386B S10 P20 935 PSU-E NB BK	No
911401512702	RS386B S10 P20 935 PSU-E MB BK	No
911401512802	RS386B S10 P20 935 PSU-E WB BK	No
911401512902	RS386B S10 P20 940 PSU-E WB BK	No
911401515102	RS386B S10 P20 930 PSR-E NB BK	Yes
911401515202	RS386B S10 P20 930 PSR-E MB BK	Yes
911401515302	RS386B S10 P20 930 PSR-E WB BK	Yes
911401515402	RS386B S10 P20 935 PSR-E NB BK	Yes
911401515502	RS386B S10 P20 935 PSR-E MB BK	Yes
911401515602	RS386B S10 P20 935 PSR-E WB BK	Yes
911401515702	RS386B S10 P20 940 PSR-E WB BK	Yes
911401523502	RS386B S10 P20 930 PSD-E NB BK	Yes
911401523602	RS386B S10 P20 930 PSD-E MB BK	Yes
911401523702	RS386B S10 P20 930 PSD-E WB BK	Yes
911401523802	RS386B S10 P20 935 PSD-E NB BK	Yes
911401523902	RS386B S10 P20 935 PSD-E MB BK	Yes
911401524002	RS386B S10 P20 935 PSD-E WB BK	Yes
911401524102	RS386B S10 P20 940 PSD-E WB BK	Yes

