

UL Goniometer Color Data Report









Laboratory Name:	Signify Monterrey
Address:	Carr. Miguel Aleman km 15.5
	La Encarnacion, 66640
City:	Apodaca
State/Province	Nuevo Leon
Country:	Mexico

ANSI/IES TM-30-18 Color Rendition Report

Source: C4L15CKMDMXU/C4RDLCL
Date: 27/01/2021 15:43

Manufacturer: Lightolier by Signify
Model: C4L15CKMDMXU/C4RDLCL



Note: This is the recommended method for displaying IES TM-30-18 information


Colors are for visual orientation purposes only
Created by UL TM-30-18 Processing application

x 0.4294
y 0.4053
u' 0.2452
v' 0.5207

CIE13.3-1995 (CRI)	
Ra	90.3
R15	90.2

Test Information

Volts	Amps	Watts	Hz	PF	THDV	THDA
119.98	0.19989	21.760	60.00	0.90690	0.180	29.070



CIE 1931 2D Plot

Color Rendering Index															
Ra	R1	R2	R3	R4	R5	R6	R7	R8	R9	R10	R11	R12	R13	R14	R15
90.3	94.7	95.6	79.4	89.8	97.8	92.5	89.4	83.0	74.3	81.4	90.0	50.1	65.2	57.3	90.2

