



Architectural Linear

Suspended, Surface, and Wall

Product Selection Guide

Explore Ledalite's comprehensive offering of award winning families and inspiring lighting solutions. Ledalite innovations support design flexibility, allowing specifiers to create their unique vision without compromise.

| Reference |                      |
|-----------|----------------------|
| ★ ★ ★     | High applicability   |
| ★ ★       | Medium applicability |
| ★         | Low applicability    |
| -         | Non-applicable       |



|   |   | Performance   | Performance  | Performance   | Statement   | Statement   | Statement   | Statement   | Statement  | Statement   | Statement   | Statement   |
|---|---|---|--|---|---|---|---|---|--|---|---|---|
| Applications  | Model   | SyncLine  | FloatPlane   | Sona  | ChopStick   | Sync  | Verge   | BoldPlay  | Jump   | ModiFly   | EyeLine   | TruVue  |
|   | Education   | ★ ★ ★   | ★ ★ ★  | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   | ★ ★ ★  | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   |
|   | Office  | ★ ★ ★   | ★ ★ ★  | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   | ★ ★ ★  | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   |
|   | Healthcare  | ★ ★ ★   | ★ ★ ★  | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   | ★ ★ ★  | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   |
| Features and Specifications                           | Fashion and Retail  | ★ ★ ★   | ★ ★ ★  | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   | ★ ★ ★  | ★ ★ ★   | ★ ★ ★   | ★ ★ ★   |
|   | Design ready, 10 Day QuickShip  | <a href="#">Design ready - QuickShip Guide</a>  | <a href="#">Design ready - QuickShip Guide</a>   | <a href="#">Design ready - QuickShip Guide</a>  | <a href="#">Design ready - QuickShip Guide</a>  | <a href="#">Design ready - QuickShip Guide</a>  | <a href="#">Design ready - QuickShip Guide</a>  | <a href="#">Design ready - QuickShip Guide</a>  | <a href="#">Design ready - QuickShip Guide</a>   | <a href="#">Design ready - QuickShip Guide</a>  | <a href="#">Design ready - QuickShip Guide</a>  | <a href="#">Design ready - QuickShip Guide</a>  |
|   | Standalone Sizes*   | 4', 6', 8'  | 4', 6', 8'   | 4', 8'  | 4', 6', 8'  | 4', 8'  | 4', 8'  | 4', 8'  | 4', 8'   | 2', 3', 4', 5', 6', 8'  | 4'  | 4', 6', 8'  |
|   | Continuous Run Increments   | 2'  | 2'   | 4'  | 2'  | 4'  | 4'  | 4'  | 4'   | 1'  | 4'  | 2' (Standard), 6" (ETO)   |
|   | Watts (Max/4ft)   | 91.4  | 65.5   | 63.7  | 57.8  | 56.9  | 56.9  | 56.9  | 45.8   | 35.4  | 53.4  | 55.7  |
|   | lm/W (Max/4ft)  | 151.7   | 146.9  | 150.7   | 124.7   | 124.1   | 124.1   | 124.1   | 120.6  | 140.3   | 124.9   | 133.2   |
|   | Lumens (Max/4ft)  | 11000   | 7602   | 8410  | 6697  | 6636  | 6636  | 6636  | 5012   | 4438  | 6498  | 6039  |
|   | Lumen Maintenance L80 (10k) > 60,000h   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
|   | Optics  | Acrylic diffuser  | Acrylic diffuser w/optional Down Kits  | Acrylic diffuser/Louvers  | Micro-structured light guide w/MesoOptics   | Symmetric & Asymmetric   | Micro-structured light guide  | Micro-structured light guide w/MesoOptics   | Acrylic bi-directional diffuser   |
|   | Lens  | Fully luminous Silk lens  | Fully luminous Silk lens   | Fully luminous Silk lens or White louver  | Fully luminous MesoOptics lens  | Ribbed MesoOptics DX Lens  | Fully luminous light guide panel  | Fully luminous MesoOptics lens  | Fully luminous Silk lens  |
| Spacing ratio   | Up to 1.28/1.43   | 1.28/1.26   | 1.25/1.28  | 1.63/1.66   | 1.62/1.79   | 1.62/1.79   | 1.62/1.79   | 1.62/1.79   | 1.12/1.56  | 1.49/1.18   | 1.29/1.54   | 1.27/1.26   |
| CCT   | Static: 2700, 3000, 3500, 4000, 5000K<br>Tunable White: 2700-6500K<br>BioUp: 2700-5000K   | Static: 2700, 3000, 3500, 4000, 5000K<br>Tunable White: 2700-6500K  | Static: 2700, 3000, 3500, 4000, 5000K<br>Tunable White: 2700-6500K   | Static: 2700, 3000, 3500, 4000, 5000K<br>Tunable White: 2700-6500K  | Static: 2700, 3000, 3500, 4000, 5000K<br>Tunable White: 2700-6500K  | Static: 2700, 3000, 3500, 4000, 5000K<br>Tunable White: 2700-6500K  | Static: 2700, 3000, 3500, 4000, 5000K<br>Tunable White: 2700-6500K  | Static: 2700, 3000, 3500, 4000, 5000K<br>Tunable White: 2700-6500K  | Static: 2700, 3000, 3500, 4000, 5000K<br>Tunable White: 2700-6500K   | Static: 2700, 3000, 3500, 4000, 5000K<br>Tunable White: 2700-6500K  | Static: 2700, 3000, 3500, 4000, 5000K<br>Tunable White: 2700-6500K  | Static: 2700, 3000, 3500, 4000, 5000K<br>Tunable White: 2700-6500K  |
| CRI   | Static White: ≥90 (AccuRender)<br>Tunable White: ≥90 (AccuRender)<br>BioUp: 80-90+  | Static White: ≥90 (AccuRender)<br>Tunable White: ≥90 (AccuRender)   | Static White: ≥90 (AccuRender)<br>Tunable White: ≥90 (AccuRender)  | Static White: ≥90 (AccuRender)<br>Tunable White: ≥90 (AccuRender)   | Static White: ≥90 (AccuRender)<br>Tunable White: ≥90 (AccuRender)   | Static White: ≥90 (AccuRender)<br>Tunable White: ≥90 (AccuRender)   | Static White: ≥90 (AccuRender)<br>Tunable White: ≥90 (AccuRender)   | Static White: ≥90 (AccuRender)<br>Tunable White: ≥90 (AccuRender)   | Static White: ≥90 (AccuRender)<br>Tunable White: ≥90 (AccuRender)  | Static White: ≥90 (AccuRender)<br>Tunable White: ≥90 (AccuRender)   | Static: ≥90 (AccuRender)  | Static White: ≥90 (AccuRender)<br>Tunable White: ≥90 (AccuRender)   |
| MDER: 0.97 w/BioUp @5000K<br>0.83 w/AccuRender @5000K | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| Mounting Types  | Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall. Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color. | Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall. Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color. | Wall mount or suspended via variable sling mount aircraft cable & tamper-resistant gripper from flat or sloped Drywall. Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color. | Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall. Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color. | Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall. Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color. | Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall. Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color. | Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall. Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color. | Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall. Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color. | Wall mount or suspended via variable sling mount aircraft cable & tamper-resistant gripper from flat or sloped Drywall. Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color. | Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall. Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color. | Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall. Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color. | Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall. Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color. |
| Related families                                      | Suspended and wall  | Suspended and wall  | Suspended and wall   | Suspended and wall  | Suspended and wall  | Suspended and wall  | Suspended and wall  | Suspended and wall  | Suspended, Surface and Wall  | Suspended and wall  | Suspended and wall  | Suspended and wall  |
| Suspension lengths up to 240"                         | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| Straight runs and/or patterns possible                | Straight runs   | Straight runs   | Straight runs  | Straight runs   | Straight runs   | Straight runs   | Straight runs   | Straight runs   | Straight runs  | Straight runs & (wall to suspended) Patterns  | Straight runs   | Straight runs   |
| Finish: standard and custom colors                    | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| Factory: Prewired with Self aligning quick connect    | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| Emergency   | Available with factory installed UL924 certified Emergency circuit. Battery pack. Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.   | Available with factory installed UL924 certified Emergency circuit. Battery pack. Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.   | Available with factory installed UL924 certified Emergency circuit. Battery pack. Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.  | Available with factory installed UL924 certified Emergency circuit. Battery pack. Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.   | Available with factory installed UL924 certified Emergency circuit. Battery pack. Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.   | Available with factory installed UL924 certified Emergency circuit. Battery pack. Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.   | Available with factory installed UL924 certified Emergency circuit. Battery pack. Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.   | Available with factory installed UL924 certified Emergency circuit. Battery pack. Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.   | Available with factory installed UL924 certified Emergency circuit. Battery pack. Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.  | Available with factory installed UL924 certified Emergency circuit. Battery pack. Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.   | Available with factory installed UL924 certified Emergency circuit. Battery pack. Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.   | Available with factory installed UL924 certified Emergency circuit. Battery pack. Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.   |
| UL Dry & Damp location rating                         | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| Advance Xitanium 0-10V (1% Dim)                       | ✓ (Also available in 10% dim)   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| Advance Xitanium DALI-2 D4i (1% Dim)                  | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| Lutron EcoSystem LDE1 (<1% Dim, Fade-to-Black)        | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| Advance Xitanium SR, DALI-2 D4i (1% Dim)              | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| Sensor location                                       | ✓ (Integral)  | ✓ (Integral)  | ✓ (Integral)   | ✓ (Integral)  | ✓ (Integral)  | ✓ (Integral)  | ✓ (Integral)  | ✓ (Integral)  | ✓ (Remote or Integral)   | ✓ (Integral)  | ✓ (Remote)  | ✓ (Remote)  |
| Basic 0-10V Daylight and Occupancy                    | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| Interact Pro Wireless Radio (RA)                      | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| Interact Pro Foundation/Advanced Wireless (CS)        | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| Interact Pro Enterprise Wireless Sensor Bundle (SB)   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| Lutron Athena Sensor/Radio Node                       | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| Lutron Vive Sensor/Radio Node                         | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   | ✓   | ✓   | ✓  | ✓   | ✓   | ✓   |
| DLC   | Standard and Premium  | Standard and Premium  | Standard and Premium   | -   | Standard and Premium  | Standard and Premium  | Standard and Premium  | Standard and Premium  | -  | Standard  | -   | Standard and Premium  |
| Declare   | ✓   | ✓   | ✓  | -   | -   | -   | -   | ✓   | -  | -   | -   | ✓   |
| Spec Sheet  |   |   |  |   |   |   |   |   |  |   |   | Coming Soon   |

\*Custom options available on request, please enquire with Ledalite.

