


Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____



Ordering Guide

Example: B1 A LED7 NF W S

Product Code	B1	LED Aluminum Bullyte
Finish	A H G	Black Bronze Verde
Source/Lumens	LED7	7W LED
Optics	NF	Narrow Flood
CCT	W	Warm
Shroud	S L	Short Shroud Long Shroud

*1 Lamp will be shipped with fixture, but not installed. Lamp not sold separately.

Specifications

HOUSING:

Die-cast aluminum. Fully-adjustable swivel arm with vibration-proof locking teeth. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately. Gasketing is silicone. Fasteners are 300 series stainless steel. Shroud is optional.

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

OPTICAL ASSEMBLY:

Clear tempered flat glass lens.

LAMPING:

7W lamp with 25° beam spread, 25,000 hours life. Color temperature (CCT): warm white (2,700K nominal). No Mercury.

ELECTRICAL ASSEMBLY:

Pre-wired with high temperature 18 AWG wire.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Width: 3 7/8" (98mm) **Length:** 8 1/2" (216mm) **Max. Weight:** 1.4 lb.

