DESCRIPTION

The 163 series is a decorative wall sconce family with rectilinear form. This product is a rectangular shape shade, with a variety of options to highlight elegant spatial forms. The integral LED light engine is available in 2700K, 3000K, 3500K, and 4000K color temperatures that evenly illuminates the shade and the bottom lens, and 83+ CRI. Shaper's Fabrique collection its known for is high quality hand tucked fabrics. Heavy gauged steel frame, laminated styrene backing, and minimum internal structure. Shades come in 11 standard fabrics, 3 vinly material, and 4 printed wood designs allowing the designer to select a look for any space.

Shaper

Catalog #	Туре
Project	
Comments	Date
Prepared by	

SPECIFICATION FEATURES

Construction

Aluminum housing, cold rolled steel cover and bracket extensions with LED boards attached. Optional matte white acrylic top cover available (TC).

163-26

Width is 26," height is 8.5," depth is 4," and ADA compliant.

Shades

Aluminum wire frame painted white. Material backed on to heavy translucent white styrene. All shades have "Hand-Tucked Rolled Edges" except for Vinyl.

Fabric Shade Selections SIW - Silk White SIY - Silk Ivory SWH - Shantung White SEG - Shantung Eggshell SBG - Shantung Beige LAT - Linen Alabaster LCK - Linen Chopstick NGS - Silk Glow GBB - Glynn Brussels Beige LOLA - Lola Sand VLW - Verona Linen White

Vinyl Coated Fabric ABR - Alabaster Vinyl NFX - Natural Flax GHY - Golden Honey **Note:** For humid environments vinyl coated fabrics are recommended.

Printed Woods PVDB - Varigated Bamboo PMA - Maple PCH - Cherry PWA - Walnut

Electrical Standard driver is electronic universal voltage (120-277V, 50/60 Hz), greater than 0.9 power factor, less than 20% harmonic distortion, and ambient temperatures of 25°C (77°F).

Control Standard driver is 0-10V with 10%

dimming.

Compliance

Components are UL recognized and luminaires are cUL listed for 25° ambient environments. Fixtures are rated for damp location listing. Made in North America. Sconce products meet ADA regulations.

Life and Warranty

Standard five-year warranty on all parts.



163-W Series

Surface Decorative LED Wall Sconce

> cULus – 1598 Damp Location LM79/LM80 Compliant

Length 26"

• Delivered Lumens (@3500K) 3918 • Wattage: 44W

• CRI: 80

• CCT: 2700K, 3000K, 3500K, 4000K

ORDERING INFORMATION (SELECT FIXTURE AND FABRIC KIT TO COMPLETE SPECIFICATION)

Sample Number: 163-26-W-L5/827-UNV-RBP

Series ¹	Size	Mounting Type	LED Lamp	LED Voltage	Options
163 = Rectilinear Curved Wall Sconce	26 = 26"	W = Wall	L5/827	UNV = (120-277V)	TC = Matte White Acrylic Top Cover
			L5/830		RBP = Remote Battery Pack
			L5/835		
			L5/840		

Notes: 1. Fabric Kit is not included. Please specify Fabric Kit (below) to complete specification.

Sample Number: 163-26-SHD-SWH

Series ¹	Size	SHD	Finish			
163 = Rectilinear Wall Shade	26 = 26"	SHD = Shade Fabric	Fabric:SIW = Silk WhiteSIY = Silk IvorySWH = Shantung WhiteSEG = Shantung EggshellSBG = Shantung BeigeGBB = Glynn Brussels Beige	LOLA = Lola Sand NGS = Nutmeg Shimmer LCK = Linen Chopstick LAT = Linen Alabaster VLW = Verona Linen White	Vinyl: ABR = Alabaster Vinyl NFX = Natural Flax GHY = Golden Honey Printed Wood: PVDB = Varigated Bamboo PMA = Maple PCH = Cherry PWA = Walnut	

Notes: 1. Fixture is not included. Please specify Fixture (above) to complete specification.

