

DESCRIPTION

The Drum shade is a traditional straight-sided fabric shade available in 4 standard sizes. The integrated LED light sources, available in 827, 830, 835 and 840 color choices, evenly illuminate the shade and bottom lens. Shaper's Fabrique Collection is known for its high quality hand-tucked fabrics, heavy gauge steel frame, laminated styrene backing and minimal internal structure. 4 sizes of shade allow this design to be used in a range of applications. With 11 standard fabrics, 3 vinyl materials, and 4 photographically imaged woods, as well as the ability to customize, allow a designer to select a look to match any pallet.

Catalog #	Type
Project	
Comments	Date
Prepared by	

SPECIFICATION FEATURES

Material/Mounting

Cold-rolled steel frame and aluminum wire body, painted white. Matte white acrylic bottom diffuser with one finial, standard. Optional matte white acrylic top cover.

LCK - Linen Chopstick
LAT - Linen Alabaster
VLW - Verona Linen White
SWH - Shantung White
SEG - Shantung Eggshell
SBG - Shantung Beige

max 40W
30":L5:4000 nominal lumens at max 38W
36":L9:8000 nominal lumens at max 72W
42":L12:11000 nominal lumens at max 91W

Finishes

MW - Matte White

Vinyl Coated Fabric

ABR - Alabaster
NFX - Natural Flax
GHY - Golden Honey

Driver

LED system coupled with electrical driver to deliver optimal performance. Electronic drivers are available for 120-277V applications. A 0-10V dimming control is available (Standard) on all models.

Shades

Solid cold-rolled steel construction. Material on heavy translucent white styrene. All shades are "Hand-Tucked" except for printed wood options.

(NOTE: For humid environments such as shower rooms or open lobbies, Vinyl Coated Fabrics are recommended)

Printed Wood

PVDB - Variegated Bamboo
PMA - Maple
PCH - Cherry
PWA - Walnut

Compliance

All Fabrique Collection products are UL and cUL approved for interior damp locations.

LED

24":L5:4000 nominal lumens at



122 Series

Diameter: 24" - 30"

- Lumen Output Source Lumens: 4000
- Wattage: 24" : 40W, 30" : 38W
- Color Rendering: CRI 83+
- Correlated Color Temperature: 4000K, 3500K, 3000K, 2700K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V

Diameter: 36"

- Lumen Output Source Lumens: 8000
- Wattage: 32W
- Color Rendering: CRI 83+
- Correlated Color Temperature: 4000K, 3500K, 3000K, 2700K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V


Diameter: 42"

- Lumen Output Source Lumens: 11,000
- Wattage: 91W
- Color Rendering: CRI 83+
- Correlated Color Temperature: 4000K, 3500K, 3000K, 2700K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V



Light ARchitect™

DIMENSIONS



ORDERING INFORMATION (SELECT FIXTURE AND FABRIC KIT TO COMPLETE SPECIFICATION)

Sample Number: 122-24-S-L5/835-UNV-MW

Series	Size	Mounting Type	LED Lamp				LED Voltage	Finish	Options
122 = Drum Surface ¹	24 = 24"	S = Surface	24"	30"	36"	42"	UNV = (120-277V)	MW = Matte White	RBP = Remote Mounted Emergency (5' Max Distance)
	30 = 30"		L5/827	L5/827	L9/827	L12/827			
	36 = 36"		L5/830	L5/830	L9/830	L12/830			
	42 = 42"		L5/835	L5/835	L9/835	L12/835			
			L5/840	L5/840	L9/840	L12/840			

Notes: 1. Fabric Kit is not included. Please specify Fabric Kit (below) to complete specification.

Sample Number: 122-24-SHD-SIW

Series	Size	SHD	Finish		
122 = Drum Surface	24 = 24" 30 = 30" 36 = 36" 42 = 42"		Fabric:		Vinyl:
			SIW = Silk White	LOLA = Lola Sand	ABR = Alabaster Vinyl
			SIY = Silk Ivory	NGS = Nutmeg Shimmer	NFX = Natural Flax
			SWH = Shantung White	LCK = Linen Chopstick	GHY = Golden Honey
			SEG = Shantung Eggshell	LAT = Linen Alabaster	
			SBG = Shantung Beige	VLW = Verona Linen White	Printed Wood:
			GBB = Glynn Brussels Beige		PVDB = Varigated Bamboo
					PMA = Maple
					PCH = Cherry
					PWA = Walnut