


# HADCO

by @signify

Landscape

Pathlyte

MSL12 Aluminum



Project:	
Location:	
Cat.No:	
Type:	
Lamps:	Qty:
Notes:	

## Ordering Guide

Example: MSL12 A S7

Product Code	MSL12	Aluminum Pathlyte
Finish	A H G	Black Bronze Verde
Mounting	S7	Mounting Stake *1

\*1 Mounting stake is optional.

## Specifications

### HOUSING:

Die-cast aluminum. Hidden fasteners and aluminum stem. Fasteners are 300 series stainless steel. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

### FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

### LAMPING:

27W maximum S-8 (1156) lamp. Lamp is included with fixture. Lower wattage lamps are acceptable.

### ELECTRICAL ASSEMBLY:

Single contact bayonet (S-8). 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

### WARRANTY:

Three-year limited warranty.

### CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

### Height :

13 1/2" (343mm)

### Width:

4 1/2" (114mm)

### Max. Weight:

1.32 lb.

@signify