#### DESCRIPTION

The rectilinear shade is a traditional straight-sided fabric shade designed for use in conference rooms, over dining tables and other rectilinear applications. The integrated LED light sources, available in 827, 830, 835 and 840 color choices, evenly illuminate the shade and bottom lens. Finial finishes are available in many painted options. With 11 standard fabrics, 3 vinyl materials, and 4 photographically imaged woods, as well as the ability to customize, allow a designer to select a look to match any pallet.

# Shaper

Catalog #	Туре
Project	
Comments	Date
Prepared by	

#### SPECIFICATION FEATURES

#### Materials

Internal components are aluminum and cold rolled steel parts with post-painted white finishes. Shades are made of heavy gauge formed and welded steel rod. Fabrics are laminated to a styrene backing to provide structural integrity and to minimize vertical support requirements. The bottom lens is opal white acrylic.

#### Finishes

MW - Matte White

DIMENSIONS

6" (15 cm)

#### Shades

Fabric SIW - Silk White SIY - Silk Ivory GBB - Glynn Brussels Beige LOLA - Lola Sand NGS - Nutmeg Shimmer LCK - Linen Chopstick LAT - Linen Alabaster VLW - Verona Linen White SWH - Shantung White SEG - Shantung Eggshell SBG - Shantung Beige

#### Vinyl Coated Fabric ABR - Alabaster NFX - Natural Flax GHY - Golden Honey

(NOTE: For humid environments such as shower rooms or open lobbies, Vinyl Coated Fabrics are recommended)

#### Printed Wood PVDB - Variegated Bamboo PMA - Maple PCH - Cherry

PWA - Walnut

### LED

38":L7:6000 Nominal Source Lumens at max 57W 48":L9:8000 Nominal Source Lumens at max 76W

#### Driver

5" (13 cm)

The Fabrique Collection utilizes common high quality LED components for matching CCT and CRI across the complete family. Low voltage LED circuits are supplied by constant current

10" (25 cm)

۰



#### Installation

Fabrique LED Surface Mounted Fixtures are designed to mount easily, using a circle strap, to a standard j-box. Shades are mounted to 4 cross-arms and can be easily removed for cleaning or as necessary for servicing.

#### Compliance

All Fabrique Collection products are UL and cUL approved for interior damp locations. Fabrique Collection products are made in the North America.



## **121 Series**

#### 38"

- Lumen Output Source Lumens: L7: 6000 nominal lumens Wattage: 57W
- Color Rendering: CRI 83+ - Correlated Color Temperature: 4000K, 3500K, 3000K, 2700K
- Rated Life of Lamp (hrs): 50,000 - Dimming: 0-10V

#### 48"

8" (20 cm)

- Lumen Output Source Lumens: L9: 8000 nominal lumens - Wattage: 76W
- Color Rendering: CRI 83+ - Correlated Color Temperature:
- 4000K, 3500K, 3000K, 2700K
- Rated Life of Lamp (hrs): 50,000 - Dimming: 0-10V



ORDERING INFORMATION (SELECT FIXTURE AND FABRIC KIT TO COMPLETE SPECIFICATION)

#### Sample Number: 121-38-S-L7/835-UNV-MW

38" (97 cm)

121-38-S

(Surface)

Series	Size	Mounting Type	LED	Lamp	LED Voltage	Finish	Options
<b>121</b> = Rectilinear Surface <sup>1</sup>	<b>38</b> = 38" <b>48</b> = 48"	<b>S</b> = Surface	38" L7/827 L7/830 L7/835 L7/840	48" L9/827 L9/830 L9/835 L9/840	<b>UNV</b> = (120-277V)	<b>MW</b> = Matte White	RBP = Remote Emergency Battery Pack (Max Distance 5')

48-1/2" (123 cm)

121-48-S

(Surface)

۰

#### Sample Number: 121-38-SHD-SIW

Notes: 1. Fabric Kit is not included. Please specify Fabric Kit (below) to complete specification.

Series	Size	SHD	Finish		
<b>121</b> = Rectilinear Surface	<b>38</b> = 38" <b>48</b> = 48"		Fabric:   SIW = Silk White   SIY = Silk Ivory   SWH = Shantung White   SEG = Shantung Eggshell   SBG = Shantung Beige   GBB = Glynn Brussels Beige	LOLA = Lola Sand NGS = Nutmeg Shimmer LCK = Linen Chopstick LAT = Linen Alabaster VLW = Verona Linen White	Vinyl:   ABR = Alabaster Vinyl   NFX = Natural Flax   GHY = Golden Honey   Printed Wood:   PVDB = Varigated Bamboo   PMA = Maple   PCH = Cherry   PWA = Walnut

