



eW Graze MX Powercore

eW Graze MX Powercore, 4000 K, 9° x 9° Beam Angle, 305 mm (1 ft)

eW Graze MX Powercore, 4000 K, 9° x 9° Beam Angle, 305 mm (1 ft)

Many architectural structures need a linear fixture capable of illuminating multiple storeys with minimal setback. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasise their brands. Graze MX Powercore is capable of illuminating over 20 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

Product data

General information	
General mornation	
Lamp family code	LED-HB [LED High Brightness]
Light source colour	Neutral white
Light source replaceable	No
Driver included	Yes
Luminaire light beam spread	9° x 9°
Protection class IEC	Safety class I
CE mark	CE mark
UL mark	UL and cUL mark
Lifetime to 70% luminous flux	100000 h
Operating and electrical	
Input Voltage	100 to 277 V

Input frequency	50 to 60 Hz
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Housing material	Extruded aluminium
Optical cover/lens material	Polycarbonate
Length	305 mm
Approval and application	
Ingress protection code	IP66 [Dust penetration-protected, jet-
	proof]

eW Graze MX Powercore

Mech. impact protection code	IK10 [20 J vandal-resistant]	
Vibration standard	Complies with ANSI C136.31, 3G	
FCC mark	FCC Class A	
Vibration rating	Complies with ANSI C136.31, 3G	
Initial performance (IEC compliant)		
Initial LED luminaire efficacy	60.1 lm/W	
Init. Corr. Colour Temperature	4000 K	
Initial input power	15 W	
Over time performance (IEC compliant)		
Lumen Maintenance 50% at 25 °C Reported	60000	
Lumen Maintenance 50% at 50 °C	60000	
Reported		
Lumen Maintenance 70% at 25 °C Reported	60000	
Lumen Maintenance 70% at 50 °C Reported	60000	

-20 to +50 °C

Product data	
Full product code	871829161014499
Order product name	BCS419 9/4000 L305
EAN/UPC – product	8718291610144
Order code	523-000080-01
SAP numerator – quantity per pack	1
Numerator – packs per outer box	4
SAP material	910503703688
Net Weight (Piece)	1.200 kg
Commercial Code	523-000080-01
Catalogue number description	eW Graze MX Powercore, 4000 K, 9° x 9°
	Beam Angle, 305 mm (1 ft)



Dimensional drawing

Application conditions Ambient temperature range





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2023, January 9 - data subject to change