



# Uni Line Inground\_Wall washer

BBP420 LED 27K 24V B4 L30

Uni Line Inground\_Wall washer, 680 lm, 9 W, 2700 K

Philips UniLine in-ground wall washer is our latest recessed luminaire for outdoor applications. Designed to enhance surroundings in subtle or dramatic ways, this discreet luminaire offers a choice of LED colors and beam angles. So you can light up façades and landscapes with dynamic lighting effects without exposing the body of the device. And because it's compatible with Uni DMX controls and 3rd party standard DMX controls, it's easy to handle too.

### Warnings and Safety

- For outdoor use only

### Product data

General Information	
Driver included	No
CE mark	CE mark
Flammability mark	-
Light Technical	
Luminous Flux	680 lm
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	75.5555555555556 lm/W
Color rendering index (CRI)	>80
Light source color	827 warm white
Optical cover type	Lens

Operating and Electrical	
Input Voltage	24 V
Line Frequency	- Hz
Power Consumption	9 W
Power Factor (Fraction)	1
Connection	-
Cable	2 cables 0.3m with connector 2-pole
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No

Uni Line Inground\_Wall washer

Control interface	-
<b>Mechanical and Housing</b>	
Housing Material	Aluminum
Optical cover material	Acrylate
Housing Color	Aluminum
<b>Approval and Application</b>	
Ingress protection code	IP67 [Dust penetration-protected, watertight]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Protection class IEC	Safety class III
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%

Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	BBP420 LED 27K 24V B4 L30
Full product name	BBP420 LED 27K 24V B4 L30
Full product code	871951452478199
Order code	911401519981
Material Nr. (12NC)	911401519981
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514524781
Numerator - Packs per outer box	4
EAN/UPC - Case	8719514525863

Dimensional drawing

