



GreenPerform Batten G3 BN398C

BN398C LED20/CW L600 PSU OP

GreenPerform Batten G3 BN398C, 14.2 W, 2100 lm, 6500 K

GreenPerform batten BN398C is a cost competitive linear solution with good performance and multiple lumen output for retail and industry applications. It offers surface mount and suspension installations to cater for different mounting options. Its multiple optic designs accommodate different applications as well.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance
CE mark	CE mark
Flammability mark	For mounting on normally flammable surfaces
Light Technical	
Luminous Flux	2,100 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	147 lm/W
Color rendering index (CRI)	>80
Light source color	865 cool daylight
Optical cover type	Polymethyl methacrylate bowl/cover
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz

Inrush current	14 A
Power Consumption	14.2 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B 33	
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Metal-Plastic
Optical cover material	Polymethyl methacrylate
Housing Color	White RAL 9003
Optical cover finish	Frosted
Overall length	573 mm

GreenPerform Batten G3 BN398C

Overall width	58 mm
Overall height	58 mm
Dimensions (Height x Width x Depth)	58 x 58 x 573 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%

Product Data	
Order product name	BN398C LED20/CW L600 PSU OP
Full product name	BN398C LED20/CW L600 PSU OP
Full product code	692382863344800
Order code	911401583351
Material Nr. (12NC)	911401583351
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828633448
Numerator - Packs per outer box	1
EAN/UPC - Case	6923828633448

Dimensional drawing

