



UniStrip G4

BCP386 12LED RGBNW 24V 45 L30 DMX

UniStrip G4, 150 lm, 3 W, Red, green, blue and white, Dynamic DMX, Safety class III

UniStrip G4 is a surface-mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colours, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

General Information	
Driver included	No
Lighting Technology	LED
CE mark	CE mark
Light Technical	
Luminous Flux	150 lm
Correlated Color Temperature (Nom)	-
Luminous Efficacy (rated) (Nom)	50 lm/W
Color rendering index (CRI)	-
Light source color	Red, green, blue and white

Optical cover type	Clear glass
Operating and Electrical	
Input Voltage	24 DC V
Line Frequency	- Hz
Power Consumption	3 W
Power Factor (Fraction)	1
Connection	2 Push-in connector 5-pole
Cable	2 cables 0.15m with connectors 5-pole

UniStrip G4

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Control interface	Dynamic DMX

Mechanical and Housing

Housing Material	Aluminum extruded
Optical cover material	Polymethyl methacrylate
Housing Color	Dark gray
Overall length	300 mm
Overall width	25.4 mm
Overall height	71.6 mm
Dimensions (Height x Width x Depth)	72 x 25 x 300 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]

Protection class IEC	Safety class III
----------------------	------------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BCP386 12LED RGBNW 24V 45 L30 DMX
Full product name	BCP386 12LED RGBNW 24V 45 L30 DMX
Full product code	871951451375499
Order code	911401780102
Material Nr. (12NC)	911401780102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514513754
Numerator - Packs per outer box	50
EAN/UPC - Case	8719514513754

Dimensional drawing

