



# FBY LED High Bay

24,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution

24,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution

The FBY LED High Bay provides versatility in form and function. With a wide range of lumen packages and accessories available, this luminaire can be used in many different applications ranging from warehouses and manufacturing facilities to retail outlets and school gymnasiums.

## Product data

General information	
Lamp Source Code	LED
Colour Temperature	4000 K
CRI	80
Photometric Distribution Type	Direct
Mounting	Suspended
Buy American Compliant Products	Yes
Operating and electrical	
Voltages	120/208/240/277/347/480/UNIV V
Luminaire Input Watts	177 W
Mechanical and housing	
Fixture Size	1 ft x 2 ft
Approval and application	
Energy Certifications	DLC Standard

Initial performance (IEC compliant)	
Luminaire Lumens	24000 lm
Product data	
Order product name	FBY24L840-277-WP6-MD360
EAN/UPC - Product	190096187461
Order code	FBY24L840-277-WP6-MD360
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401496083
Net Weight (Piece)	3.000 kg
Catalog Number	FBY24L840-277-WP6-MD360
Catalog Number Description	24,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution