



# T8 High CRI Lamps

## F32T8/TL965/ALTO 30PK

Philips T8 High CRI lamps featuring ALTO II technology are ideal when better color rendering properties are preferred.

### Product data

General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Bulb Finish	Coated glass
Features	ALTO® (ALTO)	Bulb Shape	T-8 (T8)
Light Technical		Approval and Application	
Color Code	965 [CCT of 6500K]	Mercury (Hg) Content (Nom)	1.7 mg
Beam Angle (Nom)	0 degree(s)		
Luminous Flux	2,600 lm	Product Data	
Color Designation	6500 Kelvin	Order product name	F32T8/TL965/ALTO 30PK
Correlated Color Temperature (Nom)	6500 K	Full product name	F32T8/TL965/ALTO 30PK
Color rendering index (CRI)	>90	Order code	479642
Operating and Electrical		Material Nr. (12NC)	927871205701
Power Consumption	32 W	Numerator - Quantity Per Pack	1
Lamp Current (Nom)	265 mA	EAN/UPC - Product/Case	046677479640
Wattage Equivalent	32 W	Numerator - Packs per outer box	30
Voltage (Nom)	137 V	EAN/UPC - Case	50046677479645
Voltage (Nom)	137 V		

## T8 High CRI Lamps

### Dimensional drawing

Product	C (max)	D (max)
F32T8/TL965/ALTO 30PK	47-13/16 inch	1-1/8 inch

