



# CorePro LEDspot LV

## CorePro LED 3-35W 6500K MR16 24D CN

CorePro LEDspot 非常适合用于聚光照明，可以提供如同卤素灯般的暖光。本产品兼容大多数带 MR16 GU5.3 支座的现有灯具，经过设计改造，可替代卤素灯或白炽射灯。CorePro LEDspot 不仅节能效果出众，而且还最大限度地降低了维护成本。

### 产品数据

|              |               |
|--------------|---------------|
| 一般信息         |               |
| 底盖           | GU5.3 [GU5.3] |
| 标称使用寿命       | 15,000 小时     |
| 切换循环         | 50,000        |
| 额定使用寿命 (小时)  | 15,000 小时     |
| 照明技术         | LED           |
| 符合欧盟 RoHS 规范 | 是             |

|                       |                    |
|-----------------------|--------------------|
| 灯技术                   |                    |
| 颜色代码                  | 865 [CCT of 6500K] |
| 颜色代码                  | 865 [CCT of 6500K] |
| 光束角度 (标称)             | 24 °               |
| 光通量                   | 290 lm             |
| 发光强度 (标称)             | 1,000 cd           |
| 颜色名称                  | 冷日光                |
| 相关色温 (标称)             | 6500 K             |
| 光效 (额定)(标称)           | 96.67 lm/W         |
| 颜色一致性                 | <6                 |
| 显色指数 (CRI)            | 80                 |
| 标称使用寿命结束时灯的光通维持率 (标称) | 70 %               |

|       |      |
|-------|------|
| 操作和电气 |      |
| 线频率   | - Hz |
| 输入频率  | - Hz |

|              |        |
|--------------|--------|
| 功耗           | 3 W    |
| 灯具电流 (标称)    | 350 mA |
| 瓦数相当         | 35 W   |
| 启动时间 (标称)    | 0.5 s  |
| 60% 灯光下的预热时间 | 1 s    |
| 功率系数 (小数)    | 0.5    |
| 电压 (标称)      | 12 V   |

|             |       |
|-------------|-------|
| 温度          |       |
| 最大外壳温度 (标称) | 76 °C |

|       |   |
|-------|---|
| 控制和调光 |   |
| 可调光   | 否 |

|       |                   |
|-------|-------------------|
| 机械和外壳 |                   |
| 灯泡外形  | MR16 [2 英寸/50 毫米] |

|         |   |
|---------|---|
| 审批和申请   |   |
| 适用于重点照明 | 是 |


|         |                                     |
|---------|-------------------------------------|
| 产品数据    |                                     |
| 订单产品名称  | CorePro LED 3-35W 6500K MR16 24D CN |
| 完整的产品名称 | CorePro LED 3-35W 6500K MR16 24D CN |
| 完整产品代码  | 694793912364300                     |

CorePro LEDspot LV

|                |               |
|----------------|---------------|
| 订购代码           | 929001239810  |
| 材料编号 (12NC)    | 929001239810  |
| 计算器 - 每包数量     | 1             |
| EAN/UPC - 产品/箱 | 6947939123643 |



|                  |               |
|------------------|---------------|
| 计算器 - 每个外包装箱中的包数 | 10            |
| EAN/UPC - 案例     | 6947939123650 |

二维绘图




| Product                             | D     | C     |
|-------------------------------------|-------|-------|
| CorePro LED 3-35W 6500K MR16 24D CN | 50 mm | 46 mm |

光度数据



Accent Lighting Spots - CorePro LED 3-35W 6500K MR16 24D CN


Spectral Power Distribution Colour - CorePro LED 3-35W 6500K MR16 24D CN




Light Distribution Diagram - CorePro LED 3-35W 6500K MR16 24D CN

CorePro LEDspot LV

寿命



Life Expectancy Diagram - CorePro LED 3-35W 6500K MR16 24D CN



Lumen Maintenance Diagram - CorePro LED 3-35W 6500K MR16 24D CN

