



Party Spot

13.5PAR38/PER/BBLUE/G/E26/ND/ULW 3/1PF

Philips 13.5-watt PAR 38s provide bright colorful light perfect for special occasions, parties and holidays. These PAR 38 lamps are available in up to four different colors and offer a festive touch to your home lighting. Brighten up your home and celebrate with color using these energy saving LED bulbs.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	10,950 hour(s)
Switching Cycle	10,000
Rated Lifetime (Hours)	10,950 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	Blue
Color Designation	Blue
Color Consistency	<6
Color rendering index (CRI)	-
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	13.5 W
Lamp Current (Nom)	165 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5


Voltage (Nom)	120 V
UL Type	Yes
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Bulb Shape	PAR38
UL Wet/ damp/ dry location	Wet location
Approval and Application	
Suitable For Accent Lighting	Yes
EyeComfort	Yes
T20 compliant	N/A

Party Spot

Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	13.5PAR38/PER/BLUE/G/E26/ND/ULW 3/1PF
Full product name	13.5PAR38/PER/BLUE/G/E26/ND/ULW 3/1PF
Order code	929001306533



Material Nr. (12NC)	929001306533
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677568269
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677568264

Dimensional drawing



Product	D	C
13.5PAR38/PER/BLUE/G/E26/ND/ULW 3/1PF	122 mm	132 mm


Photometric data




Light Distribution Diagram - 13.5PAR38/PER/BLUE/G/E26/ND/ULW 3/1PF

Accent Lighting Spots - 13.5PAR38/PER/BLUE/G/E26/ND/ULW 3/1PF

Lifetime



Lumen Maintenance Diagram - 13.5PAR38/PER/BBLUE/G/E26/ND/ULW 3/1PF



Life Expectancy Diagram - 13.5PAR38/PER/BBLUE/G/E26/ND/ULW 3/1PF

