



# CorePro Plastic LED-spesialiteter



## Corepro LED T25 ND 3.2-25W E14 827

LED-spesialitetene kan enkelt monteres i visse bruksområder.

### Produktdata

| Generell informasjon                                                                  |                    |
|---------------------------------------------------------------------------------------|--------------------|
| Sokkelbase                                                                            | E14 [E14]          |
| Nominell levetid                                                                      | 15 000 time(r)     |
| Brytersyklus                                                                          | 50 000             |
| Lighting Technology                                                                   | LED                |
| I samsvar med EU RoHS                                                                 | Ja                 |
| Teknisk belysning                                                                     |                    |
| Fargekode                                                                             | 827 [CCT of 2700K] |
| Spredningsvinkel (nom.)                                                               | 160 grad(er)       |
| Lysytelse                                                                             | 250 lm             |
| Fargebetegnelse                                                                       | Varmhvit (WW)      |
| Korrelert fargetemperatur (nom)                                                       | 2700 K             |
| Lysutbytte (vurdert) (Nom)                                                            | 78,00 lm/W         |
| Fargesamsvar                                                                          | <6                 |
| Fargegjengivelsesindeks (CRI)                                                         | 80                 |
| Nominell vedlikeholdsfaktor for lyskildelumen ved utgangen av nominell levetid (nom.) | 70 %               |
| Flimmerverdi (PstLM)                                                                  | 1                  |
| Stroboskopisk effekt                                                                  | 0,4                |
| Photobiological safety according to EN 62471                                          | RG0                |


| Drift og elektronikk                        |               |
|---------------------------------------------|---------------|
| Line Frequency                              | 50 to 60 Hz   |
| Inngangsfrekvens                            | 50 til 60 Hz  |
| Effektforbruk                               | 3,2 W         |
| lyskildestrøm (nom.)                        | 35 mA         |
| Effekten som tilsvare                       | 25 W          |
| Starttid (nom.)                             | 0,5 s         |
| Tiden det tar før lyset er på 60 %          | 0.5 s         |
| Effektfaktor (brøk)                         | 0.4           |
| Spennning (nom.)                            | 220-240 V     |
| Temperatur                                  |               |
| Maksimal temperatur for innfatningen (nom.) | 80 °C         |
| Kontroller og dimming                       |               |
| Kan dimmes                                  | Nei           |
| Mekanikk og innfatning                      |               |
| Lyspæreoverflate                            | Matt          |
| Lyspæreform                                 | T25 [T 25 mm] |
| Godkjenning og bruksområde                  |               |
| Energieffektivitetsklasse                   | G             |

CorePro Plastic LED-spesialiteter

|                            |                                    |
|----------------------------|------------------------------------|
| Energiforbruk kWh/1000 t   | 4 kWh                              |
| EPREL-registreringsnummer  | 391880                             |
| EyeComfort                 | Ja                                 |
| Produktdata                |                                    |
| Produktnavn for bestilling | Corepro LED T25 ND 3.2-25W E14 827 |
| Fullstendig produktnavn    | Corepro LED T25 ND 3.2-25W E14 827 |
| Full EOC                   | 871951438984700                    |


|                                   |               |
|-----------------------------------|---------------|
| Lokal kodebeskrivelse             | 3758226       |
| Bestillingskode                   | 38984700      |
| Materialenr. (12NC)               | 929001325802  |
| Lokal bestillingskode             | 3758226       |
| SAP-teller – antall per pakke     | 1             |
| EAN/UPC – produkt/boks            | 8719514389847 |
| SAP-teller – pakker per utvendige | 12            |
| EAN/UPC – boks                    | 8719514389854 |

Målskisse




| Product                            | D     | C     |
|------------------------------------|-------|-------|
| Corepro LED T25 ND 3.2-25W E14 827 | 25 mm | 71 mm |

Fotometriske data




Spectral Power Distribution Colour - Corepro LED T25 ND 3.2-25W E14 827



General uniform lighting - Corepro LED T25 ND 3.2-25W E14 827


# CorePro Plastic LED-spesialiteter

## Fotometriske data




Light Distribution Diagram - Corepro LED T25 ND 3.2-25W E14 827

## Levetid



Life Expectancy Diagram - Corepro LED T25 ND 3.2-25W E14 827



Lumen Maintenance Diagram - Corepro LED T25 ND 3.2-25W E14 827

