



LED Lamps

LEDStick 9.5W E27 3000K 1PF/6 AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data

| General Information | |
|---------------------------------------|--------------------|
| Cap-Base | E27 |
| Nominal lifetime | 15,000 hour(s) |
| Switching Cycle | 50,000 |
| Rated Lifetime (Hours) | 15,000 hour(s) |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |
| Light Technical | |
| Color Code | 830 [CCT of 3000K] |
| Color Code | 830 [CCT of 3000K] |
| Beam Angle (Nom) | 200 degree(s) |
| Luminous Flux | 950 lm |
| Color Designation | White (WH) |
| Correlated Color Temperature (Nom) | 3000 K |
| Luminous Efficacy (rated) (Nom) | 100 lm/W |
| Color Consistency | <6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 9.5 W |

| | |
|---------------------------|-----------|
| Lamp Current (Nom) | 75 mA |
| Wattage Equivalent | 68 W |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.51 |
| Voltage (Nom) | 220-240 V |

| Temperature | |
|---------------------------|---------------|
| Ambient temperature range | -20 to +45 °C |
| T-Case Maximum (Nom) | 85 °C |

| Controls and Dimming | |
|----------------------|----|
| Dimmable | No |

| Mechanical and Housing | |
|------------------------|---------|
| Bulb Finish | Frosted |
| Bulb Material | Plastic |
| Bulb Shape | Stick |


| Approval and Application | |
|-------------------------------|--------|
| Energy Consumption kWh/1000 h | 10 kWh |
| EyeComfort | Yes |

LEDLamps

| | |
|---------------------|----------------------------------|
| LED Innovations | EyeComfort |
| Product Data | |
| Order product name | LEDStick 9.5W E27 3000K 1PF/6 AU |
| Full product name | LEDStick 9.5W E27 3000K 1PF/6 AU |
| Full product code | 871869960527800 |
| Order code | 929001901469 |
| Material Nr. (12NC) | 929001901469 |



| | |
|---------------------------------|---------------|
| Local order code | LSTK9.5WES830 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718699605278 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8718699605285 |

Dimensional drawing




| Product | D | C |
|----------------------------------|---------|----------|
| LEDStick 9.5W E27 3000K 1PF/6 AU | 37.2 mm | 114.3 mm |

Photometric data



Spectral Power Distribution Colour - LEDStick 9.5W E27 3000K 1PF/6 AU

General uniform lighting - LEDStick 9.5W E27 3000K 1PF/6 AU



Light Distribution Diagram - LEDStick 9.5W E27 3000K 1PF/6 AU

LEDLamps

Lifetime



Life Expectancy Diagram - LEDStick 9.5W E27 3000K 1PF/6 AU

Lumen Maintenance Diagram - LEDStick 9.5W E27 3000K 1PF/6 AU

