



LEDLamps

LEDBulb 14.5W E27 6500K 230VA67 1CT/6APR

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data


General Information		Power Consumption	
Cap-Base	E27		14.5 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	135 mA
Switching Cycle	50,000	Wattage Equivalent	120 W
Rated Lifetime (Hours)	12,000 hour(s)	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.51
Light Technical		Voltage (Nom)	220-240 V
Color Code	865 [CCT of 6500K]	Temperature	
Color Code	865 [CCT of 6500K]	Ambient temperature range	-20 to +45 °C
Beam Angle (Nom)	150 degree(s)	T-Case Maximum (Nom)	90 °C
Luminous Flux	1,800 lm	Controls and Dimming	
Color Designation	Cool Daylight	Dimmable	No
Correlated Color Temperature (Nom)	6500 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	124 lm/W	Bulb Finish	Frosted
Color Consistency	<6	Bulb Material	Plastic
Color rendering index (CRI)	80	Bulb Shape	A67
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Photobiological safety according to EN 62471 RG1		Energy Consumption kWh/1000 h	15 kWh
Operating and Electrical			
Input Frequency	50 to 60 Hz		

LEDLamps

EyeComfort	No
Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	LEDBulb 14.5W E27 6500K 230VA67 1CT/ 6APR
Full product name	LEDBulb 14.5W E27 6500K 230VA67 1CT/ 6APR


Full product code	871869964049100
Order code	929002003949
Material Nr. (12NC)	929002003949
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699640491
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699640507

Dimensional drawing




Product	D	C
LEDBulb 14.5W E27 6500K 230VA67 1CT/6APR	68 mm	132 mm

Photometric data




Light Distribution Diagram - LEDBulb 14.5W E27 6500K 230VA67 1CT/6APR




Spectral Power Distribution Colour - LEDBulb 14.5W E27 6500K 230VA67 1CT/6APR

Photometric data




General uniform lighting - LEDBulb 14.5W E27 6500K 230VA67 1CT/6APR

Lifetime



Life Expectancy Diagram - LEDBulb 14.5W E27 6500K 230VA67 1CT/6APR



Lumen Maintenance Diagram - LEDBulb 14.5W E27 6500K 230VA67 1CT/6APR

