



LEDLamps

LEDBulb 19W E27 6500K 230VA80 1CT/6APR

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data


General Information		Temperature	
Cap-Base	E27	Lamp Current (Nom)	170 mA
Nominal lifetime	15000 hour(s)	Wattage Equivalent	160 W
Switching Cycle	50000	Starting Time (Nom)	0.5 s
Rated Lifetime (Hours)	12000 hour(s)	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.51
EU RoHS compliant	Yes	Voltage (Nom)	220-240 V
Light Technical		Controls and Dimming	
Color Code	865 [CCT of 6500K]	Dimmable	No
Beam Angle (Nom)	150 degree(s)	Mechanical and Housing	
Luminous Flux	2300 lm	Bulb Finish	Frosted
Color Designation	Cool Daylight	Bulb Material	Plastic
Correlated Color Temperature (Nom)	6500 K	Bulb Shape	A80
Luminous Efficacy (rated) (Nom)	121 lm/W	Approval and Application	
Color Consistency	<6	Energy Consumption kWh/1000 h	19 kWh
Color rendering index (CRI)	80	EyeComfort	No
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Photobiological safety according to EN 62471	RG1		
Operating and Electrical			
Input Frequency	50 to 60 Hz		
Power Consumption	19 W		

LEDLamps

Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	LEDBulb 19W E27 6500K 230VA80 1CT/6APR
Full product name	LEDBulb 19W E27 6500K 230VA80 1CT/6APR
Full product code	871869964053800


Order code	929002004149
Material Nr. (12NC)	929002004149
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699640538
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699640545

Dimensional drawing




Product	D	C
LEDBulb 19W E27 6500K 230VA80 1CT/6APR	80 mm	155 mm

Photometric data




General uniform lighting - LEDBulb 19W E27 6500K 230VA80 1CT/6APR




Spectral Power Distribution Colour - LEDBulb 19W E27 6500K 230VA80 1CT/6APR

Photometric data




Light Distribution Diagram - LEDBulb 19W E27 6500K 230VA80 1CT/6APR

Lifetime



Life Expectancy Diagram - LEDBulb 19W E27 6500K 230VA80 1CT/6APR



Lumen Maintenance Diagram - LEDBulb 19W E27 6500K 230VA80 1CT/6APR

