



LEDLamps

LEDBulb 8.5-60W E27 2700K D 1PF/6 AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data

| General Information | |
|---------------------------------------|--------------------|
| Cap-Base | E27 |
| Nominal lifetime | 15,000 h |
| Switching Cycle | 50,000 |
| Rated Lifetime (Hours) | 15,000 h |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |
| Light Technical | |
| Color Code | 927 [CCT of 2700K] |
| Color Code | 927 [CCT of 2700K] |
| Beam Angle (Nom) | 150 degree(s) |
| Luminous Flux | 806 lm |
| Color Designation | Warm White (WW) |
| Correlated Color Temperature (Nom) | 2700 K |
| Luminous Efficacy (rated) (Nom) | 94 lm/W |
| Color Consistency | <6 |
| Color rendering index (CRI) | 90 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 8.5 W |


| Lamp Current (Nom) | 45 mA |
|-------------------------------|----------------------------|
| Wattage Equivalent | 60 W |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.9 |
| Voltage (Nom) | 220-240 V |
| Temperature | |
| Ambient temperature range | -20 to +45 °C |
| T-Case Maximum (Nom) | 85 °C |
| Controls and Dimming | |
| Dimmable | Only with specific dimmers |
| Mechanical and Housing | |
| Bulb Finish | Frosted |
| Bulb Material | Plastic |
| Bulb Shape | A60 |
| Approval and Application | |
| Energy Consumption kWh/1000 h | 9 kWh |
| EyeComfort | Yes |

LEDLamps

| | |
|------------------------|--------------------------------------|
| LED Innovations | EyeComfort |
| | |
| Product Data | |
| Order product name | LEDBulb 8.5-60W E27 2700K D 1PF/6 AU |
| Full product name | LEDBulb 8.5-60W E27 2700K D 1PF/6 AU |
| Full product code | 871951433359800 |
| Local code description | WD85A60WWE27 |
| Order code | 929002069119 |



| | |
|--|---------------|
| Material Nr. (12NC) | 929002069119 |
| Local order code | WD85A60WWE27 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8719514333598 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8719514386952 |

Dimensional drawing




| Product | D | C |
|--------------------------------------|-------|--------|
| LEDBulb 8.5-60W E27 2700K D 1PF/6 AU | 60 mm | 110 mm |

Photometric data



General uniform lighting - LEDBulb 8.5-60W E27 2700K D 1PF/6 AU

Light Distribution Diagram - LEDBulb 8.5-60W E27 2700K D 1PF/6 AU



Spectral Power Distribution Colour - LEDBulb 8.5-60W E27 2700K D 1PF/6 AU

Lifetime



Life Expectancy Diagram - LEDBulb 8.5-60W E27 2700K D 1PF/6 AU



Lumen Maintenance Diagram - LEDBulb 8.5-60W E27 2700K D 1PF/6 AU

