



# Specialty Lamps

## 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	927 [CCT of 2700K]
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	220 degree(s)
Luminous Flux	800 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %


Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	8.8 W
Lamp Current (Nom)	74 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	203 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A19

Specialty Lamps

UL Wet/ damp/ dry location	Damp location
Approval and Application	
Energy Certifications	Energy Star
EyeComfort	Yes
T20 compliant	Yes
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF


Full product name	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF
Order code	573238
Material Nr. (12NC)	929002333693
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677573232
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677573237

Dimensional drawing




Product	D	C
8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	2-7/16 inch	4-3/8 inch

Photometric data




Spectral Power Distribution Colour - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF



General uniform lighting - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

Specialty Lamps

Photometric data




Light Distribution Diagram - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

Lifetime



Life Expectancy Diagram - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF



Lumen Maintenance Diagram - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

