



BR/R LED

15BR30/PER/927/P/E26/WG/HO/T20 4/1PF

Philips Dimmable LED Reflector Lamps provide a soft, diffused level of light and smooth dimming to reduce glare. The sleek, lightweight design is ideal for downlighting.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Color Code	922-927 [CCT of 2200K-2700K]
Beam Angle (Nom)	110 degree(s)
Luminous Flux	1,400 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2200 2700 K
Luminous Efficacy (rated) (Nom)	93 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power Consumption	15 W
Lamp Current (Nom)	125 mA

Wattage Equivalent	100 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
Ambient temperature range	-4 to +113 °F
T-Case Maximum (Nom)	203 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	BR30
UL Wet/ damp/ dry location	Damp location
Approval and Application	
Energy Certifications	Energy Star
EyeComfort	Yes
T20 compliant	Yes

BR/R LED

Application Conditions


can it be used in closed luminaires Yes

Product Data

Order product name	15BR30/PER/927/P/E26/WG/HO/T20 4/1PF
Full product name	15BR30/PER/927/P/E26/WG/HO/T20 4/1PF
Order code	571471



Material Nr. (12NC)	929002351433
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677571474
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677571479

Dimensional drawing




Product	D	C
15BR30/PER/927/P/E26/WG/HO/T20 4/1PF	3-3/4 inch	5-1/8 inch

Photometric data



Light Distribution Diagram - 15BR30/PER/927/P/E26/WG/HO/T20 4/1PF

General uniform lighting - 15BR30/PER/927/P/E26/WG/HO/T20 4/1PF



Spectral Power Distribution Colour - 15BR30/PER/927/P/E26/WG/HO/T20 4/1PF

