

LEDclassic 11W A60 E27 smoky ND RFSRT4 Classic filament LEDbulbs

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process, we innovate to reduce our environmental impact by taking climate action and by focusing on circularity and bring wider benefits to the world we operate in via social aspects as food availability, health & wellbeing, and safety & security.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



- Dimmable: No
- Luminous efficacy (rated) (nom.): 43.00 lm/W
- Power (Rated) (Nom): 2.3 W

Circularity

• Nominal lifetime (nom.): 15000 h



- SAP Weight Paper Unit (Case): 0.168 kg
- SAP Weight Paper Unit (Piece): 0.023 kg



- EU REACH SVHC declaration: Yes
- EU RoHS compliant: Yes



Weight & Materials

• Net Weight (Piece): 0.028 kg

Further reading at: https://www.philips.com/a-w/about/ sustainability/sustainable-planet/greenproducts-and-green-innovation.html