



TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

TForce Core HB 80W E40 865 GN3

Philips TrueForce Core LED I&R lamps offer an easy and short payback LED solution to replace High Intensity Discharge (HID) lamps. The products bring the energy efficiency and long lifetime benefits of LED to HID replacement and provide instant saving and low initial investment. With the right lamp size and light distribution, you can easily retrofit TrueForce Core LED I&R lamps and bypass the existing ballast while enhancing the lighting quality.

Product data


General Information		Operating and Electrical	
Cap-Base	E40	Luminous Efficacy (rated) (Nom)	112.00 lm/W
Nominal lifetime	25,000 hour(s)	Color Consistency	<6
Switching Cycle	50,000	Color rendering index (CRI)	80
Lighting Technology	LED	LLMF At End Of Nominal Lifetime (Nom)	70 %
EU RoHS compliant	Yes		
Light Technical			
Color Code	865 [CCT of 6500K]	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	180 degree(s)	Input Frequency	50 to 60 Hz
Luminous Flux	9,000 lm	Power Consumption	80 W
Color Designation	Cool Daylight	Lamp Current (Nom)	780 mA
Correlated Color Temperature (Nom)	6500 K	Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.5

TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	83 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	T-shape
Approval and Application	
Energy Consumption kWh/1000 h	80 kWh


Product Data	
Order product name	TForce Core HB 80W E40 865 GN3
Full product name	TForce Core HB 80W E40 865 GN3
Full product code	871869978079100
Order code	929002409308
Material Nr. (12NC)	929002409308
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699780791
Numerator - Packs per outer box	4
EAN/UPC - Case	8718699780807

Dimensional drawing




Product	D	C
TForce Core HB 80W E40 865 GN3	160 mm	269 mm

Photometric data




General uniform lighting - TForce Core HB 80W E40 865 GN3



Spectral Power Distribution Colour - TForce Core HB 80W E40 865 GN3


TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

Photometric data




Light Distribution Diagram - TForce Core HB 80W E40 865 GN3

Lifetime



Life Expectancy Diagram - TForce Core HB 80W E40 865 GN3



Lumen Maintenance Diagram - TForce Core HB 80W E40 865 GN3

