



CorePro LEDcandle



CorePro lustre ND 7-60W E14 840 P48 FR

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LED lamps deliver huge energy savings and minimize maintenance cost.

Product data

General Information	
Cap base	E14 [E14]
Nominal lifetime	15,000 h
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Colour Code	840 [CCT of 4000K]
Luminous Flux	806 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	115.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Photobiological safety according to EN 62471 RG1	

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	7 W
Lamp current (nom.)	59 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.51
Voltage (nom.)	220-240 V

Temperature	
T-Case maximum (nom.)	87 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Lamp Finish	Frosted
Bulb shape	P48 [P 48 mm]

Approval and Application	
Energy Efficiency Class	E

CorePro LEDcandle


Energy consumption kWh/1,000 hours	7 kWh
EPREL registration number	453216
EyeComfort	Yes

Product Data

Order product name	CorePro lustre ND 7-60W E14 840 P48 FR
Full product name	CorePro lustre ND 7-60W E14 840 P48 FR
Full EOC	871951431308800



Order code	31308800
Material no. (12 NC)	929002973302
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514313088
Numerator – packs per outer box	10
EAN/UPC - Case	8719514313095

Dimensional drawing




Product	D	C
CorePro lustre ND 7-60W E14 840 P48 FR	48 mm	95 mm

Photometric data



General uniform lighting - CorePro lustre ND 7-60W E14 840 P48 FR



Spectral Power Distribution Colour - CorePro lustre ND 7-60W E14 840 P48 FR



Light Distribution Diagram - CorePro lustre ND 7-60W E14 840 P48 FR

CorePro LEDcandle

Lifetime



Life Expectancy Diagram - CorePro lustre ND 7-60W E14 840 P48 FR

Lumen Maintenance Diagram - CorePro lustre ND 7-60W E14 840 P48 FR

