

MASTER LED spot VLE D 3.7-35W GU10 927 60D MASTER VALUE LEDspot MV

Delivering a warm, halogen-like accent beam, the MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it achieves more natural colours, creating cosy and comfortable ambience for residential and hospitality projects, and emphasising the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. The MASTER VALUE also offers more energy savings than normal LED spots.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process, we innovate to reduce our environmental impact by taking climate action and by focusing on circularity and bring wider benefits to the world we operate in via social aspects as food availability, health & wellbeing, and safety & security.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



- Dimmable: Only with specific dimmers
- Energy Efficiency Class: F
- Luminous efficacy (rated) (nom.): 72.00 lm/W
- Power (Rated) (Nom): 3.7 W



• Nominal lifetime (nom.): 25000 h



- Copy SAP Weight Paper Unit (Case): 0.208 kg
- Copy SAP Weight Paper Unit (Piece): 0.015 kg



• EU RoHS compliant: Yes



Weight & Materials

• Copy Net Weight (Piece): 0.038 kg

Energy efficiency ranking / External awards



Further reading at: https://www.philips.com/a-w/about/ sustainability/sustainable-planet/greenproducts-and-green-innovation.html