



Classic filament LEDbulbs

LED classic-giant 40W E27 T65 GOLD DIM

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information		Flickering value (PstLM) - Flickering value as per EN 61000-3-3	
Cap-Base	E27	Stroboscopic effect visibility measure (SVM)	1
Nominal lifetime	15,000 hour(s)	Photobiological safety according to EN 62471	0.4
Switching Cycle	20,000		RG1
Rated Lifetime (Hours)	15,000 hour(s)		
Lighting Technology	LED		
CE mark	Yes		
EU RoHS compliant	Yes		
Light Technical		Operating and Electrical	
Color Code	818 [CCT of 1800K]	Line Frequency	50 to 60 Hz
Color Code	818 [CCT of 1800K]	Input Frequency	50 to 60 Hz
Beam Angle (Nom)	330 degree(s)	Power Consumption	7 W
Luminous Flux	470 lm	Lamp Current (Nom)	43 mA
Color Designation	1800	Wattage Equivalent	40 W
Correlated Color Temperature (Nom)	1800 K	Starting Time (Nom)	0.5 s
Luminous Efficacy (rated) (Nom)	67 lm/W	Warm-up time to 60% light	0.5 s
Color Consistency	<6	Power Factor (Fraction)	0.7
Color rendering index (CRI)	80	Voltage (Nom)	220-240 V
LLMF At End Of Nominal Lifetime (Nom)	70 %		
		Temperature	
		Ambient temperature range	-20 to +45 °C
		T-Case Maximum (Nom)	45 °C

Classic filament LEDbulbs

Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Amber
Bulb Material	Glass
Bulb Shape	T65
Approval and Application	
Energy Consumption kWh/1000 h	7 kWh
EyeComfort	Yes
Product Data	
Order product name	LED classic-giant 40W E27 T65 GOLD DIM


Full product name	LED classic-giant 40W E27 T65 GOLD DIM
Full product code	871951431380400
Order code	929002983701
Material Nr. (12NC)	929002983701
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514313804
Numerator - Packs per outer box	2
EAN/UPC - Case	8719514313811

Dimensional drawing




Product	D	C
LED classic-giant 40W E27 T65 GOLD DIM	66 mm	273 mm

Photometric data




Spectral Power Distribution Colour - LED classic-giant 40W E27 T65 GOLD DIM



Light Distribution Diagram - LED classic-giant 40W E27 T65 GOLD DIM


Classic filament LEDbulbs

Photometric data




General uniform lighting - LED classic-giant 40W E27 T65 GOLD DIM

Lifetime



Life Expectancy Diagram - LED classic-giant 40W E27 T65 GOLD DIM



Lumen Maintenance Diagram - LED classic-giant 40W E27 T65 GOLD DIM

