

# Classic filament LEDbulbs

## 5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	330 degree(s)
Luminous Flux	500 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz


Power Consumption	5.5 W
Lamp Current (Nom)	62 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
Ambient temperature range	-20 to +45 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	A19
UL Wet/ damp/ dry location	Wet location

Classic filament LEDbulbs

Approval and Application	
Energy Certifications	Energy Star
T20 compliant	Yes
Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20


Full product name	5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20
Order code	929002988503
Material Nr. (12NC)	929002988503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677565787
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677565782

Dimensional drawing




Product	D	C
5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20	60 mm	105 mm


Photometric data



Spectral Power Distribution Colour - 5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20



General uniform lighting - 5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20



Light Distribution Diagram - 5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - 5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20



Lumen Maintenance Diagram - 5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20

