

MAS LEDtube VLE UN 1200mm UO 15.5W830 T8 MASTER Value LEDtube Universal T8

The new Philips MASTER Value LEDtube Universal T8 brings ease and simplicity to your lighting project. That's because you do not need to match the driver technology anymore: a unique design enables the Philips MASTER Value LEDtube Universal T8 to directly fit in luminaires operating on either electromagnetic ballasts or HF electronic ballasts or mains power connection. It is so simple to operate and you no longer need to stock two types of tubes! Perfectly safe, reliable & easy to install Philips MASTER Value LEDtube Universal T8 is the ideal alternative to standard fluorescent tubes to maximize value over lifetime with high energy saving and lower maintenance costs.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process, we innovate to reduce our environmental impact by taking climate action and by focusing on circularity and bring wider benefits to the world we operate in via social aspects as food availability, health & wellbeing, and safety & security.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.

Energy

- **Dimmable:** No
- **Energy Efficiency Class:** D
- **Luminous Efficacy (rated) (Nom):** 148.00 lm/W
- **Power (Rated) (Nom):** 15.5 W

Circularity

- **Nominal Lifetime (Nom):** 60000 h

Packaging

- **Copy SAP Weight Paper Unit (Case):** 2.028 lb
- **Copy SAP Weight Paper Unit (Piece):** 0.097 lb

Substances

- **EU REACH SVHC declaration:** Yes
- **EU RoHS compliant:** Yes

Weight & Materials

- **Copy Net Weight (Piece):** 0.529 lb

Energy efficiency ranking / External awards

