



A-Shape LED

6.5A19/LED/927/FR/P/E26/ND 4/2CT

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data


General Information		Temperature	
Cap-Base	E26 [Single Contact Medium Screw]	Lamp Current (Nom)	77 mA
Nominal lifetime	11,000 hour(s)	Wattage Equivalent	40 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Rated Lifetime (Hours)	11,000 hour(s)	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.5
EU RoHS compliant	Yes	Voltage (Nom)	120 V
Light Technical		Controls and Dimming	
Color Code	927 [CCT of 2700K]	Dimmable	No
Color Code	927 [CCT of 2700K]	Mechanical and Housing	
Beam Angle (Nom)	150 degree(s)	Bulb Finish	Frosted
Luminous Flux	450 lm	Bulb Shape	A19 [A 19mm]
Color Designation	Warm White (WW)	UL Wet/ damp/ dry location	Damp location
Correlated Color Temperature (Nom)	2700 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	69.00 lm/W	Energy Certifications	No
Color Consistency	<6	EyeComfort	Yes
Color rendering index (CRI)	90	T20 compliant	No
LLMF At End Of Nominal Lifetime (Nom)	0.7 %		
Operating and Electrical			
Line Frequency	60 Hz		
Input Frequency	60 Hz		
Power Consumption	6.5 W		

A-Shape LED

Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	6.5A19/LED/927/FR/P/E26/ND 4/2CT
Full product name	6.5A19/LED/927/FR/P/E26/ND 4/2CT
Order code	565424


Material Nr. (12NC)	929003004503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677565428
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677565423

Dimensional drawing




Product	D	C
6.5A19/LED/927/FR/P/E26/ND 4/2CT	60 mm	104 mm


Photometric data



Spectral Power Distribution Colour - 6.5A19/LED/927/FR/P/E26/ND 4/2CT




Light Distribution Diagram - 6.5A19/LED/927/FR/P/E26/ND 4/2CT




General uniform lighting - 6.5A19/LED/927/FR/P/E26/ND 4/2CT

A-Shape LED

Lifetime



Lumen Maintenance Diagram - 6.5A19/LED/927/FR/P/E26/ND 4/2CT



Life Expectancy Diagram - 6.5A19/LED/927/FR/P/E26/ND 4/2CT

