




# Classic filament LEDbulbs

## LEDclassic 60W A60 2700K B22 D CL AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

### Product data

| General Information    |          |
|------------------------|----------|
| Cap-Base               | B22      |
| Nominal lifetime       | 15,000 h |
| Switching Cycle        | 20,000   |
| Rated Lifetime (Hours) | 15,000 h |
| Lighting Technology    | LED      |
| EU RoHS compliant      | Yes      |

| Light Technical                       |                    |
|---------------------------------------|--------------------|
| Color Code                            | 927 [CCT of 2700K] |
| Color Code                            | 927 [CCT of 2700K] |
| Luminous Flux                         | 806 lm             |
| Color Designation                     | Warm White (WW)    |
| Correlated Color Temperature (Nom)    | 2700 K             |
| Luminous Efficacy (rated) (Nom)       | 134 lm/W           |
| Color Consistency                     | <6                 |
| Color rendering index (CRI)           | 90                 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %               |

| Operating and Electrical |             |
|--------------------------|-------------|
| Input Frequency          | 50 to 60 Hz |
| Power Consumption        | 6 W         |

|                           |           |
|---------------------------|-----------|
| Lamp Current (Nom)        | 40 mA     |
| Wattage Equivalent        | 60 W      |
| Starting Time (Nom)       | 0.5 s     |
| Warm-up time to 60% light | 0.5 s     |
| Power Factor (Fraction)   | 0.6       |
| Voltage (Nom)             | 220-240 V |

| Temperature               |               |
|---------------------------|---------------|
| Ambient temperature range | -20 to +45 °C |
| T-Case Maximum (Nom)      | 70 °C         |

| Controls and Dimming |                            |
|----------------------|----------------------------|
| Dimmable             | Only with specific dimmers |

| Mechanical and Housing |       |
|------------------------|-------|
| Bulb Finish            | Clear |
| Bulb Material          | Glass |
| Bulb Shape             | A60   |


| Approval and Application      |       |
|-------------------------------|-------|
| Energy Consumption kWh/1000 h | 6 kWh |

Classic filament LEDbulbs

|                        |                                      |
|------------------------|--------------------------------------|
| EyeComfort             | Yes                                  |
| Product Data           |                                      |
| Order product name     | LEDclassic 60W A60 2700K B22 D CL AU |
| Full product name      | LEDclassic 60W A60 2700K B22 D CL AU |
| Full product code      | 871951437719600                      |
| Local code description | FIL60WA60WWBCD                       |
| Order code             | 929003010579                         |


|                                 |                |
|---------------------------------|----------------|
| Material Nr. (12NC)             | 929003010579   |
| Local order code                | FIL60WA60WWBCD |
| Numerator - Quantity Per Pack   | 1              |
| EAN/UPC - Product/Case          | 8719514377196  |
| Numerator - Packs per outer box | 6              |
| EAN/UPC - Case                  | 8719514377202  |

Dimensional drawing




| Product                              | D     | C      |
|--------------------------------------|-------|--------|
| LEDclassic 60W A60 2700K B22 D CL AU | 60 mm | 103 mm |


Photometric data



Spectral Power Distribution Colour - LEDclassic 60W A60 2700K B22 D CL AU



Light Distribution Diagram - LEDclassic 60W A60 2700K B22 D CL AU




General uniform lighting - LEDclassic 60W A60 2700K B22 D CL AU

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LEDclassic 60W A60 2700K B22 D CL AU



Lumen Maintenance Diagram - LEDclassic 60W A60 2700K B22 D CL AU

