



Classic filament LEDbulbs

LEDclassic 60W ST64 2700K E27 D CL AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 h
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	927 [CCT of 2700K]
Color Code	927 [CCT of 2700K]
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	134 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	6 W

Lamp Current (Nom)	40 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V

Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	70 °C

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	ST64


Approval and Application	
Energy Consumption kWh/1000 h	6 kWh
EyeComfort	Yes

Classic filament LEDbulbs

LED Innovations	EyeComfort
Product Data	
Order product name	LEDclassic 60W ST64 2700K E27 D CL AU
Full product name	LEDclassic 60W ST64 2700K E27 D CL AU
Full product code	871951437721900
Local code description	FIL60WST64WWESD
Order code	929003010779


Material Nr. (12NC)	929003010779
Local order code	FIL60WST64WWESD
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514377219
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514377226

Dimensional drawing




Product	D	C
LEDclassic 60W ST64 2700K E27 D CL AU	64 mm	140 mm


Photometric data



Spectral Power Distribution Colour - LEDclassic 60W ST64 2700K E27 D CL AU




Light Distribution Diagram - LEDclassic 60W ST64 2700K E27 D CL AU




General uniform lighting - LEDclassic 60W ST64 2700K E27 D CL AU

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LEDclassic 60W ST64 2700K E27 D CL AU



Lumen Maintenance Diagram - LEDclassic 60W ST64 2700K E27 D CL AU

