

**PHILIPS**

Eco passport

## MASTERVLE LEDBulbD10.5-100W B22A60 927FRGUK MASTER Value Glass LED bulbs

Featuring a classic heritage design, these filament LED bulbs combine the familiar shapes of incandescent bulbs with the benefits of long-lasting LED technology. These MASTER Value Glass LED bulbs offer more energy savings than normal glass LED bulbs. At the same time, they also provide customers with good light experience, enhanced by excellent dimming performance (dimmmable glass LED bulbs). MASTER Value Glass LED Bulbs deliver significant energy savings, using 30% less energy compared to normal LED bulbs and provide excellent quality of light. By offering a lifetime of 15,000 hours, these dimmmable LED bulbs also reduce maintenance costs.



### Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process, we innovate to reduce our environmental impact by taking climate action and by focusing on circularity and bring wider benefits to the world we operate in via social aspects as food availability, health & wellbeing, and safety & security.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



#### Energy

- **Dimmable:** Yes
- **Energy Efficiency Class:** D
- **Luminous efficacy (rated) (nom.):** 144.00 lm/W
- **Power (Rated) (Nom):** 10.5 W



#### Circularity

- **Nominal lifetime (nom.):** 15000 h



#### Packaging

- **SAP Weight Paper Unit (Case):** 0.430 kg
- **SAP Weight Paper Unit (Piece):** 0.022 kg



#### Substances

- **EU RoHS compliant:** Yes



#### Weight & Materials

- **SAP net weight (piece):** 0.030 kg

Energy efficiency ranking / External awards



Further reading at:

<https://www.philips.com/a-w/about/sustainability/sustainable-planet/green-products-and-green-innovation.html>

© 2022 Signify Holding. All rights reserved.