



Contractor-grade Plastic (Non-Dimmable) A-Shape Lamps

5A19/LED/930/FR/P/E26/ND/T20 6/1FB

Most affordable A19 lamp ideal for residential, back of house closets.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	11,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	250 degree(s)
Luminous Flux	450 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %


Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	5 W
Lamp Current (Nom)	46 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	No

Contractor-grade Plastic (Non-Dimmable) A-Shape Lamps

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19
Approval and Application	
Energy Certifications	No
Product Data	
Order product name	5A19/LED/930/FR/P/E26/ND/T20 6/1FB


Full product name	5A19/LED/930/FR/P/E26/ND/T20 6/1FB
Order code	929003020004
Material Nr. (12NC)	929003020004
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677571597
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677571592

Dimensional drawing




Product	D	C
5A19/LED/930/FR/P/E26/ND/T20 6/1FB	60 mm	104 mm

Photometric data




Light Distribution Diagram - 5A19/LED/930/FR/P/E26/ND/T20 6/1FB



General uniform lighting - 5A19/LED/930/FR/P/E26/ND/T20 6/1FB


Contractor-grade Plastic (Non-Dimmable) A-Shape Lamps

Photometric data




Spectral Power Distribution Colour - 5A19/LED/930/FR/P/E26/ND/T20 6/1FB

Lifetime



Lumen Maintenance Diagram - 5A19/LED/930/FR/P/E26/ND/T20 6/1FB



Life Expectancy Diagram - 5A19/LED/930/FR/P/E26/ND/T20 6/1FB

