

## **5A19/LED/950/FR/P/E26/ND/T20 6/1FB** LED A19-A21

Philips A19/A21 LED lamps are the smart alternative to standard incandescent. The unique lamp design provides omni-directional light with excellent dimming performance.



## Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.




- Dimmable: No
- Luminous Efficacy (rated) (Nom): 90.00 lm/W
- Power (Rated) (Nom): 5 W

## Circularity

• Nominal Lifetime (Nom): 11000 h



- SAP Weight Paper Unit (Case): 0.170 kg
- SAP Weight Paper Unit (Piece): 0.015 kg



- EU REACH SVHC declaration: Yes
- EU RoHS compliant: Yes



Weight & Materials

• Net Weight (Piece): 0.030 kg