

PHILIPS

Eco passport

13PAR38/LED/940/F40/DIM/GULW/T20 6/1FB LED PAR38

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process, we innovate to reduce our environmental impact by taking climate action and by focusing on circularity and bring wider benefits to the world we operate in via social aspects as food availability, health & wellbeing, and safety & security.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



Energy

- **Dimmable:** Only with specific dimmers
- **Luminous Efficacy (rated) (Nom):** 92.00 lm/W
- **Power (Rated) (Nom):** 13 W



Circularity

- **Nominal Lifetime (Nom):** 25000 h



Packaging

- **SAP Weight Paper Unit (Case):** 0.643 kg
- **SAP Weight Paper Unit (Piece):** 0.097 kg



Substances

- **EU REACH SVHC declaration:** Yes
- **EU RoHS compliant:** Yes



Weight & Materials

- **Net Weight (Piece):** 0.385 kg

Further reading at:

<https://www.signify.com/global/sustainability/sustainable-lighting>

© 2021 Signify Holding. All rights reserved.